

T1 Filing Compliance (2018 Tax Year)

Table 2B: Late-Filing Penalty Assessed by Forward Sortation Area (FSA)

Province or Territory	FSA	All Returns (#)	Late Returns with Nil Balance (#)	Late Returns with Refunds (#)	Late Returns with Balance Owing (#)	All Late Returns (#)	Late Returns with Penalty (#)	Total Penalty (\$)	Average Penalty (\$)
10	A0A	39,270	850	1,600	1,040	3,490	700	103,000	150
	A0B	17,410	320	680	430	1,430	290	62,000	210
	A0C	10,900	220	380	240	840	170	19,000	110
	A0E	19,250	320	540	350	1,200	220	43,000	190
	A0G	30,640	540	810	550	1,900	380	55,000	150
	A0H	15,330	270	380	290	940	200	43,000	220
	A0J	6,890	140	190	100	430	70	12,000	190
	A0K	22,790	380	760	640	1,780	460	81,000	180
	A0L	6,520	90	280	140	510	100	14,000	150
	A0M	5,220	70	110	60	240	40	6,000	130
	A0N	12,430	240	270	210	710	150	21,000	140
	A0P	9,660	210	690	230	1,130	140	36,000	260
	A0R	1,920	20	140	30	190	30	4,000	150
	A1A	22,530	360	1,290	520	2,170	380	130,000	340
	A1B	14,500	360	790	340	1,490	220	58,000	260
	A1C	9,860	310	530	270	1,120	180	42,000	230
	A1E	21,750	510	1,140	580	2,230	380	76,000	200
	A1G	4,520	90	260	130	470	90	12,000	130
	A1H	4,060	30	230	120	390	90	31,000	350
	A1K	9,590	110	550	250	900	190	28,000	150
	A1L	15,740	180	880	410	1,470	300	65,000	210
	A1M	6,160	90	320	180	580	130	30,000	240
	A1N	18,740	300	910	460	1,670	330	62,000	190
	A1S	5,390	90	260	140	490	100	14,000	140
	A1V	9,410	130	410	220	750	160	67,000	430
	A1W	8,910	130	540	190	860	150	37,000	250
	A1X	11,740	200	660	290	1,160	200	36,000	180
	A1Y	4,650	110	160	130	400	80	13,000	170
	A2A	7,690	140	310	160	610	100	20,000	200
	A2B	3,970	80	110	90	270	60	8,000	140
	A2H	21,070	330	850	470	1,650	340	66,000	200
	A2N	7,330	170	290	150	610	110	24,000	210
	A2V	5,480	60	220	50	330	40	20,000	530
	A5A	6,780	90	230	110	440	80	13,000	170
	A8A	5,810	100	170	100	370	70	14,000	200
TOTAL		423,880	7,610	17,940	9,650	35,200	6,700	1,365,000	200
11	C0A	36,250	490	1,840	980	3,300	720	120,000	170
	C0B	24,010	270	1,000	510	1,780	380	70,000	180
	C1A	20,670	350	1,000	530	1,870	390	84,000	220
	C1B	10,290	110	560	260	940	200	49,000	240
	C1C	3,630	30	160	80	280	60	11,000	190
	C1E	9,350	110	430	180	730	120	25,000	200
	C1N	13,980	170	570	290	1,020	190	25,000	130
TOTAL		118,180	1,550	5,550	2,820	9,920	2,050	383,000	190
12	B0C	2,300	40	100	80	210	60	18,000	320
	B0E	21,510	460	980	480	1,920	340	90,000	260
	B0H	8,280	160	440	210	810	160	88,000	560
	B0J	33,060	580	1,520	820	2,920	550	137,000	250
	B0K	29,300	670	1,560	750	2,970	490	96,000	190
	B0L	2,030	50	100	40	200	30	5,000	140
	B0M	13,900	290	670	360	1,320	230	31,000	130
	B0N	31,700	700	1,690	940	3,330	630	159,000	250
	B0P	32,720	780	1,900	840	3,510	590	116,000	200
	B0R	4,990	90	170	90	350	60	16,000	270
	B0S	14,720	330	720	330	1,380	220	38,000	180
	B0T	12,450	210	360	200	770	130	31,000	240
	B0V	4,920	110	220	100	430	70	15,000	210
	B0W	23,740	280	710	400	1,390	250	47,000	190
	B1A	12,390	340	500	310	1,160	210	29,000	140
	B1B	1,070	20	40	20	80	10	1,000	130
	B1C	1,530	10	50	40	100	30	9,000	330
	B1E	1,330	30	60	40	130	30	5,000	190
	B1G	1,580	50	60	50	160	30	4,000	150

12	B1H	7,900	280	430	240	950	150	28,000	180
12	B1J	940	20	40	30	80	20	2,000	110
12	B1K	2,610	50	140	70	270	60	16,000	280
12	B1L	4,010	60	230	120	410	80	17,000	210
12	B1M	1,060	30	40	30	90	20	2,000	100
12	B1N	4,630	150	220	140	510	100	14,000	140
12	B1P	12,150	390	610	310	1,300	210	55,000	270
12	B1R	3,510	60	160	80	300	60	19,000	300
12	B1S	6,560	230	300	140	660	100	22,000	230
12	B1T	310	10	30	10	50	10	2,000	240
12	B1V	5,080	160	280	150	590	90	20,000	220
12	B1W	2,100	280	40	20	330	-	-	-
12	B1X	680	20	60	20	90	10	11,000	1,030
12	B1Y	5,110	120	250	160	530	110	15,000	140
12	B2A	6,590	170	290	180	640	140	23,000	170
12	B2C	250	10	20	10	40	10	1,000	110
12	B2E	40	-	-	-	10	-	-	-
12	B2G	11,430	220	760	320	1,300	250	82,000	330
12	B2H	11,860	270	610	290	1,170	190	38,000	200
12	B2J	80	-	-	-	10	-	-	-
12	B2N	16,430	430	800	440	1,670	300	55,000	180
12	B2R	2,070	20	140	60	220	50	11,000	230
12	B2S	5,980	80	380	190	640	130	25,000	190
12	B2T	13,170	180	920	430	1,530	310	84,000	270
12	B2V	9,680	110	590	240	940	180	33,000	190
12	B2W	26,430	410	1,520	790	2,730	560	110,000	200
12	B2X	9,190	200	550	310	1,060	220	54,000	250
12	B2Y	11,690	310	760	350	1,410	240	52,000	220
12	B2Z	6,680	140	450	240	830	170	31,000	190
12	B3A	15,990	470	880	530	1,880	360	67,000	190
12	B3B	1,100	30	70	40	140	30	6,000	250
12	B3E	5,420	90	350	200	640	150	25,000	160
12	B3G	8,200	120	490	280	890	210	34,000	170
12	B3H	12,400	260	690	240	1,190	180	89,000	510
12	B3J	5,340	120	280	120	520	90	20,000	230
12	B3K	15,990	450	1,030	520	2,000	370	82,000	230
12	B3L	13,110	270	800	400	1,470	310	78,000	260
12	B3M	25,470	530	1,330	640	2,500	480	98,000	210
12	B3N	10,710	220	710	330	1,260	260	55,000	210
12	B3P	7,370	150	430	220	790	160	28,000	180
12	B3R	6,620	250	380	210	840	120	19,000	160
12	B3S	10,390	180	470	240	900	190	35,000	190
12	B3T	13,130	200	880	450	1,530	330	67,000	200
12	B3V	4,800	60	300	150	510	110	22,000	200
12	B3Z	13,210	160	880	410	1,460	310	70,000	230
12	B4A	14,430	240	840	380	1,450	280	60,000	220
12	B4B	10,870	160	640	330	1,130	240	89,000	370
12	B4C	14,540	240	880	460	1,580	310	57,000	180
12	B4E	14,160	200	870	440	1,520	320	68,000	210
12	B4G	3,810	70	280	140	490	90	25,000	270
12	B4H	10,790	240	540	280	1,050	190	32,000	170
12	B4N	14,070	300	770	360	1,430	250	34,000	140
12	B4P	6,350	150	390	190	720	130	90,000	680
12	B4R	2,350	30	150	50	230	40	5,000	120
12	B4V	16,930	240	590	270	1,100	190	35,000	190
12	B5A	13,240	260	500	260	1,010	170	44,000	260
12	B6L	10,140	140	480	260	880	170	29,000	170
12	B9A	3,600	80	220	100	390	70	21,000	300
TOTAL		746,250	15,430	39,560	19,960	74,940	13,910	3,144,000	230
13	E0A	20	-	-	-	-	-	-	-
13	E0B	20	-	-	-	-	-	-	-
13	E0G	10	-	-	-	-	-	-	-
13	E0J	10	-	-	-	-	-	-	-
13	E0L	10	-	-	-	-	-	-	-
13	E1A	34,860	180	1,740	650	2,560	440	84,000	190
13	E1B	16,140	70	860	350	1,280	240	35,000	140
13	E1C	19,250	140	1,060	350	1,560	230	42,000	180
13	E1E	8,670	60	490	200	740	130	19,000	150
13	E1G	17,840	120	1,010	350	1,480	250	45,000	180
13	E1H	6,260	30	270	110	400	70	14,000	190
13	E1J	2,880	10	140	60	210	50	9,000	190
13	E1N	9,260	40	420	140	600	100	11,000	120
13	E1V	11,210	70	700	210	980	150	21,000	140
13	E1W	6,140	20	180	40	240	30	9,000	290
13	E1X	12,260	30	240	110	380	70	10,000	140
13	E2A	14,580	60	570	160	790	120	23,000	190

13	E2E	15,430	80	910	280	1,270	200	54,000	270
13	E2G	4,020	20	240	80	340	60	15,000	250
13	E2H	3,720	30	210	70	310	60	21,000	380
13	E2J	12,710	70	660	250	980	170	30,000	180
13	E2K	13,360	110	720	250	1,090	170	28,000	160
13	E2L	6,280	50	370	120	550	90	18,000	210
13	E2M	15,020	80	850	290	1,210	200	39,000	190
13	E2N	3,640	20	220	80	320	60	12,000	220
13	E2P	1,080	-	60	30	90	20	2,000	90
13	E2R	10	-	-	-	-	-	-	-
13	E2S	5,520	30	310	120	460	80	15,000	180
13	E2V	10,730	50	540	220	810	150	26,000	170
13	E3A	22,510	180	1,280	450	1,910	310	70,000	220
13	E3B	28,690	190	1,630	530	2,350	380	108,000	290
13	E3C	9,380	50	520	160	720	120	33,000	270
13	E3E	3,480	20	190	70	280	50	7,000	150
13	E3G	6,520	30	380	120	530	80	27,000	350
13	E3L	7,120	50	340	90	490	60	9,000	140
13	E3N	11,520	60	380	140	580	80	7,000	80
13	E3V	10,100	40	260	80	380	60	9,000	150
13	E3Y	6,090	10	130	50	190	30	6,000	200
13	E3Z	3,540	20	90	40	140	20	4,000	160
13	E4A	2,570	20	150	50	230	40	9,000	210
13	E4B	3,570	30	230	60	320	40	5,000	120
13	E4C	1,770	10	120	40	170	30	9,000	300
13	E4E	7,330	50	340	140	530	100	35,000	340
13	E4G	2,160	20	110	40	170	20	4,000	160
13	E4H	3,350	30	180	80	290	50	7,000	140
13	E4J	3,860	30	190	90	310	60	13,000	210
13	E4K	4,720	30	180	70	280	50	7,000	130
13	E4L	5,840	40	330	90	450	70	9,000	140
13	E4M	1,520	10	80	30	130	20	3,000	160
13	E4N	3,500	10	110	40	160	30	4,000	160
13	E4P	12,840	50	450	180	680	130	38,000	300
13	E4R	5,640	20	180	90	290	70	19,000	260
13	E4S	6,360	20	170	70	260	50	8,000	170
13	E4T	1,840	10	80	40	130	20	5,000	250
13	E4V	3,650	20	120	50	180	30	6,000	200
13	E4W	6,850	20	320	70	410	40	13,000	340
13	E4X	2,640	10	60	30	100	20	3,000	130
13	E4Y	2,720	10	70	20	90	20	3,000	170
13	E4Z	4,470	40	240	90	360	60	10,000	170
13	E5A	1,470	10	80	20	110	10	1,000	110
13	E5B	2,510	10	160	60	220	40	11,000	280
13	E5C	3,420	20	200	80	300	60	21,000	340
13	E5E	680	10	50	30	90	30	16,000	560
13	E5G	2,010	10	80	40	130	30	10,000	340
13	E5H	2,350	10	120	50	180	30	7,000	220
13	E5J	1,610	10	80	40	130	20	4,000	170
13	E5K	5,640	30	330	130	480	100	22,000	230
13	E5L	2,320	20	100	40	170	30	5,000	190
13	E5M	1,670	20	100	30	150	30	4,000	160
13	E5N	9,380	60	580	160	790	110	25,000	240
13	E5P	2,040	10	100	30	140	30	8,000	300
13	E5R	1,270	10	60	20	80	10	2,000	120
13	E5S	1,480	10	100	40	150	20	2,000	80
13	E5T	2,450	20	150	50	210	30	5,000	200
13	E5V	610	10	30	10	50	10	2,000	200
13	E6A	1,000	10	40	20	70	10	1,000	130
13	E6B	1,250	10	70	30	110	20	4,000	210
13	E6C	1,680	10	90	50	150	30	4,000	130
13	E6E	1,160	10	50	30	100	20	2,000	70
13	E6G	2,080	10	110	50	170	30	8,000	290
13	E6H	1,010	10	50	20	80	10	1,000	70
13	E6J	1,010	10	50	20	80	20	2,000	130
13	E6K	2,990	20	190	60	270	40	9,000	240
13	E6L	3,720	30	190	70	290	40	16,000	370
13	E7A	3,140	10	70	20	100	10	2,000	150
13	E7B	4,950	10	130	30	170	20	4,000	190
13	E7C	4,490	20	150	40	210	30	3,000	100
13	E7E	3,620	10	90	40	140	20	2,000	80
13	E7G	3,130	10	80	30	130	20	1,000	90
13	E7H	4,440	20	250	70	340	40	5,000	150
13	E7J	1,620	10	100	30	140	20	2,000	120
13	E7K	1,920	10	90	30	130	20	2,000	110
13	E7L	4,150	20	190	80	290	50	9,000	180

13	E7M	8,060	60	390	120	560	70	15,000	220
13	E7N	2,450	20	100	50	160	30	1,000	50
13	E7P	2,840	20	90	40	150	20	3,000	120
13	E8A	3,120	20	140	40	200	30	4,000	150
13	E8B	2,040	10	110	30	140	10	2,000	150
13	E8C	3,000	30	150	30	210	20	1,000	50
13	E8E	4,450	20	190	60	260	40	4,000	100
13	E8G	2,350	20	90	30	140	20	4,000	220
13	E8J	4,890	10	100	50	150	30	3,000	120
13	E8K	7,450	20	190	60	270	40	6,000	140
13	E8L	2,090	10	50	20	80	20	6,000	420
13	E8M	1,810	-	50	10	60	-	-	-
13	E8N	2,180	-	50	20	70	10	2,000	180
13	E8P	3,040	10	80	30	120	20	2,000	110
13	E8R	2,880	10	60	20	80	10	3,000	190
13	E8S	4,050	10	70	30	110	20	9,000	520
13	E8T	5,220	10	70	20	100	20	5,000	300
13	E9A	1,990	-	50	20	70	20	3,000	190
13	E9B	1,960	10	110	50	170	40	3,000	80
13	E9C	1,840	20	90	40	150	20	2,000	100
13	E9E	3,150	20	160	70	240	50	10,000	220
13	E9G	4,380	30	180	40	240	30	10,000	370
13	E9H	2,740	10	50	20	80	20	3,000	190
TOTAL		613,270	3,370	28,510	10,010	41,890	6,880	1,397,000	200
24	G0A	67,150	550	1,700	750	3,010	530	46,000	90
24	G0B	20	-	-	-	-	-	-	-
24	G0C	40,800	680	960	420	2,060	290	28,000	100
24	G0E	4,200	50	100	50	200	30	2,000	70
24	G0G	13,790	700	540	150	1,390	70	6,000	80
24	G0H	8,390	340	240	90	660	50	3,000	50
24	G0J	24,500	280	410	230	920	140	9,000	60
24	G0K	9,560	100	250	100	440	60	4,000	70
24	G0L	50,030	350	740	320	1,410	210	11,000	50
24	G0M	27,850	190	450	170	810	120	6,000	50
24	G0N	16,110	120	280	100	500	70	6,000	80
24	G0P	5,520	50	120	40	220	30	2,000	70
24	G0R	69,910	450	1,090	400	1,930	280	20,000	70
24	G0S	55,600	350	1,190	450	1,990	300	19,000	60
24	G0T	12,020	90	210	100	400	70	5,000	60
24	G0V	14,680	100	270	130	500	80	6,000	70
24	G0W	27,920	1,350	820	210	2,380	100	5,000	50
24	G0X	48,590	720	1,150	450	2,330	280	23,000	80
24	G0Y	7,640	60	100	50	210	40	3,000	100
24	G0Z	7,170	70	140	60	270	40	2,000	60
24	G1A	10	-	-	-	-	-	-	-
24	G1B	13,370	60	360	120	540	90	7,000	80
24	G1C	30,000	190	710	300	1,200	220	18,000	80
24	G1E	22,250	270	700	310	1,290	220	16,000	70
24	G1G	20,220	140	580	220	940	160	10,000	70
24	G1H	24,840	240	720	310	1,270	230	15,000	70
24	G1J	18,140	380	770	350	1,490	220	13,000	60
24	G1K	14,540	330	630	270	1,220	170	16,000	90
24	G1L	17,540	320	740	320	1,380	220	13,000	60
24	G1M	15,990	210	460	230	900	160	10,000	70
24	G1N	6,660	140	290	110	530	80	4,000	50
24	G1P	13,350	100	460	150	710	100	6,000	60
24	G1R	13,010	210	630	190	1,030	150	15,000	100
24	G1S	20,750	200	710	190	1,100	150	19,000	130
24	G1T	5,450	50	160	40	250	30	3,000	100
24	G1V	15,810	190	630	160	980	120	13,000	110
24	G1W	17,800	170	650	180	990	130	20,000	160
24	G1X	20,890	180	630	200	1,020	150	16,000	110
24	G1Y	10,480	80	300	80	460	60	11,000	180
24	G2A	12,460	100	370	130	590	90	6,000	70
24	G2B	19,800	150	520	200	880	140	9,000	60
24	G2C	9,700	60	250	100	400	60	6,000	110
24	G2E	17,360	90	500	160	740	110	18,000	160
24	G2G	8,940	50	280	80	410	60	7,000	130
24	G2J	2,550	20	70	30	120	20	2,000	60
24	G2K	9,750	40	240	90	360	80	163,000	2,090
24	G2L	11,630	60	290	110	470	80	8,000	100
24	G2M	4,180	20	140	60	220	40	2,000	60
24	G2N	6,390	30	160	80	270	50	3,000	60
24	G3A	16,200	70	460	130	660	100	24,000	250
24	G3B	6,220	30	250	80	370	60	7,000	120
24	G3C	7,100	50	240	120	400	90	6,000	70

24	G3E	12,260	60	330	120	500	90	4,000	50
24	G3G	8,070	50	240	100	380	60	4,000	70
24	G3H	7,640	50	240	100	380	70	3,000	50
24	G3J	8,090	70	280	130	470	90	6,000	60
24	G3K	14,300	110	430	190	730	130	8,000	60
24	G3L	8,850	70	210	100	390	80	5,000	60
24	G3M	5,610	50	120	60	230	30	2,000	50
24	G3N	7,740	30	250	100	370	70	5,000	80
24	G3S	3,530	20	160	50	240	50	3,000	70
24	G3Z	6,260	40	100	40	180	40	3,000	70
24	G4A	2,590	20	30	20	70	10	-	40
24	G4R	15,380	400	510	180	1,090	120	8,000	70
24	G4S	4,050	40	90	40	170	30	2,000	90
24	G4T	11,120	70	230	50	340	40	16,000	400
24	G4V	5,580	90	140	70	300	40	2,000	50
24	G4W	11,960	110	190	110	400	70	4,000	50
24	G4X	12,520	110	220	100	440	70	11,000	150
24	G4Z	7,780	60	170	70	300	50	4,000	70
24	G5A	7,030	40	80	50	160	40	2,000	50
24	G5B	4,830	40	110	60	210	40	2,000	60
24	G5C	9,560	90	220	80	390	50	8,000	170
24	G5H	5,600	80	140	60	280	40	2,000	40
24	G5J	5,100	20	50	20	90	20	1,000	80
24	G5L	24,370	240	620	230	1,090	160	20,000	120
24	G5M	7,030	30	190	50	270	30	2,000	70
24	G5N	6,790	30	160	30	230	20	4,000	180
24	G5R	16,640	100	300	140	540	90	9,000	100
24	G5T	2,440	20	30	10	50	-	-	-
24	G5V	9,690	60	150	60	270	40	2,000	60
24	G5X	5,000	40	90	40	160	30	1,000	60
24	G5Y	19,580	170	310	110	590	70	3,000	50
24	G5Z	5,490	20	80	20	120	10	2,000	170
24	G6A	1,750	10	30	10	50	-	-	-
24	G6B	6,960	60	90	30	180	20	2,000	80
24	G6C	6,030	30	130	50	210	40	2,000	50
24	G6E	11,140	70	240	80	390	60	4,000	60
24	G6G	16,760	140	350	100	600	70	6,000	90
24	G6H	6,000	50	120	30	200	20	1,000	50
24	G6J	8,270	50	240	70	360	50	4,000	80
24	G6K	6,450	20	170	60	240	40	3,000	70
24	G6L	12,490	100	230	90	420	60	3,000	50
24	G6P	24,810	220	370	180	770	110	6,000	60
24	G6R	3,570	10	70	20	100	20	1,000	70
24	G6S	4,180	20	60	20	110	20	2,000	110
24	G6T	8,350	40	150	40	220	20	2,000	100
24	G6V	26,870	200	570	240	1,020	170	11,000	60
24	G6W	19,860	110	510	180	800	130	10,000	70
24	G6X	7,800	60	240	80	380	60	3,000	50
24	G6Y	4,680	20	110	30	160	30	2,000	60
24	G6Z	18,980	80	550	170	810	140	9,000	60
24	G7A	18,560	80	520	160	760	100	6,000	60
24	G7B	14,690	120	260	120	500	80	4,000	50
24	G7G	13,710	80	230	120	430	80	7,000	90
24	G7H	23,510	180	410	170	760	110	8,000	70
24	G7J	12,160	110	220	90	420	60	3,000	60
24	G7K	540	-	10	-	20	-	-	-
24	G7N	5,090	10	90	50	160	40	4,000	100
24	G7P	5,830	40	100	50	180	30	2,000	70
24	G7S	16,090	80	290	130	500	90	6,000	60
24	G7T	940	-	20	10	30	-	-	-
24	G7X	21,430	230	410	180	820	110	7,000	70
24	G7Y	540	-	10	10	10	-	-	-
24	G7Z	2,270	10	30	10	50	-	-	-
24	G8A	5,030	20	80	40	140	20	1,000	50
24	G8B	18,620	120	280	110	510	70	4,000	50
24	G8C	3,420	-	30	10	40	10	-	60
24	G8E	3,150	20	40	30	90	20	1,000	40
24	G8G	3,270	10	40	10	60	-	-	-
24	G8H	8,470	90	120	60	260	40	2,000	50
24	G8J	3,410	20	50	20	90	10	1,000	50
24	G8K	8,640	30	110	40	180	20	3,000	120
24	G8L	12,260	110	240	60	410	40	2,000	50
24	G8M	4,290	30	60	20	100	10	1,000	90
24	G8N	2,100	10	30	10	50	10	-	30
24	G8P	5,910	70	200	40	310	30	3,000	90
24	G8T	23,430	370	760	270	1,400	170	14,000	80

24	G8V	7,870	50	240	90	370	60	4,000	70
24	G8W	8,850	90	220	80	390	50	3,000	60
24	G8Y	27,230	270	820	250	1,340	180	12,000	70
24	G8Z	10,840	210	460	170	840	130	10,000	80
24	G9A	16,210	480	560	240	1,290	150	8,000	50
24	G9B	14,450	110	450	150	700	110	7,000	60
24	G9C	2,770	30	80	30	130	20	1,000	50
24	G9H	10,670	90	230	90	410	70	4,000	50
24	G9N	13,470	240	300	140	680	90	5,000	60
24	G9P	9,870	80	140	70	280	40	2,000	60
24	G9R	1,830	10	30	20	60	10	-	30
24	G9T	13,520	190	280	150	610	100	7,000	80
24	G9X	9,030	110	190	100	390	60	2,000	30
24	H0M	1,250	320	50	20	390	-	-	110
24	H1A	26,610	430	990	420	1,840	290	26,000	90
24	H1B	16,150	340	630	300	1,260	190	9,000	40
24	H1C	11,040	190	530	240	960	160	11,000	70
24	H1E	35,300	740	1,460	640	2,840	430	45,000	100
24	H1G	37,530	1,450	1,780	770	3,990	470	45,000	100
24	H1H	27,930	950	1,310	540	2,790	350	21,000	60
24	H1J	8,540	170	310	130	600	100	9,000	90
24	H1K	27,230	550	1,150	480	2,170	310	18,000	60
24	H1L	26,550	660	1,150	500	2,310	340	21,000	60
24	H1M	24,230	400	850	340	1,590	250	22,000	90
24	H1N	19,030	470	780	320	1,570	230	18,000	80
24	H1P	14,180	290	560	230	1,080	160	16,000	100
24	H1R	23,350	530	880	370	1,780	250	17,000	70
24	H1S	20,750	540	850	300	1,690	200	18,000	90
24	H1T	24,680	720	990	390	2,100	280	27,000	100
24	H1V	16,860	500	860	380	1,740	270	35,000	130
24	H1W	22,370	660	1,290	480	2,430	310	23,000	70
24	H1X	23,600	580	1,150	450	2,180	300	20,000	70
24	H1Y	21,460	460	1,150	440	2,060	350	34,000	100
24	H1Z	26,110	950	1,290	500	2,730	300	19,000	60
24	H2A	15,050	480	800	280	1,550	190	11,000	60
24	H2B	13,740	350	640	240	1,220	170	12,000	70
24	H2C	14,170	270	600	220	1,090	160	16,000	100
24	H2E	18,380	540	880	330	1,750	220	18,000	80
24	H2G	16,850	400	1,000	350	1,740	250	30,000	120
24	H2H	11,030	230	700	270	1,200	200	65,000	320
24	H2J	19,770	350	1,270	430	2,050	320	31,000	100
24	H2K	21,940	680	1,230	500	2,410	360	32,000	90
24	H2L	19,680	580	990	410	1,970	300	51,000	170
24	H2M	14,520	290	670	210	1,170	150	14,000	90
24	H2N	5,070	150	270	100	520	60	4,000	70
24	H2P	11,240	210	580	230	1,020	160	17,000	100
24	H2R	17,770	340	1,020	290	1,650	200	16,000	80
24	H2S	20,970	450	1,290	440	2,170	300	35,000	120
24	H2T	12,150	330	820	280	1,430	210	20,000	90
24	H2V	21,800	820	1,780	480	3,080	330	62,000	190
24	H2W	7,900	250	550	190	990	150	30,000	200
24	H2X	14,600	710	770	240	1,720	170	23,000	140
24	H2Y	3,070	70	160	90	310	60	12,000	200
24	H2Z	2,070	120	90	50	250	30	34,000	1,170
24	H3A	3,160	150	150	40	340	30	10,000	310
24	H3B	15,430	110	80	30	220	20	5,000	190
24	H3C	10,500	240	530	230	1,000	180	21,000	120
24	H3E	16,670	320	530	230	1,080	160	38,000	240
24	H3G	6,840	320	330	130	790	90	37,000	440
24	H3H	14,030	650	870	190	1,700	140	14,000	100
24	H3J	8,260	330	390	120	840	80	14,000	180
24	H3K	11,470	390	620	280	1,290	200	16,000	80
24	H3L	15,540	310	660	190	1,160	130	8,000	60
24	H3M	12,330	320	490	150	960	110	19,000	180
24	H3N	22,290	1,220	1,190	420	2,830	270	33,000	120
24	H3P	7,880	140	260	90	490	70	10,000	160
24	H3R	7,660	140	260	70	470	60	21,000	390
24	H3S	24,330	850	1,180	350	2,380	220	43,000	200
24	H3T	9,060	280	490	100	870	70	4,000	60
24	H3V	5,400	190	280	80	550	60	7,000	110
24	H3W	23,490	780	1,170	390	2,330	260	23,000	90
24	H3X	18,140	500	790	310	1,600	230	27,000	120
24	H3Y	7,440	90	170	80	340	60	21,000	350
24	H3Z	9,320	250	340	140	730	110	25,000	240
24	H4A	19,900	490	1,160	420	2,070	300	40,000	130
24	H4B	15,840	550	870	290	1,710	220	17,000	80

24	H4C	12,850	370	820	300	1,480	200	21,000	100
24	H4E	23,850	680	1,200	500	2,380	350	26,000	80
24	H4G	23,050	670	1,240	500	2,410	350	26,000	80
24	H4H	15,190	360	730	350	1,440	250	20,000	80
24	H4J	13,440	430	540	170	1,140	110	10,000	90
24	H4K	9,030	210	350	120	680	90	20,000	230
24	H4L	28,670	790	1,290	390	2,470	270	27,000	100
24	H4M	9,680	300	460	170	930	120	17,000	140
24	H4N	22,670	740	950	300	1,980	190	23,000	120
24	H4P	6,310	160	280	100	540	70	25,000	370
24	H4R	22,010	520	880	340	1,740	250	44,000	180
24	H4S	450	10	20	10	30	-	-	50
24	H4T	70	10	10	-	20	-	-	-
24	H4V	15,790	500	860	300	1,660	230	28,000	120
24	H4W	19,570	550	740	300	1,580	190	81,000	420
24	H4X	4,940	110	260	100	470	80	25,000	320
24	H4Z	30	-	-	-	10	-	-	-
24	H5A	10	-	-	-	-	-	-	-
24	H5B	100	-	-	-	-	-	-	-
24	H7A	16,350	250	650	310	1,210	210	13,000	60
24	H7B	2,240	20	100	40	160	30	2,000	90
24	H7C	6,340	130	230	110	480	80	6,000	80
24	H7E	21,400	300	810	320	1,430	220	29,000	130
24	H7G	17,160	370	700	320	1,390	200	14,000	70
24	H7H	10,700	150	450	160	750	110	9,000	80
24	H7J	1,780	20	70	40	130	30	4,000	120
24	H7K	17,980	220	610	250	1,070	170	17,000	100
24	H7L	28,980	330	1,110	390	1,830	290	26,000	90
24	H7M	23,450	350	880	360	1,590	250	18,000	70
24	H7N	34,500	710	1,340	600	2,640	390	27,000	70
24	H7P	28,640	380	1,060	440	1,880	300	33,000	110
24	H7R	23,310	410	1,000	430	1,830	270	21,000	80
24	H7S	6,160	130	260	90	480	50	5,000	100
24	H7T	20,150	400	680	320	1,410	220	22,000	100
24	H7V	18,450	490	650	310	1,450	220	17,000	80
24	H7W	34,010	830	1,250	590	2,670	380	43,000	110
24	H7X	20,610	320	810	290	1,420	190	18,000	100
24	H7Y	7,360	100	280	120	500	80	12,000	160
24	H8N	24,620	710	1,150	510	2,370	350	27,000	80
24	H8P	18,010	430	890	400	1,720	280	27,000	100
24	H8R	23,320	730	1,290	530	2,540	340	30,000	90
24	H8S	19,140	510	850	430	1,790	290	24,000	80
24	H8T	11,710	190	530	220	940	160	20,000	130
24	H8Y	14,780	350	720	280	1,350	190	14,000	80
24	H8Z	12,080	280	640	270	1,180	190	13,000	70
24	H9A	12,320	240	470	190	900	120	12,000	100
24	H9B	16,650	410	830	310	1,550	200	19,000	90
24	H9C	9,410	130	420	130	680	90	15,000	160
24	H9E	2,430	40	100	60	210	40	3,000	80
24	H9G	12,510	280	600	240	1,120	170	21,000	130
24	H9H	20,380	460	940	360	1,760	250	39,000	150
24	H9J	17,370	320	790	310	1,420	220	20,000	90
24	H9K	6,570	120	280	110	510	80	17,000	200
24	H9P	3,130	60	180	70	310	50	3,000	50
24	H9R	19,460	350	1,000	370	1,710	270	30,000	110
24	H9S	18,460	350	840	380	1,560	280	34,000	120
24	H9W	15,080	240	690	230	1,150	160	34,000	210
24	H9X	7,520	130	320	120	570	80	10,000	120
24	J0A	15,370	150	330	120	600	80	6,000	70
24	J0B	51,200	600	1,150	450	2,200	330	38,000	110
24	J0C	18,530	200	480	210	900	150	9,000	60
24	J0E	40,410	480	1,110	500	2,090	350	32,000	90
24	J0G	15,400	190	340	140	670	90	5,000	50
24	J0H	41,670	360	990	400	1,750	270	18,000	70
24	J0J	33,740	430	970	450	1,840	290	28,000	100
24	J0K	117,190	1,980	2,900	1,390	6,280	910	74,000	80
24	J0L	65,440	1,280	1,820	850	3,950	580	46,000	80
24	J0M	13,740	1,970	2,470	580	5,020	250	17,000	70
24	J0N	39,130	520	1,310	580	2,410	400	30,000	70
24	J0P	32,490	380	1,140	510	2,020	350	31,000	90
24	J0R	30,840	430	1,070	540	2,040	400	63,000	160
24	J0S	26,510	410	720	340	1,470	240	21,000	90
24	J0T	39,770	730	1,340	680	2,750	460	40,000	90
24	J0V	21,780	410	690	320	1,420	200	22,000	110
24	J0W	13,900	270	350	140	760	90	6,000	70
24	J0X	36,110	740	1,260	660	2,670	440	49,000	110

24	J0Y	22,410	690	750	230	1,660	140	12,000	90
24	J0Z	27,200	440	770	270	1,480	170	13,000	80
24	J1A	7,610	60	110	30	200	20	2,000	100
24	J1C	5,230	30	100	40	170	30	2,000	50
24	J1E	19,360	290	410	160	870	100	4,000	40
24	J1G	15,920	220	340	130	690	90	10,000	110
24	J1H	21,110	540	690	270	1,500	180	14,000	80
24	J1J	12,080	140	270	100	510	80	11,000	140
24	J1K	5,350	80	190	60	330	50	2,000	50
24	J1L	12,370	100	210	90	410	70	7,000	110
24	J1M	4,390	70	180	60	300	40	2,000	60
24	J1N	25,900	160	540	210	910	150	12,000	80
24	J1R	8,210	60	190	70	320	50	7,000	130
24	J1S	6,310	40	130	70	240	40	4,000	90
24	J1T	6,430	80	110	50	240	30	1,000	40
24	J1X	27,150	290	560	280	1,130	190	15,000	80
24	J1Z	4,380	50	130	50	230	40	2,000	60
24	J2A	9,300	90	280	130	490	90	6,000	70
24	J2B	24,680	420	750	290	1,460	180	8,000	50
24	J2C	25,310	310	570	230	1,110	160	9,000	60
24	J2E	3,430	30	100	50	180	40	2,000	70
24	J2G	23,640	350	530	230	1,100	130	6,000	50
24	J2H	16,990	120	300	120	530	80	8,000	100
24	J2J	14,540	130	280	130	530	90	5,000	50
24	J2K	13,790	190	370	160	710	130	8,000	70
24	J2L	7,880	60	220	110	390	80	6,000	80
24	J2M	5,760	50	160	60	270	40	4,000	90
24	J2N	7,260	80	220	90	400	70	4,000	60
24	J2R	8,470	40	130	70	240	40	3,000	80
24	J2S	23,710	340	450	240	1,040	140	11,000	80
24	J2T	13,720	110	240	120	460	70	4,000	60
24	J2W	22,810	190	710	270	1,170	200	25,000	130
24	J2X	15,750	180	440	190	810	130	9,000	70
24	J2Y	4,530	40	130	60	220	40	2,000	40
24	J3A	7,280	130	210	90	430	70	4,000	60
24	J3B	26,470	450	970	410	1,830	280	17,000	60
24	J3E	23,810	150	640	270	1,050	190	24,000	130
24	J3G	25,600	140	650	280	1,060	210	15,000	80
24	J3H	21,350	150	540	240	930	190	22,000	120
24	J3L	39,810	330	1,300	570	2,200	400	41,000	100
24	J3M	8,450	70	200	110	380	70	6,000	80
24	J3N	13,160	70	390	180	640	140	18,000	130
24	J3P	21,240	220	350	170	740	120	8,000	70
24	J3R	11,940	140	290	130	560	80	6,000	70
24	J3T	6,980	50	120	50	220	30	1,000	50
24	J3V	21,090	140	680	250	1,070	180	35,000	190
24	J3X	17,140	110	530	190	830	140	10,000	70
24	J3Y	50,840	560	1,690	760	3,010	530	50,000	90
24	J3Z	4,350	40	190	60	300	50	5,000	110
24	J4B	34,700	220	1,030	320	1,570	230	48,000	210
24	J4G	8,090	80	330	120	530	80	8,000	100
24	J4H	12,830	200	480	200	880	130	20,000	160
24	J4J	23,650	550	1,030	440	2,020	270	21,000	80
24	J4K	20,450	560	950	420	1,920	270	28,000	100
24	J4L	24,210	500	940	420	1,860	270	23,000	90
24	J4M	10,250	100	350	150	600	100	7,000	70
24	J4N	8,750	70	220	90	380	60	7,000	120
24	J4P	8,640	140	300	140	580	90	15,000	160
24	J4R	8,390	180	340	110	620	70	7,000	100
24	J4S	5,110	60	140	60	260	50	22,000	450
24	J4T	14,220	290	620	280	1,180	200	13,000	70
24	J4V	13,140	260	620	260	1,130	170	122,000	730
24	J4W	14,830	340	620	260	1,210	170	15,000	90
24	J4X	15,340	290	550	210	1,040	170	24,000	150
24	J4Y	18,980	320	740	290	1,350	210	31,000	150
24	J4Z	20,860	360	910	370	1,630	250	22,000	90
24	J5A	21,950	180	670	330	1,180	220	12,000	50
24	J5B	6,250	60	200	100	360	70	4,000	60
24	J5C	13,500	110	430	190	740	130	7,000	60
24	J5J	12,710	190	520	280	1,000	180	19,000	100
24	J5K	12,380	150	460	270	880	190	15,000	80
24	J5L	17,180	170	590	270	1,030	200	19,000	90
24	J5M	16,280	300	620	320	1,240	210	17,000	80
24	J5R	36,770	390	1,300	510	2,200	380	53,000	140
24	J5T	11,040	120	280	160	550	110	8,000	70
24	J5V	6,170	90	100	40	230	30	4,000	170

24	J5W	20,420	170	580	260	1,020	170	17,000	100
24	J5X	6,850	80	220	100	400	70	5,000	70
24	J5Y	22,970	240	720	310	1,270	210	16,000	70
24	J5Z	22,400	210	650	300	1,150	190	26,000	140
24	J6A	28,410	310	760	350	1,430	240	25,000	100
24	J6E	36,880	530	680	310	1,520	200	19,000	100
24	J6J	19,020	330	690	340	1,360	230	17,000	70
24	J6K	19,460	310	760	350	1,410	230	20,000	90
24	J6N	12,740	120	350	170	640	120	10,000	80
24	J6R	10,630	80	300	140	520	90	6,000	70
24	J6S	19,920	300	480	280	1,070	190	14,000	80
24	J6T	14,170	270	360	200	830	120	5,000	40
24	J6V	10,680	80	290	130	510	100	10,000	110
24	J6W	25,690	330	850	430	1,610	270	25,000	90
24	J6X	19,520	200	670	290	1,170	210	16,000	70
24	J6Y	15,380	150	610	260	1,020	180	20,000	110
24	J6Z	15,100	140	510	220	880	160	23,000	150
24	J7A	11,470	100	360	150	610	110	15,000	140
24	J7B	10,590	90	320	110	530	80	52,000	640
24	J7C	35,210	340	1,200	550	2,090	370	34,000	90
24	J7E	23,180	470	930	390	1,790	240	24,000	100
24	J7G	13,850	150	480	180	800	120	30,000	260
24	J7H	5,950	70	220	100	380	70	4,000	60
24	J7J	19,410	200	630	380	1,220	260	20,000	80
24	J7K	27,640	280	860	400	1,530	270	20,000	70
24	J7L	9,710	130	390	210	720	130	12,000	90
24	J7M	18,320	280	760	360	1,400	240	13,000	60
24	J7N	22,250	220	780	390	1,380	260	21,000	80
24	J7P	20,280	250	650	290	1,180	190	11,000	60
24	J7R	29,820	380	1,020	500	1,900	330	20,000	60
24	J7T	21,220	240	860	370	1,470	280	37,000	130
24	J7V	50,640	690	2,110	930	3,740	660	50,000	80
24	J7W	11,220	170	510	210	890	160	12,000	80
24	J7X	4,140	40	140	90	270	60	4,000	70
24	J7Y	20,820	410	720	360	1,490	250	26,000	110
24	J7Z	24,270	540	860	370	1,770	230	11,000	50
24	J8A	7,780	120	290	160	560	100	9,000	90
24	J8B	11,000	190	400	220	810	150	22,000	150
24	J8C	9,130	200	320	120	640	70	6,000	90
24	J8E	8,460	90	310	150	550	100	21,000	210
24	J8G	6,490	160	210	120	490	80	8,000	90
24	J8H	11,500	320	400	190	910	120	6,000	50
24	J8L	15,060	260	430	260	960	180	14,000	70
24	J8M	9,600	130	340	200	670	140	15,000	110
24	J8N	9,540	120	370	210	700	150	17,000	110
24	J8P	26,440	520	1,060	550	2,140	360	45,000	130
24	J8R	21,920	190	750	340	1,290	220	22,000	100
24	J8T	31,750	540	1,100	510	2,150	350	28,000	80
24	J8V	20,410	190	630	310	1,120	230	29,000	120
24	J8X	6,960	250	360	140	760	70	8,000	110
24	J8Y	17,850	430	730	350	1,520	230	17,000	70
24	J8Z	11,150	210	420	170	790	120	8,000	70
24	J9A	16,290	210	640	240	1,100	160	20,000	120
24	J9B	5,300	60	220	90	370	60	27,000	420
24	J9E	6,330	230	140	60	440	40	2,000	60
24	J9H	22,840	410	1,100	460	1,960	330	39,000	120
24	J9J	24,340	320	1,080	400	1,810	290	30,000	100
24	J9L	11,800	200	230	110	540	80	6,000	80
24	J9P	26,510	280	710	330	1,320	220	18,000	80
24	J9T	10,710	140	300	110	550	70	6,000	90
24	J9V	2,920	20	80	20	130	20	-	30
24	J9X	19,200	190	600	240	1,030	170	17,000	100
24	J9Y	8,240	50	210	80	350	70	9,000	140
24	J9Z	6,210	90	160	50	300	30	1,000	50
TOTAL		6,608,190	106,570	222,670	90,760	420,000	61,970	6,419,000	100
35	K0A	81,580	470	5,420	2,020	7,910	1,530	385,000	250
35	K0B	17,090	100	920	330	1,340	220	45,000	210
35	K0C	41,890	260	2,600	810	3,670	570	122,000	210
35	K0E	30,960	230	2,110	740	3,070	530	113,000	210
35	K0G	29,920	230	2,120	740	3,100	540	115,000	210
35	K0H	35,160	250	2,720	920	3,890	670	171,000	260
35	K0J	27,280	220	1,830	490	2,540	330	77,000	230
35	K0K	89,720	700	6,790	2,230	9,720	1,510	395,000	260
35	K0L	59,070	530	4,530	1,440	6,500	980	221,000	230
35	K0M	40,940	310	3,010	1,080	4,400	770	249,000	320
35	K1A	80	-	10	-	20	-	-	-

35	K1B	13,230	100	1,010	330	1,430	220	42,000	190
35	K1C	30,120	180	1,830	570	2,580	430	88,000	210
35	K1E	12,160	50	730	270	1,040	190	41,000	220
35	K1G	26,150	220	1,980	570	2,760	410	107,000	260
35	K1H	12,600	90	870	250	1,210	190	60,000	320
35	K1J	21,110	170	1,560	410	2,140	300	61,000	200
35	K1K	23,460	210	1,900	500	2,610	340	59,000	170
35	K1L	13,160	110	1,050	350	1,510	220	69,000	310
35	K1M	5,270	40	350	130	510	100	56,000	560
35	K1N	18,930	180	1,590	420	2,180	300	94,000	310
35	K1P	720	-	50	10	60	10	7,000	660
35	K1R	14,170	100	1,080	330	1,510	240	76,000	320
35	K1S	21,800	150	1,650	480	2,270	360	123,000	340
35	K1T	27,170	270	2,270	570	3,120	400	75,000	190
35	K1V	40,410	340	3,080	880	4,300	620	149,000	240
35	K1W	8,570	40	610	190	840	140	39,000	280
35	K1X	1,360	20	110	40	170	30	13,000	420
35	K1Y	14,980	90	1,170	350	1,610	270	128,000	470
35	K1Z	16,400	120	1,430	350	1,900	230	66,000	290
35	K2A	13,320	80	920	260	1,250	190	54,000	280
35	K2B	24,600	230	1,830	460	2,520	310	76,000	240
35	K2C	20,910	160	1,550	450	2,160	310	104,000	330
35	K2E	15,150	120	1,010	310	1,440	220	52,000	240
35	K2G	37,770	290	2,910	770	3,970	560	111,000	200
35	K2H	20,440	140	1,490	460	2,090	340	77,000	230
35	K2J	54,610	490	4,240	1,250	5,980	920	258,000	280
35	K2K	18,900	160	1,450	370	1,980	280	89,000	320
35	K2L	14,790	100	1,170	370	1,640	270	40,000	150
35	K2M	21,350	160	1,580	450	2,190	340	83,000	250
35	K2P	13,230	100	930	310	1,330	230	124,000	530
35	K2R	1,040	10	80	20	110	20	19,000	960
35	K2S	25,550	170	1,820	560	2,540	420	116,000	280
35	K2T	7,920	100	670	150	920	120	28,000	230
35	K2V	3,220	20	210	60	290	50	9,000	190
35	K2W	6,090	60	550	130	740	100	30,000	310
35	K4A	42,980	240	2,950	980	4,170	700	142,000	200
35	K4B	3,810	30	220	100	340	70	16,000	230
35	K4C	3,660	20	210	80	320	50	16,000	320
35	K4K	12,350	60	660	310	1,030	200	46,000	230
35	K4M	9,720	70	660	260	990	200	94,000	470
35	K4P	7,590	50	550	210	810	160	53,000	330
35	K4R	5,990	30	350	130	500	100	24,000	240
35	K6A	10,710	50	490	140	680	100	18,000	180
35	K6H	24,920	250	1,630	380	2,260	230	37,000	160
35	K6J	14,120	120	840	250	1,210	160	32,000	200
35	K6K	2,600	10	120	40	170	30	6,000	230
35	K6T	540	-	30	10	50	10	1,000	150
35	K6V	22,380	110	1,460	450	2,030	310	67,000	210
35	K7A	13,150	80	1,030	340	1,440	240	47,000	200
35	K7C	14,230	100	1,100	430	1,630	290	59,000	200
35	K7G	6,940	50	450	180	680	130	30,000	230
35	K7H	12,790	70	850	290	1,210	210	43,000	200
35	K7K	23,670	180	2,150	560	2,890	370	81,000	220
35	K7L	13,590	100	960	270	1,340	200	112,000	550
35	K7M	36,650	250	2,860	770	3,870	550	148,000	270
35	K7N	5,980	30	390	150	570	110	16,000	160
35	K7P	17,960	80	1,230	380	1,690	280	58,000	210
35	K7R	11,540	60	810	250	1,120	180	48,000	270
35	K7S	10,760	70	680	230	990	160	29,000	180
35	K7V	10,960	70	790	220	1,070	150	22,000	140
35	K8A	21,020	120	1,280	410	1,810	270	47,000	180
35	K8B	370	-	20	-	30	-	-	-
35	K8H	10,640	50	680	190	920	130	34,000	270
35	K8N	23,880	170	1,760	580	2,510	390	107,000	270
35	K8P	16,920	120	1,270	330	1,720	220	46,000	210
35	K8R	1,220	10	60	20	90	20	4,000	250
35	K8V	21,870	140	1,630	530	2,300	350	59,000	170
35	K9A	21,730	150	1,620	450	2,230	310	89,000	280
35	K9H	21,770	190	1,830	440	2,460	300	61,000	210
35	K9J	34,240	280	2,790	720	3,790	500	100,000	200
35	K9K	10,750	70	790	180	1,030	130	35,000	270
35	K9L	6,010	40	450	130	620	100	21,000	210
35	K9V	22,550	150	1,660	490	2,300	330	64,000	190
35	LOA	10,980	80	1,010	300	1,390	220	45,000	210
35	LOB	12,260	100	1,100	370	1,570	270	94,000	350
35	LOC	7,450	60	610	190	860	140	46,000	330

35	LOE	16,180	160	1,410	450	2,030	320	78,000	240
35	LOG	32,550	300	2,620	890	3,800	630	179,000	290
35	LOH	1,210	10	140	50	200	40	9,000	230
35	LOJ	3,870	20	200	70	280	50	57,000	1,160
35	LOK	28,390	240	2,350	790	3,390	530	113,000	210
35	LOL	31,940	270	2,670	870	3,810	610	181,000	290
35	LOM	26,650	210	2,170	810	3,190	540	140,000	260
35	LON	2,150	20	250	60	330	50	11,000	220
35	LOP	6,340	60	480	190	730	140	56,000	410
35	LOR	62,470	450	4,300	1,430	6,180	1,010	244,000	240
35	LOS	46,880	350	2,900	1,000	4,250	740	223,000	300
35	L1A	12,560	80	940	280	1,300	190	44,000	230
35	L1B	9,710	60	710	250	1,010	170	48,000	270
35	L1C	33,000	250	2,880	880	4,010	580	138,000	240
35	L1E	21,020	160	1,840	560	2,560	390	74,000	190
35	L1G	32,130	250	2,690	890	3,820	580	109,000	190
35	L1H	23,500	240	2,170	670	3,080	390	100,000	250
35	L1J	31,460	270	2,840	880	3,990	570	106,000	190
35	L1K	29,310	260	2,590	880	3,730	600	121,000	200
35	L1L	6,210	90	610	190	890	130	29,000	230
35	L1M	15,000	150	1,490	430	2,060	310	83,000	270
35	L1N	37,390	320	3,350	1,000	4,670	710	164,000	230
35	L1P	12,480	130	1,210	380	1,730	260	55,000	210
35	L1R	30,240	270	2,890	740	3,900	530	138,000	260
35	L1S	31,720	300	2,930	930	4,160	630	122,000	190
35	L1T	38,560	500	4,200	1,220	5,920	780	166,000	210
35	L1V	40,980	390	3,940	1,230	5,570	880	237,000	270
35	L1W	13,830	120	1,310	430	1,850	300	97,000	320
35	L1X	15,570	210	1,630	510	2,350	370	110,000	300
35	L1Y	1,600	20	160	40	210	20	4,000	180
35	L1Z	20,970	330	2,250	700	3,280	480	90,000	190
35	L2A	12,960	100	1,070	350	1,520	260	49,000	190
35	L2E	14,500	150	1,240	390	1,790	250	54,000	220
35	L2G	22,450	220	1,770	570	2,560	410	60,000	150
35	L2H	21,620	190	1,550	470	2,210	330	75,000	230
35	L2J	12,380	70	820	270	1,170	200	55,000	280
35	L2M	25,850	170	1,860	570	2,600	390	74,000	190
35	L2N	24,670	160	1,590	500	2,250	360	82,000	230
35	L2P	11,380	80	850	260	1,200	180	31,000	180
35	L2R	18,840	160	1,640	480	2,270	310	70,000	230
35	L2S	14,530	130	1,210	290	1,640	210	34,000	170
35	L2T	8,670	80	650	190	920	130	29,000	220
35	L2V	13,220	110	1,000	300	1,420	210	27,000	130
35	L2W	1,630	20	120	30	160	20	27,000	1,480
35	L3B	18,150	130	1,370	390	1,900	250	43,000	170
35	L3C	25,740	180	1,800	520	2,500	360	68,000	190
35	L3K	15,300	110	960	310	1,370	190	60,000	310
35	L3L	-	-	-	-	-	-	-	-
35	L3M	21,190	120	1,370	480	1,970	340	96,000	290
35	L3P	30,740	310	2,290	580	3,190	440	159,000	360
35	L3R	53,370	630	3,380	760	4,770	570	219,000	380
35	L3S	44,700	630	3,780	900	5,310	640	158,000	250
35	L3T	42,190	510	2,840	790	4,150	600	183,000	300
35	L3V	36,250	270	2,840	860	3,970	580	104,000	180
35	L3X	33,240	320	2,760	710	3,780	530	129,000	240
35	L3Y	33,900	270	2,660	820	3,760	560	124,000	220
35	L3Z	27,490	290	2,320	810	3,430	570	179,000	320
35	L4A	35,010	370	2,870	840	4,070	620	135,000	220
35	L4B	31,720	440	2,260	510	3,210	390	102,000	260
35	L4C	59,900	840	4,550	1,220	6,600	910	254,000	280
35	L4E	39,720	610	3,320	920	4,850	700	235,000	330
35	L4G	45,520	420	3,590	980	4,990	720	220,000	310
35	L4H	52,820	630	4,480	1,350	6,460	1,010	286,000	280
35	L4J	62,920	600	3,850	1,070	5,530	840	259,000	310
35	L4K	14,250	140	1,060	330	1,530	250	72,000	290
35	L4L	46,420	440	3,120	1,060	4,610	790	197,000	250
35	L4M	34,030	260	2,940	980	4,170	650	183,000	280
35	L4N	72,750	620	6,540	2,180	9,330	1,410	298,000	210
35	L4P	21,340	180	1,940	700	2,820	480	136,000	280
35	L4R	15,290	110	1,180	390	1,680	260	81,000	310
35	L4S	28,080	450	2,240	470	3,150	350	76,000	220
35	L4T	29,970	510	2,950	850	4,300	570	82,000	140
35	L4V	70	-	10	-	10	-	-	-
35	L4W	17,490	180	1,170	370	1,710	280	69,000	240
35	L4X	14,710	170	1,060	310	1,540	220	60,000	270
35	L4Y	18,950	170	1,290	390	1,850	290	44,000	150

35	L4Z	30,450	400	2,520	670	3,580	470	115,000	250
35	L5A	37,830	410	2,700	770	3,880	530	109,000	210
35	L5B	50,960	740	3,820	1,020	5,570	720	168,000	230
35	L5C	24,110	260	1,790	540	2,600	380	98,000	260
35	L5E	10,130	100	840	260	1,190	210	55,000	270
35	L5G	15,700	130	1,120	450	1,700	330	118,000	360
35	L5H	13,710	120	920	330	1,360	240	170,000	700
35	L5J	21,760	170	1,660	540	2,370	380	130,000	340
35	L5K	10,450	120	790	220	1,130	160	51,000	320
35	L5L	35,960	370	2,960	760	4,100	550	98,000	180
35	L5M	83,420	1,260	7,090	1,880	10,230	1,390	356,000	260
35	L5N	66,040	720	5,800	1,540	8,060	1,130	207,000	180
35	L5P	20	-	10	-	10	-	-	-
35	L5R	31,060	450	2,530	670	3,650	480	102,000	210
35	L5S	160	10	10	10	30	-	-	-
35	L5T	240	-	30	20	40	10	2,000	170
35	L5V	41,420	640	3,670	840	5,150	610	113,000	190
35	L5W	19,500	300	1,780	460	2,540	330	85,000	250
35	L6A	66,670	810	5,310	1,480	7,600	1,080	280,000	260
35	L6B	22,340	310	2,040	510	2,850	380	77,000	200
35	L6C	39,240	570	2,940	550	4,060	420	138,000	330
35	L6E	28,160	400	2,430	500	3,330	370	78,000	210
35	L6G	4,780	60	320	80	460	60	14,000	230
35	L6H	49,720	530	3,910	1,070	5,510	810	274,000	340
35	L6J	19,470	200	1,170	390	1,760	310	281,000	920
35	L6K	10,800	110	820	250	1,180	180	93,000	510
35	L6L	23,430	200	1,660	550	2,400	410	162,000	400
35	L6M	50,500	600	4,190	1,150	5,940	860	331,000	380
35	L6P	69,710	1,390	7,690	2,420	11,510	1,820	637,000	350
35	L6R	71,750	1,280	6,920	2,180	10,380	1,650	290,000	180
35	L6S	42,400	520	3,950	1,210	5,680	840	132,000	160
35	L6T	29,450	370	2,520	740	3,630	500	85,000	170
35	L6V	31,800	360	3,100	890	4,350	590	121,000	210
35	L6W	17,420	190	1,510	440	2,150	290	58,000	200
35	L6X	55,430	830	5,550	1,720	8,090	1,180	205,000	170
35	L6Y	71,840	1,130	6,670	1,910	9,710	1,370	276,000	200
35	L6Z	26,010	310	2,440	790	3,530	560	112,000	200
35	L7A	68,080	1,040	6,750	2,210	10,000	1,570	286,000	180
35	L7B	12,730	110	900	360	1,370	270	113,000	420
35	L7C	22,210	310	2,000	720	3,020	560	147,000	260
35	L7E	26,130	230	2,230	640	3,100	440	96,000	220
35	L7G	36,100	220	2,990	820	4,040	600	158,000	260
35	L7J	10,550	90	1,030	310	1,430	220	53,000	240
35	L7K	6,640	60	570	210	840	160	46,000	290
35	L7L	35,840	270	2,730	800	3,790	610	169,000	280
35	L7M	36,940	300	2,680	780	3,760	600	168,000	280
35	L7N	10,570	60	700	240	990	170	65,000	380
35	L7P	23,010	140	1,670	530	2,330	370	104,000	280
35	L7R	12,800	90	880	320	1,290	240	98,000	410
35	L7S	9,680	50	660	220	930	170	36,000	210
35	L7T	14,360	90	910	370	1,370	270	89,000	330
35	L8B	15,910	100	1,210	390	1,700	290	76,000	270
35	L8E	31,200	280	2,210	740	3,230	480	126,000	260
35	L8G	17,880	110	1,070	340	1,520	240	43,000	180
35	L8H	19,550	150	1,610	520	2,290	280	38,000	130
35	L8J	19,290	180	1,480	420	2,080	300	95,000	310
35	L8K	24,670	190	1,690	570	2,450	380	88,000	230
35	L8L	21,980	290	2,190	600	3,070	370	62,000	170
35	L8M	9,660	110	1,010	290	1,410	190	44,000	230
35	L8N	10,690	120	1,120	260	1,510	160	32,000	210
35	L8P	17,340	140	1,470	410	2,010	270	103,000	380
35	L8R	7,950	90	680	150	930	90	14,000	160
35	L8S	10,620	110	830	190	1,130	140	36,000	250
35	L8T	15,190	100	1,040	300	1,450	200	33,000	170
35	L8V	16,440	100	1,150	340	1,580	210	36,000	170
35	L8W	20,140	160	1,530	440	2,120	300	45,000	150
35	L9A	19,510	140	1,350	420	1,910	290	52,000	180
35	L9B	19,120	160	1,320	370	1,860	280	73,000	260
35	L9C	31,050	260	2,230	660	3,150	450	95,000	210
35	L9E	4,980	80	430	150	660	110	23,000	220
35	L9G	19,100	150	1,250	420	1,820	330	217,000	660
35	L9H	24,780	150	1,770	560	2,480	440	162,000	370
35	L9J	700	-	40	20	60	10	6,000	540
35	L9K	10,820	130	870	260	1,250	190	63,000	330
35	L9L	11,880	90	940	290	1,320	200	38,000	190
35	L9M	12,150	120	1,050	300	1,470	190	59,000	310

35	L9N	11,860	110	1,030	320	1,470	210	43,000	200
35	L9P	13,540	100	1,180	340	1,620	260	70,000	270
35	L9R	18,020	130	1,280	420	1,830	270	51,000	190
35	L9S	22,150	210	1,910	710	2,830	440	124,000	280
35	L9T	73,720	1,010	6,710	2,070	9,780	1,490	430,000	290
35	L9V	12,150	120	1,020	470	1,600	320	63,000	200
35	L9W	36,340	270	3,060	1,050	4,370	730	223,000	310
35	L9X	8,190	60	630	180	860	130	52,000	390
35	L9Y	20,540	140	1,600	590	2,340	440	162,000	370
35	L9Z	18,210	140	1,260	440	1,840	290	61,000	210
35	M1B	51,600	630	4,830	1,250	6,710	800	151,000	190
35	M1C	28,920	340	2,700	750	3,790	550	156,000	290
35	M1E	36,560	400	3,270	890	4,560	580	92,000	160
35	M1G	22,820	350	1,950	400	2,700	260	49,000	190
35	M1H	19,180	300	1,690	390	2,380	250	59,000	240
35	M1J	27,940	350	2,450	550	3,360	360	48,000	130
35	M1K	38,150	470	3,180	790	4,450	510	92,000	180
35	M1L	26,400	330	2,150	620	3,100	460	92,000	200
35	M1M	18,120	210	1,670	500	2,370	370	100,000	270
35	M1N	16,870	170	1,620	450	2,240	330	131,000	390
35	M1P	34,660	470	2,690	630	3,780	400	79,000	200
35	M1R	23,520	270	1,960	570	2,790	400	80,000	200
35	M1S	31,210	350	2,070	470	2,890	350	107,000	310
35	M1T	27,910	290	2,030	450	2,760	330	78,000	240
35	M1V	44,190	480	2,520	530	3,530	380	61,000	160
35	M1W	39,570	500	2,460	510	3,470	380	69,000	180
35	M1X	12,150	180	1,240	270	1,690	180	32,000	180
35	M2H	20,130	250	1,440	270	1,960	200	63,000	310
35	M2J	47,490	610	3,270	740	4,620	540	137,000	260
35	M2K	19,130	280	1,340	350	1,960	270	122,000	460
35	M2L	9,310	110	590	170	870	130	62,000	470
35	M2M	27,750	400	1,920	440	2,750	350	79,000	230
35	M2N	60,250	870	4,500	970	6,340	740	254,000	340
35	M2P	6,260	60	350	100	520	80	70,000	870
35	M2R	34,060	360	2,220	510	3,080	350	102,000	290
35	M3A	26,250	310	2,230	610	3,140	390	83,000	210
35	M3B	11,490	110	640	200	940	170	145,000	870
35	M3C	30,230	440	2,290	550	3,270	390	107,000	280
35	M3H	29,610	260	1,920	570	2,760	430	120,000	280
35	M3J	22,810	290	2,050	480	2,820	300	56,000	190
35	M3K	6,320	50	400	140	590	100	22,000	210
35	M3L	14,860	160	1,290	380	1,830	250	37,000	150
35	M3M	19,500	180	1,420	470	2,070	290	54,000	190
35	M3N	31,070	290	2,840	650	3,790	360	51,000	140
35	M4A	11,320	160	870	240	1,270	160	54,000	330
35	M4B	14,170	170	1,350	360	1,870	260	62,000	240
35	M4C	34,660	390	3,080	800	4,270	560	144,000	260
35	M4E	18,450	190	1,780	590	2,560	440	223,000	510
35	M4G	14,930	120	1,000	300	1,420	240	117,000	490
35	M4H	13,310	270	920	200	1,400	130	17,000	130
35	M4J	26,490	250	2,410	630	3,300	490	137,000	280
35	M4K	23,480	200	2,030	610	2,840	470	158,000	340
35	M4L	23,160	220	2,240	700	3,160	540	196,000	370
35	M4M	17,900	130	1,630	460	2,230	360	141,000	400
35	M4N	12,250	100	660	240	1,000	180	230,000	1,270
35	M4P	16,470	130	1,200	350	1,680	260	74,000	290
35	M4R	8,760	70	570	190	830	140	84,000	610
35	M4S	21,190	190	1,500	450	2,130	360	228,000	640
35	M4T	9,090	50	450	180	680	150	102,000	690
35	M4V	14,410	90	760	300	1,140	220	339,000	1,580
35	M4W	11,980	120	680	270	1,070	220	190,000	860
35	M4X	15,430	150	1,210	310	1,670	220	57,000	260
35	M4Y	23,650	200	1,960	530	2,690	400	112,000	280
35	M5A	32,170	300	3,030	830	4,150	560	243,000	440
35	M5B	10,170	90	900	220	1,200	150	53,000	350
35	M5C	3,150	30	240	70	330	60	52,000	870
35	M5E	8,350	70	610	200	870	150	55,000	370
35	M5G	19,340	110	590	120	810	90	34,000	370
35	M5H	2,890	30	210	80	320	60	91,000	1,510
35	M5J	11,730	110	840	300	1,250	240	166,000	680
35	M5K	210	-	10	10	10	-	-	-
35	M5L	40	-	-	-	-	-	-	-
35	M5M	19,720	190	1,190	340	1,720	260	222,000	860
35	M5N	12,450	100	740	220	1,050	160	92,000	560
35	M5P	15,300	110	890	310	1,300	220	168,000	760
35	M5R	19,310	150	1,380	460	1,990	340	187,000	550

35	M5S	12,250	120	1,000	250	1,370	200	97,000	490
35	M5T	14,020	140	1,190	270	1,600	170	40,000	230
35	M5V	37,630	300	2,960	1,110	4,360	860	320,000	370
35	M5W	140	-	10	10	20	-	1,000	170
35	M5X	90	-	10	-	10	-	-	-
35	M6A	16,460	160	1,400	380	1,940	250	57,000	230
35	M6B	22,530	210	1,530	450	2,190	300	124,000	410
35	M6C	18,280	160	1,360	400	1,910	300	112,000	370
35	M6E	29,720	290	2,550	760	3,610	540	110,000	200
35	M6G	23,010	200	1,990	710	2,890	560	234,000	420
35	M6H	34,120	370	3,040	1,070	4,490	810	192,000	240
35	M6J	23,800	190	2,010	700	2,910	540	380,000	710
35	M6K	28,980	240	2,550	850	3,630	620	195,000	310
35	M6L	16,100	180	1,230	330	1,740	240	50,000	210
35	M6M	32,190	350	2,830	880	4,060	580	110,000	190
35	M6N	31,360	320	2,790	830	3,940	580	111,000	190
35	M6P	29,720	230	2,720	760	3,710	590	166,000	280
35	M6R	13,890	120	1,310	470	1,890	370	180,000	490
35	M6S	25,360	180	2,160	630	2,970	490	242,000	490
35	M7A	10	-	-	-	-	-	-	-
35	M8V	30,840	240	2,520	780	3,540	560	164,000	290
35	M8W	16,760	140	1,440	460	2,040	360	92,000	260
35	M8X	8,660	60	480	150	690	130	78,000	620
35	M8Y	16,470	150	1,330	460	1,940	340	106,000	320
35	M8Z	13,810	110	970	330	1,400	260	78,000	300
35	M9A	28,300	240	1,900	570	2,700	430	191,000	450
35	M9B	26,090	240	1,820	570	2,620	420	188,000	440
35	M9C	30,860	270	2,170	660	3,100	500	141,000	280
35	M9L	9,760	130	850	220	1,200	140	18,000	130
35	M9M	18,270	240	1,720	490	2,450	330	62,000	190
35	M9N	19,390	250	1,840	570	2,650	360	79,000	220
35	M9P	16,450	150	1,210	340	1,690	240	54,000	220
35	M9R	26,630	300	2,080	620	3,000	440	83,000	190
35	M9V	43,310	540	3,840	980	5,360	650	101,000	160
35	M9W	32,830	420	3,230	880	4,530	560	110,000	200
35	N0A	29,010	280	2,380	620	3,280	420	99,000	230
35	N0B	63,300	390	4,080	1,270	5,730	970	261,000	270
35	N0C	12,320	100	940	320	1,360	210	53,000	260
35	N0E	27,850	180	1,650	500	2,340	370	119,000	320
35	N0G	63,720	530	3,990	1,120	5,640	770	193,000	250
35	N0H	39,860	280	2,720	810	3,810	560	205,000	370
35	N0J	24,440	180	1,320	470	1,970	330	101,000	300
35	N0K	18,410	100	890	230	1,220	160	47,000	290
35	N0L	38,810	270	2,860	850	3,980	610	157,000	260
35	N0M	52,800	320	3,050	890	4,260	610	148,000	240
35	N0N	32,240	180	2,040	570	2,790	400	104,000	260
35	N0P	41,850	250	2,420	730	3,400	490	99,000	210
35	N0R	37,010	240	2,360	780	3,380	560	94,000	170
35	N1A	9,740	40	590	200	830	130	45,000	350
35	N1C	3,010	20	240	70	330	50	19,000	360
35	N1E	31,760	170	2,350	760	3,280	510	99,000	200
35	N1G	20,870	130	1,560	400	2,090	290	67,000	230
35	N1H	32,810	190	2,370	740	3,300	530	124,000	230
35	N1K	7,940	50	570	120	740	80	26,000	330
35	N1L	11,330	100	860	220	1,180	170	55,000	330
35	N1M	13,130	70	880	270	1,220	190	61,000	310
35	N1P	5,570	20	410	160	590	90	15,000	170
35	N1R	32,160	240	2,300	750	3,290	510	111,000	220
35	N1S	14,790	90	1,020	340	1,450	240	60,000	250
35	N1T	13,880	140	1,140	330	1,600	250	90,000	360
35	N2A	23,310	160	1,440	430	2,040	310	73,000	240
35	N2B	13,510	80	850	290	1,210	200	37,000	190
35	N2C	13,010	100	800	250	1,150	160	25,000	150
35	N2E	29,290	240	1,950	560	2,760	390	62,000	160
35	N2G	10,840	90	860	250	1,200	160	38,000	240
35	N2H	16,330	140	1,270	400	1,800	260	57,000	220
35	N2J	14,560	90	980	270	1,330	190	56,000	290
35	N2K	21,730	160	1,440	390	1,990	280	195,000	690
35	N2L	23,380	210	1,670	360	2,240	240	111,000	470
35	N2M	26,100	200	1,820	530	2,540	360	61,000	170
35	N2N	20,090	140	1,350	400	1,890	260	53,000	200
35	N2P	16,310	160	1,120	370	1,650	260	58,000	220
35	N2R	10,430	110	770	270	1,150	210	44,000	210
35	N2T	16,180	120	1,100	270	1,490	190	80,000	420
35	N2V	13,740	150	990	260	1,410	190	46,000	240
35	N2Z	9,170	60	610	180	850	140	41,000	290

35	N3A	12,700	50	710	210	970	150	31,000	210
35	N3B	9,310	40	460	140	630	100	22,000	220
35	N3C	20,100	140	1,560	480	2,180	350	77,000	220
35	N3E	390	10	40	20	60	10	3,000	310
35	N3H	17,420	110	1,160	360	1,630	240	50,000	210
35	N3L	11,730	80	790	230	1,100	170	40,000	240
35	N3P	6,510	50	450	130	630	90	20,000	220
35	N3R	28,220	140	1,770	610	2,520	420	116,000	280
35	N3S	19,140	160	1,700	480	2,330	290	51,000	180
35	N3T	25,210	220	1,990	580	2,790	380	88,000	230
35	N3V	1,290	10	70	20	100	10	1,000	90
35	N3W	11,020	80	840	240	1,160	180	49,000	280
35	N3Y	18,280	110	1,070	310	1,480	210	39,000	180
35	N4B	6,340	30	350	90	470	50	5,000	100
35	N4G	16,270	70	760	260	1,090	180	55,000	310
35	N4K	23,010	120	1,570	410	2,100	290	55,000	190
35	N4L	6,600	50	430	140	620	90	15,000	160
35	N4N	8,290	50	470	110	630	80	10,000	130
35	N4S	25,240	140	1,590	540	2,270	340	138,000	410
35	N4T	9,640	70	580	180	830	130	18,000	140
35	N4V	2,410	10	150	50	210	30	6,000	180
35	N4W	9,080	30	420	120	580	90	13,000	150
35	N4X	7,950	30	390	120	530	80	14,000	170
35	N4Z	1,850	10	120	30	160	20	4,000	180
35	N5A	25,810	140	1,550	480	2,160	350	101,000	290
35	N5C	11,880	80	810	230	1,120	170	40,000	230
35	N5H	11,520	90	530	180	790	140	41,000	290
35	N5L	2,730	10	160	80	250	50	11,000	220
35	N5P	15,530	100	1,020	360	1,470	240	47,000	200
35	N5R	22,060	110	1,300	440	1,850	290	55,000	190
35	N5V	23,540	150	1,770	480	2,400	290	53,000	180
35	N5W	18,090	140	1,590	510	2,250	300	65,000	210
35	N5X	25,890	190	1,610	450	2,250	320	68,000	210
35	N5Y	25,500	190	1,900	520	2,610	350	78,000	230
35	N5Z	17,660	150	1,590	440	2,180	280	47,000	170
35	N6A	8,510	50	650	160	860	120	47,000	410
35	N6B	7,490	50	720	180	950	100	25,000	250
35	N6C	23,230	150	1,880	600	2,630	410	80,000	190
35	N6E	20,470	190	1,440	470	2,100	310	69,000	220
35	N6G	33,400	320	2,400	660	3,370	470	126,000	270
35	N6H	31,780	270	2,210	600	3,080	450	107,000	240
35	N6J	21,330	150	1,560	490	2,200	320	76,000	240
35	N6K	28,110	180	1,850	510	2,540	380	122,000	320
35	N6L	2,810	40	200	60	300	40	13,000	300
35	N6M	4,820	20	320	100	440	60	14,000	230
35	N6N	580	-	30	10	50	10	3,000	270
35	N6P	7,180	50	510	160	720	120	65,000	540
35	N7A	9,810	50	620	130	790	90	22,000	240
35	N7G	14,720	80	960	300	1,340	210	43,000	210
35	N7L	19,900	100	1,140	340	1,580	230	41,000	180
35	N7M	19,330	120	1,350	390	1,870	250	61,000	240
35	N7S	22,030	120	1,330	410	1,860	290	78,000	270
35	N7T	19,700	130	1,610	410	2,150	260	55,000	210
35	N7V	9,590	40	540	180	760	130	26,000	210
35	N7W	2,180	10	60	30	100	30	4,000	140
35	N7X	940	10	50	20	80	20	6,000	310
35	N8A	10,830	70	740	170	980	100	17,000	170
35	N8H	20,090	130	1,130	330	1,590	220	51,000	240
35	N8M	8,900	40	500	140	680	100	22,000	220
35	N8N	20,170	120	1,120	320	1,570	250	53,000	210
35	N8P	10,290	60	550	160	760	130	28,000	220
35	N8R	9,790	70	560	170	800	110	22,000	200
35	N8S	17,730	110	1,100	360	1,560	240	41,000	170
35	N8T	13,440	90	840	230	1,170	150	45,000	290
35	N8V	10	-	-	-	-	-	-	-
35	N8W	18,910	120	1,200	370	1,690	270	46,000	170
35	N8X	12,390	120	970	270	1,350	180	26,000	150
35	N8Y	14,510	80	1,040	330	1,450	210	56,000	260
35	N9A	18,870	190	1,460	360	2,020	230	35,000	160
35	N9B	13,700	200	1,050	260	1,500	170	33,000	200
35	N9C	8,700	90	680	140	900	100	9,000	90
35	N9E	16,760	160	980	340	1,470	260	45,000	170
35	N9G	15,500	180	940	280	1,400	220	57,000	260
35	N9H	9,590	60	500	150	710	120	32,000	270
35	N9J	15,570	70	780	280	1,130	220	60,000	280
35	N9K	2,060	10	120	30	160	30	4,000	140

35	N9V	16,490	80	870	330	1,280	230	57,000	250
35	N9Y	11,720	60	640	180	890	140	41,000	300
35	P0A	13,700	110	890	360	1,370	240	73,000	310
35	P0B	7,080	60	520	190	760	140	45,000	310
35	P0C	3,090	30	250	100	370	60	23,000	370
35	P0E	2,590	20	210	90	320	60	11,000	180
35	P0G	2,630	20	200	80	300	50	12,000	220
35	P0H	25,600	210	1,710	520	2,440	340	181,000	540
35	P0J	16,570	100	1,120	310	1,530	210	56,000	260
35	P0K	8,790	60	640	180	870	120	28,000	230
35	P0L	18,060	230	1,560	310	2,100	160	45,000	280
35	P0M	39,390	230	2,810	850	3,900	580	122,000	210
35	P0N	7,200	40	510	170	720	100	32,000	310
35	P0P	14,910	230	1,620	300	2,150	150	33,000	210
35	P0R	10,230	80	690	170	940	110	15,000	140
35	P0S	7,920	40	520	200	760	120	22,000	180
35	P0T	24,570	220	2,010	470	2,700	290	54,000	190
35	P0V	14,450	350	2,020	200	2,580	100	24,000	240
35	P0W	4,820	60	400	110	580	80	15,000	190
35	P0X	5,410	90	600	90	780	60	12,000	210
35	P0Y	50	-	-	-	-	-	-	-
35	P1A	13,010	100	1,000	250	1,350	170	37,000	220
35	P1B	25,540	200	2,220	570	2,980	360	61,000	170
35	P1C	2,680	20	190	40	250	40	8,000	210
35	P1H	13,610	80	990	370	1,450	260	91,000	350
35	P1L	13,640	80	960	370	1,410	260	76,000	300
35	P1P	7,900	70	630	200	900	130	46,000	350
35	P2A	10,880	90	940	260	1,280	170	40,000	240
35	P2B	7,810	60	510	120	700	70	8,000	120
35	P2N	5,440	50	480	140	670	80	18,000	230
35	P3A	18,880	100	1,350	400	1,850	280	65,000	240
35	P3B	12,090	60	1,070	280	1,410	190	36,000	190
35	P3C	12,140	100	1,150	300	1,540	170	31,000	190
35	P3E	21,760	130	1,500	420	2,040	310	366,000	1,180
35	P3G	3,270	20	240	80	340	60	24,000	370
35	P3L	6,200	20	420	140	580	100	17,000	170
35	P3N	6,240	40	420	130	590	100	15,000	150
35	P3P	11,990	50	730	260	1,040	180	20,000	110
35	P3Y	5,920	30	440	120	580	80	21,000	260
35	P4N	19,570	90	1,270	370	1,740	240	44,000	180
35	P4P	2,520	20	160	50	220	30	8,000	260
35	P4R	3,620	10	180	70	270	50	21,000	470
35	P5A	9,360	90	710	180	980	110	16,000	140
35	P5E	4,290	30	280	80	380	60	8,000	130
35	P5N	6,700	30	270	120	420	90	27,000	300
35	P6A	27,830	180	2,020	560	2,760	340	67,000	200
35	P6B	18,280	90	1,180	310	1,580	210	28,000	140
35	P6C	15,170	50	1,000	360	1,420	230	34,000	150
35	P7A	22,040	150	1,700	380	2,230	260	66,000	260
35	P7B	17,520	150	1,430	290	1,870	210	60,000	290
35	P7C	16,530	110	1,380	320	1,820	210	42,000	200
35	P7E	16,210	110	1,340	350	1,800	240	37,000	160
35	P7G	9,710	50	650	200	890	140	24,000	170
35	P7J	3,700	30	340	60	430	50	9,000	180
35	P7K	5,320	20	280	80	390	70	10,000	150
35	P7L	1,580	10	130	40	170	30	6,000	220
35	P8N	8,560	60	760	170	990	130	24,000	180
35	P8T	3,720	40	370	90	490	60	15,000	260
35	P9A	7,800	90	780	220	1,090	160	29,000	190
35	P9N	11,040	50	830	240	1,120	170	41,000	250
TOTAL		10,652,080	98,120	817,090	239,820	1,155,030	169,080	45,777,000	270
46	R0A	30,870	180	1,710	580	2,470	390	111,000	290
46	R0B	28,190	190	1,470	200	1,850	70	13,000	180
46	R0C	40,240	200	2,560	760	3,530	520	130,000	250
46	R0E	35,120	140	2,060	620	2,830	410	96,000	230
46	R0G	31,240	120	1,440	410	1,980	290	90,000	310
46	R0H	10,210	50	450	150	650	100	25,000	250
46	R0J	21,140	70	930	240	1,230	160	49,000	310
46	R0K	19,590	70	790	260	1,120	180	40,000	220
46	R0L	20,570	80	1,120	270	1,470	200	47,000	240
46	R0M	14,640	50	660	180	890	140	52,000	370
46	R1A	16,410	60	1,070	320	1,440	220	68,000	310
46	R1B	260	-	10	-	10	-	-	-
46	R1C	3,100	20	210	60	290	40	7,000	160
46	R1N	14,620	30	620	170	820	110	23,000	220
46	R2C	25,770	90	1,400	440	1,930	290	61,000	210

46	R2E	7,720	40	430	120	590	100	25,000	260
46	R2G	27,020	70	1,440	370	1,880	260	66,000	260
46	R2H	12,360	60	780	210	1,040	150	38,000	260
46	R2J	20,890	80	1,310	340	1,730	250	63,000	260
46	R2K	25,640	80	1,510	420	2,010	280	55,000	190
46	R2L	10,810	60	700	210	970	130	30,000	240
46	R2M	29,770	120	1,790	420	2,330	290	76,000	260
46	R2N	25,010	90	1,370	320	1,780	240	60,000	250
46	R2P	25,860	130	1,220	360	1,710	280	63,000	230
46	R2R	18,780	80	820	230	1,130	160	29,000	180
46	R2V	28,160	90	1,490	420	1,990	280	58,000	210
46	R2W	20,090	130	1,570	330	2,030	170	65,000	380
46	R2X	14,700	50	590	170	810	100	17,000	180
46	R2Y	15,070	60	880	230	1,170	150	31,000	200
46	R3A	3,210	20	230	40	290	20	3,000	150
46	R3B	9,650	50	640	140	820	80	15,000	200
46	R3C	15,290	50	880	190	1,120	130	43,000	330
46	R3E	14,380	70	690	160	920	100	16,000	170
46	R3G	18,650	90	1,420	350	1,850	240	45,000	190
46	R3H	150	-	10	-	10	-	3,000	1,160
46	R3J	21,330	80	1,200	330	1,610	230	76,000	340
46	R3K	10,180	30	560	120	710	90	14,000	170
46	R3L	15,170	50	1,130	250	1,430	180	50,000	280
46	R3M	17,090	60	950	300	1,300	210	85,000	410
46	R3N	12,610	40	860	210	1,110	150	51,000	350
46	R3P	16,410	40	730	180	950	150	61,000	420
46	R3R	19,720	60	1,150	290	1,500	200	66,000	330
46	R3S	420	-	30	20	50	20	12,000	800
46	R3T	37,640	220	2,350	430	3,000	320	73,000	230
46	R3V	4,960	20	330	90	440	50	13,000	240
46	R3W	9,610	20	540	150	710	110	36,000	320
46	R3X	14,180	70	870	200	1,140	150	37,000	240
46	R3Y	18,910	110	1,240	260	1,610	190	72,000	380
46	R4A	3,250	10	220	70	300	50	18,000	380
46	R4G	1,110	10	60	10	70	10	2,000	180
46	R4H	1,840	10	110	30	140	20	2,000	140
46	R4J	930	-	70	20	80	10	3,000	240
46	R4K	640	-	40	10	50	10	1,000	90
46	R4L	900	-	60	20	80	10	8,000	640
46	R5A	2,660	10	180	60	240	40	10,000	250
46	R5G	18,290	100	810	280	1,190	210	48,000	230
46	R5H	4,390	30	310	100	430	60	10,000	180
46	R5J	260	-	20	10	40	10	1,000	120
46	R5K	960	-	70	10	80	-	-	-
46	R5L	-	-	-	-	-	-	-	-
46	R5M	10	-	-	-	-	-	-	-
46	R5N	-	-	-	-	-	-	-	-
46	R6M	8,410	40	350	120	500	80	21,000	260
46	R6W	14,700	70	430	190	690	140	48,000	350
46	R7A	24,580	80	1,200	330	1,600	220	56,000	260
46	R7B	16,800	40	730	220	990	140	25,000	170
46	R7C	2,040	-	80	20	100	10	5,000	470
46	R7N	8,060	20	350	80	450	60	9,000	160
46	R8A	4,590	10	410	60	470	30	5,000	170
46	R8N	9,210	40	800	130	970	70	20,000	270
46	R9A	5,810	30	350	60	440	30	14,000	450
TOTAL		982,770	4,020	54,810	14,310	73,130	9,760	2,576,000	260
47	S0A	41,130	290	1,700	530	2,530	340	98,000	290
47	S0C	16,210	80	590	240	900	160	67,000	420
47	S0E	26,200	140	970	280	1,390	170	45,000	260
47	S0G	49,330	280	2,170	710	3,150	460	133,000	290
47	S0H	16,750	60	610	270	950	190	74,000	390
47	S0J	35,940	410	2,180	460	3,040	240	57,000	240
47	S0K	66,840	320	2,640	910	3,880	600	204,000	340
47	S0L	24,090	90	700	280	1,070	200	88,000	440
47	S0M	34,140	400	2,070	510	2,980	280	110,000	400
47	S0N	16,180	90	550	180	820	110	49,000	450
47	S0P	4,930	90	500	40	630	10	1,000	90
47	S2V	660	-	30	10	40	-	-	-
47	S3N	15,180	70	620	170	860	100	17,000	170
47	S4A	10,030	30	300	120	450	70	36,000	520
47	S4H	9,740	20	270	120	420	70	27,000	370
47	S4L	4,530	10	190	60	260	50	29,000	640
47	S4N	23,070	110	1,010	310	1,430	190	43,000	220
47	S4P	11,790	130	500	170	790	110	33,000	290
47	S4R	27,480	130	1,050	330	1,510	210	42,000	200

47	S4S	26,890	150	1,150	300	1,600	210	72,000	350
47	S4T	23,180	160	1,220	370	1,750	230	102,000	450
47	S4V	23,440	100	860	230	1,190	170	71,000	420
47	S4W	8,250	60	340	90	500	70	37,000	500
47	S4X	21,590	70	680	260	1,010	180	61,000	350
47	S4Y	3,830	10	120	40	170	30	10,000	330
47	S4Z	990	10	30	10	40	10	3,000	530
47	S6H	23,060	100	970	280	1,340	170	51,000	290
47	S6J	3,950	10	150	40	200	20	6,000	260
47	S6K	950	10	40	10	50	10	4,000	750
47	S6V	30,610	220	1,650	440	2,320	240	61,000	250
47	S6W	190	-	-	-	10	-	-	-
47	S6X	1,730	10	70	30	100	20	14,000	740
47	S7B	60	-	10	-	10	-	-	-
47	S7C	360	-	20	10	30	-	-	-
47	S7H	27,840	150	1,410	330	1,890	240	76,000	320
47	S7J	24,320	90	1,120	310	1,520	190	75,000	400
47	S7K	33,120	210	1,580	480	2,270	350	116,000	340
47	S7L	30,350	220	1,710	440	2,360	260	66,000	260
47	S7M	23,370	200	1,390	390	1,980	210	48,000	230
47	S7N	20,230	120	1,020	240	1,390	150	57,000	370
47	S7P	180	-	10	-	10	-	-	-
47	S7R	5,830	30	240	90	360	60	17,000	260
47	S7S	4,660	20	220	50	290	30	8,000	250
47	S7T	10,680	60	460	140	660	100	34,000	330
47	S7V	9,340	60	360	100	520	80	25,000	320
47	S7W	10,840	70	530	160	760	120	47,000	380
47	S9A	11,650	80	700	150	940	90	28,000	310
47	S9H	15,410	60	590	170	820	110	33,000	310
47	S9V	10,610	90	590	220	900	130	45,000	350
47	S9X	6,310	40	330	100	470	50	10,000	210
TOTAL		848,020	5,160	38,180	11,170	54,510	7,100	2,347,000	330
48	T0A	43,450	1,690	2,200	970	4,870	620	170,000	270
48	T0B	46,470	820	1,840	1,000	3,660	660	193,000	290
48	T0C	45,210	1,600	1,880	950	4,430	620	179,000	290
48	T0E	28,930	880	1,600	760	3,240	500	128,000	260
48	T0G	29,210	1,160	1,570	580	3,310	320	78,000	240
48	T0H	57,760	2,100	3,260	1,110	6,470	730	250,000	340
48	T0J	37,170	950	1,420	700	3,070	470	124,000	270
48	T0K	42,010	1,240	1,670	730	3,640	460	122,000	270
48	T0L	40,970	1,650	1,700	860	4,220	530	212,000	400
48	T0M	49,510	860	2,260	1,200	4,320	820	249,000	300
48	T0P	1,670	180	160	60	400	20	7,000	280
48	T0V	10	-	-	-	-	-	-	-
48	T1A	20,100	450	790	410	1,650	270	58,000	220
48	T1B	24,700	270	820	340	1,430	220	52,000	240
48	T1C	6,920	80	240	120	440	80	11,000	140
48	T1G	8,130	90	260	120	470	80	26,000	320
48	T1H	20,890	440	910	360	1,710	230	41,000	180
48	T1J	19,230	440	800	330	1,570	210	51,000	240
48	T1K	33,740	530	1,360	480	2,380	320	141,000	450
48	T1L	7,450	40	510	220	770	160	25,000	160
48	T1M	7,530	110	260	110	480	70	13,000	190
48	T1P	12,690	220	760	340	1,330	230	51,000	220
48	T1R	13,100	190	550	280	1,010	190	33,000	170
48	T1S	30,530	450	1,600	780	2,830	550	193,000	350
48	T1V	12,600	210	530	270	1,000	180	45,000	260
48	T1W	12,120	130	700	350	1,180	260	93,000	360
48	T1X	15,930	350	930	440	1,730	320	89,000	280
48	T1Y	42,650	1,130	2,140	960	4,230	640	115,000	180
48	T1Z	590	10	20	10	50	-	-	-
48	T2A	44,050	1,180	2,060	1,080	4,310	620	101,000	160
48	T2B	16,680	480	920	460	1,850	290	54,000	190
48	T2C	16,020	320	1,000	380	1,690	230	62,000	270
48	T2E	26,070	580	1,560	740	2,880	500	123,000	250
48	T2G	12,010	360	680	360	1,400	210	71,000	350
48	T2H	7,740	180	380	200	760	120	31,000	250
48	T2J	34,000	550	1,770	740	3,070	500	138,000	280
48	T2K	25,880	600	1,430	690	2,720	440	103,000	240
48	T2L	10,480	180	540	190	910	140	50,000	350
48	T2M	15,320	280	890	340	1,500	250	87,000	350
48	T2N	18,220	300	980	340	1,620	270	109,000	410
48	T2P	13,210	240	540	210	990	160	58,000	360
48	T2R	11,910	190	650	290	1,120	190	61,000	320
48	T2S	10,860	140	520	250	910	170	93,000	550
48	T2T	20,810	360	1,090	520	1,970	360	198,000	550

48	T2V	25,250	410	1,270	540	2,220	370	167,000	450
48	T2W	32,290	720	1,770	770	3,270	530	132,000	250
48	T2X	35,250	490	1,850	760	3,100	550	184,000	340
48	T2Y	46,110	700	2,070	890	3,660	600	151,000	250
48	T2Z	49,730	740	2,720	1,220	4,680	830	211,000	260
48	T3A	41,690	780	1,980	630	3,390	440	158,000	360
48	T3B	27,290	510	1,500	640	2,650	420	148,000	350
48	T3C	17,320	360	890	390	1,640	260	86,000	330
48	T3E	30,100	510	1,610	670	2,790	480	143,000	300
48	T3G	44,460	820	2,380	840	4,050	600	200,000	330
48	T3H	52,650	870	2,530	960	4,360	740	369,000	500
48	T3J	58,690	1,670	2,900	1,340	5,910	920	159,000	170
48	T3K	59,230	1,100	3,200	1,230	5,530	830	218,000	260
48	T3L	21,830	320	1,170	340	1,830	260	86,000	330
48	T3M	31,030	450	1,620	810	2,880	570	191,000	330
48	T3N	14,860	340	740	370	1,450	260	45,000	170
48	T3P	13,090	260	700	290	1,250	200	61,000	310
48	T3R	20,720	390	980	390	1,770	290	78,000	270
48	T3S	250	10	20	10	40	-	-	-
48	T3T	10	-	10	-	10	-	-	-
48	T3Z	8,600	140	410	160	710	120	87,000	740
48	T4A	12,700	170	720	360	1,250	260	64,000	250
48	T4B	36,120	540	2,020	1,030	3,590	700	167,000	240
48	T4C	24,980	330	1,430	610	2,370	430	111,000	260
48	T4E	3,590	50	150	50	250	40	10,000	280
48	T4G	9,610	150	400	190	730	140	59,000	430
48	T4H	9,580	160	430	200	790	120	40,000	340
48	T4J	9,080	180	360	140	680	90	14,000	170
48	T4L	13,540	230	590	260	1,080	180	58,000	330
48	T4M	4,050	30	190	110	330	70	22,000	310
48	T4N	23,490	660	1,090	530	2,280	330	125,000	380
48	T4P	23,660	390	1,000	540	1,930	330	73,000	220
48	T4R	27,620	320	1,240	510	2,070	340	78,000	230
48	T4S	14,680	250	740	410	1,400	260	83,000	320
48	T4T	11,460	400	560	210	1,170	130	46,000	360
48	T4V	16,530	230	590	260	1,080	160	53,000	320
48	T4X	16,490	220	920	430	1,570	290	98,000	340
48	T5A	25,280	690	1,340	600	2,630	400	73,000	180
48	T5B	11,260	540	690	330	1,550	180	28,000	150
48	T5C	11,760	360	540	270	1,160	160	36,000	220
48	T5E	23,440	740	1,140	520	2,410	330	83,000	250
48	T5G	9,270	410	570	250	1,230	140	26,000	180
48	T5H	20,050	1,230	1,020	530	2,770	270	48,000	180
48	T5J	7,970	270	290	130	690	80	39,000	510
48	T5K	16,660	350	850	360	1,560	250	64,000	260
48	T5L	12,690	360	710	320	1,380	210	30,000	150
48	T5M	11,490	310	630	290	1,220	180	57,000	320
48	T5N	10,820	210	580	250	1,040	170	54,000	320
48	T5P	15,450	530	760	410	1,700	240	49,000	200
48	T5R	18,710	380	930	430	1,740	280	65,000	230
48	T5S	4,540	100	270	130	500	80	20,000	260
48	T5T	53,470	1,090	2,620	1,130	4,830	740	176,000	240
48	T5V	320	10	20	10	30	-	-	-
48	T5W	15,000	530	860	410	1,790	260	51,000	200
48	T5X	30,540	680	1,590	680	2,950	440	126,000	290
48	T5Y	35,270	750	1,880	870	3,500	570	119,000	210
48	T5Z	24,610	490	1,230	490	2,210	360	74,000	210
48	T6A	11,000	210	640	240	1,090	160	34,000	210
48	T6B	7,380	140	390	140	670	100	28,000	290
48	T6C	14,780	290	890	380	1,560	260	51,000	200
48	T6E	16,550	380	1,080	420	1,880	290	127,000	440
48	T6G	8,160	180	410	120	700	90	24,000	270
48	T6H	20,880	440	1,100	400	1,940	280	76,000	270
48	T6J	35,220	660	1,660	670	2,990	470	96,000	210
48	T6K	21,130	570	1,160	460	2,190	310	59,000	190
48	T6L	37,760	930	2,190	880	4,000	590	102,000	170
48	T6M	22,140	340	1,170	480	1,990	340	180,000	520
48	T6N	80	-	10	-	10	-	-	-
48	T6P	1,390	40	70	40	160	20	5,000	200
48	T6R	34,650	630	1,690	550	2,870	390	133,000	340
48	T6S	30	-	10	-	10	-	-	-
48	T6T	31,590	770	1,770	750	3,290	560	101,000	180
48	T6V	15,610	300	780	380	1,450	250	45,000	180
48	T6W	45,160	740	2,340	920	4,000	650	210,000	320
48	T6X	29,150	510	1,560	710	2,780	500	106,000	210
48	T7A	9,760	150	470	240	850	140	36,000	250

48	T7E	10,740	170	430	240	840	140	49,000	340
48	T7N	6,670	100	280	100	470	70	16,000	230
48	T7P	6,080	140	240	100	480	70	20,000	290
48	T7S	9,540	140	570	240	950	140	82,000	590
48	T7V	8,050	100	400	170	670	110	21,000	190
48	T7X	32,910	740	1,900	870	3,510	570	210,000	370
48	T7Y	12,930	180	730	300	1,210	220	67,000	310
48	T7Z	15,010	230	790	380	1,400	240	80,000	330
48	T8A	33,060	410	1,800	640	2,860	470	117,000	250
48	T8B	5,420	70	240	100	400	70	34,000	520
48	T8C	3,400	50	180	80	320	60	21,000	350
48	T8E	6,220	100	410	140	650	110	38,000	360
48	T8G	3,650	50	240	90	370	60	18,000	290
48	T8H	21,830	290	1,120	460	1,860	330	91,000	280
48	T8L	20,450	250	1,090	470	1,810	330	251,000	760
48	T8N	50,360	660	2,770	1,000	4,440	750	271,000	360
48	T8R	11,830	280	670	280	1,230	180	43,000	240
48	T8S	7,080	160	490	140	790	100	23,000	230
48	T8T	5,510	80	280	120	470	70	42,000	590
48	T8V	25,240	550	1,640	580	2,770	360	133,000	370
48	T8W	15,130	170	1,090	340	1,600	250	96,000	390
48	T8X	16,150	200	1,080	380	1,660	250	106,000	430
48	T9A	11,760	310	530	270	1,100	170	35,000	200
48	T9C	5,760	110	240	120	470	90	19,000	220
48	T9E	24,200	320	1,200	570	2,080	360	98,000	270
48	T9G	5,290	90	290	120	500	70	32,000	440
48	T9H	20,310	400	1,700	580	2,670	370	147,000	400
48	T9J	1,770	20	180	50	250	30	5,000	140
48	T9K	28,370	550	2,660	680	3,880	450	112,000	250
48	T9M	13,780	390	830	360	1,580	230	58,000	250
48	T9N	8,820	170	350	180	700	120	32,000	270
48	T9S	5,820	90	320	130	540	90	35,000	370
48	T9V	16,720	180	660	300	1,150	200	55,000	280
48	T9W	6,280	70	260	90	410	60	13,000	230
48	T9X	4,620	40	190	80	320	60	26,000	450
TOTAL		3,083,840	65,270	158,170	67,550	290,990	45,290	13,200,000	290
59	V0A	11,450	90	670	310	1,070	220	53,000	250
59	V0B	27,200	320	1,460	640	2,420	470	111,000	230
59	V0C	18,070	270	1,640	450	2,350	280	103,000	370
59	V0E	55,820	690	3,360	1,260	5,300	840	201,000	240
59	V0G	21,390	280	1,470	520	2,280	370	78,000	210
59	V0H	46,700	550	2,530	1,040	4,110	760	154,000	200
59	V0J	39,370	590	3,190	870	4,650	580	116,000	200
59	V0K	26,650	420	1,780	570	2,770	350	84,000	240
59	V0L	3,660	90	370	80	540	40	14,000	320
59	V0M	9,080	150	640	230	1,020	150	33,000	220
59	V0N	57,610	830	4,290	1,880	7,000	1,360	409,000	300
59	V0P	5,540	130	470	150	740	110	21,000	190
59	V0R	55,320	670	3,740	1,610	6,020	1,160	285,000	240
59	V0S	300	10	40	10	60	-	-	-
59	V0T	5,820	130	750	190	1,070	110	27,000	260
59	V0V	1,280	40	150	50	230	30	5,000	200
59	V0W	330	10	30	10	50	-	-	-
59	V0X	17,480	260	1,260	420	1,940	290	67,000	240
59	V1A	6,700	50	370	150	570	110	25,000	240
59	V1B	17,870	160	900	340	1,400	250	64,000	260
59	V1C	20,440	160	970	390	1,510	260	73,000	280
59	V1E	16,560	180	850	320	1,350	210	41,000	190
59	V1G	11,820	110	770	290	1,160	200	134,000	680
59	V1H	11,510	120	620	250	1,000	180	36,000	200
59	V1J	18,730	200	1,590	510	2,300	320	138,000	430
59	V1K	7,710	100	610	170	890	90	18,000	200
59	V1L	13,870	150	1,100	370	1,620	270	51,000	190
59	V1M	24,620	240	1,510	520	2,270	360	94,000	260
59	V1N	10,390	90	560	210	860	140	29,000	210
59	V1P	6,850	70	450	180	700	130	36,000	270
59	V1R	8,000	60	390	130	580	80	13,000	150
59	V1S	9,560	70	550	150	780	110	16,000	150
59	V1T	23,630	300	1,490	580	2,370	390	87,000	220
59	V1V	17,790	160	930	380	1,470	260	54,000	210
59	V1W	28,380	270	1,490	620	2,380	450	186,000	410
59	V1X	26,700	280	1,690	700	2,660	470	105,000	220
59	V1Y	29,360	270	1,870	820	2,960	580	165,000	290
59	V1Z	11,920	120	720	320	1,160	220	63,000	290
59	V2A	33,400	350	1,700	700	2,740	480	97,000	200
59	V2B	31,160	280	2,090	740	3,100	490	78,000	160

59	V2C	20,240	180	1,220	430	1,830	300	67,000	220
59	V2E	11,900	90	670	210	970	140	31,000	230
59	V2G	14,260	180	1,020	360	1,550	240	46,000	200
59	V2H	5,880	60	370	110	540	80	16,000	200
59	V2J	18,070	220	1,130	330	1,680	220	62,000	280
59	V2K	15,960	150	1,020	360	1,530	250	72,000	290
59	V2L	8,030	80	680	210	980	130	32,000	250
59	V2M	17,400	140	1,170	380	1,690	260	53,000	200
59	V2N	24,910	220	1,590	610	2,410	420	151,000	360
59	V2P	28,770	430	1,930	810	3,170	530	137,000	260
59	V2R	39,810	420	2,380	950	3,750	650	160,000	250
59	V2S	37,410	530	2,480	920	3,930	630	125,000	200
59	V2T	44,990	780	3,600	1,250	5,630	870	241,000	280
59	V2V	25,890	410	2,120	880	3,420	560	167,000	300
59	V2W	15,280	170	1,070	440	1,680	300	86,000	280
59	V2X	37,580	440	2,720	1,060	4,220	720	187,000	260
59	V2Y	28,730	320	1,810	650	2,780	470	141,000	300
59	V2Z	12,100	140	700	320	1,160	220	59,000	270
59	V3A	34,400	350	2,270	860	3,490	610	390,000	640
59	V3B	46,400	520	2,610	930	4,060	650	143,000	220
59	V3C	30,900	320	1,900	650	2,870	460	110,000	240
59	V3E	30,910	340	1,710	510	2,560	370	119,000	330
59	V3G	18,940	240	1,240	440	1,920	330	101,000	310
59	V3H	28,540	300	1,760	620	2,680	490	145,000	300
59	V3J	32,810	320	1,990	610	2,910	430	112,000	260
59	V3K	24,170	270	1,450	490	2,210	340	67,000	200
59	V3L	22,430	240	1,450	510	2,190	370	81,000	220
59	V3M	34,890	380	2,110	760	3,240	550	141,000	250
59	V3N	31,180	310	1,710	540	2,560	390	90,000	230
59	V3R	46,580	600	2,660	1,020	4,280	690	146,000	210
59	V3S	75,780	1,140	5,560	1,980	8,680	1,480	384,000	260
59	V3T	33,000	420	2,720	760	3,910	440	96,000	220
59	V3V	37,980	650	3,020	1,060	4,720	740	245,000	330
59	V3W	72,490	1,300	5,580	1,830	8,710	1,340	321,000	240
59	V3X	23,150	390	1,880	630	2,890	460	108,000	240
59	V3Y	14,840	170	930	390	1,490	270	63,000	230
59	V3Z	23,710	290	1,340	510	2,130	350	131,000	370
59	V4A	30,080	350	1,570	550	2,470	410	105,000	250
59	V4B	16,470	190	920	460	1,570	360	92,000	260
59	V4C	34,790	480	2,550	900	3,930	640	145,000	230
59	V4E	9,720	130	640	190	950	140	39,000	280
59	V4G	320	10	20	20	40	20	2,000	130
59	V4K	19,620	200	1,190	460	1,850	340	84,000	250
59	V4L	6,430	70	310	120	510	100	26,000	260
59	V4M	11,530	120	660	260	1,030	190	62,000	330
59	V4N	61,390	770	3,690	1,400	5,860	970	254,000	260
59	V4P	10,080	90	450	180	720	140	368,000	2,670
59	V4R	11,620	130	840	330	1,300	230	59,000	260
59	V4S	5,530	90	410	170	680	110	32,000	280
59	V4T	23,160	230	1,370	540	2,150	360	101,000	290
59	V4V	12,980	150	840	390	1,380	270	64,000	240
59	V4W	15,540	200	1,160	440	1,800	300	90,000	300
59	V4X	10,020	150	830	300	1,280	220	71,000	320
59	V4Z	3,630	60	240	100	390	70	24,000	350
59	V5A	18,770	220	1,110	310	1,630	240	53,000	230
59	V5B	17,670	220	1,010	280	1,510	210	54,000	260
59	V5C	25,080	260	1,370	440	2,070	320	83,000	260
59	V5E	21,520	250	1,020	310	1,580	230	59,000	250
59	V5G	16,230	160	920	270	1,350	190	51,000	260
59	V5H	32,380	390	1,550	470	2,410	350	93,000	270
59	V5J	18,320	230	930	260	1,420	180	42,000	230
59	V5K	18,190	200	1,090	370	1,660	280	128,000	460
59	V5L	14,760	180	1,290	440	1,920	330	69,000	210
59	V5M	18,780	190	880	220	1,290	160	38,000	240
59	V5N	27,270	250	1,710	560	2,520	410	87,000	210
59	V5P	26,560	280	1,280	380	1,930	280	50,000	180
59	V5R	39,020	360	1,710	540	2,600	390	117,000	300
59	V5S	23,830	250	1,150	400	1,800	280	75,000	270
59	V5T	19,020	170	1,350	560	2,080	410	103,000	250
59	V5V	18,840	190	1,170	420	1,790	320	97,000	300
59	V5W	16,370	180	970	260	1,410	200	42,000	210
59	V5X	23,570	320	1,380	420	2,120	320	63,000	200
59	V5Y	14,010	120	840	270	1,230	200	89,000	440
59	V5Z	18,950	200	940	320	1,460	240	84,000	350
59	V6A	16,250	210	1,310	380	1,900	240	55,000	230
59	V6B	26,740	280	1,740	560	2,580	410	190,000	460

59	V6C	6,510	60	180	70	320	50	51,000	970
59	V6E	24,000	230	1,410	560	2,200	400	137,000	340
59	V6G	21,350	220	1,330	600	2,140	440	143,000	320
59	V6H	16,840	140	840	330	1,310	260	142,000	550
59	V6J	18,280	150	960	410	1,520	310	91,000	300
59	V6K	19,680	170	1,260	420	1,860	330	107,000	320
59	V6L	7,880	70	330	80	480	60	20,000	340
59	V6M	13,270	110	560	180	850	130	150,000	1,150
59	V6N	10,360	90	440	140	680	110	49,000	450
59	V6P	24,610	270	1,140	350	1,760	240	109,000	450
59	V6R	14,190	150	840	250	1,230	180	69,000	380
59	V6S	9,360	100	440	90	630	70	25,000	360
59	V6T	9,110	100	460	70	640	50	10,000	180
59	V6V	9,590	120	510	170	800	120	32,000	260
59	V6W	1,540	20	90	40	140	20	6,000	250
59	V6X	31,970	410	1,470	360	2,230	280	81,000	290
59	V6Y	40,810	510	1,580	390	2,470	290	75,000	260
59	V6Z	14,570	140	800	280	1,230	190	103,000	540
59	V7A	21,770	250	1,080	330	1,650	240	61,000	250
59	V7B	660	10	30	20	60	20	4,000	230
59	V7C	32,570	420	1,390	310	2,120	230	67,000	300
59	V7E	30,410	340	1,450	410	2,190	310	71,000	230
59	V7G	9,410	120	580	190	890	140	68,000	490
59	V7H	9,810	100	610	170	880	130	33,000	250
59	V7J	12,640	140	800	290	1,220	230	97,000	420
59	V7K	9,530	100	580	190	860	140	51,000	360
59	V7L	20,730	210	1,190	480	1,880	360	138,000	390
59	V7M	18,320	200	1,070	410	1,680	310	71,000	230
59	V7N	11,700	120	670	240	1,030	190	62,000	320
59	V7P	10,650	170	680	210	1,060	160	40,000	250
59	V7R	11,750	130	600	190	930	150	68,000	440
59	V7S	8,120	120	360	120	590	90	33,000	370
59	V7T	7,750	100	350	140	580	100	72,000	690
59	V7V	12,240	160	450	190	800	130	65,000	490
59	V7W	6,650	50	280	110	440	80	44,000	550
59	V7X	430	-	20	10	20	-	-	-
59	V7Y	460	-	-	10	10	-	-	-
59	V8A	15,330	160	800	260	1,210	160	54,000	330
59	V8B	9,300	110	830	350	1,280	270	69,000	260
59	V8C	6,020	50	420	160	630	120	39,000	330
59	V8E	8,750	30	670	280	970	220	47,000	210
59	V8G	14,250	150	1,020	380	1,540	230	56,000	240
59	V8J	9,170	110	730	300	1,140	200	49,000	240
59	V8K	8,910	160	730	350	1,240	280	230,000	840
59	V8L	20,180	160	940	370	1,470	270	64,000	240
59	V8M	13,080	120	760	260	1,130	180	41,000	230
59	V8N	19,320	160	1,100	320	1,580	230	56,000	240
59	V8P	13,520	120	760	240	1,130	190	41,000	220
59	V8R	18,160	150	1,160	370	1,680	280	59,000	210
59	V8S	12,960	90	680	250	1,020	190	56,000	290
59	V8T	16,390	190	1,190	410	1,800	280	47,000	170
59	V8V	22,020	220	1,260	520	1,990	370	105,000	280
59	V8W	7,070	70	430	150	650	100	31,000	320
59	V8X	18,970	180	1,180	430	1,780	320	99,000	310
59	V8Y	8,120	70	360	100	530	70	17,000	240
59	V8Z	24,200	190	1,540	540	2,280	400	102,000	260
59	V9A	30,060	310	2,080	770	3,160	550	104,000	190
59	V9B	35,700	330	2,320	1,050	3,710	760	158,000	210
59	V9C	18,300	170	1,240	460	1,870	320	67,000	210
59	V9E	4,130	20	230	90	340	60	13,000	220
59	V9G	12,410	130	770	310	1,200	220	59,000	270
59	V9H	7,800	60	440	170	670	120	32,000	270
59	V9J	7,250	90	450	200	740	160	51,000	330
59	V9K	13,920	150	700	310	1,150	220	56,000	250
59	V9L	28,130	380	1,940	670	2,990	460	122,000	270
59	V9M	14,310	130	790	290	1,210	210	64,000	310
59	V9N	25,610	260	1,480	580	2,330	410	99,000	240
59	V9P	23,170	230	1,120	470	1,820	330	78,000	240
59	V9R	24,090	270	1,760	690	2,720	460	110,000	240
59	V9S	12,990	150	910	390	1,450	280	48,000	170
59	V9T	27,330	270	1,490	650	2,410	460	105,000	230
59	V9V	8,820	60	430	150	640	120	26,000	220
59	V9W	24,160	240	1,470	570	2,280	380	81,000	210
59	V9X	8,240	80	590	240	910	160	31,000	200
59	V9Y	20,480	220	1,170	460	1,850	300	62,000	210
59	V9Z	13,830	190	1,080	490	1,760	350	88,000	250

TOTAL		3,771,270	43,280	232,780	83,520	359,580	59,150	16,704,000	280
60	X0E	15,760	60	1,220	260	1,530	130	45,000	350
60	X0G	390	-	30	-	30	-	-	-
60	X1A	15,160	50	1,590	260	1,900	180	60,000	330
TOTAL		31,310	100	2,840	520	3,470	310	105,000	340
61	Y0A	1,340	60	120	40	220	20	8,000	420
61	Y0B	5,250	100	440	120	660	80	37,000	490
61	Y1A	22,060	380	1,870	460	2,700	320	112,000	350
TOTAL		28,660	530	2,430	620	3,580	410	157,000	380
62	X0A	11,590	250	1,110	210	1,570	110	44,000	390
62	X0B	3,910	90	240	40	370	20	5,000	280
62	X0C	6,440	160	350	50	560	30	19,000	560
TOTAL		21,940	490	1,690	300	2,490	160	68,000	420
99	Out	154,340	19,990	16,420	4,710	41,120	2,620	1,631,000	620
TOTAL		154,340	19,990	16,420	4,710	41,120	2,620	1,631,000	620
Canada		28,083,990	371,480	1,638,640	555,720	2,565,840	385,390	95,272,000	250