



Table 1b - FSA Statistics for All Returns, by Total Income - 2015 Tax Year

| FSA   | Total         | Total Income<br>(\$000) | Under<br>\$5,000 | \$5,000<br>to<br>\$9,999 | \$10,000<br>to<br>\$14,999 | \$15,000<br>to<br>\$19,999 | \$20,000<br>to<br>\$24,999 | \$25,000<br>to<br>\$29,999 | \$30,000<br>to<br>\$34,999 | \$35,000<br>to<br>\$39,999 | \$40,000<br>to<br>\$44,999 | \$45,000<br>to<br>\$49,999 | \$50,000<br>to<br>\$54,999 | \$55,000<br>to<br>\$59,999 | \$60,000<br>to<br>\$69,999 | \$70,000<br>to<br>\$79,999 | \$80,000<br>to<br>\$89,999 | \$90,000<br>to<br>\$99,999 | \$100,000<br>to<br>\$149,999 | \$150,000<br>to<br>\$249,999 | \$250,000<br>and over |
|-------|---------------|-------------------------|------------------|--------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|----------------------------|------------------------------|------------------------------|-----------------------|
| PR 13 | New Brunswick |                         |                  |                          |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                              |                              |                       |
| EOA   |               |                         |                  |                          |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                              |                              |                       |
| EOC   |               |                         |                  |                          |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                              |                              |                       |
| EOE   |               |                         |                  |                          |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                              |                              |                       |
| EOG   |               |                         |                  |                          |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                              |                              |                       |
| E1A   | 33,580        | 1,512,076               | 2,160            | 2,170                    | 2,230                      | 2,910                      | 2,600                      | 2,330                      | 2,090                      | 2,230                      | 2,160                      | 1,700                      | 1,380                      | 1,290                      | 2,120                      | 1,810                      | 1,350                      | 790                        | 1,540                        | 530                          | 200                   |
| E1B   | 15,920        | 690,006                 | 910              | 910                      | 1,000                      | 1,250                      | 1,270                      | 1,240                      | 1,150                      | 1,250                      | 1,170                      | 940                        | 780                        | 580                        | 1,020                      | 760                        | 510                        | 330                        | 570                          | 220                          | 60                    |
| E1C   | 19,370        | 638,974                 | 1,420            | 2,050                    | 1,760                      | 2,410                      | 2,050                      | 1,620                      | 1,410                      | 1,300                      | 1,090                      | 860                        | 560                        | 490                        | 690                        | 530                        | 330                        | 210                        | 390                          | 150                          | 60                    |
| E1E   | 8,630         | 370,170                 | 540              | 610                      | 540                        | 780                        | 750                        | 680                        | 570                        | 650                        | 590                        | 460                        | 350                        | 310                        | 470                        | 410                        | 280                        | 160                        | 310                          | 130                          | 50                    |
| E1G   | 17,380        | 831,758                 | 1,200            | 1,020                    | 990                        | 1,160                      | 1,130                      | 1,100                      | 1,110                      | 1,160                      | 1,160                      | 980                        | 820                        | 740                        | 1,300                      | 990                        | 720                        | 510                        | 900                          | 310                          | 100                   |
| E1H   | 6,050         | 241,801                 | 360              | 370                      | 440                        | 570                        | 480                        | 490                        | 470                        | 500                        | 440                        | 350                        | 270                        | 220                        | 340                        | 250                        | 150                        | 90                         | 170                          | 60                           | 20                    |
| E1J   | 2,840         | 122,508                 | 180              | 170                      | 210                        | 230                        | 230                        | 190                        | 170                        | 200                        | 200                        | 170                        | 140                        | 100                        | 190                        | 140                        | 100                        | 70                         | 120                          | 40                           | 10                    |
| E1N   | 9,330         | 344,937                 | 630              | 700                      | 730                        | 1,040                      | 870                        | 760                        | 680                        | 630                        | 560                        | 450                        | 410                        | 310                        | 490                        | 350                        | 280                        | 120                        | 220                          | 70                           | 20                    |
| E1V   | 11,360        | 450,378                 | 910              | 820                      | 810                        | 1,280                      | 970                        | 890                        | 700                        | 670                        | 620                        | 520                        | 520                        | 410                        | 600                        | 540                        | 410                        | 190                        | 350                          | 140                          | 40                    |
| E1W   | 6,190         | 231,798                 | 380              | 410                      | 500                        | 940                        | 620                        | 540                        | 480                        | 430                        | 300                        | 240                        | 190                        | 150                        | 220                        | 250                        | 160                        | 100                        | 200                          | 90                           | 20                    |
| E1X   | 12,220        | 405,125                 | 860              | 1,120                    | 1,170                      | 1,780                      | 1,090                      | 1,050                      | 970                        | 760                        | 620                        | 480                        | 340                        | 290                        | 440                        | 410                        | 270                        | 140                        | 340                          | 70                           | 10                    |
| E2A   | 14,820        | 559,954                 | 1,060            | 1,330                    | 1,220                      | 1,880                      | 1,410                      | 1,180                      | 930                        | 920                        | 760                        | 650                        | 530                        | 390                        | 640                        | 540                        | 410                        | 220                        | 490                          | 210                          | 70                    |
| E2E   | 15,210        | 884,971                 | 1,080            | 830                      | 860                        | 940                        | 910                        | 810                        | 770                        | 870                        | 830                        | 720                        | 600                        | 600                        | 1,090                      | 980                        | 760                        | 540                        | 1,250                        | 570                          | 210                   |
| E2G   | 3,980         | 204,124                 | 250              | 230                      | 260                        | 270                        | 280                        | 220                        | 220                        | 220                        | 220                        | 200                        | 170                        | 160                        | 270                        | 240                        | 190                        | 160                        | 320                          | 90                           | 30                    |
| E2H   | 3,840         | 216,640                 | 300              | 280                      | 250                        | 340                        | 280                        | 230                        | 210                        | 200                        | 190                        | 170                        | 140                        | 140                        | 200                        | 180                        | 140                        | 100                        | 260                          | 150                          | 100                   |
| E2J   | 12,870        | 457,364                 | 820              | 900                      | 1,010                      | 1,430                      | 1,370                      | 1,090                      | 980                        | 920                        | 820                        | 670                        | 530                        | 390                        | 610                        | 440                        | 290                        | 180                        | 350                          | 50                           | 10                    |
| E2K   | 13,030        | 493,500                 | 1,300            | 1,160                    | 1,160                      | 1,470                      | 1,100                      | 930                        | 790                        | 770                        | 680                        | 540                        | 420                        | 360                        | 570                        | 490                        | 330                        | 220                        | 510                          | 180                          | 60                    |
| E2L   | 6,160         | 194,668                 | 520              | 980                      | 660                        | 860                        | 570                        | 450                        | 320                        | 330                        | 250                        | 200                        | 160                        | 130                        | 200                        | 140                        | 100                        | 70                         | 140                          | 60                           | 40                    |
| E2M   | 15,210        | 632,102                 | 1,010            | 1,060                    | 1,040                      | 1,360                      | 1,410                      | 1,110                      | 1,000                      | 1,040                      | 940                        | 770                        | 620                        | 520                        | 880                        | 760                        | 490                        | 340                        | 680                          | 150                          | 30                    |
| E2N   | 3,550         | 149,677                 | 220              | 240                      | 250                        | 320                        | 310                        | 220                        | 230                        | 260                        | 250                        | 180                        | 150                        | 140                        | 220                        | 160                        | 130                        | 80                         | 190                          | 30                           | 10                    |
| E2P   | 1,110         | 44,141                  | 70               | 50                       | 80                         | 100                        | 100                        | 90                         | 100                        | 100                        | 70                         | 70                         | 50                         | 40                         | 70                         | 40                         | 20                         | 20                         | 40                           | 10                           |                       |
| E2R   |               |                         |                  |                          |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                            |                              |                              |                       |
| E2S   | 5,520         | 239,492                 | 420              | 360                      | 380                        | 420                        | 420                        | 390                        | 330                        | 370                        | 360                        | 310                        | 250                        | 220                        | 320                        | 220                        | 200                        | 150                        | 310                          | 80                           | 10                    |
| E2V   | 10,570        | 456,044                 | 850              | 610                      | 620                        | 700                        | 710                        | 620                        | 550                        | 570                        | 600                        | 560                        | 510                        | 610                        | 1,350                      | 750                        | 390                        | 230                        | 280                          | 60                           | 10                    |
| E3A   | 21,920        | 878,428                 | 1,930            | 1,520                    | 1,580                      | 1,950                      | 1,740                      | 1,490                      | 1,410                      | 1,430                      | 1,370                      | 1,150                      | 960                        | 890                        | 1,300                      | 1,050                      | 660                        | 420                        | 790                          | 240                          | 60                    |
| E3B   | 28,190        | 1,293,731               | 2,670            | 2,080                    | 1,960                      | 2,220                      | 1,940                      | 1,690                      | 1,590                      | 1,590                      | 1,610                      | 1,320                      | 1,100                      | 1,060                      | 1,930                      | 1,470                      | 1,000                      | 690                        | 1,500                        | 550                          | 240                   |
| E3C   | 9,210         | 488,252                 | 590              | 510                      | 520                        | 530                        | 500                        | 460                        | 470                        | 530                        | 580                        | 530                        | 440                        | 420                        | 770                        | 670                        | 480                        | 300                        | 630                          | 190                          | 80                    |
| E3E   | 3,450         | 170,713                 | 390              | 210                      | 190                        | 240                        | 180                        | 170                        | 160                        | 200                        | 200                        | 160                        | 150                        | 150                        | 240                        | 230                        | 160                        | 110                        | 210                          | 90                           | 30                    |
| E3G   | 6,530         | 305,649                 | 470              | 380                      | 410                        | 440                        | 450                        | 390                        | 400                        | 450                        | 400                        | 340                        | 320                        | 310                        | 450                        | 390                        | 260                        | 160                        | 370                          | 110                          | 30                    |
| E3L   | 7,220         | 250,047                 | 550              | 640                      | 680                        | 860                        | 780                        | 590                        | 470                        | 430                        | 370                        | 280                        | 240                        | 190                        | 350                        | 250                        | 200                        | 120                        | 170                          | 40                           | 20                    |
| E3N   | 11,810        | 396,401                 | 860              | 1,070                    | 1,010                      | 1,560                      | 1,110                      | 1,050                      | 880                        | 810                        | 710                        | 500                        | 370                        | 280                        | 450                        | 440                        | 250                        | 140                        | 220                          | 80                           | 30                    |
| E3V   | 10,000        | 371,190                 | 500              | 920                      | 820                        | 1,280                      | 950                        | 810                        | 690                        | 680                        | 590                        | 480                        | 340                        | 300                        | 470                        | 410                        | 210                        | 110                        | 310                          | 90                           | 40                    |
| E3Y   | 6,130         | 208,201                 | 370              | 510                      | 540                        | 790                        | 570                        | 490                        | 480                        | 450                        | 400                        | 300                        | 250                        | 170                        | 250                        | 210                        | 130                        | 90                         | 110                          | 30                           | 10                    |
| E3Z   | 3,610         | 132,254                 | 230              | 280                      | 310                        | 460                        | 330                        | 310                        | 260                        | 230                        | 220                        | 150                        | 150                        | 110                        | 180                        | 130                        | 80                         | 50                         | 100                          | 40                           | 10                    |
| E4A   | 2,590         | 82,249                  | 190              | 220                      | 280                        | 390                        | 290                        | 180                        | 160                        | 150                        | 110                        | 120                        | 100                        | 80                         | 100                        | 80                         | 40                         | 30                         | 50                           | 10                           |                       |
| E4B   | 3,680         | 118,392                 | 280              | 320                      | 350                        | 570                        | 370                        | 300                        | 220                        | 220                        | 210                        | 140                        | 130                        | 110                        | 150                        | 110                        | 70                         | 40                         | 70                           | 20                           |                       |
| E4C   | 1,830         | 67,069                  | 120              | 160                      | 170                        | 250                        | 170                        | 130                        | 110                        | 120                        | 110                        | 90                         | 70                         | 50                         | 80                         | 50                         | 40                         | 30                         | 70                           | 20                           | 10                    |
| E4E   | 7,400         | 286,263                 | 570              | 620                      | 590                        | 900                        | 680                        | 570                        | 470                        | 440                        | 380                        | 320                        | 270                        | 260                        | 370                        | 280                        | 160                        | 100                        | 310                          | 110                          | 30                    |
| E4G   | 2,170         | 81,958                  | 210              | 150                      | 170                        | 230                        | 220                        | 170                        | 140                        | 130                        | 110                        | 120                        | 90                         | 70                         | 90                         | 70                         | 40                         | 30                         | 90                           | 30                           | 10                    |
| E4H   | 3,400         | 115,013                 | 220              | 260                      | 270                        | 430                        | 330                        | 310                        | 260                        | 280                        | 210                        | 180                        | 130                        | 100                        | 160                        | 90                         | 50                         | 40                         | 60                           | 10                           | 10                    |
| E4J   | 3,920         | 135,477                 | 270              | 300                      | 330                        | 460                        | 390                        | 330                        | 310                        | 280                        | 220                        | 210                        | 140                        | 120                        | 200                        | 150                        | 80                         | 40                         | 70                           | 10                           | 10                    |
| E4K   | 4,800         | 183,770                 | 290              | 300                      | 320                        | 460                        | 420                        | 380                        | 360                        | 410                        | 330                        | 290                        | 240                        | 190                        | 270                        | 210                        | 110                        | 70                         | 100                          | 30                           | 10                    |
| E4L   | 5,770         | 236,123                 | 450              | 420                      | 420                        | 570                        | 480                        | 390                        | 390                        | 430                        | 380                        | 290                        | 220                        | 170                        | 310                        | 230                        | 200                        | 100                        | 230                          | 80                           | 20                    |
| E4M   | 1,540         | 52,248                  | 110              | 130                      | 120                        | 220                        | 170                        | 140                        | 130                        | 100                        | 70                         | 60                         | 50                         | 40                         | 70                         | 40                         | 40                         | 20                         | 30                           | 10                           |                       |
| E4N   | 3,430         | 128,702                 | 170              | 190                      | 280                        | 430                        | 350                        | 380                        | 340                        | 270                        | 230                        | 130                        | 130                        | 110                        | 140                        | 110                        | 40                         | 30                         | 60                           | 20                           | 10                    |
| E4P   | 12,470        | 497,784                 | 610              | 750                      | 900                        | 1,370                      | 1,150                      | 1,090                      | 970                        | 910                        | 800                        | 680                        | 540                        | 460                        | 680                        | 500                        | 340                        | 210                        | 340                          | 120                          | 50                    |
| E4R   | 5,580         | 221,077                 | 280              | 300                      | 440                        | 590                        | 500                        | 490                        | 430                        | 420                        | 410                        | 290                        | 230                        | 200                        | 280                        | 250                        | 160                        | 90                         | 150                          | 60                           | 20                    |
| E4S   | 6,320         | 207,230                 | 360              | 460                      | 580                        | 880                        | 630                        | 610                        | 570                        | 470                        | 390                        | 290                        | 200                        | 160                        | 230                        | 180                        | 120                        | 60                         | 120                          | 30                           | 10                    |
| E4T   | 1,870         | 55,157                  | 150              | 170                      | 200                        | 250                        | 200                        | 170                        | 130                        | 140                        | 100                        | 90                         | 50                         | 40                         | 60                         | 30                         | 30                         | 20                         | 30                           |                              |                       |
| E4V   | 3,690         | 130,507                 | 200              | 240                      | 280                        | 420                        | 370                        | 320                        | 290                        | 290                        | 280                        | 190                        | 170                        | 120                        | 190                        | 110                        | 90                         | 40                         | 70                           | 10                           |                       |
| E4W   | 6,860         | 184,820                 | 1,420            | 490                      | 550                        | 850                        | 610                        | 560                        | 560                        | 420                        | 290                        | 230                        | 160                        | 130                        | 200                        | 140                        | 90                         | 50                         | 90                           | 30                           | 10                    |
| E4X   | 2,600         | 81,294                  | 140              | 180                      | 260                        | 370                        | 260                        | 270                        | 250                        | 220                        | 150                        | 130                        | 70                         | 60                         | 90                         | 70                         | 30                         | 20                         | 40                           | 10                           |                       |
| E4Y   | 2,750         | 80,422                  | 190              | 210                      | 300                        | 450                        | 290                        | 230                        | 210                        | 200                        | 150                        | 120                        | 80                         | 70                         | 90                         | 40                         | 40                         | 20                         | 40                           |                              |                       |
| E4Z   | 4,520         | 153,536                 | 360              | 340                      | 410                        | 560                        | 460                        | 360                        | 320                        | 320                        | 270                        | 220                        | 180                        | 140                        | 210                        | 140                        | 70                         | 40                         | 100                          | 30                           | </                    |

Table 1b - FSA Statistics for All Returns, by Total Income - 2015 Tax Year

| FSA   | Total   | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-------|---------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| E7G   | 3,190   | 97,297               | 310           | 290                | 340                  | 430                  | 340                  | 240                  | 200                  | 160                  | 180                  | 160                  | 110                  | 90                   | 140                  | 70                   | 50                   | 20                   | 50                     | 10                     |                    |
| E7H   | 4,420   | 122,577              | 790           | 390                | 400                  | 530                  | 420                  | 310                  | 280                  | 250                  | 230                  | 170                  | 130                  | 100                  | 110                  | 110                  | 60                   | 40                   | 70                     | 20                     | 10                 |
| E7J   | 1,650   | 53,517               | 140           | 150                | 150                  | 220                  | 180                  | 130                  | 120                  | 110                  | 110                  | 60                   | 50                   | 40                   | 80                   | 40                   | 20                   | 20                   | 30                     | 20                     |                    |
| E7K   | 2,010   | 64,677               | 180           | 170                | 170                  | 230                  | 200                  | 180                  | 140                  | 170                  | 130                  | 100                  | 70                   | 50                   | 80                   | 50                   | 30                   | 20                   | 30                     | 10                     |                    |
| E7L   | 4,220   | 154,034              | 360           | 340                | 380                  | 450                  | 390                  | 310                  | 290                  | 300                  | 250                  | 240                  | 160                  | 120                  | 210                  | 140                  | 90                   | 50                   | 100                    | 40                     | 20                 |
| E7M   | 8,040   | 305,925              | 700           | 680                | 700                  | 870                  | 700                  | 590                  | 560                  | 470                  | 490                  | 360                  | 310                  | 290                  | 370                  | 290                  | 210                  | 130                  | 200                    | 80                     | 50                 |
| E7N   | 2,470   | 88,694               | 190           | 200                | 220                  | 260                  | 220                  | 190                  | 180                  | 190                  | 150                  | 110                  | 100                  | 70                   | 120                  | 80                   | 70                   | 40                   | 60                     | 20                     | 10                 |
| E7P   | 2,900   | 99,972               | 270           | 260                | 250                  | 340                  | 250                  | 220                  | 200                  | 210                  | 190                  | 140                  | 110                  | 100                  | 140                  | 90                   | 50                   | 20                   | 60                     | 20                     | 10                 |
| E8A   | 3,100   | 103,191              | 150           | 250                | 280                  | 420                  | 290                  | 270                  | 230                  | 240                  | 220                  | 190                  | 130                  | 70                   | 120                  | 90                   | 50                   | 20                   | 40                     | 10                     |                    |
| E8B   | 2,040   | 62,096               | 130           | 180                | 190                  | 310                  | 180                  | 160                  | 200                  | 190                  | 130                  | 100                  | 80                   | 50                   | 70                   | 30                   | 20                   | 10                   | 10                     |                        |                    |
| E8C   | 3,040   | 97,310               | 300           | 290                | 230                  | 420                  | 300                  | 240                  | 210                  | 190                  | 190                  | 130                  | 110                  | 80                   | 110                  | 90                   | 60                   | 30                   | 60                     | 10                     | 10                 |
| E8E   | 4,440   | 165,983              | 250           | 320                | 310                  | 510                  | 380                  | 390                  | 350                  | 340                  | 310                  | 250                  | 180                  | 150                  | 190                  | 180                  | 100                  | 50                   | 140                    | 30                     | 10                 |
| E8G   | 2,440   | 73,629               | 210           | 310                | 260                  | 390                  | 220                  | 220                  | 140                  | 140                  | 90                   | 90                   | 60                   | 40                   | 70                   | 80                   | 40                   | 20                   | 50                     | 10                     | 10                 |
| E8J   | 4,880   | 169,131              | 290           | 390                | 460                  | 640                  | 450                  | 380                  | 360                  | 380                  | 340                  | 230                  | 160                  | 140                  | 200                  | 170                  | 100                  | 60                   | 110                    | 30                     | 10                 |
| E8K   | 7,380   | 272,042              | 480           | 600                | 600                  | 920                  | 640                  | 560                  | 530                  | 510                  | 470                  | 340                  | 300                  | 210                  | 350                  | 320                  | 170                  | 110                  | 210                    | 60                     | 20                 |
| E8L   | 2,070   | 66,356               | 190           | 170                | 220                  | 330                  | 160                  | 160                  | 130                  | 140                  | 120                  | 80                   | 70                   | 40                   | 90                   | 50                   | 30                   | 30                   | 50                     | 10                     |                    |
| E8M   | 1,800   | 57,601               | 150           | 160                | 180                  | 280                  | 170                  | 140                  | 120                  | 110                  | 100                  | 60                   | 60                   | 40                   | 60                   | 70                   | 40                   | 20                   | 50                     | 10                     |                    |
| E8N   | 2,230   | 70,170               | 140           | 180                | 210                  | 430                  | 250                  | 200                  | 170                  | 150                  | 110                  | 70                   | 50                   | 50                   | 70                   | 40                   | 30                   | 20                   | 50                     | 20                     |                    |
| E8P   | 3,060   | 100,372              | 200           | 280                | 320                  | 470                  | 250                  | 260                  | 260                  | 190                  | 160                  | 120                  | 90                   | 70                   | 90                   | 100                  | 60                   | 30                   | 80                     | 20                     |                    |
| E8R   | 2,940   | 81,256               | 240           | 290                | 330                  | 560                  | 260                  | 270                  | 240                  | 180                  | 130                  | 90                   | 80                   | 50                   | 70                   | 50                   | 30                   | 20                   | 40                     | 10                     |                    |
| E8S   | 4,170   | 147,905              | 210           | 380                | 360                  | 660                  | 350                  | 330                  | 370                  | 260                  | 210                  | 140                  | 120                  | 120                  | 170                  | 160                  | 90                   | 60                   | 130                    | 40                     | 10                 |
| E8T   | 5,320   | 189,725              | 270           | 380                | 530                  | 890                  | 410                  | 500                  | 490                  | 360                  | 270                  | 190                  | 160                  | 110                  | 160                  | 140                  | 110                  | 80                   | 230                    | 60                     | 10                 |
| E9A   | 2,040   | 71,501               | 90            | 120                | 140                  | 260                  | 180                  | 240                  | 250                  | 180                  | 110                  | 90                   | 70                   | 60                   | 70                   | 60                   | 40                   | 30                   | 40                     | 10                     | 10                 |
| E9B   | 1,960   | 63,222               | 150           | 190                | 190                  | 270                  | 170                  | 160                  | 140                  | 110                  | 110                  | 100                  | 70                   | 60                   | 80                   | 50                   | 50                   | 20                   | 40                     | 10                     |                    |
| E9C   | 1,880   | 57,872               | 190           | 180                | 200                  | 290                  | 160                  | 130                  | 110                  | 100                  | 100                  | 90                   | 70                   | 50                   | 80                   | 50                   | 30                   | 20                   | 30                     | 10                     |                    |
| E9E   | 3,200   | 109,496              | 380           | 250                | 250                  | 430                  | 280                  | 240                  | 210                  | 180                  | 170                  | 130                  | 110                  | 90                   | 130                  | 110                  | 70                   | 40                   | 80                     | 30                     | 10                 |
| E9G   | 4,300   | 113,426              | 730           | 340                | 400                  | 680                  | 380                  | 350                  | 340                  | 260                  | 180                  | 140                  | 90                   | 90                   | 120                  | 80                   | 60                   | 20                   | 50                     | 20                     |                    |
| E9H   | 2,710   | 76,686               | 220           | 210                | 300                  | 460                  | 220                  | 310                  | 300                  | 170                  | 130                  | 80                   | 70                   | 40                   | 70                   | 40                   | 40                   | 20                   | 30                     | 10                     |                    |
| TOTAL | 611,300 | 23,904,935           | 45,760        | 45,950             | 47,880               | 66,380               | 52,820               | 46,420               | 41,930               | 40,620               | 36,220               | 29,320               | 23,510               | 19,980               | 31,760               | 25,140               | 16,930               | 10,550               | 21,020                 | 6,830                  | 2,290              |