



Tableau 1c - RTA pour toutes les déclarations produites, hommes - année d'imposition 2019

| RTA   | Total        | Revenu total<br>(000\$) | Moins de<br>5 000\$ | 5 000\$<br>à<br>9 999\$ | 10 000\$<br>à<br>14 999\$ | 15 000\$<br>à<br>19 999\$ | 20 000\$<br>à<br>24 999\$ | 25 000\$<br>à<br>29 999\$ | 30 000\$<br>à<br>34 999\$ | 35 000\$<br>à<br>39 999\$ | 40 000\$<br>à<br>44 999\$ | 45 000\$<br>à<br>49 999\$ | 50 000\$<br>à<br>54 999\$ | 55 000\$<br>à<br>59 999\$ | 60 000\$<br>à<br>69 999\$ | 70 000\$<br>à<br>79 999\$ | 80 000\$<br>à<br>89 999\$ | 90 000\$<br>à<br>99 999\$ | 100 000\$<br>à<br>149 999\$ | 150 000\$<br>à<br>249 999\$ | Plus de<br>250 000\$ |
|-------|--------------|-------------------------|---------------------|-------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|-----------------------------|-----------------------------|----------------------|
| PR 47 | Saskatchewan |                         |                     |                         |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                             |                             |                      |
| S0A   | 20 870       | 1 104 761               | 2 150               | 970                     | 1 230                     | 1 600                     | 1 740                     | 1 040                     | 960                       | 910                       | 970                       | 1 020                     | 850                       | 750                       | 1 270                     | 1 030                     | 830                       | 600                       | 1 930                       | 870                         | 160                  |
| S0C   | 8 390        | 577 229                 | 500                 | 280                     | 360                       | 400                       | 500                       | 350                       | 340                       | 350                       | 360                       | 410                       | 360                       | 290                       | 620                       | 590                       | 500                       | 420                       | 1 150                       | 470                         | 130                  |
| S0E   | 13 050       | 672 627                 | 1 380               | 550                     | 800                       | 900                       | 970                       | 630                       | 620                       | 580                       | 580                       | 680                       | 580                       | 540                       | 930                       | 770                       | 590                       | 480                       | 1 000                       | 350                         | 120                  |
| S0G   | 25 110       | 1 477 021               | 2 440               | 960                     | 1 280                     | 1 460                     | 1 580                     | 1 190                     | 1 100                     | 1 140                     | 1 110                     | 1 250                     | 1 100                     | 1 070                     | 1 770                     | 1 580                     | 1 240                     | 1 030                     | 2 570                       | 980                         | 280                  |
| S0H   | 8 550        | 471 923                 | 420                 | 350                     | 590                       | 580                       | 650                       | 470                       | 400                       | 440                       | 450                       | 510                       | 400                       | 400                       | 640                       | 550                       | 390                       | 300                       | 700                         | 240                         | 90                   |
| S0J   | 18 150       | 665 767                 | 5 480               | 930                     | 990                       | 1 190                     | 1 320                     | 730                       | 690                       | 630                       | 620                       | 660                       | 520                       | 440                       | 770                       | 720                       | 530                       | 440                       | 1 050                       | 350                         | 90                   |
| S0K   | 34 230       | 2 148 579               | 2 180               | 1 290                   | 1 500                     | 1 880                     | 2 000                     | 1 490                     | 1 410                     | 1 510                     | 1 570                     | 1 720                     | 1 550                     | 1 510                     | 2 730                     | 2 460                     | 1 860                     | 1 600                     | 4 060                       | 1 580                       | 320                  |
| S0L   | 12 320       | 795 801                 | 480                 | 450                     | 540                       | 770                       | 700                       | 600                       | 600                       | 580                       | 600                       | 660                       | 590                       | 540                       | 940                       | 880                       | 710                       | 570                       | 1 390                       | 550                         | 150                  |
| S0M   | 17 280       | 742 899                 | 4 300               | 990                     | 970                       | 1 120                     | 1 200                     | 690                       | 580                       | 580                       | 580                       | 630                       | 500                       | 450                       | 860                       | 790                       | 660                       | 520                       | 1 180                       | 530                         | 140                  |
| S0N   | 8 160        | 444 063                 | 410                 | 320                     | 690                       | 740                       | 640                       | 390                       | 400                       | 430                       | 410                       | 500                       | 320                       | 320                       | 530                       | 520                       | 350                       | 290                       | 570                         | 250                         | 90                   |
| S0P   | 2 490        | 78 862                  | 1 190               | 110                     | 120                       | 100                       | 130                       | 40                        | 50                        | 40                        | 40                        | 60                        | 40                        | 50                        | 50                        | 70                        | 70                        | 60                        | 200                         | 50                          | 10                   |
| S2V   | 310          | 31 631                  | 10                  |                         | 10                        | 10                        | 10                        | 10                        | 10                        | 20                        | 10                        | 10                        | 10                        | 10                        | 30                        | 20                        | 10                        | 20                        | 70                          | 40                          | 20                   |
| S3N   | 7 510        | 426 024                 | 510                 | 340                     | 370                       | 510                       | 510                       | 410                       | 340                       | 350                       | 350                       | 410                       | 370                       | 330                       | 610                       | 460                       | 360                       | 290                       | 690                         | 240                         | 70                   |
| S4A   | 5 160        | 426 246                 | 190                 | 160                     | 170                       | 200                       | 210                       | 170                       | 180                       | 170                       | 190                       | 200                       | 200                       | 190                       | 400                       | 390                       | 310                       | 290                       | 980                         | 480                         | 100                  |
| S4H   | 4 790        | 341 369                 | 210                 | 160                     | 210                       | 270                       | 280                       | 200                       | 200                       | 210                       | 210                       | 230                       | 230                       | 210                       | 410                       | 330                       | 280                       | 250                       | 610                         | 250                         | 70                   |
| S4K   |              |                         |                     |                         |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                             |                             |                      |
| S4L   | 2 360        | 235 775                 | 90                  | 70                      | 90                        | 80                        | 70                        | 70                        | 60                        | 70                        | 80                        | 80                        | 80                        | 90                        | 140                       | 140                       | 140                       | 160                       | 490                         | 290                         | 100                  |
| S4M   |              |                         |                     |                         |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                             |                             |                      |
| S4N   | 12 010       | 606 428                 | 950                 | 600                     | 650                       | 680                       | 720                       | 620                       | 650                       | 630                       | 660                       | 640                       | 610                       | 590                       | 1 040                     | 770                       | 610                       | 480                       | 870                         | 200                         | 50                   |
| S4P   | 6 060        | 307 940                 | 550                 | 330                     | 450                       | 700                       | 700                       | 310                       | 310                       | 270                       | 250                       | 230                       | 210                       | 180                       | 330                       | 260                       | 210                       | 150                       | 390                         | 160                         | 80                   |
| S4R   | 13 690       | 731 341                 | 880                 | 610                     | 670                       | 690                       | 870                       | 650                       | 630                       | 740                       | 770                       | 830                       | 750                       | 690                       | 1 300                     | 960                       | 760                       | 550                       | 1 030                       | 250                         | 60                   |
| S4S   | 14 060       | 906 193                 | 1 470               | 760                     | 730                       | 750                       | 730                       | 590                       | 630                       | 580                       | 600                       | 670                       | 540                       | 540                       | 920                       | 840                       | 700                       | 610                       | 1 430                       | 670                         | 310                  |
| S4T   | 11 520       | 555 164                 | 1 130               | 660                     | 740                       | 770                       | 820                       | 550                       | 540                       | 570                       | 630                       | 560                       | 540                       | 510                       | 900                       | 680                       | 500                       | 410                       | 760                         | 210                         | 60                   |
| S4V   | 12 050       | 1 096 107               | 810                 | 450                     | 450                       | 460                       | 440                       | 390                       | 370                       | 430                       | 410                       | 470                       | 460                       | 460                       | 850                       | 820                       | 740                       | 660                       | 1 910                       | 990                         | 500                  |
| S4W   | 4 650        | 298 049                 | 450                 | 200                     | 180                       | 210                       | 180                       | 170                       | 190                       | 180                       | 210                       | 210                       | 200                       | 190                       | 400                       | 360                       | 270                       | 210                       | 580                         | 190                         | 60                   |
| S4X   | 10 660       | 761 182                 | 580                 | 320                     | 410                       | 400                       | 380                       | 360                       | 350                       | 420                       | 470                       | 520                       | 480                       | 470                       | 920                       | 830                       | 760                       | 660                       | 1 600                       | 610                         | 130                  |
| S4Y   | 1 950        | 162 422                 | 80                  | 60                      | 60                        | 60                        | 40                        | 50                        | 50                        | 70                        | 70                        | 70                        | 70                        | 70                        | 140                       | 160                       | 140                       | 140                       | 420                         | 170                         | 40                   |
| S4Z   | 470          | 30 765                  | 30                  | 10                      | 10                        | 20                        | 20                        | 20                        | 30                        | 20                        | 30                        | 30                        | 30                        | 30                        | 40                        | 30                        | 40                        | 30                        | 60                          | 20                          | 10                   |
| S6H   | 11 520       | 651 518                 | 730                 | 490                     | 610                       | 710                       | 770                       | 610                       | 580                       | 630                       | 570                       | 600                       | 550                       | 520                       | 840                       | 700                       | 630                       | 470                       | 1 040                       | 390                         | 90                   |
| S6J   | 1 950        | 150 037                 | 130                 | 60                      | 80                        | 100                       | 90                        | 80                        | 70                        | 80                        | 70                        | 100                       | 90                        | 60                        | 140                       | 110                       | 100                       | 90                        | 290                         | 180                         | 40                   |
| S6K   | 470          | 38 501                  | 30                  | 10                      | 10                        | 10                        | 20                        | 10                        | 10                        | 20                        | 20                        | 20                        | 20                        | 10                        | 30                        | 40                        | 40                        | 30                        | 110                         | 50                          | 10                   |
| S6V   | 14 890       | 738 401                 | 1 750               | 840                     | 860                       | 970                       | 1 030                     | 760                       | 750                       | 760                       | 720                       | 700                       | 620                       | 590                       | 970                       | 790                       | 680                       | 510                       | 1 150                       | 340                         | 110                  |
| S6W   | 90           | 8 982                   |                     | 10                      |                           | 10                        |                           |                           | 10                        |                           | 10                        | 10                        |                           | 10                        | 10                        |                           |                           | 10                        | 10                          | 10                          | 10                   |
| S6X   | 820          | 71 600                  | 50                  | 40                      | 30                        | 30                        | 20                        | 20                        | 20                        | 20                        | 30                        | 30                        | 30                        | 30                        | 60                        | 50                        | 50                        | 60                        | 180                         | 60                          | 20                   |
| S7A   |              |                         |                     |                         |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                             |                             |                      |
| S7B   | 120          | 6 201                   | 10                  | 10                      |                           | 10                        | 10                        |                           |                           | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        |                             |                             |                      |
| S7C   | 280          | 25 599                  | 10                  |                         | 10                        | 10                        | 10                        |                           | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 20                        | 10                        | 20                        | 20                        | 70                          | 40                          | 10                   |
| S7H   | 14 120       | 798 971                 | 1 250               | 720                     | 750                       | 910                       | 820                       | 710                       | 730                       | 740                       | 700                       | 660                       | 630                       | 570                       | 1 040                     | 880                       | 650                       | 540                       | 1 160                       | 500                         | 170                  |
| S7J   | 11 650       | 768 200                 | 690                 | 560                     | 570                       | 600                       | 620                       | 510                       | 540                       | 570                       | 560                       | 590                       | 530                       | 540                       | 900                       | 800                       | 600                       | 520                       | 1 230                       | 520                         | 210                  |
| S7K   | 16 430       | 1 166 526               | 1 090               | 670                     | 780                       | 940                       | 920                       | 710                       | 770                       | 650                       | 720                       | 770                       | 690                       | 640                       | 1 260                     | 1 100                     | 900                       | 700                       | 1 780                       | 920                         | 420                  |
| S7L   | 15 400       | 723 454                 | 1 290               | 870                     | 930                       | 1 040                     | 990                       | 780                       | 820                       | 880                       | 880                       | 860                       | 810                       | 720                       | 1 230                     | 910                       | 710                       | 480                       | 980                         | 210                         | 40                   |
| S7M   | 11 800       | 564 469                 | 1 060               | 760                     | 890                       | 940                       | 840                       | 630                       | 610                       | 610                       | 620                       | 600                       | 560                       | 470                       | 800                       | 640                       | 490                       | 320                       | 660                         | 220                         | 80                   |
| S7N   | 10 140       | 710 258                 | 1 000               | 550                     | 540                       | 510                       | 500                       | 480                       | 410                       | 430                       | 410                       | 460                       | 390                       | 330                       | 730                       | 610                       | 450                       | 1 040                     | 570                         | 280                         | 20                   |
| S7P   | 100          | 17 015                  |                     |                         |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           | 10                        | 10                        |                           | 10                        | 20                          | 20                          | 20                   |
| S7R   | 2 950        | 179 125                 | 190                 | 120                     | 130                       | 120                       | 120                       | 120                       | 110                       | 130                       | 140                       | 150                       | 170                       | 130                       | 280                       | 250                       | 190                       | 140                       | 350                         | 100                         | 10                   |
| S7S   | 2 310        | 170 051                 | 140                 | 110                     | 110                       | 120                       | 80                        | 80                        | 90                        | 100                       | 90                        | 100                       | 70                        | 90                        | 160                       | 130                       | 130                       | 120                       | 340                         | 190                         | 60                   |
| S7T   | 5 570        | 470 189                 | 430                 | 230                     | 180                       | 200                       | 210                       | 180                       | 180                       | 220                       | 220                       | 230                       | 180                       | 190                       | 400                       | 380                       | 320                       | 340                       | 860                         | 440                         | 200                  |
| S7V   | 5 040        | 448 344                 | 380                 | 210                     | 230                       | 210                       | 190                       | 170                       | 170                       | 150                       | 170                       | 200                       | 170                       | 170                       | 350                       | 360                       | 300                       | 240                       | 710                         | 430                         | 240                  |
| S7W   | 5 720        | 461 538                 | 450                 | 280                     | 230                       | 190                       | 220                       | 180                       | 190                       | 190                       | 180                       | 210                       | 210                       | 200                       | 360                       | 350                       | 330                       | 310                       | 950                         | 520                         | 170                  |
| S9A   | 5 640        | 281 969                 | 570                 | 330                     | 340                       | 360                       | 380                       | 300                       | 290                       | 250                       | 300                       | 290                       | 300                       | 210                       | 390                       | 330                       | 240                       | 200                       | 380                         | 150                         | 40                   |
| S9H   | 7 580        | 476 017                 | 310                 | 280                     | 390                       | 490                       | 470                       | 350                       | 350                       | 390                       | 420                       | 440                       | 370                       | 370                       | 590                       | 470                       | 410                       | 310                       | 770                         | 320                         | 100                  |
| S9V   | 5 530        | 357 517                 | 310                 | 200                     | 240                       | 260                       | 250                       | 230                       | 230                       | 250                       | 240                       | 240                       | 260                       | 230                       | 450                       | 460                       | 370                       | 310                       | 680                         | 270                         | 40                   |
| S9X   | 3 110        | 162 725                 | 390                 | 150                     | 170                       | 200                       | 210                       | 130                       | 130                       | 120                       | 140                       | 120                       | 110                       | 130                       | 210                       | 170                       | 140                       | 130                       | 330                         | 90                          | 20                   |
| TOTAL | 429 060      | 25 544 758              | 41 100              | 19 420                  | 22 340                    | 25 450                    | 26 180                    | 19 230                    | 18 710                    | 19 090                    | 19 410                    | 20 660                    | 18 350                    | 17 140                    | 30 780                    | 26 550                    | 21 280                    | 17 490                    | 42 750                      | 17 520                      | 5 610                |