



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA                                    | Total          | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|--|----------------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| <b>PR 10 Newfoundland and Labrador</b> |                |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| AOA                                    | 39,430         | 1,667,547             | 1,710         | 1,850              | 2,990                | 4,200                | 4,230                | 3,250                | 3,070                | 2,870                | 2,380                | 2,020                | 1,600                | 1,360                | 1,970                | 1,520                | 1,070                | 860                  | 1,710                  | 630                    | 150                |
| AOB                                    | 17,350         | 706,595               | 690           | 770                | 1,390                | 1,980                | 1,990                | 1,500                | 1,400                | 1,290                | 1,010                | 890                  | 710                  | 590                  | 840                  | 600                  | 400                  | 320                  | 670                    | 240                    | 60                 |
| AOC                                    | 10,800         | 381,471               | 450           | 490                | 950                  | 1,400                | 1,360                | 1,020                | 910                  | 880                  | 740                  | 540                  | 410                  | 310                  | 470                  | 250                  | 160                  | 140                  | 230                    | 80                     | 10                 |
| AOE                                    | 19,100         | 767,231               | 810           | 960                | 1,680                | 2,120                | 2,380                | 1,520                | 1,440                | 1,330                | 1,100                | 920                  | 670                  | 600                  | 890                  | 680                  | 490                  | 450                  | 740                    | 270                    | 50                 |
| AOG                                    | 30,460         | 1,094,947             | 1,520         | 1,450              | 3,010                | 3,970                | 3,530                | 2,690                | 2,570                | 2,230                | 1,750                | 1,560                | 1,140                | 860                  | 1,250                | 830                  | 530                  | 460                  | 840                    | 220                    | 60                 |
| AOH                                    | 15,220         | 529,368               | 1,170         | 810                | 1,400                | 1,750                | 1,790                | 1,350                | 1,210                | 1,060                | 850                  | 710                  | 530                  | 470                  | 610                  | 440                  | 310                  | 220                  | 440                    | 90                     | 20                 |
| AOJ                                    | 6,890          | 263,512               | 370           | 350                | 680                  | 910                  | 900                  | 540                  | 520                  | 400                  | 350                  | 310                  | 210                  | 180                  | 320                  | 210                  | 170                  | 130                  | 220                    | 110                    | 20                 |
| AOK                                    | 22,400         | 891,260               | 800           | 930                | 1,890                | 2,730                | 2,400                | 2,040                | 1,820                | 1,750                | 1,450                | 1,200                | 870                  | 750                  | 1,060                | 710                  | 530                  | 380                  | 800                    | 230                    | 70                 |
| AOL                                    | 6,600          | 289,073               | 250           | 240                | 460                  | 650                  | 620                  | 470                  | 560                  | 490                  | 440                  | 420                  | 340                  | 270                  | 360                  | 310                  | 210                  | 160                  | 290                    | 70                     | 20                 |
| AOM                                    | 5,160          | 208,753               | 190           | 260                | 410                  | 560                  | 570                  | 470                  | 390                  | 320                  | 290                  | 260                  | 160                  | 200                  | 330                  | 230                  | 170                  | 130                  | 170                    | 40                     | 10                 |
| AON                                    | 12,280         | 408,099               | 640           | 640                | 1,290                | 1,830                | 1,380                | 1,190                | 1,030                | 880                  | 720                  | 540                  | 390                  | 320                  | 490                  | 270                  | 210                  | 150                  | 260                    | 60                     | 10                 |
| AOP                                    | 9,750          | 501,076               | 880           | 480                | 560                  | 600                  | 670                  | 590                  | 520                  | 480                  | 450                  | 460                  | 440                  | 400                  | 680                  | 560                  | 420                  | 400                  | 910                    | 200                    | 60                 |
| AOR                                    | 1,980          | 160,519               | 90            | 60                 | 70                   | 70                   | 100                  | 90                   | 80                   | 90                   | 80                   | 70                   | 50                   | 50                   | 100                  | 100                  | 80                   | 90                   | 440                    | 270                    | 10                 |
| A1A                                    | 23,240         | 1,487,400             | 1,110         | 930                | 1,100                | 1,480                | 1,630                | 1,420                | 1,360                | 1,330                | 1,210                | 1,270                | 1,000                | 870                  | 1,510                | 1,350                | 1,110                | 930                  | 2,130                  | 980                    | 530                |
| A1B                                    | 15,660         | 819,585               | 1,130         | 900                | 1,130                | 1,260                | 1,410                | 1,240                | 1,010                | 800                  | 750                  | 700                  | 560                  | 500                  | 860                  | 700                  | 550                  | 430                  | 990                    | 490                    | 260                |
| A1C                                    | 10,170         | 516,739               | 550           | 550                | 790                  | 940                  | 1,050                | 820                  | 680                  | 590                  | 540                  | 440                  | 370                  | 350                  | 520                  | 390                  | 330                  | 270                  | 600                    | 250                    | 160                |
| A1E                                    | 21,880         | 1,096,649             | 910           | 870                | 1,330                | 1,840                | 2,180                | 1,690                | 1,560                | 1,520                | 1,280                | 1,260                | 940                  | 820                  | 1,370                | 1,090                | 760                  | 660                  | 1,220                  | 390                    | 180                |
| A1G                                    | 4,590          | 235,171               | 160           | 140                | 230                  | 320                  | 390                  | 350                  | 310                  | 320                  | 300                  | 310                  | 200                  | 200                  | 330                  | 280                  | 170                  | 170                  | 300                    | 100                    | 30                 |
| A1H                                    | 4,550          | 342,337               | 180           | 130                | 170                  | 200                  | 250                  | 210                  | 170                  | 200                  | 190                  | 190                  | 200                  | 180                  | 340                  | 310                  | 280                  | 290                  | 630                    | 330                    | 110                |
| A1K                                    | 9,830          | 633,783               | 340           | 300                | 450                  | 540                  | 650                  | 580                  | 560                  | 590                  | 530                  | 570                  | 480                  | 390                  | 710                  | 640                  | 500                  | 420                  | 960                    | 440                    | 180                |
| A1L                                    | 16,580         | 1,057,823             | 580           | 510                | 670                  | 840                  | 1,030                | 900                  | 890                  | 850                  | 870                  | 910                  | 830                  | 750                  | 1,270                | 1,140                | 960                  | 910                  | 1,800                  | 700                    | 180                |
| A1M                                    | 6,470          | 415,160               | 270           | 200                | 290                  | 410                  | 490                  | 400                  | 360                  | 360                  | 330                  | 330                  | 300                  | 260                  | 450                  | 420                  | 310                  | 280                  | 620                    | 300                    | 120                |
| A1N                                    | 18,900         | 982,698               | 650           | 590                | 920                  | 1,230                | 1,540                | 1,440                | 1,370                | 1,350                | 1,170                | 1,270                | 1,060                | 880                  | 1,340                | 1,040                | 790                  | 620                  | 1,120                  | 400                    | 130                |
| A1S                                    | 5,470          | 273,618               | 200           | 200                | 310                  | 410                  | 490                  | 430                  | 400                  | 360                  | 320                  | 350                  | 280                  | 200                  | 350                  | 290                  | 220                  | 160                  | 340                    | 130                    | 30                 |
| A1V                                    | 9,640          | 516,074               | 360           | 350                | 620                  | 710                  | 770                  | 670                  | 730                  | 620                  | 560                  | 560                  | 450                  | 380                  | 630                  | 500                  | 400                  | 380                  | 610                    | 290                    | 80                 |
| A1W                                    | 9,060          | 520,268               | 330           | 320                | 420                  | 590                  | 730                  | 580                  | 530                  | 530                  | 540                  | 510                  | 450                  | 400                  | 660                  | 530                  | 440                  | 370                  | 750                    | 280                    | 110                |
| A1X                                    | 12,300         | 620,967               | 520           | 440                | 680                  | 900                  | 1,010                | 870                  | 830                  | 770                  | 710                  | 740                  | 600                  | 540                  | 880                  | 730                  | 540                  | 460                  | 780                    | 240                    | 70                 |
| A1Y                                    | 4,640          | 192,853               | 200           | 190                | 360                  | 540                  | 560                  | 410                  | 370                  | 330                  | 270                  | 250                  | 170                  | 140                  | 230                  | 150                  | 110                  | 110                  | 170                    | 80                     | 20                 |
| A2A                                    | 7,780          | 373,894               | 310           | 370                | 500                  | 620                  | 700                  | 610                  | 530                  | 560                  | 480                  | 470                  | 370                  | 310                  | 470                  | 310                  | 250                  | 270                  | 450                    | 140                    | 60                 |
| A2B                                    | 3,980          | 147,723               | 200           | 210                | 350                  | 450                  | 500                  | 370                  | 310                  | 280                  | 270                  | 220                  | 140                  | 90                   | 190                  | 100                  | 70                   | 80                   | 130                    | 30                     | 10                 |
| A2H                                    | 21,170         | 974,555               | 790           | 910                | 1,400                | 1,800                | 2,190                | 1,690                | 1,640                | 1,480                | 1,330                | 1,250                | 1,000                | 850                  | 1,170                | 900                  | 720                  | 620                  | 980                    | 320                    | 130                |
| A2N                                    | 7,450          | 304,560               | 330           | 380                | 680                  | 800                  | 850                  | 600                  | 520                  | 480                  | 440                  | 390                  | 320                  | 230                  | 360                  | 250                  | 200                  | 210                  | 290                    | 90                     | 30                 |
| A2V                                    | 5,720          | 470,505               | 260           | 160                | 210                  | 220                  | 260                  | 250                  | 290                  | 270                  | 240                  | 210                  | 200                  | 170                  | 250                  | 220                  | 220                  | 190                  | 1,240                  | 800                    | 60                 |
| ASA                                    | 6,950          | 321,608               | 270           | 290                | 490                  | 670                  | 680                  | 610                  | 550                  | 490                  | 390                  | 350                  | 290                  | 250                  | 360                  | 290                  | 230                  | 190                  | 370                    | 140                    | 40                 |
| A8A                                    | 5,880          | 236,034               | 280           | 260                | 440                  | 630                  | 710                  | 540                  | 500                  | 410                  | 330                  | 290                  | 250                  | 180                  | 280                  | 220                  | 130                  | 130                  | 240                    | 70                     | 20                 |
| <b>TOTAL</b>                           | <b>429,320</b> | <b>20,409,453</b>     | <b>19,480</b> | <b>18,450</b>      | <b>30,290</b>        | <b>40,190</b>        | <b>41,960</b>        | <b>33,400</b>        | <b>30,980</b>        | <b>28,530</b>        | <b>24,650</b>        | <b>22,700</b>        | <b>17,970</b>        | <b>15,290</b>        | <b>23,860</b>        | <b>18,520</b>        | <b>14,010</b>        | <b>12,020</b>        | <b>24,420</b>          | <b>9,500</b>           | <b>3,090</b>       |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total                       | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|--------------|-----------------------------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| <b>PR 11</b> | <b>Prince Edward Island</b> |                      |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| COA          | 38,340                      | 1,750,378            | 1,790         | 1,310              | 1,870                | 2,740                | 3,530                | 3,080                | 3,240                | 3,030                | 2,720                | 2,520                | 2,010                | 1,670                | 2,630                | 1,820                | 1,360                | 940                  | 1,450                  | 460                    | 180                |
| COB          | 25,000                      | 1,087,802            | 960           | 800                | 1,430                | 1,950                | 2,370                | 2,080                | 2,290                | 2,140                | 1,960                | 1,710                | 1,470                | 1,060                | 1,530                | 1,000                | 680                  | 460                  | 780                    | 260                    | 100                |
| C1A          | 21,740                      | 994,318              | 1,250         | 820                | 1,120                | 1,730                | 2,280                | 2,000                | 2,080                | 1,610                | 1,290                | 1,150                | 970                  | 810                  | 1,260                | 880                  | 650                  | 490                  | 830                    | 330                    | 190                |
| C1B          | 11,030                      | 614,674              | 500           | 350                | 470                  | 640                  | 780                  | 790                  | 660                  | 670                  | 640                  | 610                  | 510                  | 890                  | 670                  | 550                  | 410                  | 690                  | 260                    | 150                    |                    |
| C1C          | 3,980                       | 182,402              | 150           | 120                | 180                  | 260                  | 350                  | 350                  | 350                  | 310                  | 300                  | 270                  | 230                  | 180                  | 300                  | 200                  | 150                  | 110                  | 130                    | 40                     | 20                 |
| C1E          | 9,940                       | 493,867              | 600           | 380                | 500                  | 620                  | 780                  | 780                  | 730                  | 670                  | 580                  | 560                  | 470                  | 470                  | 730                  | 520                  | 440                  | 330                  | 520                    | 180                    | 80                 |
| C1N          | 14,520                      | 648,538              | 520           | 500                | 750                  | 1,150                | 1,530                | 1,400                | 1,300                | 1,100                | 1,010                | 1,000                | 790                  | 580                  | 910                  | 580                  | 440                  | 300                  | 460                    | 140                    | 100                |
| <b>TOTAL</b> | <b>124,550</b>              | <b>5,771,978</b>     | <b>5,770</b>  | <b>4,270</b>       | <b>6,310</b>         | <b>9,090</b>         | <b>11,620</b>        | <b>10,460</b>        | <b>10,770</b>        | <b>9,520</b>         | <b>8,530</b>         | <b>7,840</b>         | <b>6,550</b>         | <b>5,290</b>         | <b>8,240</b>         | <b>5,670</b>         | <b>4,260</b>         | <b>3,020</b>         | <b>4,860</b>           | <b>1,680</b>           | <b>810</b>         |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total              | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|--------------|--------------------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| <b>PR 12</b> | <b>Nova Scotia</b> |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| B0C          | 2,270              | 96,896                | 50            | 80                 | 100                  | 200                  | 270                  | 220                  | 240                  | 240                  | 170                  | 120                  | 110                  | 80                   | 110                  | 80                   | 50                   | 50                   | 70                     | 20                     | 10                 |
| B0E          | 21,690             | 866,470               | 1,530         | 1,010              | 1,480                | 1,920                | 2,690                | 1,690                | 1,640                | 1,630                | 1,310                | 1,190                | 960                  | 750                  | 1,050                | 850                  | 580                  | 410                  | 700                    | 250                    | 60                 |
| B0H          | 8,340              | 338,946               | 450           | 370                | 610                  | 860                  | 990                  | 650                  | 600                  | 590                  | 520                  | 450                  | 360                  | 280                  | 420                  | 330                  | 250                  | 190                  | 300                    | 90                     | 30                 |
| B0J          | 33,880             | 1,551,446             | 1,660         | 1,310              | 2,070                | 2,720                | 3,960                | 2,770                | 2,560                | 2,270                | 1,930                | 1,880                | 1,580                | 1,250                | 2,120                | 1,640                | 1,200                | 830                  | 1,470                  | 500                    | 190                |
| B0K          | 29,680             | 1,232,273             | 1,570         | 1,390              | 2,050                | 2,390                | 3,520                | 2,520                | 2,250                | 2,050                | 1,800                | 1,800                | 1,390                | 1,140                | 1,710                | 1,210                | 850                  | 630                  | 1,020                  | 270                    | 130                |
| B0L          | 2,040              | 75,020                | 100           | 90                 | 180                  | 220                  | 260                  | 160                  | 160                  | 170                  | 130                  | 130                  | 90                   | 70                   | 90                   | 70                   | 40                   | 30                   | 50                     | 10                     | 10                 |
| B0M          | 13,960             | 551,696               | 770           | 640                | 1,100                | 1,330                | 1,680                | 1,140                | 1,020                | 1,010                | 870                  | 820                  | 660                  | 500                  | 760                  | 530                  | 360                  | 260                  | 400                    | 100                    | 40                 |
| B0N          | 32,550             | 1,388,322             | 2,020         | 1,370              | 2,150                | 2,600                | 3,650                | 2,510                | 2,370                | 2,160                | 1,980                | 1,810                | 1,520                | 1,280                | 2,010                | 1,510                | 1,150                | 790                  | 1,240                  | 330                    | 120                |
| B0P          | 33,480             | 1,463,140             | 1,830         | 1,440              | 2,250                | 2,690                | 3,530                | 2,580                | 2,530                | 2,260                | 1,920                | 1,910                | 1,530                | 1,260                | 2,180                | 1,840                | 1,170                | 790                  | 1,280                  | 350                    | 150                |
| B0R          | 5,020              | 195,659               | 260           | 250                | 380                  | 470                  | 650                  | 410                  | 430                  | 330                  | 310                  | 260                  | 240                  | 180                  | 290                  | 170                  | 110                  | 80                   | 150                    | 40                     | 20                 |
| B0S          | 15,060             | 565,547               | 920           | 720                | 1,210                | 1,610                | 1,960                | 1,350                | 1,160                | 1,060                | 900                  | 770                  | 580                  | 440                  | 730                  | 560                  | 380                  | 230                  | 360                    | 110                    | 40                 |
| B0T          | 12,680             | 496,015               | 730           | 590                | 990                  | 1,170                | 1,640                | 1,080                | 1,000                | 900                  | 790                  | 710                  | 520                  | 430                  | 620                  | 440                  | 320                  | 210                  | 390                    | 100                    | 50                 |
| B0V          | 4,990              | 191,091               | 260           | 220                | 400                  | 540                  | 720                  | 500                  | 400                  | 320                  | 300                  | 270                  | 180                  | 170                  | 210                  | 150                  | 100                  | 80                   | 110                    | 40                     | 20                 |
| B0W          | 23,930             | 993,444               | 1,090         | 1,030              | 1,740                | 2,280                | 2,960                | 1,990                | 1,820                | 1,630                | 1,470                | 1,330                | 1,040                | 850                  | 1,260                | 990                  | 730                  | 490                  | 910                    | 260                    | 80                 |
| B1A          | 12,550             | 474,831               | 550           | 700                | 1,060                | 1,130                | 1,630                | 1,280                | 1,080                | 870                  | 760                  | 630                  | 480                  | 360                  | 620                  | 410                  | 280                  | 250                  | 360                    | 80                     | 30                 |
| B1B          | 1,080              | 44,899                | 40            | 60                 | 80                   | 80                   | 130                  | 100                  | 90                   | 80                   | 60                   | 60                   | 40                   | 40                   | 80                   | 40                   | 20                   | 20                   | 40                     | 10                     | 10                 |
| B1C          | 1,500              | 69,345                | 40            | 60                 | 80                   | 90                   | 170                  | 100                  | 120                  | 140                  | 140                  | 90                   | 70                   | 60                   | 100                  | 70                   | 40                   | 30                   | 60                     | 20                     | 10                 |
| B1E          | 1,360              | 51,512                | 50            | 90                 | 110                  | 110                  | 180                  | 140                  | 130                  | 90                   | 90                   | 60                   | 50                   | 40                   | 70                   | 60                   | 30                   | 30                   | 40                     | 10                     | 10                 |
| B1G          | 1,560              | 57,999                | 60            | 80                 | 140                  | 130                  | 170                  | 120                  | 130                  | 110                  | 80                   | 60                   | 50                   | 40                   | 70                   | 50                   | 40                   | 30                   | 40                     | 10                     | 10                 |
| B1H          | 7,910              | 296,544               | 260           | 440                | 700                  | 660                  | 1,100                | 810                  | 670                  | 590                  | 480                  | 400                  | 300                  | 250                  | 380                  | 240                  | 180                  | 170                  | 240                    | 50                     | 10                 |
| B1J          | 970                | 51,219                | 40            | 30                 | 40                   | 70                   | 100                  | 70                   | 70                   | 60                   | 60                   | 70                   | 40                   | 40                   | 80                   | 50                   | 30                   | 30                   | 60                     | 20                     | 10                 |
| B1K          | 2,680              | 132,192               | 80            | 110                | 120                  | 190                  | 280                  | 210                  | 210                  | 200                  | 160                  | 170                  | 120                  | 120                  | 170                  | 150                  | 120                  | 80                   | 130                    | 40                     | 20                 |
| B1L          | 4,090              | 206,366               | 140           | 140                | 190                  | 290                  | 410                  | 310                  | 270                  | 290                  | 230                  | 260                  | 200                  | 170                  | 300                  | 230                  | 170                  | 150                  | 210                    | 90                     | 30                 |
| B1M          | 1,080              | 49,678                | 70            | 50                 | 70                   | 60                   | 110                  | 70                   | 80                   | 70                   | 60                   | 70                   | 50                   | 40                   | 60                   | 60                   | 30                   | 60                   | 30                     | 10                     | 10                 |
| B1N          | 4,790              | 163,768               | 200           | 260                | 400                  | 500                  | 620                  | 540                  | 460                  | 370                  | 300                  | 260                  | 170                  | 140                  | 200                  | 120                  | 90                   | 60                   | 80                     | 100                    | 50                 |
| B1P          | 13,180             | 495,615               | 780           | 650                | 1,120                | 1,360                | 1,730                | 1,250                | 1,080                | 900                  | 700                  | 630                  | 500                  | 380                  | 600                  | 390                  | 330                  | 230                  | 400                    | 100                    | 50                 |
| B1R          | 3,630              | 179,625               | 130           | 140                | 190                  | 230                  | 360                  | 270                  | 220                  | 260                  | 250                  | 250                  | 170                  | 160                  | 240                  | 190                  | 170                  | 140                  | 190                    | 50                     | 30                 |
| B1S          | 6,820              | 315,359               | 640           | 300                | 420                  | 570                  | 700                  | 490                  | 440                  | 450                  | 350                  | 360                  | 260                  | 240                  | 400                  | 260                  | 220                  | 210                  | 310                    | 120                    | 70                 |
| B1T          | 320                | 14,310                | 10            | 10                 | 20                   | 30                   | 40                   | 30                   | 20                   | 30                   | 20                   | 20                   | 10                   | 20                   | 20                   | 10                   | 10                   | 10                   | 10                     | 10                     | 10                 |
| B1V          | 4,980              | 191,378               | 180           | 260                | 440                  | 390                  | 630                  | 480                  | 420                  | 390                  | 330                  | 280                  | 220                  | 190                  | 260                  | 170                  | 110                  | 80                   | 120                    | 30                     | 10                 |
| B1W          | 2,170              | 18,900                | 1,130         | 210                | 250                  | 290                  | 160                  | 40                   | 20                   | 20                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                     | 10                     | 10                 |
| B1X          | 720                | 34,997                | 30            | 30                 | 40                   | 50                   | 80                   | 60                   | 60                   | 40                   | 50                   | 40                   | 40                   | 30                   | 50                   | 40                   | 20                   | 10                   | 30                     | 10                     | 10                 |
| B1Y          | 5,160              | 228,341               | 170           | 240                | 350                  | 380                  | 570                  | 430                  | 420                  | 410                  | 340                  | 290                  | 230                  | 220                  | 340                  | 230                  | 170                  | 140                  | 180                    | 50                     | 30                 |
| B2A          | 6,580              | 258,648               | 280           | 290                | 540                  | 580                  | 810                  | 610                  | 530                  | 460                  | 440                  | 390                  | 280                  | 230                  | 350                  | 240                  | 170                  | 120                  | 180                    | 50                     | 20                 |
| B2C          | 260                | 10,445                | 20            | 10                 | 10                   | 30                   | 30                   | 20                   | 20                   | 10                   | 20                   | 10                   | 10                   | 10                   | 20                   | 10                   | 10                   | 10                   | 10                     | 10                     | 10                 |
| B2E          | 40                 | 1,277                 |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| B2G          | 11,950             | 596,885               | 510           | 480                | 720                  | 870                  | 1,180                | 860                  | 850                  | 820                  | 780                  | 680                  | 580                  | 490                  | 700                  | 580                  | 500                  | 360                  | 660                    | 240                    | 90                 |
| B2H          | 12,130             | 578,172               | 510           | 530                | 820                  | 970                  | 1,300                | 960                  | 910                  | 780                  | 740                  | 720                  | 590                  | 460                  | 700                  | 540                  | 420                  | 320                  | 550                    | 220                    | 90                 |
| B2J          | 70                 | 4,688                 | 10            |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| B2N          | 16,890             | 723,887               | 910           | 750                | 1,300                | 1,430                | 1,980                | 1,440                | 1,380                | 1,110                | 1,010                | 890                  | 720                  | 580                  | 970                  | 670                  | 510                  | 370                  | 550                    | 220                    | 100                |
| B2R          | 2,150              | 141,442               | 70            | 60                 | 80                   | 110                  | 140                  | 130                  | 130                  | 90                   | 90                   | 130                  | 100                  | 100                  | 150                  | 130                  | 100                  | 230                  | 80                     | 40                     | 40                 |
| B2S          | 6,230              | 316,374               | 270           | 220                | 330                  | 340                  | 500                  | 430                  | 460                  | 400                  | 370                  | 350                  | 330                  | 290                  | 490                  | 370                  | 340                  | 240                  | 410                    | 100                    | 20                 |
| B2T          | 13,840             | 892,736               | 610           | 450                | 590                  | 710                  | 890                  | 790                  | 750                  | 730                  | 670                  | 740                  | 630                  | 560                  | 1,060                | 880                  | 850                  | 650                  | 1,510                  | 560                    | 210                |
| B2V          | 9,930              | 576,867               | 410           | 320                | 410                  | 500                  | 600                  | 610                  | 550                  | 550                  | 560                  | 600                  | 500                  | 450                  | 840                  | 730                  | 660                  | 500                  | 840                    | 240                    | 70                 |
| B2W          | 27,190             | 1,446,203             | 1,090         | 880                | 1,070                | 1,420                | 2,070                | 1,830                | 1,900                | 1,770                | 1,860                | 1,760                | 1,450                | 1,310                | 2,190                | 1,960                | 1,360                | 1,020                | 1,760                  | 510                    | 180                |
| B2X          | 9,690              | 521,741               | 440           | 350                | 500                  | 580                  | 760                  | 710                  | 660                  | 590                  | 530                  | 580                  | 420                  | 450                  | 680                  | 570                  | 520                  | 370                  | 660                    | 240                    | 70                 |
| B2Y          | 12,250             | 616,993               | 540           | 420                | 760                  | 810                  | 1,190                | 910                  | 880                  | 830                  | 680                  | 730                  | 550                  | 490                  | 810                  | 640                  | 530                  | 420                  | 770                    | 220                    | 80                 |
| B2Z          | 6,950              | 352,790               | 240           | 220                | 320                  | 470                  | 580                  | 530                  | 450                  | 480                  | 420                  | 420                  | 350                  | 310                  | 510                  | 450                  | 340                  | 270                  | 460                    | 110                    | 30                 |
| B3A          | 16,870             | 772,889               | 740           | 590                | 1,230                | 1,180                | 1,660                | 1,500                | 1,400                | 1,300                | 1,100                | 910                  | 780                  | 630                  | 1,020                | 770                  | 550                  | 400                  | 780                    | 240                    | 100                |
| B3B          | 1,140              | 62,250                | 90            | 40                 | 50                   | 70                   | 110                  | 80                   | 80                   | 80                   | 80                   | 60                   | 50                   | 50                   | 90                   | 50                   | 40                   | 20                   | 60                     | 20                     | 20                 |
| B3E          | 5,650              | 299,768               | 220           | 190                | 260                  | 310                  | 420                  | 370                  | 390                  | 370                  | 330                  | 370                  | 270                  | 270                  | 470                  | 370                  | 310                  | 220                  | 390                    | 100                    | 40                 |
| B3G          | 8,690              | 431,064               | 400           | 310                | 360                  | 450                  | 690                  | 590                  | 610                  | 570                  | 520                  | 580                  | 460                  | 420                  | 710                  | 600                  | 560                  | 330                  | 430                    | 80                     | 20                 |
| B3H          | 13,910             | 1,030,161             | 1,480         | 710                | 820                  | 900                  | 1,100                | 850                  | 670                  | 540                  | 530                  | 530                  | 440                  | 400                  | 710                  | 640                  | 530                  | 430                  | 1,110                  | 880                    | 660                |
| B3J          | 6,940              | 457,856               | 800           | 310                | 330                  | 530                  | 640                  | 470                  | 360                  | 330                  | 270                  | 300                  | 250                  | 200                  | 390                  | 380                  | 320                  | 210                  | 440                    | 230                    | 190                |
| B3K          | 17,560             | 879,041               | 890           | 680                | 1,140                | 1,240                | 1,680                | 1,360                | 1,200                | 1,070                | 880                  | 950                  | 790                  | 630                  | 1,200                | 960                  | 820                  | 550                  | 1,060                  | 330                    | 150                |
| B3L          | 13,960             | 754,328               | 900           | 590                | 810                  | 910                  | 1,240                | 1,080                | 910                  | 800                  | 710                  | 68                   |                      |                      |                      |                      |                      |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total                | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|--------------|----------------------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| <b>PR 13</b> | <b>New Brunswick</b> |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| E1A          | 37,500               | 1,939,503             | 1,650         | 1,570              | 1,720                | 2,380                | 3,050                | 2,670                | 2,570                | 2,590                | 2,460                | 2,360                | 1,920                | 1,670                | 2,710                | 2,090                | 1,730                | 1,160                | 2,140                  | 760                    | 300                |
| E1B          | 16,650               | 813,492               | 670           | 670                | 730                  | 990                  | 1,430                | 1,190                | 1,240                | 1,380                | 1,250                | 1,140                | 900                  | 740                  | 1,190                | 870                  | 670                  | 460                  | 780                    | 270                    | 80                 |
| E1C          | 20,020               | 770,630               | 1,010         | 1,350              | 1,270                | 1,730                | 2,230                | 1,960                | 1,800                | 1,620                | 1,350                | 1,140                | 840                  | 630                  | 940                  | 670                  | 440                  | 310                  | 500                    | 180                    | 80                 |
| E1E          | 9,130                | 451,267               | 410           | 380                | 420                  | 640                  | 830                  | 710                  | 670                  | 710                  | 610                  | 560                  | 440                  | 390                  | 620                  | 480                  | 350                  | 250                  | 410                    | 180                    | 80                 |
| E1G          | 19,210               | 1,025,141             | 940           | 800                | 860                  | 1,050                | 1,310                | 1,250                | 1,230                | 1,270                | 1,300                | 1,250                | 1,030                | 890                  | 1,450                | 1,190                | 980                  | 620                  | 1,220                  | 420                    | 170                |
| E1H          | 6,460                | 307,712               | 250           | 260                | 370                  | 440                  | 560                  | 490                  | 490                  | 490                  | 470                  | 430                  | 350                  | 300                  | 430                  | 310                  | 240                  | 140                  | 280                    | 100                    | 50                 |
| E1J          | 2,960                | 148,238               | 120           | 120                | 150                  | 190                  | 220                  | 190                  | 220                  | 170                  | 220                  | 210                  | 130                  | 160                  | 230                  | 170                  | 160                  | 80                   | 170                    | 50                     | 20                 |
| E1N          | 9,330                | 395,007               | 370           | 480                | 520                  | 770                  | 960                  | 800                  | 700                  | 720                  | 680                  | 520                  | 480                  | 400                  | 640                  | 380                  | 330                  | 200                  | 290                    | 80                     | 30                 |
| E1V          | 11,260               | 508,206               | 550           | 460                | 640                  | 920                  | 1,110                | 930                  | 870                  | 810                  | 710                  | 620                  | 520                  | 410                  | 720                  | 550                  | 470                  | 330                  | 440                    | 150                    | 50                 |
| E1W          | 6,120                | 258,512               | 190           | 260                | 360                  | 690                  | 730                  | 500                  | 480                  | 550                  | 460                  | 350                  | 240                  | 190                  | 310                  | 220                  | 160                  | 130                  | 220                    | 70                     | 30                 |
| E1X          | 12,300               | 469,000               | 420           | 720                | 870                  | 1,440                | 1,350                | 990                  | 1,130                | 1,130                | 850                  | 680                  | 510                  | 390                  | 560                  | 380                  | 310                  | 180                  | 300                    | 70                     | 30                 |
| E2A          | 14,870               | 612,475               | 730           | 920                | 890                  | 1,420                | 1,770                | 1,300                | 1,160                | 1,040                | 930                  | 780                  | 620                  | 520                  | 790                  | 530                  | 450                  | 290                  | 450                    | 210                    | 80                 |
| E2E          | 16,020               | 1,045,447             | 700           | 580                | 700                  | 850                  | 1,100                | 1,010                | 850                  | 920                  | 880                  | 830                  | 730                  | 620                  | 1,170                | 970                  | 880                  | 660                  | 1,530                  | 760                    | 320                |
| E2G          | 4,150                | 241,953               | 190           | 180                | 170                  | 240                  | 320                  | 270                  | 250                  | 240                  | 240                  | 210                  | 200                  | 150                  | 290                  | 240                  | 200                  | 170                  | 390                    | 170                    | 50                 |
| E2H          | 3,800                | 251,873               | 200           | 160                | 190                  | 240                  | 310                  | 290                  | 240                  | 240                  | 230                  | 180                  | 170                  | 120                  | 220                  | 180                  | 160                  | 130                  | 260                    | 180                    | 120                |
| E2J          | 12,940               | 519,145               | 590           | 570                | 700                  | 970                  | 1,430                | 1,270                | 1,050                | 1,080                | 970                  | 810                  | 630                  | 510                  | 790                  | 520                  | 380                  | 210                  | 380                    | 80                     | 20                 |
| E2K          | 13,820               | 624,162               | 910           | 840                | 840                  | 1,100                | 1,440                | 1,190                | 1,090                | 980                  | 830                  | 720                  | 540                  | 410                  | 700                  | 560                  | 420                  | 300                  | 580                    | 260                    | 110                |
| E2L          | 6,510                | 259,659               | 360           | 580                | 500                  | 670                  | 700                  | 630                  | 500                  | 450                  | 350                  | 270                  | 210                  | 190                  | 270                  | 230                  | 150                  | 100                  | 210                    | 100                    | 50                 |
| E2M          | 15,200               | 716,589               | 620           | 650                | 750                  | 1,010                | 1,370                | 1,260                | 1,100                | 1,160                | 1,040                | 920                  | 790                  | 620                  | 1,020                | 760                  | 590                  | 450                  | 820                    | 210                    | 60                 |
| E2N          | 3,630                | 176,013               | 140           | 140                | 180                  | 210                  | 330                  | 250                  | 270                  | 290                  | 270                  | 230                  | 180                  | 140                  | 230                  | 210                  | 140                  | 100                  | 250                    | 60                     | 10                 |
| E2P          | 1,090                | 47,845                | 50            | 40                 | 40                   | 60                   | 100                  | 100                  | 100                  | 100                  | 90                   | 90                   | 70                   | 50                   | 80                   | 50                   | 30                   | 20                   | 30                     | 10                     | 10                 |
| E2R          |                      |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| E2S          | 5,560                | 264,338               | 270           | 240                | 270                  | 330                  | 460                  | 430                  | 380                  | 420                  | 370                  | 370                  | 280                  | 230                  | 380                  | 300                  | 240                  | 150                  | 380                    | 80                     | 10                 |
| E2V          | 10,980               | 543,572               | 650           | 380                | 450                  | 590                  | 720                  | 670                  | 640                  | 600                  | 580                  | 590                  | 530                  | 560                  | 1,450                | 1,050                | 630                  | 310                  | 470                    | 100                    | 20                 |
| E3A          | 23,190               | 1,071,881             | 1,350         | 1,050              | 1,240                | 1,520                | 2,060                | 1,750                | 1,650                | 1,610                | 1,540                | 1,410                | 1,080                | 930                  | 1,600                | 1,250                | 1,000                | 630                  | 1,130                  | 340                    | 90                 |
| E3B          | 30,110               | 1,590,617             | 1,820         | 1,510              | 1,440                | 1,860                | 2,340                | 2,140                | 1,960                | 1,790                | 1,700                | 1,710                | 1,380                | 1,140                | 2,160                | 1,800                | 1,420                | 950                  | 1,900                  | 770                    | 320                |
| E3C          | 9,800                | 569,301               | 430           | 330                | 370                  | 450                  | 610                  | 540                  | 550                  | 570                  | 600                  | 570                  | 510                  | 500                  | 800                  | 750                  | 610                  | 450                  | 850                    | 250                    | 80                 |
| E3E          | 3,610                | 204,870               | 290           | 150                | 160                  | 220                  | 250                  | 210                  | 170                  | 200                  | 190                  | 190                  | 160                  | 140                  | 280                  | 240                  | 180                  | 160                  | 290                    | 120                    | 40                 |
| E3G          | 6,710                | 357,367               | 320           | 280                | 300                  | 400                  | 510                  | 430                  | 420                  | 410                  | 420                  | 410                  | 330                  | 300                  | 540                  | 440                  | 320                  | 230                  | 460                    | 160                    | 40                 |
| E3L          | 7,140                | 290,533               | 300           | 390                | 490                  | 660                  | 790                  | 660                  | 620                  | 520                  | 450                  | 370                  | 290                  | 220                  | 380                  | 280                  | 220                  | 150                  | 260                    | 70                     | 20                 |
| E3N          | 11,510               | 446,172               | 500           | 690                | 760                  | 1,120                | 1,280                | 1,030                | 1,020                | 980                  | 760                  | 640                  | 500                  | 340                  | 540                  | 400                  | 320                  | 200                  | 310                    | 90                     | 30                 |
| E3V          | 10,290               | 441,387               | 350           | 580                | 610                  | 960                  | 1,230                | 840                  | 820                  | 730                  | 700                  | 620                  | 460                  | 380                  | 530                  | 430                  | 320                  | 180                  | 370                    | 130                    | 50                 |
| E3Y          | 6,130                | 244,710               | 260           | 300                | 470                  | 580                  | 660                  | 500                  | 470                  | 440                  | 430                  | 360                  | 300                  | 240                  | 370                  | 240                  | 180                  | 120                  | 190                    | 50                     | 10                 |
| E3Z          | 3,520                | 161,886               | 160           | 180                | 200                  | 350                  | 380                  | 300                  | 250                  | 230                  | 230                  | 200                  | 170                  | 140                  | 190                  | 140                  | 120                  | 70                   | 150                    | 50                     | 20                 |
| E4A          | 2,610                | 95,570                | 160           | 140                | 210                  | 280                  | 350                  | 230                  | 180                  | 140                  | 160                  | 110                  | 110                  | 90                   | 160                  | 110                  | 70                   | 60                   | 50                     | 10                     | 10                 |
| E4B          | 3,560                | 135,342               | 160           | 190                | 230                  | 370                  | 480                  | 330                  | 290                  | 270                  | 210                  | 170                  | 140                  | 140                  | 190                  | 130                  | 100                  | 70                   | 80                     | 20                     | 10                 |
| E4C          | 1,820                | 73,246                | 90            | 100                | 130                  | 180                  | 220                  | 140                  | 110                  | 120                  | 120                  | 100                  | 90                   | 60                   | 110                  | 70                   | 40                   | 40                   | 70                     | 10                     | 10                 |
| E4E          | 7,440                | 310,995               | 390           | 390                | 480                  | 650                  | 690                  | 620                  | 510                  | 480                  | 400                  | 310                  | 240                  | 240                  | 400                  | 310                  | 220                  | 120                  | 270                    | 100                    | 30                 |
| E4G          | 2,160                | 86,354                | 130           | 100                | 130                  | 180                  | 220                  | 180                  | 180                  | 170                  | 160                  | 120                  | 110                  | 80                   | 140                  | 100                  | 50                   | 40                   | 70                     | 20                     | 10                 |
| E4H          | 3,430                | 134,332               | 180           | 170                | 190                  | 270                  | 410                  | 280                  | 310                  | 290                  | 260                  | 210                  | 170                  | 140                  | 180                  | 150                  | 70                   | 50                   | 70                     | 20                     | 10                 |
| E4J          | 3,900                | 155,556               | 200           | 180                | 230                  | 300                  | 440                  | 350                  | 350                  | 310                  | 290                  | 210                  | 200                  | 170                  | 240                  | 140                  | 130                  | 60                   | 100                    | 20                     | 10                 |
| E4K          | 4,810                | 218,664               | 210           | 180                | 220                  | 340                  | 440                  | 350                  | 330                  | 420                  | 360                  | 340                  | 300                  | 220                  | 350                  | 230                  | 170                  | 120                  | 170                    | 40                     | 20                 |
| E4L          | 6,120                | 278,910               | 300           | 280                | 350                  | 480                  | 640                  | 530                  | 450                  | 440                  | 390                  | 340                  | 280                  | 220                  | 350                  | 250                  | 210                  | 150                  | 320                    | 100                    | 40                 |
| E4M          | 1,620                | 61,739                | 80            | 90                 | 120                  | 160                  | 200                  | 160                  | 140                  | 130                  | 120                  | 80                   | 60                   | 40                   | 60                   | 60                   | 30                   | 20                   | 50                     | 10                     | 10                 |
| E4N          | 3,710                | 163,938               | 130           | 120                | 220                  | 350                  | 420                  | 320                  | 340                  | 360                  | 330                  | 240                  | 170                  | 140                  | 200                  | 120                  | 80                   | 50                   | 90                     | 20                     | 10                 |
| E4P          | 13,360               | 618,563               | 430           | 480                | 640                  | 1,070                | 1,370                | 1,020                | 1,020                | 1,090                | 1,010                | 900                  | 630                  | 610                  | 950                  | 650                  | 450                  | 290                  | 520                    | 170                    | 70                 |
| E4R          | 5,870                | 274,443               | 180           | 210                | 310                  | 470                  | 550                  | 450                  | 410                  | 470                  | 470                  | 390                  | 290                  | 270                  | 380                  | 280                  | 240                  | 150                  | 260                    | 70                     | 30                 |
| E4S          | 6,460                | 253,777               | 250           | 340                | 640                  | 680                  | 580                  | 570                  | 560                  | 460                  | 410                  | 290                  | 230                  | 320                  | 210                  | 180                  | 110                  | 150                  | 40                     | 20                     | 10                 |
| E4T          | 1,830                | 64,895                | 80            | 110                | 140                  | 230                  | 210                  | 150                  | 150                  | 140                  | 150                  | 110                  | 90                   | 50                   | 80                   | 50                   | 40                   | 20                   | 30                     | 10                     | 10                 |
| E4V          | 3,770                | 157,140               | 140           | 150                | 210                  | 290                  | 380                  | 300                  | 300                  | 310                  | 290                  | 250                  | 210                  | 180                  | 270                  | 170                  | 130                  | 70                   | 110                    | 30                     | 10                 |
| E4W          | 7,000                | 232,370               | 730           | 330                | 520                  | 810                  | 910                  | 630                  | 550                  | 550                  | 430                  | 340                  | 240                  | 160                  | 220                  | 210                  | 130                  | 80                   | 130                    | 30                     | 10                 |
| E4X          | 2,630                | 96,471                | 80            | 120                | 200                  | 300                  | 280                  | 220                  | 220                  | 280                  | 210                  | 170                  | 110                  | 90                   | 130                  | 80                   | 50                   | 30                   | 40                     | 20                     | 10                 |
| E4Y          | 2,730                | 91,625                | 130           | 160                | 220                  | 370                  | 350                  | 250                  | 180                  | 230                  | 170                  | 160                  | 120                  | 100                  | 110                  | 80                   | 50                   | 20                   | 40                     | 20                     | 10                 |
| E4Z          | 4,640                | 175,888               | 280           | 260                | 300                  | 430                  | 510                  | 400                  | 350                  | 360                  | 340                  | 260                  | 230                  | 180                  | 230                  | 190                  | 110                  | 80                   | 100                    | 30                     | 10                 |
| ESA          | 1,450                | 52,171                | 80            | 110                | 130                  | 160                  | 140                  | 130                  | 100                  | 100                  | 70                   | 70                   | 50                   | 60                   | 70                   | 50                   | 30                   | 30                   | 30                     | 10                     | 10                 |
| ESB          | 2,610                | 133,243               | 110           | 100                | 130                  | 190                  | 240                  | 220                  | 190                  | 170                  | 170                  | 150                  | 120                  | 100                  | 170                  | 130                  | 120                  | 80                   | 170                    | 50                     | 20                 |
| ESC          | 3,480                | 151,120               | 140           | 180                | 220                  | 250                  | 360                  | 280                  | 300                  | 290                  | 250                  | 200                  | 160                  | 130                  | 190                  | 130                  | 100                  | 90                   | 170                    | 30                     | 20                 |
| ESE          |                      |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| ESG          | 2,060                | 111,544               | 100           | 90                 | 120                  | 160                  | 210                  | 160                  | 130                  | 120                  | 120                  | 110                  | 70                   | 60                   | 120                  | 110                  | 80                   | 70                   | 160                    | 60                     | 20                 |
| ESH          | 2,380                | 95,001                | 100           | 120                | 150                  | 210                  | 260                  | 210                  | 210                  | 190                  | 200                  | 140                  | 100                  | 80                   | 130                  | 90                   | 60                   | 40                   | 90                     | 20                     | 10                 |
| ESJ          | 1,590                | 78,279                | 70            | 70                 | 80                   | 100                  | 140                  | 120                  | 110                  | 120                  | 90                   | 100                  | 70                   | 90                   | 120                  | 80                   | 70                   | 30                   | 110                    | 20                     | 10                 |
| ESK          | 5,770                | 297,949               | 260           | 220                | 250                  | 350                  | 450                  | 390                  | 360                  | 370                  | 390                  | 350                  | 310                  | 250                  | 460                  | 330                  | 290                  | 200                  | 380                    | 130                    | 30                 |
| ESL          | 2,320                | 88,910                | 130           | 120                | 170                  | 190                  | 230                  | 180                  | 210                  | 190                  | 170                  | 160                  | 110                  | 80                   | 160                  | 90                   | 40                   | 30                   | 50                     | 20                     | 10                 |
| ESM          | 1,690                | 71,918                | 100           | 80                 | 110                  | 160                  | 170                  | 140                  | 120                  | 110                  | 110</                |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA   | Total   | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-------|---------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| E7J   | 1,580   | 59,749                | 90            | 80                 | 100                  | 150                  | 190                  | 130                  | 120                  | 140                  | 110                  | 90                   | 70                   | 80                   | 100                  | 40                   | 30                   | 20                   | 40                     | 10                     |                    |
| E7K   | 1,920   | 73,368                | 110           | 120                | 140                  | 150                  | 230                  | 170                  | 150                  | 140                  | 150                  | 110                  | 110                  | 60                   | 80                   | 60                   | 60                   | 30                   | 40                     | 20                     | 10                 |
| E7L   | 4,280   | 188,333               | 260           | 240                | 310                  | 340                  | 470                  | 340                  | 300                  | 300                  | 290                  | 230                  | 200                  | 180                  | 260                  | 170                  | 120                  | 90                   | 130                    | 50                     | 30                 |
| E7M   | 8,340   | 379,142               | 530           | 430                | 510                  | 670                  | 860                  | 670                  | 630                  | 570                  | 570                  | 490                  | 360                  | 330                  | 470                  | 350                  | 280                  | 170                  | 270                    | 110                    | 60                 |
| E7N   | 2,470   | 106,688               | 140           | 140                | 170                  | 220                  | 230                  | 200                  | 190                  | 190                  | 180                  | 140                  | 110                  | 90                   | 120                  | 90                   | 80                   | 50                   | 90                     | 30                     | 10                 |
| E7P   | 2,860   | 115,968               | 150           | 190                | 200                  | 270                  | 280                  | 220                  | 200                  | 200                  | 190                  | 170                  | 150                  | 100                  | 190                  | 110                  | 80                   | 40                   | 70                     | 20                     | 20                 |
| E8A   | 3,130   | 124,838               | 100           | 140                | 220                  | 280                  | 370                  | 280                  | 230                  | 230                  | 260                  | 190                  | 190                  | 130                  | 180                  | 110                  | 90                   | 50                   | 60                     | 20                     | 10                 |
| E8B   | 2,030   | 74,557                | 60            | 110                | 130                  | 200                  | 270                  | 180                  | 180                  | 180                  | 130                  | 150                  | 80                   | 90                   | 80                   | 30                   | 20                   | 20                   | 10                     |                        |                    |
| E8C   | 2,950   | 103,530               | 230           | 190                | 170                  | 280                  | 390                  | 260                  | 220                  | 260                  | 200                  | 170                  | 120                  | 100                  | 120                  | 70                   | 30                   | 60                   | 20                     | 10                     |                    |
| E8E   | 4,440   | 187,593               | 160           | 200                | 250                  | 310                  | 490                  | 410                  | 340                  | 370                  | 360                  | 300                  | 240                  | 180                  | 250                  | 190                  | 150                  | 90                   | 130                    | 40                     | 10                 |
| E8G   | 2,310   | 75,912                | 120           | 190                | 210                  | 330                  | 260                  | 210                  | 200                  | 170                  | 150                  | 90                   | 90                   | 50                   | 70                   | 50                   | 40                   | 20                   | 40                     | 20                     |                    |
| E8J   | 4,890   | 195,518               | 190           | 240                | 320                  | 470                  | 560                  | 440                  | 390                  | 390                  | 360                  | 300                  | 230                  | 180                  | 240                  | 210                  | 140                  | 70                   | 100                    | 50                     | 20                 |
| E8K   | 7,500   | 320,372               | 280           | 360                | 450                  | 720                  | 780                  | 630                  | 560                  | 600                  | 550                  | 440                  | 340                  | 280                  | 430                  | 320                  | 240                  | 140                  | 290                    | 70                     | 30                 |
| E8L   | 2,090   | 71,852                | 90            | 110                | 190                  | 260                  | 230                  | 180                  | 190                  | 180                  | 180                  | 110                  | 90                   | 60                   | 90                   | 50                   | 50                   | 20                   | 30                     | 10                     |                    |
| E8M   | 1,810   | 66,248                | 90            | 100                | 130                  | 210                  | 240                  | 150                  | 170                  | 160                  | 120                  | 90                   | 70                   | 50                   | 70                   | 50                   | 40                   | 30                   | 40                     | 10                     | 10                 |
| E8N   | 2,150   | 73,479                | 80            | 120                | 160                  | 280                  | 310                  | 200                  | 180                  | 190                  | 160                  | 90                   | 80                   | 50                   | 90                   | 70                   | 40                   | 20                   | 40                     | 10                     |                    |
| E8P   | 3,070   | 113,139               | 90            | 170                | 220                  | 410                  | 330                  | 250                  | 260                  | 310                  | 210                  | 190                  | 100                  | 110                  | 130                  | 90                   | 60                   | 40                   | 80                     | 20                     |                    |
| E8R   | 2,900   | 95,331                | 110           | 190                | 260                  | 390                  | 350                  | 250                  | 290                  | 290                  | 230                  | 130                  | 90                   | 70                   | 100                  | 60                   | 40                   | 30                   | 40                     | 10                     |                    |
| E8S   | 4,100   | 169,003               | 120           | 230                | 280                  | 450                  | 430                  | 300                  | 340                  | 420                  | 290                  | 240                  | 170                  | 120                  | 200                  | 170                  | 110                  | 60                   | 120                    | 50                     | 20                 |
| E8T   | 5,150   | 200,668               | 150           | 240                | 340                  | 700                  | 540                  | 370                  | 450                  | 600                  | 400                  | 250                  | 180                  | 150                  | 210                  | 150                  | 140                  | 70                   | 130                    | 50                     | 20                 |
| E9A   | 2,020   | 84,092                | 40            | 90                 | 150                  | 230                  | 170                  | 130                  | 160                  | 210                  | 190                  | 150                  | 90                   | 70                   | 120                  | 70                   | 50                   | 30                   | 50                     | 20                     | 10                 |
| E9B   | 1,940   | 71,452                | 80            | 120                | 160                  | 220                  | 190                  | 180                  | 150                  | 150                  | 110                  | 120                  | 70                   | 90                   | 120                  | 60                   | 60                   | 30                   | 40                     |                        |                    |
| E9C   | 1,860   | 67,026                | 100           | 110                | 170                  | 220                  | 250                  | 140                  | 140                  | 110                  | 100                  | 80                   | 70                   | 70                   | 120                  | 70                   | 50                   | 30                   | 40                     | 10                     |                    |
| E9E   | 3,170   | 118,076               | 250           | 160                | 220                  | 300                  | 360                  | 270                  | 250                  | 210                  | 180                  | 180                  | 150                  | 110                  | 160                  | 110                  | 100                  | 60                   | 80                     | 20                     | 10                 |
| E9G   | 4,440   | 133,912               | 580           | 280                | 380                  | 530                  | 450                  | 310                  | 340                  | 390                  | 280                  | 220                  | 120                  | 100                  | 160                  | 100                  | 80                   | 50                   | 60                     | 10                     |                    |
| E9H   | 2,700   | 87,255                | 100           | 170                | 250                  | 340                  | 300                  | 230                  | 250                  | 330                  | 210                  | 140                  | 100                  | 60                   | 90                   | 50                   | 30                   | 20                   | 30                     | 10                     |                    |
| TOTAL | 628,600 | 28,288,114            | 30,760        | 30,670             | 36,220               | 50,890               | 61,640               | 49,780               | 46,940               | 46,690               | 42,230               | 36,610               | 29,030               | 24,060               | 38,820               | 28,820               | 22,210               | 14,580               | 26,420                 | 8,900                  | 3,320              |

Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total         | Total Income (\$000) | Under \$5,000 | \$5,000    | \$10,000    | \$15,000    | \$20,000    | \$25,000    | \$30,000    | \$35,000    | \$40,000    | \$45,000    | \$50,000    | \$55,000    | \$60,000    | \$70,000    | \$80,000    | \$90,000    | \$100,000    | \$150,000    | \$250,000 |  |
|--------------|---------------|----------------------|---------------|------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|--------------|--------------|-----------|--|
|              |               |                      |               | to \$9,999 | to \$14,999 | to \$19,999 | to \$24,999 | to \$29,999 | to \$34,999 | to \$39,999 | to \$44,999 | to \$49,999 | to \$54,999 | to \$59,999 | to \$69,999 | to \$79,999 | to \$89,999 | to \$99,999 | to \$149,999 | to \$249,999 | and over  |  |
| <b>PR 24</b> | <b>Quebec</b> |                      |               |            |             |             |             |             |             |             |             |             |             |             |             |             |             |             |              |              |           |  |
| GOA          | 67,290        | 3,444,018            | 2,550         | 1,950      | 3,460       | 5,020       | 5,800       | 4,250       | 4,250       | 4,570       | 4,420       | 4,330       | 3,720       | 3,240       | 5,130       | 4,130       | 3,000       | 2,030       | 3,830        | 1,110        | 510       |  |
| GOC          | 40,840        | 1,618,508            | 2,170         | 1,780      | 3,460       | 4,450       | 4,200       | 2,960       | 3,190       | 3,140       | 2,740       | 2,470       | 1,910       | 1,490       | 2,030       | 1,400       | 1,110       | 680         | 1,160        | 330          | 170       |  |
| GOE          | 4,090         | 148,938              | 150           | 220        | 380         | 500         | 500         | 320         | 300         | 300         | 260         | 260         | 190         | 140         | 170         | 110         | 80          | 50          | 110          | 30           |           |  |
| GOG          | 13,780        | 690,911              | 1,890         | 560        | 800         | 920         | 850         | 680         | 730         | 790         | 740         | 640         | 580         | 500         | 760         | 560         | 420         | 380         | 1,340        | 620          | 30        |  |
| GOH          | 8,290         | 317,043              | 1,120         | 400        | 640         | 770         | 750         | 520         | 510         | 490         | 480         | 430         | 300         | 260         | 390         | 320         | 230         | 180         | 430          | 80           | 10        |  |
| GOJ          | 24,260        | 887,224              | 1,060         | 1,140      | 2,220       | 3,110       | 2,800       | 1,890       | 1,780       | 1,760       | 1,530       | 1,390       | 1,070       | 840         | 1,310       | 820         | 580         | 280         | 510          | 140          | 30        |  |
| GOK          | 9,630         | 406,655              | 350           | 350        | 730         | 950         | 910         | 650         | 720         | 710         | 690         | 650         | 510         | 430         | 670         | 420         | 310         | 180         | 290          | 70           | 30        |  |
| GOL          | 50,130        | 2,048,943            | 1,830         | 1,930      | 4,030       | 5,260       | 5,420       | 3,810       | 3,710       | 3,630       | 3,530       | 3,310       | 2,600       | 2,050       | 2,920       | 1,900       | 1,390       | 820         | 1,460        | 370          | 180       |  |
| GOM          | 28,210        | 1,171,188            | 1,020         | 960        | 2,100       | 2,750       | 2,980       | 2,160       | 2,050       | 2,100       | 2,070       | 1,920       | 1,560       | 1,360       | 1,810       | 1,210       | 760         | 410         | 660          | 230          | 110       |  |
| GON          | 16,360        | 675,245              | 610           | 610        | 1,340       | 1,720       | 1,810       | 1,200       | 1,120       | 1,160       | 1,100       | 1,100       | 900         | 740         | 970         | 650         | 420         | 260         | 420          | 170          | 60        |  |
| GOP          | 5,520         | 225,071              | 240           | 200        | 450         | 590         | 570         | 450         | 410         | 400         | 370         | 360         | 260         | 230         | 320         | 190         | 150         | 80          | 160          | 50           | 30        |  |
| GOR          | 70,020        | 2,971,770            | 2,520         | 2,430      | 5,040       | 6,730       | 7,420       | 5,140       | 4,850       | 4,870       | 4,820       | 4,830       | 4,090       | 3,340       | 4,820       | 2,980       | 2,150       | 1,210       | 1,970        | 560          | 270       |  |
| GOS          | 56,920        | 2,568,070            | 1,850         | 1,740      | 3,530       | 4,810       | 5,270       | 4,070       | 3,740       | 4,240       | 4,160       | 4,190       | 3,340       | 2,830       | 4,310       | 3,000       | 2,070       | 1,100       | 1,910        | 560          | 220       |  |
| GOT          | 11,860        | 486,089              | 530           | 500        | 910         | 1,180       | 1,270       | 950         | 910         | 780         | 760         | 650         | 600         | 470         | 710         | 470         | 390         | 240         | 450          | 100          | 20        |  |
| GOV          | 14,910        | 691,921              | 620           | 600        | 980         | 1,160       | 1,330       | 1,060       | 990         | 960         | 940         | 930         | 790         | 680         | 1,170       | 820         | 560         | 320         | 780          | 190          | 50        |  |
| GOW          | 28,320        | 1,090,381            | 3,800         | 1,320      | 2,270       | 2,540       | 2,510       | 1,730       | 1,690       | 1,690       | 1,550       | 1,480       | 1,200       | 950         | 1,610       | 1,160       | 840         | 490         | 1,170        | 270          | 70        |  |
| GOX          | 48,980        | 2,095,072            | 2,380         | 1,850      | 3,500       | 4,580       | 5,160       | 3,670       | 3,420       | 3,400       | 3,190       | 3,100       | 2,540       | 2,010       | 3,070       | 2,100       | 1,520       | 1,010       | 1,780        | 520          | 190       |  |
| GOY          | 7,810         | 309,656              | 330           | 290        | 620         | 850         | 820         | 640         | 540         | 630         | 560         | 530         | 420         | 300         | 450         | 280         | 180         | 100         | 190          | 70           | 20        |  |
| G0Z          | 7,270         | 287,172              | 370           | 310        | 580         | 720         | 760         | 530         | 550         | 530         | 530         | 530         | 360         | 280         | 420         | 260         | 180         | 110         | 170          | 50           | 20        |  |
| G1A          |               |                      |               |            |             |             |             |             |             |             |             |             |             |             |             |             |             |             |              |              |           |  |
| G1B          | 13,490        | 715,804              | 420           | 330        | 590         | 740         | 870         | 720         | 810         | 920         | 950         | 970         | 890         | 750         | 1,230       | 920         | 790         | 530         | 850          | 160          | 60        |  |
| G1C          | 30,480        | 1,591,846            | 810           | 760        | 1,380       | 2,040       | 2,340       | 1,960       | 1,950       | 2,220       | 2,140       | 2,250       | 1,770       | 1,630       | 2,430       | 1,890       | 1,510       | 1,030       | 1,750        | 440          | 190       |  |
| G1E          | 22,710        | 1,018,289            | 600           | 720        | 1,330       | 1,860       | 2,270       | 1,710       | 1,750       | 1,870       | 1,620       | 1,630       | 1,270       | 1,020       | 1,610       | 1,090       | 790         | 510         | 740          | 230          | 90        |  |
| G1G          | 20,160        | 1,029,367            | 580           | 570        | 950         | 1,230       | 1,540       | 1,360       | 1,490       | 1,480       | 1,480       | 1,490       | 1,240       | 1,010       | 1,610       | 1,290       | 980         | 670         | 1,030        | 260          | 110       |  |
| G1H          | 25,040        | 1,125,519            | 690           | 720        | 1,330       | 1,820       | 2,370       | 1,980       | 2,010       | 2,100       | 1,950       | 1,770       | 1,470       | 1,240       | 1,790       | 1,160       | 930         | 580         | 810          | 230          | 70        |  |
| G1J          | 18,410        | 715,728              | 690           | 890        | 1,390       | 1,740       | 1,950       | 1,610       | 1,560       | 1,490       | 1,290       | 1,120       | 910         | 710         | 1,010       | 710         | 510         | 300         | 460          | 80           | 20        |  |
| G1K          | 14,860        | 649,401              | 590           | 800        | 1,180       | 1,410       | 1,300       | 1,110       | 1,050       | 990         | 950         | 850         | 710         | 630         | 930         | 630         | 520         | 330         | 610          | 180          | 80        |  |
| G1L          | 17,550        | 703,857              | 570           | 790        | 1,260       | 1,690       | 1,800       | 1,500       | 1,450       | 1,400       | 1,290       | 1,090       | 870         | 670         | 1,030       | 730         | 560         | 290         | 430          | 100          | 30        |  |
| G1M          | 16,490        | 712,116              | 540           | 620        | 1,000       | 1,470       | 1,840       | 1,300       | 1,260       | 1,250       | 1,170       | 1,120       | 860         | 720         | 1,050       | 710         | 510         | 350         | 550          | 130          | 50        |  |
| G1N          | 6,640         | 257,005              | 240           | 280        | 490         | 700         | 670         | 580         | 590         | 550         | 450         | 430         | 340         | 250         | 360         | 260         | 160         | 100         | 150          | 30           | 10        |  |
| G1P          | 13,380        | 593,416              | 450           | 420        | 670         | 930         | 1,180       | 1,020       | 1,030       | 1,110       | 1,040       | 1,000       | 820         | 720         | 1,030       | 660         | 490         | 280         | 430          | 90           | 30        |  |
| G1R          | 13,290        | 794,708              | 500           | 480        | 690         | 940         | 1,050       | 870         | 840         | 860         | 750         | 820         | 660         | 580         | 990         | 770         | 670         | 420         | 850          | 350          | 220       |  |
| G1S          | 21,460        | 1,420,528            | 780           | 600        | 890         | 1,370       | 1,610       | 1,190       | 1,100       | 1,130       | 1,210       | 1,230       | 1,080       | 1,000       | 1,640       | 1,460       | 1,120       | 870         | 1,830        | 850          | 500       |  |
| G1T          | 5,800         | 625,251              | 260           | 190        | 220         | 290         | 280         | 230         | 200         | 210         | 200         | 250         | 210         | 210         | 370         | 380         | 320         | 270         | 720          | 540          | 480       |  |
| G1V          | 17,450        | 935,952              | 1,250         | 780        | 920         | 1,300       | 1,500       | 1,120       | 1,080       | 1,050       | 960         | 970         | 900         | 770         | 1,180       | 880         | 620         | 490         | 940          | 450          | 310       |  |
| G1W          | 18,070        | 1,154,090            | 740           | 580        | 750         | 960         | 1,120       | 1,000       | 940         | 1,100       | 1,030       | 1,160       | 930         | 890         | 1,230       | 950         | 750         | 1,560       | 640          | 350          | 20        |  |
| G1X          | 21,680        | 1,266,649            | 830           | 720        | 950         | 1,200       | 1,670       | 1,360       | 1,270       | 1,310       | 1,320       | 1,490       | 1,200       | 1,120       | 1,690       | 1,230       | 1,030       | 830         | 1,510        | 620          | 330       |  |
| G1Y          | 10,790        | 794,256              | 330           | 270        | 390         | 500         | 520         | 450         | 440         | 480         | 520         | 700         | 590         | 540         | 950         | 800         | 740         | 590         | 1,270        | 470          | 260       |  |
| G2A          | 12,490        | 677,309              | 410           | 350        | 570         | 750         | 850         | 750         | 720         | 780         | 810         | 870         | 740         | 640         | 1,080       | 890         | 660         | 490         | 830          | 230          | 80        |  |
| G2B          | 20,160        | 1,024,380            | 620           | 590        | 1,070       | 1,300       | 1,610       | 1,320       | 1,270       | 1,400       | 1,360       | 1,440       | 1,160       | 1,030       | 1,650       | 1,270       | 930         | 630         | 1,120        | 310          | 100       |  |
| G2C          | 10,140        | 571,545              | 260           | 230        | 400         | 540         | 730         | 550         | 600         | 630         | 700         | 680         | 590         | 540         | 880         | 670         | 650         | 440         | 800          | 200          | 60        |  |
| G2E          | 17,650        | 947,003              | 480           | 500        | 800         | 1,020       | 1,320       | 1,130       | 1,100       | 1,180       | 1,160       | 1,260       | 1,070       | 940         | 1,450       | 1,160       | 910         | 630         | 1,130        | 310          | 110       |  |
| G2G          | 9,010         | 506,993              | 270           | 250        | 410         | 490         | 570         | 500         | 490         | 620         | 580         | 620         | 580         | 480         | 780         | 630         | 480         | 360         | 710          | 180          | 60        |  |
| G2J          | 2,730         | 170,836              | 50            | 60         | 90          | 130         | 240         | 180         | 200         | 200         | 200         | 220         | 190         | 160         | 240         | 170         | 110         | 80          | 130          | 50           | 40        |  |
| G2K          | 10,650        | 673,985              | 260           | 200        | 350         | 430         | 590         | 630         | 580         | 670         | 690         | 800         | 640         | 620         | 960         | 820         | 650         | 420         | 890          | 300          | 170       |  |
| G2L          | 11,950        | 676,545              | 340           | 320        | 480         | 660         | 820         | 700         | 650         | 830         | 750         | 880         | 690         | 620         | 1,030       | 770         | 720         | 430         | 910          | 250          | 100       |  |
| G2M          | 4,320         | 246,992              | 110           | 110        | 170         | 220         | 250         | 240         | 250         | 290         | 280         | 290         | 240         | 390         | 300         | 250         | 230         | 350         | 100          | 20           | 20        |  |
| G2N          | 6,520         | 342,499              | 200           | 170        | 270         | 360         | 400         | 390         | 400         | 450         | 480         | 470         | 390         | 330         | 650         | 500         | 370         | 220         | 390          | 80           | 30        |  |
| G3A          | 16,840        | 1,214,089            | 500           | 480        | 670         | 850         | 940         | 820         | 750         | 850         | 860         | 1,060       | 880         | 810         | 1,410       | 1,180       | 1,040       | 780         | 1,790        | 740          | 430       |  |
| G3B          | 6,540         | 525,117              | 240           | 190        | 220         | 290         | 330         | 310         | 250         | 270         | 320         | 330         | 290         | 280         | 530         | 460         | 410         | 340         | 820          | 410          | 240       |  |
| G3C          | 7,690         | 476,310              | 280           | 200        | 310         | 400         | 460         | 380         | 400         | 440         | 450         | 470         | 440         | 390         | 650         | 590         | 510         | 340         | 670          | 220          | 80        |  |
| G3E          | 12,500        | 684,638              | 390           | 330        | 480         | 660         | 840         | 640         | 690         | 770         | 760         | 840         | 780         | 710         | 1,160       | 980         | 830         | 530         | 870          | 190          | 40        |  |
| G3G          | 7,970         | 392,757              | 220           | 210        | 350         | 450         | 590         | 590         | 590         | 620         | 600         | 600         | 500         | 430         | 570         | 570         | 390         | 240         | 350          | 60           | 20        |  |
| G3H          | 7,900         | 398,023              | 260           | 210        | 420         | 530         | 630         | 480         | 510         | 530         | 570         | 530         | 460         | 430         | 700         | 530         | 360         | 240         | 410          | 80           | 30        |  |
| G3J          | 8,140         | 418,669              | 250           | 200        | 340         | 480         | 550         | 460         | 450         | 580         | 560         | 550         | 520         | 460         | 810         | 700         | 430         | 260         | 440          | 80           | 20        |  |
| G3K          | 15,040        | 805,471              | 460           | 440        | 620         | 780         | 900         | 830         | 870         | 890         | 980         | 980         | 920         | 850         | 1,570       | 1,230       | 970         | 640         | 920          | 170          | 40        |  |
| G3L          | 9,040         | 411,702              | 270           | 290        | 570         | 790         | 960         | 630         | 590         | 630         | 650         | 600         | 490         | 450         | 690         | 520         | 280         | 190         | 340          | 80           | 30        |  |
| G3M          | 5,770         | 260,132              | 170           | 180        | 340         | 430         | 660         | 440         | 420         | 450         | 380         | 390         | 320         | 260         | 360         | 340         | 230         | 140         | 280          | 60           | 10        |  |
| G3N          | 8,180         | 481,673              | 240           | 230        | 340         | 410         | 460         | 460         | 430         | 480         | 530         | 480         | 470         | 460         | 840         | 760         | 520         | 330         | 530          | 170          | 80        |  |
| G3S          | 4,450         | 266,354              | 160           | 100        | 140         | 210         | 220         | 190         | 170         | 210         | 210         |             |             |             |             |             |             |             |              |              |           |  |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total  | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-----|--------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| G6C | 6,240  | 326,123               | 180           | 160                | 310                  | 390                  | 410                  | 350                  | 340                  | 440                  | 470                  | 490                  | 400                  | 350                  | 530                  | 410                  | 320                  | 210                  | 350                    | 110                    | 30                 |
| G6E | 10,850 | 536,981               | 280           | 320                | 610                  | 830                  | 1,040                | 750                  | 720                  | 720                  | 710                  | 740                  | 670                  | 580                  | 810                  | 660                  | 450                  | 270                  | 460                    | 170                    | 80                 |
| G6G | 16,960 | 706,595               | 550           | 630                | 1,270                | 1,670                | 2,140                | 1,410                | 1,270                | 1,260                | 1,120                | 1,030                | 860                  | 740                  | 960                  | 630                  | 470                  | 280                  | 450                    | 150                    | 80                 |
| G6H | 5,990  | 237,073               | 190           | 190                | 430                  | 590                  | 730                  | 550                  | 470                  | 420                  | 430                  | 400                  | 330                  | 270                  | 350                  | 220                  | 170                  | 90                   | 140                    | 30                     | 10                 |
| G6J | 8,510  | 452,380               | 300           | 230                | 380                  | 460                  | 580                  | 480                  | 520                  | 520                  | 550                  | 610                  | 520                  | 490                  | 770                  | 610                  | 460                  | 330                  | 560                    | 120                    | 40                 |
| G6K | 6,560  | 400,779               | 210           | 170                | 280                  | 360                  | 400                  | 360                  | 310                  | 360                  | 360                  | 380                  | 350                  | 340                  | 580                  | 480                  | 470                  | 310                  | 580                    | 190                    | 80                 |
| G6L | 12,740 | 513,697               | 400           | 440                | 970                  | 1,310                | 1,430                | 970                  | 950                  | 980                  | 930                  | 900                  | 750                  | 580                  | 760                  | 470                  | 320                  | 180                  | 270                    | 70                     | 50                 |
| G6P | 24,900 | 1,003,356             | 700           | 940                | 2,050                | 2,820                | 3,330                | 2,060                | 1,940                | 1,850                | 1,670                | 1,490                | 1,120                | 970                  | 1,260                | 910                  | 590                  | 320                  | 570                    | 220                    | 120                |
| G6R | 3,710  | 182,258               | 120           | 120                | 220                  | 310                  | 300                  | 250                  | 250                  | 230                  | 250                  | 240                  | 200                  | 190                  | 270                  | 210                  | 160                  | 100                  | 210                    | 50                     | 20                 |
| G6S | 4,370  | 207,145               | 120           | 130                | 270                  | 350                  | 440                  | 340                  | 310                  | 310                  | 310                  | 280                  | 240                  | 200                  | 290                  | 210                  | 180                  | 80                   | 210                    | 60                     | 30                 |
| G6T | 8,750  | 450,799               | 270           | 240                | 460                  | 580                  | 670                  | 550                  | 560                  | 600                  | 610                  | 650                  | 520                  | 440                  | 750                  | 560                  | 410                  | 220                  | 470                    | 150                    | 60                 |
| G6V | 27,350 | 1,325,005             | 720           | 850                | 1,540                | 2,080                | 2,780                | 2,030                | 1,940                | 2,010                | 1,860                | 1,970                | 1,560                | 1,320                | 1,920                | 1,340                | 1,040                | 700                  | 1,100                  | 390                    | 200                |
| G6W | 20,660 | 1,108,582             | 570           | 530                | 960                  | 1,320                | 1,610                | 1,330                | 1,280                | 1,520                | 1,390                | 1,430                | 1,190                | 1,090                | 1,690                | 1,250                | 1,020                | 670                  | 1,280                  | 400                    | 150                |
| G6X | 7,680  | 382,096               | 190           | 190                | 360                  | 460                  | 670                  | 510                  | 530                  | 640                  | 590                  | 570                  | 490                  | 420                  | 650                  | 460                  | 290                  | 230                  | 320                    | 100                    | 20                 |
| G6Y | 5,300  | 338,303               | 160           | 140                | 220                  | 320                  | 340                  | 260                  | 280                  | 270                  | 310                  | 330                  | 290                  | 270                  | 460                  | 380                  | 330                  | 230                  | 470                    | 190                    | 70                 |
| G6Z | 19,280 | 1,127,535             | 570           | 510                | 740                  | 1,020                | 1,230                | 1,040                | 1,050                | 1,130                | 1,190                | 1,320                | 1,180                | 1,080                | 1,700                | 1,350                | 1,200                | 830                  | 1,520                  | 460                    | 170                |
| G7A | 19,600 | 1,259,673             | 620           | 490                | 770                  | 1,030                | 1,210                | 990                  | 950                  | 1,060                | 1,080                | 1,260                | 1,080                | 1,000                | 1,590                | 1,400                | 1,270                | 920                  | 1,940                  | 660                    | 300                |
| G7B | 14,690 | 674,734               | 520           | 540                | 960                  | 1,160                | 1,390                | 1,030                | 1,050                | 1,080                | 980                  | 930                  | 790                  | 610                  | 1,060                | 740                  | 510                  | 330                  | 790                    | 180                    | 40                 |
| G7G | 13,640 | 654,253               | 490           | 490                | 830                  | 980                  | 1,210                | 990                  | 940                  | 990                  | 930                  | 900                  | 790                  | 620                  | 960                  | 630                  | 540                  | 340                  | 740                    | 180                    | 80                 |
| G7H | 23,880 | 1,216,760             | 880           | 870                | 1,450                | 2,080                | 2,450                | 1,640                | 1,540                | 1,560                | 1,440                | 1,550                | 1,150                | 980                  | 1,540                | 1,080                | 900                  | 590                  | 1,350                  | 550                    | 290                |
| G7J | 12,140 | 579,286               | 420           | 510                | 800                  | 1,010                | 1,050                | 890                  | 850                  | 870                  | 800                  | 770                  | 640                  | 540                  | 810                  | 560                  | 470                  | 250                  | 620                    | 200                    | 80                 |
| G7K | 620    | 28,507                | 20            | 20                 | 30                   | 40                   | 50                   | 40                   | 50                   | 50                   | 50                   | 50                   | 50                   | 40                   | 40                   | 20                   | 20                   | 20                   | 30                     | 10                     | 0                  |
| G7N | 5,140  | 295,942               | 210           | 140                | 230                  | 290                  | 340                  | 270                  | 310                  | 330                  | 320                  | 330                  | 290                  | 240                  | 450                  | 340                  | 280                  | 170                  | 450                    | 120                    | 40                 |
| G7P | 6,000  | 296,118               | 270           | 210                | 340                  | 430                  | 500                  | 380                  | 380                  | 410                  | 380                  | 380                  | 340                  | 310                  | 470                  | 290                  | 220                  | 150                  | 430                    | 80                     | 30                 |
| G7S | 16,000 | 850,896               | 510           | 490                | 750                  | 1,050                | 1,170                | 1,010                | 980                  | 1,030                | 1,010                | 1,130                | 1,000                | 860                  | 1,220                | 920                  | 820                  | 450                  | 1,180                  | 330                    | 100                |
| G7T | 1,150  | 69,082                | 30            | 20                 | 40                   | 70                   | 50                   | 60                   | 60                   | 50                   | 60                   | 80                   | 80                   | 70                   | 110                  | 80                   | 70                   | 50                   | 140                    | 30                     | 0                  |
| G7X | 21,380 | 912,554               | 770           | 940                | 1,500                | 1,980                | 2,200                | 1,690                | 1,630                | 1,560                | 1,410                | 1,410                | 1,140                | 920                  | 1,340                | 790                  | 620                  | 350                  | 850                    | 220                    | 80                 |
| G7Y | 570    | 27,206                | 20            | 20                 | 30                   | 40                   | 50                   | 30                   | 30                   | 40                   | 40                   | 30                   | 40                   | 50                   | 50                   | 20                   | 20                   | 10                   | 30                     | 0                      | 0                  |
| G7Z | 2,260  | 120,007               | 80            | 70                 | 120                  | 130                  | 170                  | 160                  | 130                  | 140                  | 150                  | 170                  | 130                  | 120                  | 190                  | 120                  | 100                  | 60                   | 190                    | 40                     | 10                 |
| G8A | 5,010  | 228,928               | 180           | 180                | 290                  | 400                  | 510                  | 370                  | 350                  | 380                  | 350                  | 320                  | 270                  | 230                  | 320                  | 220                  | 190                  | 110                  | 270                    | 60                     | 10                 |
| G8B | 18,620 | 821,710               | 610           | 740                | 1,370                | 1,720                | 1,940                | 1,420                | 1,350                | 1,310                | 1,250                | 1,210                | 940                  | 780                  | 1,130                | 760                  | 620                  | 350                  | 850                    | 200                    | 80                 |
| G8C | 3,620  | 208,065               | 120           | 120                | 200                  | 230                  | 230                  | 170                  | 170                  | 210                  | 200                  | 240                  | 220                  | 180                  | 310                  | 190                  | 230                  | 150                  | 340                    | 80                     | 30                 |
| G8E | 3,150  | 150,352               | 130           | 120                | 180                  | 260                  | 290                  | 230                  | 230                  | 220                  | 230                  | 190                  | 170                  | 140                  | 200                  | 140                  | 110                  | 70                   | 190                    | 40                     | 20                 |
| G8G | 3,280  | 143,294               | 120           | 120                | 230                  | 270                  | 330                  | 230                  | 230                  | 230                  | 200                  | 250                  | 180                  | 150                  | 210                  | 140                  | 110                  | 50                   | 160                    | 30                     | 10                 |
| G8H | 8,320  | 356,587               | 330           | 340                | 650                  | 750                  | 910                  | 620                  | 570                  | 670                  | 550                  | 510                  | 410                  | 340                  | 460                  | 370                  | 260                  | 180                  | 270                    | 90                     | 40                 |
| G8J | 3,390  | 147,661               | 170           | 140                | 240                  | 310                  | 330                  | 240                  | 240                  | 210                  | 210                  | 200                  | 170                  | 150                  | 240                  | 180                  | 120                  | 60                   | 130                    | 40                     | 10                 |
| G8K | 8,490  | 387,963               | 290           | 370                | 610                  | 770                  | 900                  | 570                  | 540                  | 550                  | 510                  | 490                  | 420                  | 400                  | 570                  | 440                  | 360                  | 230                  | 360                    | 80                     | 50                 |
| G8L | 12,160 | 518,261               | 470           | 500                | 960                  | 1,280                | 1,380                | 910                  | 830                  | 870                  | 710                  | 690                  | 550                  | 440                  | 690                  | 550                  | 480                  | 250                  | 420                    | 140                    | 60                 |
| G8M | 4,300  | 190,104               | 170           | 170                | 320                  | 410                  | 410                  | 250                  | 290                  | 310                  | 290                  | 250                  | 210                  | 190                  | 300                  | 250                  | 150                  | 110                  | 160                    | 40                     | 20                 |
| G8N | 2,090  | 91,281                | 70            | 100                | 150                  | 190                  | 210                  | 140                  | 150                  | 150                  | 140                  | 130                  | 110                  | 80                   | 140                  | 110                  | 60                   | 40                   | 90                     | 30                     | 10                 |
| G8P | 5,860  | 324,969               | 210           | 190                | 350                  | 360                  | 520                  | 350                  | 300                  | 280                  | 290                  | 280                  | 300                  | 290                  | 540                  | 400                  | 320                  | 260                  | 460                    | 110                    | 50                 |
| G8T | 23,140 | 885,945               | 790           | 960                | 1,780                | 2,450                | 2,980                | 2,010                | 1,790                | 1,800                | 1,610                | 1,450                | 1,110                | 850                  | 1,220                | 780                  | 540                  | 300                  | 540                    | 140                    | 50                 |
| G8V | 8,150  | 429,810               | 260           | 240                | 430                  | 490                  | 600                  | 540                  | 540                  | 540                  | 540                  | 570                  | 470                  | 400                  | 620                  | 480                  | 410                  | 260                  | 560                    | 150                    | 50                 |
| G8W | 9,100  | 476,378               | 280           | 300                | 520                  | 630                  | 830                  | 600                  | 570                  | 590                  | 590                  | 650                  | 500                  | 420                  | 650                  | 460                  | 390                  | 290                  | 580                    | 180                    | 80                 |
| G8Y | 27,670 | 1,404,983             | 1,060         | 1,010              | 1,590                | 2,060                | 2,530                | 2,000                | 1,790                | 1,840                | 1,720                | 1,820                | 1,520                | 1,220                | 1,920                | 1,360                | 1,090                | 810                  | 1,560                  | 550                    | 250                |
| G8Z | 11,170 | 436,434               | 570           | 560                | 860                  | 1,110                | 1,320                | 1,010                | 910                  | 810                  | 720                  | 670                  | 520                  | 390                  | 550                  | 340                  | 250                  | 160                  | 280                    | 120                    | 50                 |
| G9A | 16,370 | 599,532               | 550           | 890                | 1,450                | 2,000                | 2,190                | 1,560                | 1,330                | 1,100                | 1,000                | 900                  | 670                  | 500                  | 730                  | 490                  | 300                  | 220                  | 340                    | 100                    | 60                 |
| G9B | 15,140 | 861,158               | 520           | 430                | 720                  | 1,010                | 1,100                | 950                  | 920                  | 990                  | 970                  | 1,010                | 810                  | 750                  | 1,180                | 870                  | 740                  | 480                  | 1,090                  | 380                    | 190                |
| G9C | 2,990  | 170,123               | 90            | 80                 | 130                  | 160                  | 200                  | 180                  | 170                  | 190                  | 160                  | 190                  | 180                  | 150                  | 260                  | 200                  | 160                  | 130                  | 270                    | 60                     | 30                 |
| G9H | 11,040 | 555,859               | 370           | 360                | 650                  | 820                  | 1,110                | 730                  | 730                  | 700                  | 720                  | 720                  | 550                  | 530                  | 810                  | 580                  | 430                  | 320                  | 650                    | 180                    | 90                 |
| G9N | 13,550 | 483,148               | 500           | 770                | 1,220                | 1,680                | 1,740                | 1,160                | 1,050                | 1,000                | 830                  | 780                  | 590                  | 470                  | 610                  | 380                  | 250                  | 150                  | 250                    | 80                     | 30                 |
| G9P | 9,940  | 433,056               | 330           | 330                | 630                  | 830                  | 1,100                | 750                  | 740                  | 760                  | 690                  | 740                  | 550                  | 470                  | 640                  | 430                  | 300                  | 190                  | 340                    | 90                     | 50                 |
| G9R | 1,870  | 94,338                | 50            | 70                 | 90                   | 140                  | 140                  | 140                  | 130                  | 120                  | 130                  | 140                  | 80                   | 100                  | 150                  | 100                  | 80                   | 70                   | 110                    | 30                     | 10                 |
| G9T | 13,440 | 546,961               | 420           | 560                | 970                  | 1,350                | 1,630                | 1,120                | 1,090                | 950                  | 940                  | 910                  | 680                  | 560                  | 730                  | 420                  | 350                  | 230                  | 350                    | 110                    | 70                 |
| G9X | 8,950  | 389,771               | 370           | 420                | 560                  | 770                  | 910                  | 660                  | 630                  | 600                  | 600                  | 580                  | 490                  | 350                  | 520                  | 440                  | 370                  | 230                  | 370                    | 70                     | 30                 |
| H0M | 1,320  | 10,103                | 830           | 100                | 120                  | 90                   | 80                   | 30                   | 20                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                     | 10                     | 0                  |
| H1A | 26,980 | 1,247,137             | 980           | 1,060              | 1,610                | 2,010                | 2,490                | 1,990                | 1,800                | 1,950                | 1,840                | 1,760                | 1,490                | 1,290                | 1,940                | 1,390                | 1,060                | 670                  | 1,230                  | 300                    | 80                 |
| H1B | 16,400 | 691,295               | 630           | 740                | 1,190                | 1,340                | 1,570                | 1,340                | 1,160                | 1,190                | 1,160                | 1,040                | 880                  | 760                  | 1,140                | 740                  | 570                  | 290                  | 540                    | 120                    | 30                 |
| H1C | 11,320 | 567,808               | 600           | 430                | 620                  | 860                  | 860                  | 790                  | 680                  | 690                  | 700                  | 640                  | 600                  | 510                  | 820                  | 640                  | 550                  | 340                  | 710                    | 210                    | 70                 |
| H1E | 35,790 | 1,548,876             | 1,610         | 1,490              | 2,420                | 3,270                | 4,000                | 3,050                | 2,600                | 2,450                | 2,270                | 2,010                | 1,670                | 1,360                | 2,120                | 1,480                | 1,180                | 810                  | 1,430                  | 430                    | 160                |
| H1G | 38,440 | 1,314,676             | 2,360         | 2,530              | 3,130                | 4,130                | 4,620                | 3,760                | 3,270                | 2,860                | 2,430                | 2,070                | 1,530                | 1,220                | 1,610                | 1,030                | 640                  | 370                  | 640                    | 180                    | 60                 |
| H1H | 29,000 | 998,464               | 1,970         |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total  | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-----|--------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| H2N | 5,270  | 199,952              | 360           | 360                | 430                  | 520                  | 580                  | 500                  | 410                  | 350                  | 300                  | 230                  | 210                  | 170                  | 250                  | 150                  | 160                  | 80                   | 160                    | 40                     | 20                 |
| H2P | 11,510 | 601,780              | 490           | 530                | 640                  | 800                  | 900                  | 800                  | 670                  | 640                  | 690                  | 600                  | 610                  | 510                  | 870                  | 700                  | 580                  | 400                  | 770                    | 240                    | 90                 |
| H2R | 18,400 | 1,025,762            | 840           | 770                | 950                  | 1,520                | 1,510                | 1,240                | 1,240                | 1,090                | 970                  | 880                  | 800                  | 770                  | 1,300                | 1,030                | 900                  | 640                  | 1,410                  | 480                    | 230                |
| H2S | 21,910 | 1,240,443            | 970           | 880                | 1,200                | 1,730                | 1,870                | 1,490                | 1,290                | 1,270                | 1,120                | 1,070                | 1,020                | 870                  | 1,490                | 1,210                | 1,130                | 810                  | 1,680                  | 630                    | 280                |
| H2T | 12,910 | 742,887              | 720           | 610                | 700                  | 1,240                | 1,130                | 910                  | 740                  | 620                  | 550                  | 590                  | 460                  | 470                  | 750                  | 630                  | 570                  | 460                  | 1,070                  | 470                    | 230                |
| H2V | 22,590 | 2,074,674            | 1,550         | 1,120              | 1,300                | 1,640                | 1,720                | 1,450                | 1,170                | 1,030                | 930                  | 810                  | 740                  | 630                  | 1,160                | 1,030                | 840                  | 700                  | 2,060                  | 1,390                  | 1,350              |
| H2W | 8,410  | 476,234              | 670           | 460                | 550                  | 730                  | 730                  | 530                  | 490                  | 410                  | 370                  | 350                  | 320                  | 260                  | 460                  | 400                  | 340                  | 230                  | 600                    | 340                    | 160                |
| H2X | 16,110 | 729,291              | 2,180         | 1,320              | 1,370                | 1,680                | 1,350                | 1,040                | 830                  | 660                  | 590                  | 520                  | 490                  | 400                  | 710                  | 630                  | 480                  | 350                  | 890                    | 390                    | 240                |
| H2Y | 3,180  | 413,129              | 190           | 120                | 180                  | 190                  | 200                  | 120                  | 100                  | 120                  | 120                  | 100                  | 90                   | 100                  | 180                  | 170                  | 140                  | 120                  | 370                    | 310                    | 270                |
| H2Z | 2,770  | 195,142              | 260           | 170                | 210                  | 290                  | 220                  | 120                  | 130                  | 110                  | 90                   | 90                   | 80                   | 80                   | 140                  | 130                  | 100                  | 100                  | 220                    | 150                    | 110                |
| H3A | 3,560  | 278,879              | 860           | 300                | 220                  | 250                  | 210                  | 140                  | 120                  | 110                  | 90                   | 80                   | 70                   | 60                   | 150                  | 120                  | 120                  | 80                   | 250                    | 200                    | 160                |
| H3B | 15,270 | 507,296              | 1,240         | 750                | 5,340                | 4,190                | 1,460                | 460                  | 260                  | 190                  | 150                  | 120                  | 90                   | 80                   | 130                  | 120                  | 90                   | 70                   | 190                    | 160                    | 210                |
| H3C | 13,640 | 1,154,877            | 1,040         | 510                | 540                  | 580                  | 630                  | 560                  | 520                  | 480                  | 460                  | 480                  | 470                  | 480                  | 980                  | 930                  | 830                  | 700                  | 1,920                  | 940                    | 580                |
| H3E | 17,310 | 1,583,821            | 1,260         | 690                | 720                  | 880                  | 1,080                | 840                  | 760                  | 680                  | 690                  | 740                  | 600                  | 550                  | 1,090                | 960                  | 780                  | 650                  | 1,950                  | 1,350                  | 1,040              |
| H3G | 8,350  | 875,952              | 1,410         | 570                | 480                  | 510                  | 550                  | 420                  | 320                  | 290                  | 240                  | 260                  | 250                  | 190                  | 400                  | 350                  | 300                  | 230                  | 610                    | 470                    | 550                |
| H3H | 16,870 | 860,496              | 2,790         | 1,330              | 1,320                | 1,660                | 1,700                | 1,170                | 850                  | 660                  | 590                  | 540                  | 470                  | 410                  | 690                  | 550                  | 450                  | 310                  | 710                    | 360                    | 330                |
| H3J | 9,080  | 568,341              | 670           | 790                | 800                  | 850                  | 780                  | 580                  | 450                  | 370                  | 310                  | 270                  | 260                  | 270                  | 400                  | 360                  | 320                  | 250                  | 650                    | 450                    | 250                |
| H3K | 11,860 | 672,758              | 610           | 750                | 930                  | 1,140                | 1,010                | 790                  | 680                  | 590                  | 520                  | 440                  | 460                  | 350                  | 650                  | 520                  | 520                  | 370                  | 950                    | 410                    | 210                |
| H3L | 16,280 | 928,469              | 950           | 860                | 1,000                | 1,250                | 1,230                | 1,090                | 1,070                | 940                  | 840                  | 780                  | 720                  | 600                  | 1,000                | 760                  | 690                  | 480                  | 1,180                  | 550                    | 300                |
| H3M | 12,500 | 553,245              | 890           | 820                | 1,010                | 1,310                | 1,310                | 1,080                | 800                  | 730                  | 620                  | 540                  | 450                  | 340                  | 560                  | 420                  | 380                  | 250                  | 590                    | 270                    | 130                |
| H3N | 24,290 | 656,837              | 2,340         | 2,670              | 2,570                | 3,340                | 3,080                | 2,450                | 1,950                | 1,430                | 1,020                | 800                  | 530                  | 410                  | 560                  | 370                  | 250                  | 160                  | 270                    | 70                     | 20                 |
| H3P | 7,900  | 878,507              | 620           | 420                | 380                  | 450                  | 470                  | 370                  | 310                  | 280                  | 240                  | 240                  | 230                  | 220                  | 360                  | 390                  | 300                  | 250                  | 830                    | 760                    | 790                |
| H3R | 7,760  | 1,025,387            | 580           | 430                | 430                  | 450                  | 470                  | 380                  | 300                  | 230                  | 270                  | 260                  | 210                  | 220                  | 330                  | 340                  | 270                  | 250                  | 780                    | 710                    | 840                |
| H3S | 25,800 | 1,073,048            | 2,580         | 2,070              | 2,190                | 2,700                | 2,570                | 2,280                | 2,010                | 1,680                | 1,240                | 1,060                | 830                  | 650                  | 950                  | 700                  | 500                  | 350                  | 740                    | 400                    | 310                |
| H3T | 9,950  | 459,368              | 1,350         | 810                | 710                  | 1,010                | 870                  | 700                  | 530                  | 470                  | 410                  | 380                  | 300                  | 260                  | 460                  | 360                  | 270                  | 190                  | 460                    | 230                    | 180                |
| H3V | 5,720  | 242,093              | 680           | 360                | 340                  | 480                  | 550                  | 420                  | 280                  | 330                  | 280                  | 250                  | 230                  | 210                  | 330                  | 260                  | 190                  | 120                  | 280                    | 100                    | 30                 |
| H3W | 24,400 | 1,028,214            | 2,060         | 1,600              | 2,000                | 2,770                | 2,430                | 2,430                | 2,030                | 1,610                | 1,240                | 960                  | 730                  | 580                  | 910                  | 630                  | 500                  | 350                  | 790                    | 460                    | 330                |
| H3X | 18,980 | 1,550,301            | 1,360         | 1,070              | 1,240                | 1,500                | 1,500                | 1,260                | 1,080                | 980                  | 880                  | 810                  | 650                  | 590                  | 940                  | 830                  | 690                  | 500                  | 1,290                  | 880                    | 950                |
| H3Y | 7,550  | 1,881,100            | 570           | 400                | 300                  | 340                  | 330                  | 270                  | 230                  | 210                  | 180                  | 160                  | 180                  | 160                  | 290                  | 260                  | 270                  | 200                  | 760                    | 850                    | 1,600              |
| H3Z | 9,460  | 1,104,899            | 730           | 450                | 440                  | 550                  | 630                  | 450                  | 420                  | 350                  | 330                  | 370                  | 290                  | 310                  | 500                  | 460                  | 350                  | 330                  | 920                    | 760                    | 840                |
| H4A | 20,610 | 1,519,192            | 1,290         | 1,020              | 1,180                | 1,580                | 1,610                | 1,250                | 1,110                | 960                  | 820                  | 840                  | 730                  | 670                  | 1,170                | 1,010                | 870                  | 660                  | 1,830                  | 1,220                  | 800                |
| H4B | 16,390 | 756,788              | 1,400         | 1,160              | 1,200                | 1,560                | 1,500                | 1,320                | 1,090                | 890                  | 800                  | 690                  | 570                  | 510                  | 500                  | 490                  | 360                  | 860                  | 430                    | 220                    | 200                |
| H4C | 13,120 | 733,701              | 640           | 710                | 820                  | 1,070                | 1,120                | 920                  | 790                  | 700                  | 630                  | 610                  | 540                  | 480                  | 870                  | 650                  | 610                  | 410                  | 1,010                  | 390                    | 170                |
| H4E | 24,220 | 1,014,596            | 1,480         | 1,440              | 1,700                | 2,120                | 2,480                | 2,020                | 1,670                | 1,530                | 1,430                | 1,270                | 1,100                | 880                  | 1,340                | 1,030                | 800                  | 530                  | 1,070                  | 270                    | 90                 |
| H4G | 23,710 | 1,093,381            | 1,220         | 1,220              | 1,520                | 1,970                | 2,210                | 1,850                | 1,640                | 1,490                | 1,320                | 1,200                | 1,100                | 950                  | 1,530                | 1,160                | 960                  | 680                  | 1,230                  | 360                    | 100                |
| H4H | 15,350 | 777,614              | 670           | 640                | 1,280                | 1,150                | 1,300                | 1,030                | 930                  | 800                  | 870                  | 820                  | 700                  | 660                  | 1,000                | 800                  | 680                  | 470                  | 1,000                  | 330                    | 130                |
| H4J | 13,790 | 543,605              | 1,170         | 1,010              | 1,180                | 1,620                | 1,350                | 1,120                | 940                  | 880                  | 750                  | 570                  | 470                  | 400                  | 450                  | 420                  | 360                  | 220                  | 530                    | 210                    | 90                 |
| H4K | 9,140  | 614,218              | 540           | 480                | 630                  | 890                  | 910                  | 660                  | 550                  | 460                  | 390                  | 380                  | 310                  | 290                  | 490                  | 370                  | 310                  | 240                  | 610                    | 380                    | 260                |
| H4L | 29,350 | 1,183,468            | 2,620         | 2,020              | 2,390                | 2,990                | 2,930                | 2,370                | 2,060                | 1,790                | 1,400                | 1,270                | 1,030                | 900                  | 1,320                | 1,010                | 790                  | 630                  | 1,250                  | 410                    | 180                |
| H4M | 9,890  | 532,592              | 760           | 590                | 660                  | 860                  | 810                  | 730                  | 610                  | 570                  | 460                  | 450                  | 380                  | 350                  | 540                  | 430                  | 310                  | 280                  | 630                    | 310                    | 180                |
| H4N | 23,530 | 814,218              | 2,490         | 2,140              | 1,930                | 2,350                | 2,460                | 2,040                | 1,640                | 1,410                | 1,170                | 960                  | 780                  | 650                  | 1,030                | 720                  | 530                  | 340                  | 650                    | 190                    | 70                 |
| H4P | 7,160  | 399,957              | 650           | 460                | 510                  | 550                  | 540                  | 490                  | 430                  | 380                  | 340                  | 310                  | 260                  | 240                  | 410                  | 340                  | 260                  | 200                  | 470                    | 210                    | 120                |
| H4R | 23,650 | 1,587,967            | 1,870         | 1,250              | 1,360                | 1,790                | 1,880                | 1,470                | 1,230                | 1,120                | 990                  | 910                  | 840                  | 760                  | 1,270                | 1,080                | 940                  | 780                  | 2,110                  | 1,220                  | 770                |
| H4S | 490    | 32,979               | 40            | 30                 | 30                   | 30                   | 30                   | 20                   | 20                   | 20                   | 20                   | 20                   | 20                   | 20                   | 40                   | 30                   | 30                   | 20                   | 50                     | 30                     | 10                 |
| H4T | 70     | 16,465               | 10            |                    |                      |                      |                      |                      | 10                   |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        | 10                 |
| H4V | 16,210 | 726,991              | 1,150         | 990                | 1,210                | 1,610                | 1,680                | 1,360                | 1,150                | 980                  | 880                  | 750                  | 590                  | 500                  | 780                  | 570                  | 460                  | 310                  | 730                    | 350                    | 180                |
| H4W | 20,310 | 1,308,325            | 1,350         | 1,100              | 1,290                | 1,760                | 1,890                | 1,440                | 1,230                | 1,080                | 980                  | 920                  | 760                  | 610                  | 1,070                | 860                  | 690                  | 500                  | 1,310                  | 860                    | 620                |
| H4X | 5,140  | 429,701              | 290           | 260                | 310                  | 340                  | 360                  | 290                  | 240                  | 240                  | 210                  | 200                  | 170                  | 160                  | 260                  | 260                  | 200                  | 190                  | 490                    | 390                    | 280                |
| H4Z | 20     | 1,823                |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| H5A |        |                      |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| H5B | 70     | 9,810                |               |                    | 10                   |                      | 10                   | 10                   |                      |                      | 10                   |                      |                      |                      |                      | 10                   |                      |                      | 10                     |                        | 10                 |
| H7A | 16,700 | 804,026              | 810           | 680                | 910                  | 1,120                | 1,370                | 1,190                | 1,110                | 1,110                | 1,100                | 1,070                | 900                  | 750                  | 1,270                | 930                  | 720                  | 460                  | 890                    | 240                    | 90                 |
| H7B | 2,250  | 113,095              | 80            | 70                 | 110                  | 150                  | 170                  | 150                  | 160                  | 150                  | 140                  | 160                  | 120                  | 130                  | 140                  | 170                  | 120                  | 70                   | 130                    | 30                     | 10                 |
| H7C | 6,480  | 305,008              | 290           | 260                | 410                  | 530                  | 600                  | 510                  | 500                  | 410                  | 400                  | 370                  | 310                  | 260                  | 430                  | 310                  | 250                  | 170                  | 280                    | 80                     | 40                 |
| H7E | 21,750 | 1,328,913            | 920           | 830                | 1,150                | 1,420                | 1,700                | 1,460                | 1,230                | 1,260                | 1,140                | 1,240                | 1,040                | 890                  | 1,470                | 1,250                | 1,120                | 750                  | 1,710                  | 740                    | 450                |
| H7G | 17,490 | 794,798              | 810           | 790                | 1,020                | 1,600                | 1,780                | 1,430                | 1,310                | 1,130                | 1,090                | 1,020                | 770                  | 700                  | 1,050                | 850                  | 580                  | 400                  | 770                    | 280                    | 100                |
| H7H | 10,850 | 560,109              | 470           | 380                | 560                  | 680                  | 800                  | 700                  | 620                  | 720                  | 670                  | 660                  | 570                  | 490                  | 930                  | 670                  | 620                  | 400                  | 700                    | 180                    | 50                 |
| H7J | 1,800  | 113,665              | 80            | 50                 | 80                   | 130                  | 130                  | 130                  | 100                  | 120                  | 90                   | 110                  | 100                  | 90                   | 130                  | 100                  | 90                   | 60                   | 130                    | 70                     | 30                 |
| H7K | 18,430 | 1,026,154            | 790           | 670                | 930                  | 1,310                | 1,410                | 1,210                | 1,070                | 1,050                | 1,110                | 1,040                | 940                  | 840                  | 1,310                | 1,070                | 950                  | 660                  | 1,340                  | 560                    | 190                |
| H7L | 29,780 | 1,711,386            | 1,410         | 1,170              | 1,440                | 1,890                | 2,230                | 1,860                | 1,730                | 1,570                | 1,480                | 1,640                | 1,440                | 1,270                | 2,130                | 1,820                | 1,680                | 1,210                | 2,620                  | 910                    | 300                |
| H7M | 23,740 | 1,163,540            | 1,010         | 830                | 1,350                | 1,750                | 2,380                | 1,770                | 1,650                | 1,570                | 1,490                | 1,440                | 1,160                | 1,030                | 1,700                | 1,150                | 950                  | 630                  | 1,310                  | 400                    | 170                |
| H7N | 35,300 | 1,548,918            | 1,850         | 1,560              | 2,280                | 2,860                | 3,640                |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |





Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total   | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-----|---------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| H9R | 20,310  | 1,191,890            | 1,180         | 800                | 1,030                | 1,210                | 1,550                | 1,290                | 1,130                | 1,200                | 1,110                | 1,100                | 920                  | 820                  | 1,400                | 1,130                | 1,020                | 720                  | 1,720                  | 710                    | 280                |
| H9S | 18,780  | 1,271,787            | 990           | 730                | 970                  | 1,110                | 1,460                | 1,200                | 1,080                | 1,060                | 980                  | 1,040                | 840                  | 700                  | 1,280                | 1,000                | 860                  | 620                  | 1,550                  | 790                    | 530                |
| H9W | 15,340  | 1,439,704            | 1,020         | 720                | 760                  | 790                  | 870                  | 770                  | 630                  | 610                  | 570                  | 610                  | 550                  | 500                  | 860                  | 850                  | 780                  | 570                  | 1,710                  | 1,240                  | 940                |
| H9X | 7,780   | 660,375              | 600           | 380                | 430                  | 470                  | 540                  | 430                  | 370                  | 350                  | 290                  | 360                  | 320                  | 270                  | 480                  | 390                  | 330                  | 250                  | 680                    | 470                    | 380                |
| JOA | 15,330  | 680,271              | 660           | 590                | 1,140                | 1,420                | 1,630                | 1,220                | 1,040                | 1,080                | 1,030                | 890                  | 800                  | 600                  | 920                  | 700                  | 500                  | 320                  | 570                    | 150                    | 80                 |
| JOB | 52,620  | 2,435,714            | 2,250         | 2,120              | 3,750                | 4,830                | 5,150                | 3,880                | 3,760                | 3,660                | 3,490                | 3,260                | 2,650                | 2,130                | 3,310                | 2,320                | 1,800                | 1,150                | 2,020                  | 700                    | 410                |
| JOC | 18,660  | 798,574              | 770           | 710                | 1,350                | 1,640                | 1,850                | 1,340                | 1,320                | 1,350                | 1,290                | 1,240                | 1,020                | 880                  | 1,350                | 860                  | 570                  | 350                  | 560                    | 150                    | 80                 |
| JOE | 41,700  | 2,060,006            | 1,510         | 1,560              | 2,640                | 3,410                | 4,030                | 3,140                | 2,940                | 2,930                | 2,800                | 2,490                | 2,140                | 1,820                | 2,920                | 2,080                | 1,430                | 880                  | 1,810                  | 750                    | 440                |
| JOG | 15,480  | 655,403              | 760           | 690                | 1,160                | 1,440                | 1,610                | 1,240                | 1,110                | 1,000                | 1,060                | 920                  | 770                  | 590                  | 900                  | 650                  | 470                  | 310                  | 610                    | 130                    | 60                 |
| JOH | 42,370  | 1,889,581            | 1,710         | 1,480              | 2,720                | 3,540                | 4,160                | 3,080                | 2,950                | 2,990                | 3,090                | 2,850                | 2,380                | 1,940                | 2,900                | 2,100                | 1,450                | 930                  | 1,480                  | 450                    | 180                |
| JOJ | 34,540  | 1,589,011            | 1,430         | 1,260              | 2,220                | 2,700                | 3,410                | 2,690                | 2,540                | 2,440                | 2,280                | 2,110                | 1,820                | 1,510                | 2,420                | 1,750                | 1,210                | 770                  | 1,380                  | 370                    | 230                |
| JOK | 120,400 | 4,996,492            | 6,180         | 4,980              | 8,610                | 11,390               | 13,090               | 9,700                | 8,870                | 8,560                | 7,770                | 7,080                | 5,770                | 4,750                | 7,080                | 5,270                | 3,810                | 2,170                | 3,800                  | 1,070                  | 480                |
| JOL | 67,940  | 3,242,239            | 4,620         | 2,370              | 3,680                | 4,840                | 5,590                | 4,560                | 4,330                | 4,450                | 4,150                | 4,030                | 3,440                | 3,140                | 5,080                | 3,980                | 3,000                | 1,930                | 3,490                  | 940                    | 350                |
| JOM | 14,180  | 420,744              | 4,810         | 900                | 1,160                | 1,200                | 940                  | 630                  | 500                  | 410                  | 330                  | 340                  | 300                  | 280                  | 450                  | 380                  | 350                  | 270                  | 710                    | 190                    | 30                 |
| JON | 40,050  | 1,988,548            | 1,890         | 1,340              | 2,080                | 2,710                | 3,400                | 2,740                | 2,630                | 2,620                | 2,510                | 2,530                | 2,070                | 1,810                | 3,030                | 2,440                | 1,930                | 1,210                | 2,340                  | 590                    | 200                |
| JOP | 33,960  | 1,867,480            | 1,460         | 1,100              | 1,780                | 2,260                | 2,880                | 2,290                | 2,180                | 2,170                | 2,090                | 2,080                | 1,700                | 1,560                | 2,560                | 1,910                | 1,630                | 1,080                | 2,070                  | 780                    | 400                |
| JOR | 32,370  | 1,919,571            | 1,160         | 940                | 1,530                | 2,160                | 2,800                | 2,180                | 2,080                | 2,030                | 1,860                | 1,970                | 1,570                | 1,370                | 2,380                | 1,870                | 1,520                | 1,050                | 2,340                  | 1,030                  | 530                |
| JOS | 27,200  | 1,214,689            | 1,240         | 1,170              | 1,860                | 2,360                | 2,730                | 2,060                | 2,010                | 1,860                | 1,770                | 1,630                | 1,300                | 1,160                | 1,730                | 1,200                | 890                  | 650                  | 1,110                  | 330                    | 150                |
| JOT | 41,300  | 1,887,534            | 1,530         | 1,540              | 2,670                | 3,840                | 4,540                | 3,470                | 3,190                | 3,100                | 2,700                | 2,630                | 2,010                | 1,610                | 2,400                | 1,690                | 1,240                | 730                  | 1,500                  | 610                    | 310                |
| JOV | 22,070  | 914,284              | 950           | 980                | 1,670                | 2,120                | 2,530                | 1,840                | 1,690                | 1,590                | 1,410                | 1,300                | 950                  | 850                  | 1,200                | 900                  | 700                  | 390                  | 720                    | 230                    | 90                 |
| JOW | 14,040  | 534,111              | 700           | 630                | 1,210                | 1,530                | 1,690                | 1,190                | 1,080                | 920                  | 920                  | 850                  | 650                  | 510                  | 690                  | 470                  | 300                  | 200                  | 340                    | 110                    | 50                 |
| JOX | 36,980  | 1,637,879            | 1,700         | 1,760              | 2,790                | 3,240                | 3,690                | 2,740                | 2,450                | 2,360                | 2,190                | 2,120                | 1,760                | 1,420                | 2,410                | 1,760                | 1,330                | 940                  | 1,420                  | 450                    | 150                |
| JOY | 22,510  | 1,068,175            | 2,270         | 930                | 1,470                | 1,690                | 1,890                | 1,290                | 1,270                | 1,260                | 1,120                | 1,110                | 1,010                | 880                  | 1,490                | 1,110                | 850                  | 600                  | 1,690                  | 470                    | 120                |
| JOZ | 27,450  | 1,280,401            | 1,810         | 1,170              | 2,000                | 2,240                | 2,580                | 1,770                | 1,690                | 1,650                | 1,440                | 1,480                | 1,150                | 1,060                | 1,750                | 1,380                | 1,030                | 800                  | 1,870                  | 480                    | 100                |
| J1A | 7,620   | 314,044              | 230           | 260                | 560                  | 740                  | 860                  | 660                  | 590                  | 580                  | 600                  | 520                  | 360                  | 360                  | 420                  | 300                  | 190                  | 110                  | 190                    | 60                     | 30                 |
| J1C | 5,390   | 264,530              | 210           | 180                | 290                  | 390                  | 470                  | 350                  | 370                  | 380                  | 410                  | 340                  | 260                  | 280                  | 390                  | 300                  | 270                  | 140                  | 260                    | 80                     | 30                 |
| J1E | 19,810  | 783,712              | 840           | 920                | 1,550                | 1,850                | 2,210                | 1,690                | 1,550                | 1,440                | 1,310                | 1,240                | 900                  | 750                  | 1,120                | 820                  | 640                  | 320                  | 500                    | 130                    | 50                 |
| J1G | 16,040  | 697,336              | 660           | 640                | 1,160                | 1,470                | 1,640                | 1,280                | 1,150                | 1,070                | 1,090                | 1,030                | 840                  | 660                  | 980                  | 690                  | 560                  | 330                  | 540                    | 170                    | 80                 |
| J1H | 21,580  | 781,383              | 1,180         | 1,380              | 1,950                | 2,360                | 2,510                | 1,920                | 1,720                | 1,500                | 1,370                | 1,150                | 840                  | 720                  | 990                  | 660                  | 420                  | 260                  | 440                    | 130                    | 90                 |
| J1J | 12,310  | 706,263              | 470           | 470                | 690                  | 810                  | 1,120                | 800                  | 800                  | 820                  | 740                  | 780                  | 650                  | 480                  | 800                  | 660                  | 530                  | 350                  | 760                    | 360                    | 240                |
| J1K | 5,540   | 233,434              | 420           | 300                | 450                  | 600                  | 480                  | 410                  | 320                  | 310                  | 300                  | 310                  | 250                  | 230                  | 310                  | 240                  | 200                  | 100                  | 230                    | 70                     | 30                 |
| J1L | 13,330  | 636,738              | 510           | 430                | 740                  | 1,070                | 1,560                | 1,090                | 930                  | 960                  | 880                  | 940                  | 630                  | 580                  | 860                  | 570                  | 440                  | 280                  | 530                    | 220                    | 130                |
| J1M | 4,500   | 208,096              | 300           | 250                | 310                  | 350                  | 430                  | 300                  | 280                  | 270                  | 260                  | 260                  | 200                  | 190                  | 270                  | 210                  | 190                  | 120                  | 200                    | 90                     | 30                 |
| J1N | 27,380  | 1,480,488            | 920           | 870                | 1,260                | 1,790                | 2,110                | 1,720                | 1,630                | 1,780                | 1,820                | 1,810                | 1,490                | 1,320                | 2,250                | 1,670                | 1,520                | 890                  | 1,760                  | 530                    | 240                |
| J1R | 8,530   | 445,326              | 280           | 250                | 430                  | 540                  | 600                  | 540                  | 500                  | 610                  | 580                  | 580                  | 480                  | 450                  | 710                  | 560                  | 450                  | 280                  | 500                    | 150                    | 40                 |
| J1S | 6,320   | 274,864              | 230           | 230                | 410                  | 530                  | 660                  | 500                  | 450                  | 440                  | 430                  | 420                  | 330                  | 290                  | 440                  | 280                  | 240                  | 160                  | 240                    | 50                     | 10                 |
| J1T | 6,410   | 226,812              | 230           | 340                | 540                  | 750                  | 920                  | 580                  | 480                  | 520                  | 370                  | 370                  | 270                  | 190                  | 290                  | 170                  | 140                  | 70                   | 140                    | 30                     | 10                 |
| J1X | 28,010  | 1,431,294            | 900           | 910                | 1,730                | 2,340                | 3,110                | 2,060                | 2,030                | 1,880                | 1,830                | 1,750                | 1,350                | 1,160                | 1,690                | 1,330                | 970                  | 690                  | 1,430                  | 530                    | 340                |
| J1Z | 4,470   | 202,511              | 190           | 160                | 260                  | 400                  | 400                  | 330                  | 300                  | 320                  | 340                  | 310                  | 240                  | 190                  | 300                  | 210                  | 180                  | 100                  | 180                    | 60                     | 20                 |
| J2A | 9,600   | 451,817              | 370           | 350                | 560                  | 720                  | 830                  | 640                  | 680                  | 720                  | 740                  | 680                  | 550                  | 480                  | 740                  | 480                  | 380                  | 190                  | 330                    | 100                    | 60                 |
| J2B | 25,550  | 1,081,637            | 990           | 1,160              | 2,060                | 2,330                | 2,780                | 1,980                | 1,910                | 1,790                | 1,650                | 1,550                | 1,240                | 1,040                | 1,600                | 1,060                | 810                  | 460                  | 770                    | 260                    | 120                |
| J2C | 25,450  | 1,155,163            | 810           | 910                | 1,710                | 2,460                | 3,240                | 1,970                | 1,760                | 1,740                | 1,610                | 1,650                | 1,230                | 1,060                | 1,540                | 1,100                | 820                  | 480                  | 920                    | 360                    | 190                |
| J2E | 3,600   | 157,089              | 120           | 140                | 230                  | 300                  | 320                  | 290                  | 270                  | 290                  | 260                  | 250                  | 230                  | 170                  | 260                  | 160                  | 110                  | 60                   | 110                    | 30                     | 20                 |
| J2G | 23,610  | 883,359              | 830           | 1,020              | 1,920                | 2,470                | 3,200                | 2,040                | 1,830                | 1,860                | 1,660                | 1,410                | 1,090                | 840                  | 1,410                | 1,090                | 500                  | 280                  | 460                    | 140                    | 60                 |
| J2H | 18,090  | 980,324              | 640           | 510                | 910                  | 1,230                | 1,520                | 1,170                | 1,110                | 1,220                | 1,180                | 1,200                | 980                  | 840                  | 1,430                | 1,140                | 870                  | 550                  | 1,030                  | 370                    | 200                |
| J2J | 14,980  | 644,871              | 490           | 520                | 980                  | 1,230                | 1,700                | 1,180                | 1,130                | 1,130                | 1,060                | 1,050                | 840                  | 660                  | 970                  | 660                  | 480                  | 270                  | 450                    | 120                    | 60                 |
| J2K | 14,470  | 602,752              | 510           | 600                | 950                  | 1,310                | 1,660                | 1,220                | 1,120                | 1,120                | 950                  | 980                  | 710                  | 570                  | 870                  | 670                  | 420                  | 260                  | 420                    | 120                    | 50                 |
| J2L | 8,880   | 658,351              | 300           | 260                | 350                  | 470                  | 600                  | 490                  | 460                  | 500                  | 510                  | 510                  | 440                  | 360                  | 670                  | 580                  | 480                  | 350                  | 850                    | 440                    | 280                |
| J2M | 5,950   | 337,331              | 240           | 210                | 320                  | 410                  | 450                  | 380                  | 340                  | 400                  | 380                  | 350                  | 300                  | 290                  | 430                  | 360                  | 290                  | 190                  | 380                    | 150                    | 100                |
| J2N | 7,770   | 322,423              | 300           | 350                | 550                  | 620                  | 860                  | 630                  | 550                  | 550                  | 550                  | 510                  | 420                  | 310                  | 520                  | 370                  | 250                  | 150                  | 210                    | 30                     | 20                 |
| J2R | 8,560   | 418,560              | 260           | 250                | 480                  | 600                  | 740                  | 580                  | 610                  | 650                  | 600                  | 570                  | 490                  | 410                  | 680                  | 450                  | 380                  | 230                  | 420                    | 110                    | 50                 |
| J2S | 24,200  | 1,044,425            | 890           | 1,060              | 1,850                | 2,250                | 2,890                | 2,010                | 1,860                | 1,740                | 1,500                | 1,490                | 1,180                | 930                  | 1,340                | 890                  | 680                  | 400                  | 800                    | 290                    | 150                |
| J2T | 14,140  | 634,104              | 440           | 450                | 850                  | 1,150                | 1,510                | 1,070                | 1,000                | 1,060                | 1,050                | 930                  | 800                  | 660                  | 960                  | 650                  | 540                  | 300                  | 530                    | 150                    | 40                 |
| J2W | 23,340  | 1,380,699            | 810           | 700                | 1,120                | 1,340                | 1,620                | 1,420                | 1,330                | 1,300                | 1,370                | 1,450                | 1,280                | 1,160                | 1,860                | 1,420                | 1,390                | 870                  | 1,920                  | 620                    | 250                |
| J2X | 16,130  | 785,066              | 550           | 560                | 1,000                | 1,250                | 1,540                | 1,180                | 1,070                | 1,130                | 1,020                | 930                  | 870                  | 740                  | 1,150                | 870                  | 730                  | 420                  | 830                    | 240                    | 90                 |
| J2Y | 4,590   | 241,757              | 190           | 150                | 210                  | 280                  | 340                  | 320                  | 270                  | 310                  | 280                  | 320                  | 250                  | 220                  | 380                  | 280                  | 260                  | 150                  | 290                    | 70                     | 40                 |
| J3A | 7,870   | 297,883              | 190           | 290                | 580                  | 820                  | 1,270                | 690                  | 620                  | 640                  | 530                  | 450                  | 360                  | 270                  | 390                  | 260                  | 170                  | 100                  | 160                    | 40                     | 20                 |
| J3B | 27,000  | 1,210,305            | 870           | 990                | 1,770                | 2,170                | 2,610                | 2,110                | 2,000                | 2,020                | 1,830                | 1,690                | 1,470                | 1,130                | 1,860                | 1,470                | 1,000                | 600                  | 1                      |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total  | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-----|--------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| J4Y | 20,060 | 1,154,491            | 1,350         | 870                | 1,170                | 1,360                | 1,540                | 1,360                | 1,190                | 1,040                | 1,010                | 970                  | 890                  | 770                  | 1,230                | 1,110                | 910                  | 700                  | 1,660                  | 630                    | 300                |
| J4Z | 22,040 | 1,076,513            | 1,370         | 1,030              | 1,370                | 1,660                | 1,860                | 1,660                | 1,530                | 1,350                | 1,230                | 1,150                | 1,040                | 840                  | 1,450                | 1,110                | 880                  | 590                  | 1,360                  | 390                    | 180                |
| J5A | 23,100 | 1,238,145            | 970           | 760                | 1,110                | 1,330                | 1,640                | 1,420                | 1,330                | 1,340                | 1,380                | 1,490                | 1,250                | 1,100                | 2,000                | 1,560                | 1,260                | 920                  | 1,690                  | 430                    | 120                |
| J5B | 6,540  | 333,334              | 240           | 210                | 320                  | 410                  | 540                  | 440                  | 380                  | 430                  | 410                  | 430                  | 360                  | 330                  | 530                  | 410                  | 350                  | 210                  | 410                    | 90                     | 30                 |
| J5C | 13,640 | 684,818              | 470           | 410                | 670                  | 920                  | 1,240                | 920                  | 860                  | 870                  | 880                  | 840                  | 720                  | 680                  | 1,150                | 850                  | 670                  | 410                  | 860                    | 160                    | 60                 |
| J5J | 13,480 | 614,624              | 590           | 480                | 710                  | 910                  | 1,150                | 1,010                | 950                  | 1,030                | 950                  | 920                  | 740                  | 610                  | 1,050                | 730                  | 600                  | 350                  | 590                    | 120                    | 20                 |
| J5K | 13,070 | 691,715              | 540           | 400                | 610                  | 830                  | 1,000                | 870                  | 800                  | 820                  | 810                  | 770                  | 660                  | 620                  | 1,050                | 820                  | 720                  | 520                  | 910                    | 260                    | 70                 |
| J5L | 17,800 | 915,186              | 650           | 560                | 870                  | 1,120                | 1,480                | 1,240                | 1,150                | 1,140                | 1,220                | 1,120                | 910                  | 910                  | 1,360                | 1,050                | 870                  | 600                  | 1,160                  | 310                    | 100                |
| J5M | 17,140 | 711,016              | 850           | 650                | 1,040                | 1,400                | 1,640                | 1,400                | 1,340                | 1,330                | 1,160                | 1,100                | 890                  | 730                  | 1,220                | 870                  | 580                  | 330                  | 490                    | 100                    | 20                 |
| J5N | 130    | 2,928                | 40            | 30                 | 20                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                     | 10                     | 10                 |
| J5R | 38,840 | 2,680,365            | 1,690         | 1,380              | 1,790                | 2,260                | 2,740                | 2,210                | 2,100                | 1,960                | 1,830                | 2,010                | 1,770                | 1,490                | 2,820                | 2,320                | 2,100                | 1,530                | 4,140                  | 1,740                  | 960                |
| J5T | 11,410 | 525,943              | 530           | 410                | 640                  | 790                  | 1,070                | 880                  | 810                  | 830                  | 750                  | 690                  | 630                  | 510                  | 810                  | 640                  | 490                  | 290                  | 500                    | 100                    | 50                 |
| J5V | 6,240  | 225,582              | 200           | 270                | 550                  | 800                  | 880                  | 530                  | 500                  | 510                  | 410                  | 340                  | 230                  | 170                  | 260                  | 180                  | 120                  | 80                   | 140                    | 30                     | 10                 |
| J5W | 20,720 | 1,076,915            | 780           | 590                | 1,040                | 1,410                | 1,840                | 1,440                | 1,310                | 1,340                | 1,270                | 1,310                | 1,060                | 960                  | 1,600                | 1,240                | 1,110                | 630                  | 1,280                  | 380                    | 130                |
| J5X | 6,940  | 307,916              | 290           | 280                | 450                  | 550                  | 640                  | 500                  | 500                  | 510                  | 450                  | 420                  | 360                  | 310                  | 480                  | 360                  | 290                  | 190                  | 270                    | 70                     | 20                 |
| J5Y | 23,470 | 1,331,624            | 920           | 790                | 1,050                | 1,410                | 1,710                | 1,400                | 1,330                | 1,380                | 1,390                | 1,460                | 1,230                | 1,090                | 1,910                | 1,520                | 1,320                | 890                  | 1,840                  | 600                    | 220                |
| J5Z | 22,620 | 1,114,845            | 770           | 670                | 1,140                | 1,440                | 2,090                | 1,570                | 1,570                | 1,600                | 1,480                | 1,480                | 1,270                | 1,120                | 1,740                | 1,310                | 1,100                | 670                  | 1,250                  | 260                    | 90                 |
| J6A | 28,820 | 1,483,631            | 980           | 860                | 1,470                | 1,980                | 2,720                | 2,140                | 1,890                | 2,070                | 1,800                | 1,930                | 1,480                | 1,340                | 2,140                | 1,620                | 1,290                | 790                  | 1,550                  | 540                    | 250                |
| J6E | 38,070 | 1,688,817            | 1,350         | 1,660              | 2,720                | 3,530                | 4,430                | 3,120                | 2,770                | 2,740                | 2,390                | 2,140                | 1,710                | 1,410                | 2,210                | 1,660                | 1,370                | 750                  | 1,370                  | 490                    | 260                |
| J6J | 19,620 | 892,905              | 1,000         | 880                | 1,270                | 1,460                | 1,910                | 1,550                | 1,410                | 1,500                | 1,210                | 1,100                | 920                  | 820                  | 1,350                | 950                  | 750                  | 470                  | 840                    | 280                    | 90                 |
| J6K | 20,010 | 886,126              | 980           | 880                | 1,230                | 1,470                | 1,870                | 1,570                | 1,360                | 1,450                | 1,300                | 1,260                | 1,000                | 850                  | 1,390                | 1,030                | 800                  | 510                  | 850                    | 180                    | 60                 |
| J6N | 12,890 | 632,903              | 460           | 460                | 740                  | 970                  | 1,280                | 970                  | 900                  | 890                  | 910                  | 750                  | 640                  | 560                  | 880                  | 700                  | 540                  | 310                  | 650                    | 170                    | 100                |
| J6R | 11,250 | 601,073              | 470           | 370                | 550                  | 650                  | 880                  | 710                  | 650                  | 730                  | 650                  | 710                  | 590                  | 550                  | 930                  | 740                  | 600                  | 360                  | 810                    | 200                    | 90                 |
| J6S | 20,530 | 908,742              | 620           | 860                | 1,420                | 1,810                | 2,320                | 1,690                | 1,610                | 1,420                | 1,320                | 1,170                | 980                  | 820                  | 1,250                | 920                  | 790                  | 460                  | 820                    | 180                    | 60                 |
| J6T | 14,550 | 612,574              | 510           | 620                | 1,120                | 1,230                | 1,560                | 1,210                | 1,120                | 1,080                | 990                  | 870                  | 760                  | 630                  | 680                  | 600                  | 430                  | 310                  | 500                    | 110                    | 50                 |
| J6V | 11,600 | 687,561              | 410           | 310                | 510                  | 690                  | 890                  | 780                  | 620                  | 680                  | 640                  | 670                  | 580                  | 550                  | 880                  | 760                  | 670                  | 480                  | 1,020                  | 360                    | 130                |
| J6W | 26,110 | 1,334,869            | 980           | 940                | 1,340                | 1,860                | 2,470                | 1,900                | 1,660                | 1,670                | 1,640                | 1,560                | 1,370                | 1,150                | 1,860                | 1,480                | 1,220                | 780                  | 1,660                  | 460                    | 190                |
| J6X | 20,360 | 1,067,120            | 660           | 600                | 920                  | 1,310                | 1,700                | 1,430                | 1,300                | 1,340                | 1,310                | 1,320                | 1,120                | 990                  | 1,600                | 1,250                | 1,040                | 680                  | 1,260                  | 390                    | 130                |
| J6Y | 16,520 | 981,184              | 690           | 520                | 770                  | 960                  | 1,180                | 900                  | 900                  | 930                  | 890                  | 910                  | 820                  | 780                  | 1,300                | 1,110                | 1,030                | 710                  | 1,450                  | 500                    | 180                |
| J6Z | 15,400 | 993,679              | 560           | 530                | 680                  | 890                  | 1,100                | 970                  | 830                  | 870                  | 880                  | 910                  | 830                  | 680                  | 1,150                | 940                  | 880                  | 590                  | 1,220                  | 580                    | 330                |
| J7A | 11,680 | 832,400              | 510           | 390                | 570                  | 710                  | 860                  | 640                  | 570                  | 570                  | 530                  | 580                  | 490                  | 480                  | 800                  | 680                  | 620                  | 460                  | 1,210                  | 640                    | 380                |
| J7B | 10,760 | 890,089              | 560           | 470                | 520                  | 640                  | 710                  | 560                  | 480                  | 450                  | 440                  | 450                  | 410                  | 420                  | 620                  | 570                  | 570                  | 430                  | 1,190                  | 770                    | 520                |
| J7C | 36,800 | 2,142,116            | 1,440         | 1,250              | 1,760                | 2,260                | 2,830                | 2,350                | 2,190                | 2,190                | 2,180                | 2,050                | 1,870                | 1,700                | 2,670                | 2,250                | 1,980                | 1,370                | 2,920                  | 1,090                  | 470                |
| J7E | 23,650 | 1,121,114            | 850           | 900                | 1,470                | 1,900                | 2,530                | 1,870                | 1,710                | 1,670                | 1,560                | 1,390                | 1,150                | 1,020                | 1,500                | 1,100                | 860                  | 520                  | 1,080                  | 400                    | 180                |
| J7G | 14,070 | 762,181              | 540           | 430                | 660                  | 940                  | 1,240                | 1,010                | 890                  | 920                  | 880                  | 860                  | 740                  | 680                  | 1,040                | 770                  | 680                  | 450                  | 930                    | 320                    | 110                |
| J7H | 6,530  | 366,618              | 230           | 200                | 300                  | 420                  | 500                  | 470                  | 440                  | 390                  | 390                  | 420                  | 320                  | 280                  | 500                  | 390                  | 320                  | 220                  | 510                    | 180                    | 60                 |
| J7J | 21,220 | 1,154,523            | 750           | 650                | 1,000                | 1,330                | 1,650                | 1,360                | 1,280                | 1,360                | 1,310                | 1,260                | 1,080                | 1,000                | 1,690                | 1,340                | 1,160                | 780                  | 1,630                  | 470                    | 140                |
| J7K | 28,710 | 1,523,270            | 940           | 830                | 1,330                | 1,820                | 2,420                | 1,900                | 1,750                | 1,770                | 1,800                | 1,750                | 1,550                | 1,370                | 2,310                | 1,850                | 1,660                | 1,040                | 2,010                  | 480                    | 150                |
| J7L | 10,600 | 564,324              | 430           | 310                | 510                  | 740                  | 850                  | 740                  | 720                  | 690                  | 630                  | 640                  | 530                  | 440                  | 780                  | 660                  | 500                  | 370                  | 760                    | 230                    | 80                 |
| J7M | 18,640 | 832,332              | 930           | 710                | 1,050                | 1,330                | 1,690                | 1,360                | 1,280                | 1,330                | 1,280                | 1,060                | 1,020                | 860                  | 1,390                | 1,080                | 840                  | 480                  | 780                    | 150                    | 30                 |
| J7N | 24,520 | 1,270,078            | 910           | 750                | 1,150                | 1,590                | 1,920                | 1,680                | 1,520                | 1,650                | 1,620                | 1,530                | 1,390                | 1,150                | 1,970                | 1,560                | 1,200                | 820                  | 1,580                  | 410                    | 130                |
| J7P | 20,660 | 1,005,261            | 750           | 700                | 1,170                | 1,470                | 1,910                | 1,560                | 1,420                | 1,490                | 1,380                | 1,330                | 1,080                | 940                  | 1,530                | 1,090                | 880                  | 530                  | 1,030                  | 300                    | 110                |
| J7R | 30,450 | 1,523,554            | 1,230         | 1,060              | 1,580                | 2,120                | 2,880                | 2,180                | 1,980                | 2,030                | 1,930                | 1,810                | 1,570                | 1,370                | 2,220                | 1,700                | 1,490                | 910                  | 1,740                  | 490                    | 170                |
| J7T | 22,750 | 1,419,129            | 1,150         | 810                | 1,130                | 1,360                | 1,500                | 1,340                | 1,200                | 1,240                | 1,180                | 1,260                | 1,060                | 960                  | 1,700                | 1,320                | 1,280                | 870                  | 2,050                  | 940                    | 420                |
| J7V | 53,990 | 2,897,486            | 2,500         | 1,930              | 2,690                | 3,520                | 4,410                | 3,650                | 3,360                | 3,300                | 3,250                | 3,110                | 2,730                | 2,360                | 4,040                | 3,210                | 2,670                | 1,800                | 3,750                  | 1,230                  | 490                |
| J7W | 11,140 | 590,043              | 520           | 390                | 530                  | 720                  | 880                  | 770                  | 660                  | 720                  | 630                  | 670                  | 570                  | 520                  | 890                  | 640                  | 550                  | 400                  | 760                    | 250                    | 80                 |
| J7X | 4,300  | 207,954              | 140           | 140                | 210                  | 280                  | 350                  | 330                  | 290                  | 330                  | 270                  | 280                  | 240                  | 200                  | 380                  | 250                  | 210                  | 150                  | 200                    | 40                     | 20                 |
| J7Y | 21,700 | 912,711              | 680           | 830                | 1,480                | 2,050                | 2,710                | 1,890                | 1,730                | 1,620                | 1,400                | 1,300                | 1,030                | 840                  | 1,330                | 840                  | 700                  | 390                  | 630                    | 180                    | 90                 |
| J7Z | 24,710 | 961,165              | 890           | 1,170              | 1,880                | 2,460                | 3,060                | 2,240                | 1,950                | 1,790                | 1,660                | 1,390                | 1,110                | 690                  | 1,400                | 900                  | 670                  | 410                  | 660                    | 300                    | 110                |
| J8A | 8,350  | 441,657              | 340           | 280                | 440                  | 560                  | 660                  | 600                  | 560                  | 580                  | 530                  | 510                  | 470                  | 410                  | 610                  | 450                  | 390                  | 240                  | 490                    | 180                    | 80                 |
| J8B | 11,500 | 576,444              | 420           | 400                | 640                  | 960                  | 1,170                | 840                  | 820                  | 790                  | 710                  | 700                  | 530                  | 520                  | 730                  | 590                  | 460                  | 290                  | 600                    | 230                    | 110                |
| J8C | 9,500  | 398,970              | 290           | 370                | 720                  | 950                  | 1,190                | 900                  | 760                  | 670                  | 600                  | 580                  | 400                  | 350                  | 490                  | 380                  | 270                  | 130                  | 290                    | 110                    | 60                 |
| J8E | 8,930  | 468,090              | 320           | 290                | 480                  | 740                  | 970                  | 700                  | 700                  | 670                  | 590                  | 560                  | 460                  | 330                  | 520                  | 380                  | 250                  | 200                  | 440                    | 220                    | 120                |
| J8G | 6,620  | 276,475              | 330           | 290                | 460                  | 580                  | 740                  | 520                  | 470                  | 420                  | 420                  | 340                  | 310                  | 270                  | 370                  | 280                  | 230                  | 140                  | 230                    | 60                     | 20                 |
| J8H | 11,860 | 472,638              | 500           | 570                | 990                  | 1,240                | 1,410                | 970                  | 970                  | 780                  | 720                  | 670                  | 540                  | 400                  | 660                  | 420                  | 350                  | 210                  | 340                    | 100                    | 40                 |
| J8L | 15,660 | 763,030              | 560           | 570                | 930                  | 1,110                | 1,270                | 1,070                | 1,020                | 990                  | 1,000                | 960                  | 810                  | 810                  | 1,230                | 970                  | 780                  | 480                  | 880                    | 170                    | 60                 |
| J8M | 9,870  | 484,671              | 320           | 350                | 490                  | 560                  | 730                  | 630                  | 610                  | 630                  | 610                  | 710                  | 630                  | 520                  | 970                  | 690                  | 520                  | 310                  | 510                    | 70                     | 20                 |
| J8N | 9,970  | 555,916              | 350           | 290                | 450                  | 630                  | 620                  | 540                  | 570                  | 590                  | 590                  | 550                  | 490                  | 520                  | 970                  | 720                  | 590                  | 380                  | 870                    | 190                    | 50                 |
| J8P | 26,940 | 1,249,243            | 910           | 960                | 1,530                | 1,820                | 2,290                | 1,970                |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA                  | Total  | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|----------------------|--------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| <b>PR 35 Ontario</b> |        |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| K0A                  | 86,740 | 5,592,041             | 3,160         | 2,270              | 3,840                | 4,650                | 5,590                | 4,180                | 4,110                | 4,370                | 4,370                | 4,840                | 4,240                | 3,830                | 7,380                | 6,320                | 5,280                | 4,370                | 9,760                  | 3,120                  | 1,070              |
| K0B                  | 17,430 | 857,800               | 750           | 560                | 1,190                | 1,480                | 1,660                | 1,110                | 1,080                | 1,080                | 970                  | 1,120                | 810                  | 770                  | 1,290                | 950                  | 700                  | 500                  | 1,010                  | 290                    | 110                |
| K0C                  | 43,070 | 2,166,327             | 1,930         | 1,340              | 2,630                | 3,250                | 3,950                | 2,830                | 2,620                | 2,700                | 2,560                | 2,530                | 2,110                | 1,880                | 3,370                | 2,450                | 1,810                | 1,470                | 2,590                  | 770                    | 280                |
| K0E                  | 32,010 | 1,588,186             | 1,360         | 1,030              | 1,980                | 2,400                | 2,900                | 2,130                | 2,110                | 2,030                | 1,940                | 1,580                | 1,460                | 2,390                | 1,740                | 1,240                | 1,020                | 1,850                | 520                    | 180                    |                    |
| K0G                  | 31,720 | 1,762,514             | 1,370         | 890                | 1,760                | 2,090                | 2,450                | 1,840                | 1,750                | 1,970                | 1,810                | 1,890                | 1,550                | 1,400                | 2,460                | 2,000                | 1,630                | 1,230                | 2,570                  | 820                    | 230                |
| K0H                  | 36,600 | 1,989,284             | 1,480         | 1,150              | 2,170                | 2,490                | 3,080                | 2,090                | 2,180                | 2,270                | 2,080                | 2,150                | 1,790                | 1,660                | 2,950                | 2,280                | 1,670                | 1,390                | 2,480                  | 880                    | 360                |
| K0J                  | 28,250 | 1,356,404             | 1,520         | 1,020              | 1,980                | 2,400                | 2,780                | 1,720                | 1,730                | 1,770                | 1,590                | 1,590                | 1,270                | 1,150                | 1,950                | 1,490                | 1,050                | 810                  | 1,760                  | 530                    | 150                |
| K0K                  | 93,880 | 4,602,205             | 4,770         | 3,010              | 6,200                | 7,220                | 8,950                | 6,320                | 6,060                | 6,020                | 5,680                | 5,630                | 4,510                | 3,910                | 6,690                | 5,090                | 3,490                | 2,530                | 5,470                  | 1,720                  | 600                |
| K0L                  | 61,670 | 2,999,136             | 2,910         | 1,960              | 3,930                | 5,160                | 6,420                | 4,440                | 3,980                | 3,930                | 3,820                | 3,700                | 2,400                | 2,400                | 4,030                | 3,000                | 2,260                | 1,690                | 3,410                  | 1,190                  | 440                |
| K0M                  | 42,690 | 2,124,128             | 1,820         | 1,340              | 2,670                | 3,470                | 4,460                | 2,930                | 2,770                | 2,740                | 2,630                | 2,580                | 2,070                | 1,820                | 2,920                | 2,140                | 1,550                | 1,230                | 2,350                  | 840                    | 360                |
| K1A                  | 80     | 8,108                 | 10            |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      | 10                   | 10                   |                      | 20                   | 10                     | 10                     |                    |
| K1B                  | 13,680 | 742,834               | 700           | 440                | 750                  | 880                  | 930                  | 850                  | 760                  | 800                  | 760                  | 780                  | 590                  | 590                  | 1,120                | 900                  | 700                  | 560                  | 1,150                  | 320                    | 90                 |
| K1C                  | 30,560 | 1,997,073             | 1,330         | 800                | 1,280                | 1,420                | 1,680                | 1,400                | 1,390                | 1,360                | 1,440                | 1,700                | 1,390                | 1,410                | 2,660                | 2,420                | 1,970                | 1,570                | 3,870                  | 1,160                  | 320                |
| K1E                  | 12,200 | 731,565               | 460           | 270                | 490                  | 580                  | 720                  | 630                  | 540                  | 670                  | 610                  | 810                  | 630                  | 610                  | 1,250                | 950                  | 790                  | 580                  | 1,260                  | 320                    | 60                 |
| K1G                  | 27,980 | 1,518,408             | 1,920         | 1,180              | 1,640                | 2,070                | 2,210                | 1,720                | 1,580                | 1,450                | 1,320                | 1,280                | 1,140                | 1,020                | 1,890                | 1,670                | 1,340                | 1,080                | 2,410                  | 790                    | 260                |
| K1H                  | 12,980 | 1,027,279             | 660           | 460                | 660                  | 840                  | 800                  | 640                  | 510                  | 540                  | 460                  | 510                  | 410                  | 350                  | 810                  | 750                  | 650                  | 630                  | 1,870                  | 980                    | 450                |
| K1J                  | 22,240 | 1,316,643             | 1,360         | 810                | 1,250                | 1,490                | 1,660                | 1,230                | 1,150                | 1,190                | 1,130                | 1,090                | 970                  | 870                  | 1,420                | 1,390                | 1,070                | 880                  | 2,240                  | 790                    | 280                |
| K1K                  | 25,570 | 1,323,573             | 1,410         | 1,160              | 1,800                | 2,130                | 2,240                | 1,700                | 1,480                | 1,390                | 1,290                | 1,250                | 1,020                | 890                  | 1,600                | 1,340                | 1,110                | 830                  | 2,020                  | 700                    | 220                |
| K1L                  | 13,940 | 704,320               | 740           | 530                | 920                  | 1,180                | 1,290                | 930                  | 910                  | 840                  | 740                  | 710                  | 630                  | 590                  | 950                  | 930                  | 550                  | 390                  | 1,000                  | 280                    | 130                |
| K1M                  | 5,430  | 806,616               | 230           | 150                | 210                  | 190                  | 250                  | 180                  | 140                  | 160                  | 160                  | 210                  | 160                  | 140                  | 300                  | 330                  | 350                  | 290                  | 890                    | 670                    | 420                |
| K1N                  | 20,540 | 1,253,810             | 1,630         | 1,090              | 1,340                | 1,520                | 1,550                | 1,200                | 980                  | 790                  | 730                  | 800                  | 610                  | 610                  | 1,270                | 1,110                | 950                  | 780                  | 2,260                  | 1,030                  | 290                |
| K1P                  | 730    | 344,388               | 40            | 20                 | 20                   | 30                   | 30                   | 20                   | 20                   | 20                   | 20                   | 20                   | 20                   | 20                   | 60                   | 50                   | 50                   | 40                   | 120                    | 70                     | 60                 |
| K1R                  | 15,150 | 1,022,894             | 620           | 520                | 820                  | 1,180                | 1,050                | 860                  | 730                  | 640                  | 550                  | 530                  | 490                  | 530                  | 1,130                | 1,000                | 940                  | 820                  | 1,880                  | 630                    | 230                |
| K1S                  | 23,970 | 2,320,398             | 1,470         | 810                | 1,050                | 1,170                | 1,210                | 990                  | 800                  | 770                  | 700                  | 810                  | 720                  | 750                  | 1,430                | 1,480                | 1,300                | 1,190                | 3,830                  | 2,330                  | 1,160              |
| K1T                  | 29,940 | 1,600,774             | 2,270         | 1,310              | 1,720                | 2,200                | 2,320                | 1,950                | 1,690                | 1,420                | 1,220                | 1,220                | 1,140                | 1,110                | 2,060                | 1,700                | 1,440                | 1,220                | 2,950                  | 800                    | 230                |
| K1V                  | 43,360 | 2,502,643             | 3,040         | 1,850              | 2,570                | 3,130                | 3,260                | 2,640                | 2,390                | 2,070                | 1,820                | 1,970                | 1,610                | 1,430                | 2,860                | 2,580                | 2,090                | 1,810                | 4,490                  | 1,470                  | 540                |
| K1W                  | 10,020 | 717,893               | 470           | 330                | 410                  | 500                  | 540                  | 460                  | 380                  | 380                  | 380                  | 430                  | 410                  | 360                  | 750                  | 760                  | 690                  | 570                  | 1,590                  | 480                    | 150                |
| K1X                  | 2,930  | 192,883               | 210           | 90                 | 100                  | 160                  | 180                  | 140                  | 120                  | 130                  | 120                  | 110                  | 80                   | 120                  | 210                  | 210                  | 180                  | 180                  | 430                    | 120                    | 40                 |
| K1Y                  | 15,930 | 1,439,568             | 570           | 460                | 660                  | 820                  | 840                  | 740                  | 590                  | 550                  | 510                  | 580                  | 530                  | 520                  | 1,050                | 1,140                | 1,020                | 930                  | 2,680                  | 1,210                  | 550                |
| K1Z                  | 17,460 | 1,120,953             | 870           | 720                | 1,190                | 1,270                | 1,320                | 1,010                | 950                  | 850                  | 720                  | 720                  | 680                  | 600                  | 1,090                | 970                  | 840                  | 710                  | 1,940                  | 720                    | 300                |
| K2A                  | 13,890 | 1,238,579             | 620           | 430                | 620                  | 730                  | 740                  | 630                  | 560                  | 540                  | 500                  | 550                  | 500                  | 460                  | 900                  | 880                  | 690                  | 650                  | 2,150                  | 1,130                  | 610                |
| K2B                  | 26,120 | 1,311,061             | 1,730         | 1,050              | 1,560                | 2,060                | 2,360                | 1,850                | 1,670                | 1,550                | 1,390                | 1,300                | 1,050                | 980                  | 1,720                | 1,340                | 1,080                | 830                  | 1,840                  | 570                    | 210                |
| K2C                  | 22,630 | 1,332,375             | 1,300         | 800                | 1,190                | 1,510                | 1,730                | 1,460                | 1,280                | 1,240                | 1,140                | 1,120                | 930                  | 880                  | 1,520                | 1,300                | 1,100                | 990                  | 2,220                  | 1,120                  | 740                |
| K2E                  | 16,040 | 928,552               | 1,020         | 580                | 840                  | 1,100                | 1,230                | 1,050                | 870                  | 840                  | 740                  | 810                  | 690                  | 620                  | 1,020                | 940                  | 770                  | 620                  | 1,530                  | 570                    | 210                |
| K2G                  | 40,540 | 2,490,462             | 2,480         | 1,520              | 2,060                | 2,570                | 3,010                | 2,470                | 2,120                | 1,890                | 1,760                | 1,910                | 1,550                | 1,410                | 2,780                | 2,410                | 2,070                | 1,700                | 4,620                  | 1,650                  | 550                |
| K2H                  | 21,380 | 1,424,594             | 880           | 690                | 970                  | 1,130                | 1,360                | 1,150                | 1,100                | 1,030                | 1,080                | 960                  | 870                  | 1,710                | 1,460                | 1,250                | 1,020                | 2,410                | 1,080                  | 900                    | 350                |
| K2J                  | 59,710 | 3,738,774             | 3,920         | 2,250              | 2,840                | 3,470                | 3,520                | 2,960                | 2,760                | 2,510                | 2,590                | 2,620                | 2,410                | 2,290                | 4,460                | 3,990                | 3,460                | 3,090                | 7,610                  | 2,320                  | 650                |
| K2K                  | 19,810 | 1,456,902             | 1,200         | 760                | 890                  | 1,080                | 1,030                | 860                  | 820                  | 840                  | 780                  | 910                  | 660                  | 730                  | 1,040                | 1,310                | 1,160                | 1,000                | 2,690                  | 1,200                  | 500                |
| K2L                  | 15,080 | 886,218               | 730           | 440                | 760                  | 860                  | 960                  | 830                  | 770                  | 820                  | 800                  | 900                  | 710                  | 660                  | 1,250                | 1,000                | 860                  | 700                  | 1,500                  | 430                    | 130                |
| K2M                  | 22,340 | 1,533,409             | 1,330         | 740                | 980                  | 1,210                | 1,160                | 970                  | 940                  | 910                  | 870                  | 950                  | 880                  | 760                  | 1,650                | 1,630                | 1,350                | 1,260                | 3,280                  | 1,180                  | 310                |
| K2P                  | 14,300 | 1,099,405             | 630           | 470                | 730                  | 860                  | 870                  | 760                  | 620                  | 570                  | 500                  | 580                  | 530                  | 520                  | 1,090                | 990                  | 720                  | 1,670                | 670                    | 310                    |                    |
| K2R                  | 1,050  | 127,583               | 40            | 40                 | 40                   | 50                   | 50                   | 50                   | 40                   | 40                   | 40                   | 40                   | 30                   | 40                   | 60                   | 80                   | 60                   | 40                   | 130                    | 100                    | 80                 |
| K2S                  | 29,220 | 2,174,055             | 1,440         | 950                | 1,120                | 1,410                | 1,560                | 1,270                | 1,180                | 1,190                | 1,080                | 1,340                | 1,100                | 1,070                | 2,150                | 1,950                | 1,760                | 1,700                | 4,560                  | 1,800                  | 610                |
| K2T                  | 8,670  | 658,825               | 780           | 430                | 420                  | 520                  | 430                  | 330                  | 300                  | 260                  | 250                  | 260                  | 230                  | 220                  | 460                  | 430                  | 470                  | 450                  | 1,550                  | 670                    | 230                |
| K2V                  | 6,080  | 393,530               | 460           | 210                | 250                  | 270                  | 310                  | 290                  | 230                  | 230                  | 220                  | 250                  | 240                  | 250                  | 450                  | 400                  | 420                  | 320                  | 910                    | 260                    | 60                 |
| K2W                  | 6,320  | 524,808               | 480           | 270                | 270                  | 360                  | 340                  | 260                  | 230                  | 220                  | 200                  | 200                  | 180                  | 190                  | 330                  | 340                  | 330                  | 290                  | 1,130                  | 500                    | 220                |
| K4A                  | 47,070 | 3,088,440             | 2,240         | 1,420              | 1,900                | 2,430                | 2,470                | 2,230                | 2,020                | 1,900                | 1,840                | 2,210                | 2,030                | 1,910                | 4,070                | 3,550                | 3,190                | 2,720                | 6,710                  | 1,800                  | 430                |
| K4B                  | 3,890  | 268,446               | 150           | 90                 | 170                  | 220                  | 240                  | 180                  | 180                  | 180                  | 150                  | 220                  | 170                  | 310                  | 290                  | 240                  | 210                  | 460                  | 180                    | 70                     |                    |
| K4C                  | 3,700  | 291,746               | 120           | 100                | 220                  | 180                  | 190                  | 180                  | 130                  | 150                  | 140                  | 190                  | 140                  | 140                  | 260                  | 270                  | 230                  | 200                  | 500                    | 260                    | 110                |
| K4K                  | 13,270 | 776,059               | 440           | 290                | 600                  | 760                  | 940                  | 740                  | 710                  | 730                  | 710                  | 780                  | 660                  | 610                  | 1,250                | 1,050                | 770                  | 610                  | 1,240                  | 310                    | 90                 |
| K4M                  | 10,810 | 1,003,513             | 500           | 310                | 410                  | 490                  | 500                  | 420                  | 380                  | 390                  | 400                  | 460                  | 390                  | 360                  | 750                  | 750                  | 680                  | 650                  | 1,690                  | 830                    | 480                |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total  | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-----|--------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| LOB | 12,590 | 798,386               | 590           | 340                | 630                  | 790                  | 970                  | 680                  | 680                  | 760                  | 730                  | 730                  | 570                  | 470                  | 850                  | 750                  | 580                  | 550                  | 1,210                  | 510                    | 210                |
| LOC | 7,820  | 467,043               | 360           | 250                | 380                  | 510                  | 580                  | 450                  | 410                  | 460                  | 390                  | 430                  | 380                  | 330                  | 550                  | 520                  | 380                  | 330                  | 770                    | 250                    | 100                |
| LOE | 17,000 | 926,868               | 900           | 560                | 1,050                | 1,430                | 1,670                | 1,160                | 1,030                | 1,070                | 910                  | 920                  | 770                  | 650                  | 1,110                | 940                  | 660                  | 580                  | 1,150                  | 340                    | 110                |
| LOG | 34,890 | 2,231,730             | 1,790         | 1,110              | 1,970                | 2,290                | 2,620                | 2,040                | 1,830                | 1,820                | 1,630                | 1,700                | 1,550                | 1,400                | 2,420                | 2,060                | 1,730                | 1,480                | 3,460                  | 1,340                  | 650                |
| LOH | 1,310  | 97,040                | 60            | 50                 | 70                   | 100                  | 110                  | 80                   | 70                   | 60                   | 50                   | 60                   | 50                   | 50                   | 60                   | 60                   | 60                   | 50                   | 130                    | 70                     | 50                 |
| LOJ | 4,080  | 489,977               | 190           | 170                | 180                  | 250                  | 280                  | 200                  | 170                  | 180                  | 130                  | 150                  | 140                  | 110                  | 240                  | 200                  | 150                  | 160                  | 460                    | 350                    | 350                |
| LOK | 30,240 | 1,539,423             | 1,480         | 940                | 1,770                | 2,240                | 2,880                | 2,010                | 1,960                | 1,860                | 1,790                | 1,800                | 1,460                | 1,330                | 2,200                | 1,630                | 1,230                | 950                  | 1,870                  | 630                    | 210                |
| LOL | 33,630 | 1,995,351             | 1,560         | 1,060              | 1,800                | 2,310                | 2,810                | 2,090                | 1,930                | 1,850                | 1,750                | 1,750                | 1,510                | 1,320                | 2,340                | 1,970                | 1,530                | 1,350                | 3,020                  | 1,170                  | 500                |
| LOM | 28,100 | 1,486,979             | 1,460         | 900                | 1,530                | 1,970                | 2,280                | 1,710                | 1,550                | 1,610                | 1,560                | 1,550                | 1,390                | 1,170                | 2,300                | 1,940                | 1,410                | 1,050                | 2,060                  | 520                    | 160                |
| LON | 2,310  | 141,503               | 140           | 80                 | 150                  | 160                  | 190                  | 140                  | 140                  | 110                  | 110                  | 120                  | 80                   | 90                   | 150                  | 120                  | 100                  | 80                   | 230                    | 90                     | 50                 |
| LOP | 6,390  | 543,633               | 330           | 230                | 320                  | 410                  | 460                  | 350                  | 320                  | 280                  | 290                  | 280                  | 250                  | 240                  | 400                  | 330                  | 280                  | 250                  | 710                    | 400                    | 290                |
| LOR | 67,810 | 4,069,953             | 3,370         | 2,190              | 3,540                | 4,210                | 5,110                | 4,000                | 3,890                | 3,710                | 3,640                | 3,660                | 2,960                | 2,820                | 4,980                | 4,170                | 3,390                | 2,920                | 6,150                  | 2,200                  | 910                |
| LOS | 49,080 | 2,999,985             | 2,150         | 1,490              | 2,510                | 3,100                | 4,070                | 3,180                | 2,990                | 3,030                | 2,680                | 2,840                | 2,170                | 1,920                | 3,510                | 2,780                | 2,160                | 1,900                | 3,940                  | 1,800                  | 870                |
| L1A | 12,850 | 701,818               | 500           | 330                | 740                  | 770                  | 1,120                | 830                  | 800                  | 900                  | 780                  | 820                  | 620                  | 560                  | 900                  | 770                  | 550                  | 430                  | 840                    | 390                    | 130                |
| L1B | 10,310 | 619,202               | 430           | 300                | 450                  | 660                  | 790                  | 600                  | 600                  | 580                  | 640                  | 600                  | 520                  | 470                  | 750                  | 600                  | 470                  | 420                  | 950                    | 370                    | 130                |
| L1C | 36,110 | 2,074,160             | 1,730         | 1,120              | 1,820                | 2,330                | 2,750                | 2,150                | 2,000                | 2,010                | 1,940                | 1,910                | 1,680                | 1,450                | 2,630                | 2,300                | 1,790                | 1,590                | 3,480                  | 1,100                  | 320                |
| L1E | 22,000 | 1,328,873             | 1,060         | 760                | 1,090                | 1,260                | 1,520                | 1,200                | 1,070                | 1,130                | 1,090                | 1,200                | 1,020                | 910                  | 1,680                | 1,500                | 1,190                | 1,040                | 2,280                  | 760                    | 240                |
| L1G | 34,250 | 1,622,562             | 1,850         | 1,200              | 2,270                | 2,670                | 3,420                | 2,600                | 2,330                | 2,150                | 2,080                | 1,990                | 1,540                | 1,310                | 2,220                | 1,660                | 1,210                | 990                  | 1,960                  | 600                    | 190                |
| L1H | 24,620 | 1,106,290             | 1,260         | 910                | 1,800                | 2,050                | 2,590                | 1,940                | 1,750                | 1,580                | 1,510                | 1,340                | 1,180                | 1,010                | 1,510                | 1,250                | 820                  | 590                  | 1,080                  | 320                    | 130                |
| L1J | 32,690 | 1,499,383             | 1,870         | 1,200              | 2,230                | 2,480                | 3,230                | 2,500                | 2,300                | 2,040                | 1,880                | 1,560                | 1,300                | 2,060                | 1,650                | 1,130                | 860                  | 1,570                | 470                    | 470                    | 160                |
| L1K | 32,190 | 1,746,067             | 2,070         | 1,280              | 1,860                | 2,240                | 2,580                | 2,030                | 1,780                | 1,600                | 1,610                | 1,650                | 1,320                | 1,220                | 2,170                | 1,870                | 1,460                | 1,400                | 2,920                  | 890                    | 270                |
| L1L | 8,720  | 427,719               | 740           | 410                | 560                  | 750                  | 840                  | 650                  | 530                  | 430                  | 370                  | 310                  | 310                  | 280                  | 480                  | 450                  | 330                  | 320                  | 690                    | 210                    | 70                 |
| L1M | 16,020 | 1,187,102             | 930           | 670                | 750                  | 910                  | 990                  | 720                  | 630                  | 600                  | 550                  | 620                  | 560                  | 520                  | 980                  | 960                  | 780                  | 980                  | 2,420                  | 1,040                  | 430                |
| L1N | 38,980 | 2,265,380             | 1,850         | 1,270              | 2,030                | 2,500                | 3,340                | 2,430                | 2,180                | 2,030                | 2,010                | 2,080                | 1,630                | 1,620                | 2,770                | 2,350                | 1,880                | 1,650                | 3,680                  | 1,270                  | 420                |
| L1P | 15,510 | 943,557               | 1,020         | 640                | 880                  | 1,130                | 1,220                | 890                  | 760                  | 680                  | 650                  | 660                  | 590                  | 530                  | 960                  | 850                  | 720                  | 690                  | 1,740                  | 670                    | 240                |
| L1R | 33,290 | 2,029,247             | 2,000         | 1,350              | 1,710                | 2,070                | 2,350                | 1,800                | 1,600                | 1,480                | 1,390                | 1,400                | 1,250                | 1,160                | 2,140                | 1,890                | 1,600                | 1,480                | 3,650                  | 1,460                  | 510                |
| L1S | 33,240 | 1,726,671             | 1,950         | 1,140              | 1,820                | 2,260                | 2,860                | 2,260                | 1,930                | 1,910                | 1,790                | 1,780                | 1,520                | 1,340                | 2,430                | 2,060                | 1,560                | 1,250                | 2,550                  | 730                    | 230                |
| L1T | 41,520 | 2,165,649             | 2,990         | 1,970              | 2,530                | 3,520                | 3,620                | 2,760                | 2,230                | 2,000                | 1,840                | 1,830                | 1,640                | 1,430                | 2,670                | 2,190                | 1,790                | 1,510                | 3,480                  | 1,150                  | 380                |
| L1V | 42,870 | 2,518,122             | 2,400         | 1,630              | 2,240                | 3,030                | 3,510                | 2,630                | 2,380                | 2,150                | 2,010                | 2,090                | 1,830                | 1,650                | 2,940                | 2,580                | 2,050                | 1,750                | 3,930                  | 1,510                  | 560                |
| L1W | 14,680 | 903,935               | 660           | 420                | 730                  | 920                  | 1,220                | 940                  | 800                  | 790                  | 800                  | 710                  | 620                  | 590                  | 1,050                | 900                  | 720                  | 650                  | 1,390                  | 540                    | 230                |
| L1X | 18,300 | 1,036,693             | 1,320         | 780                | 960                  | 1,450                | 1,510                | 1,180                | 940                  | 820                  | 810                  | 840                  | 740                  | 690                  | 1,190                | 990                  | 910                  | 730                  | 1,640                  | 570                    | 230                |
| L1Y | 1,630  | 135,750               | 70            | 50                 | 100                  | 90                   | 140                  | 80                   | 80                   | 70                   | 80                   | 70                   | 50                   | 50                   | 120                  | 80                   | 70                   | 70                   | 180                    | 100                    | 60                 |
| L1Z | 22,990 | 1,261,395             | 1,750         | 1,050              | 1,260                | 1,890                | 1,930                | 1,510                | 1,150                | 1,070                | 920                  | 870                  | 900                  | 840                  | 1,500                | 1,280                | 1,030                | 920                  | 2,200                  | 730                    | 200                |
| L2A | 13,520 | 588,534               | 680           | 450                | 970                  | 1,150                | 1,490                | 1,050                | 1,040                | 1,010                | 890                  | 780                  | 620                  | 560                  | 790                  | 560                  | 390                  | 310                  | 550                    | 180                    | 70                 |
| L2E | 15,380 | 586,544               | 720           | 530                | 1,140                | 1,520                | 2,010                | 1,600                | 1,500                | 1,170                | 940                  | 770                  | 610                  | 480                  | 760                  | 500                  | 330                  | 260                  | 400                    | 110                    | 30                 |
| L2G | 24,400 | 976,445               | 1,240         | 820                | 1,650                | 2,290                | 3,040                | 2,480                | 2,320                | 1,940                | 1,510                | 1,290                | 990                  | 800                  | 1,180                | 790                  | 550                  | 430                  | 760                    | 240                    | 90                 |
| L2H | 23,590 | 1,116,618             | 1,300         | 860                | 1,460                | 2,020                | 2,380                | 2,030                | 1,990                | 1,580                | 1,230                | 1,110                | 950                  | 760                  | 1,290                | 900                  | 800                  | 780                  | 1,430                  | 470                    | 160                |
| L2J | 12,650 | 627,170               | 510           | 340                | 730                  | 910                  | 1,330                | 950                  | 1,020                | 950                  | 790                  | 760                  | 560                  | 480                  | 780                  | 620                  | 480                  | 370                  | 720                    | 250                    | 100                |
| L2M | 26,860 | 1,186,828             | 1,270         | 830                | 1,750                | 2,130                | 2,820                | 2,080                | 2,210                | 2,060                | 1,770                | 1,580                | 1,280                | 1,090                | 1,670                | 1,270                | 840                  | 680                  | 1,120                  | 320                    | 100                |
| L2N | 25,290 | 1,331,162             | 990           | 720                | 1,330                | 1,820                | 2,510                | 1,860                | 1,780                | 1,760                | 1,550                | 1,480                | 1,260                | 1,010                | 1,720                | 1,350                | 910                  | 800                  | 1,560                  | 620                    | 270                |
| L2P | 11,810 | 491,955               | 630           | 400                | 760                  | 930                  | 1,240                | 1,000                | 980                  | 930                  | 810                  | 700                  | 590                  | 510                  | 710                  | 490                  | 350                  | 250                  | 410                    | 90                     | 30                 |
| L2R | 19,890 | 898,196               | 1,140         | 730                | 1,570                | 1,900                | 2,160                | 1,650                | 1,360                | 1,360                | 1,060                | 990                  | 820                  | 660                  | 1,090                | 800                  | 530                  | 450                  | 890                    | 400                    | 170                |
| L2S | 15,220 | 757,386               | 880           | 550                | 1,040                | 1,190                | 1,410                | 1,220                | 1,010                | 960                  | 840                  | 800                  | 650                  | 530                  | 900                  | 750                  | 540                  | 540                  | 940                    | 370                    | 130                |
| L2T | 9,350  | 462,916               | 720           | 400                | 580                  | 710                  | 890                  | 700                  | 660                  | 600                  | 540                  | 490                  | 360                  | 320                  | 500                  | 460                  | 280                  | 260                  | 580                    | 210                    | 80                 |
| L2V | 14,830 | 650,436               | 900           | 530                | 980                  | 1,160                | 1,490                | 1,180                | 1,160                | 1,010                | 870                  | 860                  | 690                  | 590                  | 920                  | 700                  | 480                  | 380                  | 670                    | 210                    | 50                 |
| L2W | 1,630  | 103,168               | 90            | 100                | 120                  | 120                  | 130                  | 90                   | 70                   | 60                   | 60                   | 60                   | 50                   | 40                   | 90                   | 80                   | 50                   | 60                   | 160                    | 90                     | 40                 |
| L3B | 19,160 | 782,857               | 940           | 680                | 1,470                | 1,710                | 2,070                | 1,690                | 1,540                | 1,460                | 1,280                | 1,080                | 910                  | 760                  | 1,090                | 750                  | 500                  | 380                  | 660                    | 150                    | 60                 |
| L3C | 27,070 | 1,267,601             | 1,280         | 870                | 1,660                | 2,010                | 2,650                | 2,060                | 2,010                | 1,950                | 1,630                | 1,610                | 1,270                | 1,200                | 1,770                | 1,300                | 970                  | 900                  | 1,430                  | 390                    | 110                |
| L3K | 15,490 | 711,126               | 670           | 450                | 1,060                | 1,270                | 1,650                | 1,190                | 1,160                | 1,110                | 970                  | 930                  | 740                  | 650                  | 1,040                | 720                  | 500                  | 400                  | 690                    | 190                    | 90                 |
| L3L | 580    | 60,921                | 40            | 20                 | 40                   | 40                   | 50                   | 40                   | 20                   | 30                   | 20                   | 20                   | 20                   | 20                   | 30                   | 20                   | 20                   | 20                   | 50                     | 40                     | 50                 |
| L3M | 22,330 | 1,410,374             | 900           | 700                | 1,040                | 1,350                | 1,690                | 1,270                | 1,190                | 1,240                | 1,240                | 1,190                | 960                  | 900                  | 1,640                | 1,420                | 1,130                | 1,020                | 2,240                  | 880                    | 340                |
| L3P | 31,650 | 1,926,870             | 2,110         | 1,370              | 1,950                | 2,710                | 2,510                | 2,000                | 1,540                | 1,530                | 1,360                | 1,370                | 1,160                | 1,090                | 1,810                | 1,610                | 1,310                | 1,190                | 3,020                  | 1,400                  | 630                |
| L3R | 54,880 | 2,977,622             | 4,790         | 2,790              | 4,070                | 6,140                | 5,260                | 3,850                | 3,060                | 2,490                | 2,180                | 2,050                | 1,720                | 1,490                | 2,660                | 2,160                | 1,820                | 1,500                | 4,040                  | 1,840                  | 2,000              |
| L3S | 47,540 | 1,899,504             | 4,160         | 2,640              | 3,590                | 5,860                | 5,240                | 3,920                | 3,190                | 2,570                | 2,100                | 1,920                | 1,640                | 1,410                | 2,280                | 1,610                | 1,270                | 1,010                | 2,220                  | 680                    | 1,400              |
| L3T | 43,840 | 2,783,622             | 3,560         | 2,000              | 2,680                | 3,870                | 3,670                | 2,660                | 2,240                | 1,990                | 1,770                | 1,740                | 1,480                | 1,320                | 2,340                | 2,110                | 1,890                | 1,530                | 3,980                  | 1,910                  | 1,100              |
| L3V | 38,410 | 1,844,508             | 1,890         | 1,240              | 2,450                | 3,050                | 3,870                | 2,960                | 2,720                | 2,490                | 2,260                | 2,220                | 1,790                | 1,500                | 2,380                | 1,950                | 1,340                | 1,060                | 2,100                  | 750                    | 280                |
| L3X | 35,740 | 2,153,242             | 2,430         | 1,660              | 2,200                | 2,810                | 2,900                | 2,230                | 1,900                | 1,650                | 1,450                | 1,440                | 1,320                | 1,170                | 2,040                | 1,790                | 1,530                | 1,410                | 3,640                  | 1,520                  | 660                |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total  | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-----|--------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| L5K | 10,910 | 647,945              | 840           | 510                | 620                  | 850                  | 870                  | 780                  | 610                  | 540                  | 470                  | 500                  | 450                  | 350                  | 610                  | 570                  | 430                  | 370                  | 930                    | 410                    | 210                |
| L5L | 37,010 | 2,130,830            | 2,620         | 1,580              | 2,150                | 2,710                | 3,140                | 2,220                | 2,060                | 1,910                | 1,740                | 1,710                | 1,500                | 1,350                | 2,320                | 2,060                | 1,650                | 1,330                | 3,060                  | 1,300                  | 620                |
| L5M | 88,330 | 4,708,521            | 9,250         | 5,170              | 5,630                | 7,190                | 6,880                | 5,320                | 4,430                | 3,940                | 3,500                | 3,450                | 2,980                | 2,740                | 4,820                | 4,180                | 3,510                | 2,980                | 8,150                  | 3,140                  | 1,080              |
| L5N | 68,970 | 3,765,919            | 5,110         | 3,030              | 3,850                | 4,890                | 5,170                | 4,170                | 3,650                | 3,380                | 3,170                | 3,250                | 2,970                | 2,690                | 4,900                | 3,810                | 3,190                | 2,640                | 6,430                  | 2,060                  | 620                |
| L5P | 20     | 956                  |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| L5R | 32,620 | 1,518,791            | 2,830         | 1,610              | 2,050                | 3,040                | 2,890                | 2,330                | 1,820                | 1,830                | 1,540                | 1,500                | 1,330                | 1,130                | 1,910                | 1,520                | 1,290                | 950                  | 2,200                  | 670                    | 210                |
| L5S | 170    | 12,905               | 10            | 10                 | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                     | 10                     | 10                 |
| L5T | 250    | 20,667               | 30            | 10                 | 20                   | 10                   | 20                   | 20                   | 20                   | 20                   | 20                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 20                     | 20                     | 10                 |
| L5V | 43,270 | 2,038,915            | 3,950         | 2,380              | 2,850                | 4,020                | 3,710                | 2,920                | 2,490                | 2,240                | 1,910                | 1,890                | 1,670                | 1,440                | 2,470                | 2,030                | 1,580                | 1,270                | 3,130                  | 1,070                  | 280                |
| L5W | 20,940 | 1,067,273            | 1,910         | 1,180              | 1,320                | 1,820                | 1,710                | 1,380                | 1,220                | 1,010                | 900                  | 850                  | 770                  | 680                  | 1,250                | 920                  | 780                  | 630                  | 1,700                  | 680                    | 240                |
| L6A | 71,700 | 4,187,117            | 5,210         | 3,130              | 4,200                | 6,060                | 6,230                | 4,690                | 3,850                | 3,410                | 3,060                | 2,830                | 2,630                | 2,350                | 4,090                | 3,420                | 2,870                | 2,670                | 6,960                  | 2,860                  | 1,180              |
| L6B | 25,350 | 1,343,675            | 2,070         | 1,250              | 1,550                | 2,400                | 2,100                | 1,640                | 1,340                | 1,140                | 970                  | 960                  | 920                  | 830                  | 1,430                | 1,240                | 1,000                | 1,040                | 2,380                  | 860                    | 240                |
| L6C | 41,380 | 2,472,750            | 3,830         | 2,390              | 2,860                | 4,140                | 3,360                | 2,400                | 2,000                | 1,720                | 1,520                | 1,330                | 1,210                | 1,150                | 2,020                | 1,710                | 1,540                | 1,400                | 4,080                  | 1,900                  | 830                |
| L6E | 29,870 | 1,527,087            | 2,730         | 1,540              | 1,920                | 2,970                | 2,500                | 2,010                | 1,540                | 1,320                | 1,210                | 1,040                | 970                  | 880                  | 1,620                | 1,340                | 1,160                | 1,110                | 2,780                  | 950                    | 280                |
| L6G | 5,730  | 276,408              | 610           | 260                | 330                  | 580                  | 490                  | 380                  | 320                  | 290                  | 260                  | 210                  | 210                  | 160                  | 300                  | 260                  | 240                  | 230                  | 420                    | 130                    | 50                 |
| L6H | 55,850 | 3,974,003            | 4,410         | 2,690              | 3,190                | 3,660                | 3,880                | 3,010                | 2,620                | 2,320                | 2,190                | 2,130                | 1,850                | 1,700                | 3,240                | 2,850                | 2,460                | 2,120                | 6,340                  | 3,410                  | 1,790              |
| L6J | 19,900 | 2,856,380            | 1,430         | 890                | 1,010                | 1,110                | 1,130                | 880                  | 730                  | 710                  | 700                  | 670                  | 570                  | 510                  | 1,130                | 1,030                | 990                  | 790                  | 2,190                  | 1,760                  | 2,090              |
| L6K | 11,380 | 898,914              | 670           | 430                | 690                  | 840                  | 1,000                | 730                  | 670                  | 610                  | 540                  | 510                  | 430                  | 360                  | 650                  | 550                  | 390                  | 330                  | 900                    | 590                    | 500                |
| L6L | 24,340 | 2,041,166            | 1,420         | 940                | 1,230                | 1,420                | 1,740                | 1,250                | 1,100                | 1,090                | 1,070                | 1,060                | 880                  | 790                  | 1,480                | 1,270                | 1,030                | 950                  | 2,670                  | 1,740                  | 1,220              |
| L6M | 54,850 | 4,211,414            | 4,960         | 2,910              | 3,290                | 3,470                | 3,410                | 2,690                | 2,160                | 1,930                | 1,820                | 1,880                | 1,650                | 1,530                | 2,910                | 2,660                | 2,340                | 2,190                | 6,910                  | 4,080                  | 2,270              |
| L6P | 79,460 | 3,312,595            | 7,190         | 4,410              | 6,290                | 8,890                | 7,430                | 6,120                | 5,230                | 4,530                | 3,910                | 3,400                | 2,930                | 2,450                | 3,810                | 2,950                | 2,270                | 1,880                | 4,060                  | 1,310                  | 420                |
| L6R | 82,630 | 3,087,674            | 8,240         | 4,810              | 6,710                | 8,730                | 7,710                | 6,640                | 6,000                | 5,060                | 4,250                | 3,720                | 3,170                | 2,540                | 4,090                | 2,990                | 2,240                | 1,640                | 3,260                  | 690                    | 160                |
| L6S | 46,270 | 2,044,215            | 3,770         | 2,120              | 3,000                | 3,760                | 4,060                | 3,370                | 3,150                | 2,810                | 2,700                | 2,480                | 2,090                | 1,790                | 2,920                | 2,220                | 1,640                | 1,190                | 2,420                  | 600                    | 180                |
| L6T | 32,210 | 1,276,734            | 2,950         | 1,600              | 2,270                | 2,930                | 3,060                | 2,470                | 2,140                | 2,030                | 1,880                | 1,670                | 1,460                | 1,230                | 1,890                | 1,340                | 1,060                | 720                  | 1,190                  | 240                    | 80                 |
| L6V | 34,960 | 1,391,745            | 2,910         | 1,650              | 2,440                | 3,150                | 3,310                | 2,760                | 2,510                | 2,270                | 2,150                | 1,880                | 1,560                | 1,350                | 2,130                | 1,610                | 1,110                | 810                  | 1,330                  | 230                    | 50                 |
| L6W | 19,170 | 877,110              | 1,380         | 860                | 1,380                | 1,670                | 1,880                | 1,360                | 1,280                | 1,120                | 1,030                | 900                  | 850                  | 720                  | 1,150                | 840                  | 700                  | 510                  | 1,130                  | 290                    | 140                |
| L6X | 64,020 | 2,775,478            | 5,810         | 3,310              | 4,460                | 5,700                | 5,920                | 4,710                | 4,230                | 3,680                | 3,180                | 2,930                | 2,570                | 2,260                | 3,620                | 2,820                | 2,250                | 1,750                | 3,620                  | 950                    | 260                |
| L6Y | 87,100 | 3,558,879            | 8,520         | 5,110              | 6,860                | 8,580                | 8,280                | 6,900                | 5,810                | 5,000                | 4,390                | 3,780                | 3,200                | 2,720                | 4,240                | 3,250                | 2,590                | 1,970                | 4,200                  | 1,310                  | 410                |
| L6Z | 28,450 | 1,405,348            | 2,150         | 1,240              | 1,790                | 2,280                | 2,440                | 1,960                | 1,720                | 1,580                | 1,470                | 1,410                | 1,260                | 1,050                | 1,910                | 1,500                | 1,140                | 900                  | 1,890                  | 560                    | 210                |
| L7A | 82,300 | 3,542,724            | 7,700         | 4,260              | 5,590                | 7,270                | 7,310                | 5,910                | 5,230                | 4,590                | 4,150                | 3,680                | 3,230                | 2,870                | 4,790                | 3,760                | 3,120                | 2,420                | 5,180                  | 1,020                  | 200                |
| L7B | 13,600 | 1,349,582            | 760           | 550                | 720                  | 920                  | 900                  | 770                  | 600                  | 570                  | 490                  | 510                  | 460                  | 440                  | 730                  | 670                  | 570                  | 560                  | 1,630                  | 1,050                  | 720                |
| L7C | 26,330 | 1,538,009            | 1,700         | 1,100              | 1,620                | 2,170                | 2,090                | 1,650                | 1,440                | 1,370                | 1,240                | 1,210                | 1,050                | 940                  | 1,600                | 1,330                | 1,100                | 930                  | 2,500                  | 940                    | 400                |
| L7E | 27,650 | 1,801,873            | 1,350         | 950                | 1,440                | 1,820                | 2,120                | 1,630                | 1,450                | 1,420                | 1,210                | 1,270                | 1,190                | 1,030                | 1,900                | 1,620                | 1,400                | 1,200                | 2,950                  | 1,150                  | 540                |
| L7G | 38,280 | 2,646,348            | 2,050         | 1,420              | 1,830                | 2,260                | 2,670                | 1,930                | 1,840                | 1,750                | 1,770                | 1,740                | 1,580                | 1,440                | 2,600                | 2,290                | 1,910                | 1,770                | 4,570                  | 1,970                  | 910                |
| L7J | 10,980 | 650,290              | 490           | 370                | 620                  | 710                  | 800                  | 640                  | 560                  | 620                  | 560                  | 610                  | 530                  | 500                  | 850                  | 660                  | 550                  | 470                  | 1,000                  | 300                    | 160                |
| L7K | 6,860  | 499,522              | 340           | 230                | 390                  | 480                  | 490                  | 420                  | 370                  | 330                  | 310                  | 290                  | 250                  | 250                  | 470                  | 360                  | 330                  | 260                  | 720                    | 350                    | 220                |
| L7L | 37,130 | 2,720,817            | 1,970         | 1,360              | 1,690                | 2,130                | 2,420                | 1,860                | 1,690                | 1,380                | 1,240                | 1,150                | 1,050                | 940                  | 1,600                | 1,330                | 1,100                | 930                  | 2,500                  | 2,110                  | 950                |
| L7M | 38,360 | 2,834,565            | 2,010         | 1,380              | 1,930                | 2,150                | 2,370                | 1,890                | 1,800                | 1,760                | 1,690                | 1,700                | 1,500                | 1,340                | 2,530                | 2,330                | 2,000                | 1,850                | 4,770                  | 2,330                  | 1,030              |
| L7N | 10,840 | 841,919              | 490           | 310                | 450                  | 630                  | 980                  | 640                  | 600                  | 610                  | 510                  | 530                  | 450                  | 360                  | 680                  | 570                  | 520                  | 410                  | 1,040                  | 650                    | 440                |
| L7P | 23,790 | 1,696,142            | 1,050         | 790                | 1,190                | 1,300                | 1,610                | 1,420                | 1,190                | 1,210                | 1,210                | 1,260                | 1,050                | 950                  | 1,750                | 1,580                | 1,100                | 980                  | 2,360                  | 1,120                  | 670                |
| L7R | 13,950 | 947,333              | 590           | 410                | 650                  | 840                  | 1,160                | 890                  | 800                  | 770                  | 690                  | 720                  | 570                  | 530                  | 950                  | 800                  | 620                  | 580                  | 1,320                  | 700                    | 380                |
| L7S | 10,000 | 633,196              | 390           | 250                | 510                  | 650                  | 860                  | 630                  | 580                  | 650                  | 570                  | 560                  | 450                  | 360                  | 700                  | 620                  | 520                  | 450                  | 380                    | 830                    | 400                |
| L7T | 14,970 | 1,202,605            | 670           | 460                | 720                  | 860                  | 1,120                | 840                  | 800                  | 850                  | 800                  | 810                  | 700                  | 610                  | 1,040                | 810                  | 710                  | 590                  | 1,440                  | 740                    | 410                |
| L8B | 16,270 | 1,089,426            | 780           | 580                | 770                  | 900                  | 1,010                | 910                  | 760                  | 760                  | 730                  | 730                  | 650                  | 620                  | 1,010                | 1,040                | 930                  | 880                  | 2,020                  | 790                    | 290                |
| L8E | 33,340 | 1,665,828            | 2,020         | 1,350              | 2,070                | 2,660                | 3,080                | 2,380                | 2,190                | 2,080                | 1,830                | 1,760                | 1,430                | 1,230                | 2,180                | 1,650                | 1,240                | 1,020                | 2,230                  | 710                    | 270                |
| L8G | 18,320 | 911,906              | 770           | 580                | 1,080                | 1,430                | 1,870                | 1,290                | 1,230                | 1,200                | 1,150                | 1,050                | 840                  | 690                  | 1,270                | 1,040                | 690                  | 550                  | 1,160                  | 340                    | 120                |
| L8H | 20,360 | 807,240              | 1,240         | 730                | 1,560                | 1,820                | 2,220                | 1,740                | 1,570                | 1,350                | 1,310                | 1,170                | 940                  | 860                  | 1,300                | 850                  | 610                  | 390                  | 1,570                  | 120                    | 50                 |
| L8J | 21,870 | 1,146,214            | 1,310         | 840                | 1,290                | 1,610                | 1,720                | 1,360                | 1,270                | 1,110                | 1,200                | 1,080                | 980                  | 850                  | 1,510                | 1,310                | 1,070                | 940                  | 1,820                  | 470                    | 130                |
| L8K | 25,600 | 1,133,637            | 1,380         | 860                | 1,620                | 2,030                | 2,670                | 1,960                | 1,780                | 1,710                | 1,590                | 1,440                | 1,260                | 1,080                | 1,870                | 1,420                | 1,100                | 660                  | 2,400                  | 240                    | 70                 |
| L8L | 23,000 | 824,726              | 1,720         | 1,000              | 2,150                | 2,430                | 2,710                | 2,020                | 1,850                | 1,510                | 1,280                | 1,060                | 900                  | 730                  | 1,240                | 790                  | 530                  | 390                  | 550                    | 120                    | 30                 |
| L8M | 9,930  | 421,940              | 520           | 380                | 900                  | 960                  | 1,150                | 790                  | 740                  | 610                  | 530                  | 460                  | 420                  | 340                  | 550                  | 390                  | 320                  | 270                  | 450                    | 120                    | 50                 |
| L8N | 11,610 | 460,948              | 860           | 440                | 1,050                | 1,250                | 1,320                | 1,000                | 870                  | 730                  | 630                  | 550                  | 470                  | 370                  | 580                  | 410                  | 290                  | 200                  | 380                    | 150                    | 70                 |
| L8P | 18,820 | 1,051,456            | 1,240         | 750                | 1,370                | 1,530                | 1,830                | 1,310                | 1,150                | 940                  | 900                  | 840                  | 730                  | 620                  | 1,120                | 940                  | 740                  | 610                  | 1,260                  | 620                    | 340                |
| L8R | 8,690  | 329,169              | 670           | 400                | 750                  | 1,040                | 1,060                | 730                  | 580                  | 510                  | 470                  | 390                  | 300                  | 290                  | 420                  | 320                  | 210                  | 160                  | 260                    | 90                     | 30                 |
| L8S | 11,810 | 541,614              | 1,510         | 730                | 870                  | 970                  | 1,010                | 830                  | 710                  | 600                  | 540                  | 480                  | 400                  | 330                  | 630                  | 490                  | 350                  | 320                  | 600                    | 300                    | 150                |
| L8T | 15,800 | 741,493              | 780           | 510                | 940                  | 1,190                | 1,530                | 1,120                | 1,050                | 1,080                | 960                  | 920                  | 820                  | 700                  | 1,100                | 880                  | 640                  | 490                  | 850                    | 210                    | 60                 |
| L8V | 17,070 | 713,329              | 920           | 550                | 1,090                | 1,480                | 1,970                | 1,300                | 1,280                | 1,100                | 1,090                | 1,010                | 810                  |                      |                      |                      |                      |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total  | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |    |
|-----|--------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|----|
| M1M | 19,450 | 1,009,213            | 1,330         | 980                | 1,320                | 1,700                | 1,970                | 1,510                | 1,220                | 1,050                | 890                  | 860                  | 760                  | 700                  | 1,130                | 790                  | 690                  | 570                  | 1,250                  | 490                    | 270                |    |
| M1N | 18,310 | 1,175,006            | 1,010         | 710                | 1,090                | 1,360                | 1,600                | 1,240                | 1,040                | 920                  | 860                  | 780                  | 680                  | 670                  | 1,130                | 1,010                | 700                  | 720                  | 1,600                  | 760                    | 430                |    |
| M1P | 37,130 | 1,413,784            | 3,850         | 1,820              | 2,610                | 3,950                | 3,870                | 3,000                | 2,220                | 1,800                | 1,730                | 1,450                | 1,200                | 1,930                | 1,440                | 1,050                | 750                  | 1,450                | 300                    | 80                     |                    |    |
| M1R | 25,760 | 1,040,039            | 2,020         | 1,220              | 1,800                | 2,610                | 2,860                | 2,240                | 1,810                | 1,560                | 1,320                | 1,200                | 1,050                | 870                  | 1,420                | 990                  | 790                  | 590                  | 1,110                  | 250                    | 70                 |    |
| M1S | 33,080 | 1,315,593            | 3,010         | 1,820              | 2,440                | 4,100                | 3,640                | 2,730                | 2,150                | 1,750                | 1,550                | 1,300                | 1,120                | 950                  | 1,560                | 1,240                | 940                  | 750                  | 1,450                  | 440                    | 150                |    |
| M1T | 29,240 | 1,193,223            | 2,480         | 1,480              | 2,140                | 3,620                | 3,150                | 2,360                | 1,860                | 1,660                | 1,360                | 1,310                | 1,080                | 890                  | 1,450                | 1,050                | 860                  | 650                  | 1,340                  | 360                    | 140                |    |
| M1V | 45,540 | 1,591,910            | 4,270         | 2,900              | 3,930                | 6,280                | 5,500                | 3,970                | 2,990                | 2,350                | 1,900                | 1,770                | 1,380                | 1,230                | 1,860                | 1,430                | 1,070                | 740                  | 1,490                  | 400                    | 100                |    |
| M1W | 41,270 | 1,699,728            | 3,650         | 2,250              | 3,050                | 4,900                | 4,480                | 3,230                | 2,630                | 2,300                | 1,870                | 1,720                | 1,500                | 1,250                | 2,010                | 1,590                | 1,140                | 930                  | 1,960                  | 610                    | 190                |    |
| M1X | 13,010 | 523,058              | 1,000         | 640                | 920                  | 1,540                | 1,240                | 1,060                | 950                  | 780                  | 710                  | 580                  | 510                  | 470                  | 690                  | 530                  | 350                  | 290                  | 600                    | 130                    | 30                 |    |
| M2H | 21,000 | 1,037,774            | 1,890         | 1,200              | 1,440                | 2,180                | 1,930                | 1,440                | 1,160                | 980                  | 940                  | 830                  | 710                  | 620                  | 990                  | 920                  | 770                  | 640                  | 1,570                  | 570                    | 240                |    |
| M2J | 52,720 | 2,484,031            | 5,370         | 2,480              | 3,280                | 4,710                | 4,860                | 3,800                | 3,120                | 2,640                | 2,540                | 2,240                | 2,040                | 1,710                | 2,870                | 2,340                | 2,060                | 1,630                | 3,520                  | 1,080                  | 420                |    |
| M2K | 21,330 | 1,366,309            | 2,130         | 940                | 1,190                | 1,650                | 1,540                | 1,230                | 900                  | 900                  | 830                  | 810                  | 740                  | 640                  | 1,240                | 1,110                | 960                  | 850                  | 2,120                  | 1,000                  | 500                |    |
| M2L | 9,580  | 1,253,659            | 780           | 500                | 530                  | 640                  | 620                  | 500                  | 430                  | 360                  | 310                  | 330                  | 260                  | 270                  | 430                  | 390                  | 320                  | 320                  | 910                    | 840                    | 860                |    |
| M2M | 28,870 | 1,452,725            | 3,030         | 1,480              | 1,930                | 2,930                | 2,630                | 2,080                | 1,830                | 1,510                | 1,240                | 1,160                | 980                  | 820                  | 1,400                | 1,110                | 900                  | 710                  | 1,910                  | 850                    | 380                |    |
| M2N | 64,430 | 3,904,072            | 7,890         | 3,330              | 3,770                | 5,200                | 4,750                | 3,550                | 2,950                | 2,610                | 2,320                | 2,240                | 2,010                | 1,860                | 3,300                | 3,070                | 2,910                | 2,320                | 6,170                  | 2,820                  | 1,380              |    |
| M2P | 6,440  | 873,036              | 550           | 300                | 330                  | 380                  | 360                  | 310                  | 260                  | 220                  | 230                  | 200                  | 150                  | 180                  | 330                  | 300                  | 260                  | 240                  | 690                    | 540                    | 600                |    |
| M2R | 35,450 | 1,566,789            | 2,500         | 1,670              | 2,440                | 4,140                | 3,840                | 2,920                | 2,530                | 2,280                | 1,860                | 1,630                | 1,370                | 1,090                | 1,770                | 1,240                | 900                  | 740                  | 1,590                  | 650                    | 310                |    |
| M3A | 27,680 | 1,418,913            | 2,060         | 1,370              | 1,830                | 2,440                | 2,600                | 2,100                | 1,710                | 1,540                | 1,270                | 1,230                | 1,140                | 960                  | 1,600                | 1,270                | 950                  | 830                  | 1,720                  | 690                    | 360                |    |
| M3B | 11,620 | 1,357,854            | 880           | 490                | 530                  | 650                  | 730                  | 590                  | 470                  | 450                  | 410                  | 390                  | 340                  | 310                  | 650                  | 580                  | 510                  | 460                  | 1,380                  | 960                    | 860                |    |
| M3C | 32,110 | 1,666,048            | 3,040         | 1,520              | 2,020                | 3,170                | 3,240                | 2,420                | 2,030                | 1,780                | 1,510                | 1,390                | 1,150                | 1,050                | 1,670                | 1,330                | 1,070                | 820                  | 1,820                  | 730                    | 350                |    |
| M3H | 31,100 | 2,097,719            | 1,960         | 1,340              | 1,740                | 2,720                | 2,790                | 2,240                | 1,880                | 1,720                | 1,500                | 1,340                | 1,190                | 960                  | 1,760                | 1,430                | 1,050                | 950                  | 2,370                  | 1,280                  | 900                |    |
| M3J | 25,940 | 949,416              | 2,700         | 1,480              | 2,080                | 2,660                | 2,870                | 2,260                | 1,950                | 1,580                | 1,290                | 1,150                | 1,010                | 790                  | 1,210                | 840                  | 590                  | 450                  | 780                    | 190                    | 80                 |    |
| M3K | 6,920  | 364,999              | 420           | 250                | 400                  | 540                  | 720                  | 540                  | 460                  | 430                  | 390                  | 370                  | 300                  | 230                  | 420                  | 320                  | 270                  | 180                  | 430                    | 160                    | 90                 |    |
| M3L | 16,220 | 585,874              | 1,090         | 720                | 1,170                | 1,890                | 2,030                | 1,500                | 1,290                | 1,080                | 940                  | 800                  | 700                  | 520                  | 800                  | 560                  | 380                  | 250                  | 410                    | 90                     | 10                 |    |
| M3M | 20,610 | 817,280              | 1,330         | 940                | 1,470                | 1,960                | 2,370                | 1,800                | 1,560                | 1,360                | 1,190                | 1,120                | 880                  | 810                  | 1,100                | 790                  | 570                  | 420                  | 750                    | 150                    | 40                 |    |
| M3N | 32,870 | 1,039,536            | 2,840         | 1,900              | 2,850                | 4,240                | 4,030                | 3,090                | 2,620                | 2,120                | 1,850                | 1,540                | 1,260                | 980                  | 1,360                | 880                  | 490                  | 290                  | 460                    | 90                     | 20                 |    |
| M4A | 11,980 | 536,383              | 850           | 570                | 820                  | 1,290                | 1,290                | 920                  | 740                  | 680                  | 620                  | 490                  | 470                  | 370                  | 660                  | 520                  | 400                  | 360                  | 630                    | 230                    | 90                 |    |
| M4B | 14,770 | 775,006              | 910           | 590                | 950                  | 1,250                | 1,450                | 1,150                | 1,000                | 860                  | 720                  | 630                  | 570                  | 520                  | 870                  | 670                  | 540                  | 440                  | 1,000                  | 470                    | 190                |    |
| M4C | 36,720 | 1,932,971            | 2,550         | 1,560              | 2,210                | 3,240                | 3,540                | 2,820                | 2,110                | 1,840                | 1,580                | 1,460                | 1,290                | 1,200                | 1,980                | 1,710                | 1,490                | 1,350                | 3,070                  | 1,200                  | 410                |    |
| M4E | 19,400 | 1,857,135            | 940           | 690                | 970                  | 1,200                | 1,330                | 950                  | 830                  | 680                  | 710                  | 700                  | 570                  | 550                  | 1,140                | 1,000                | 880                  | 940                  | 2,550                  | 1,620                  | 1,150              |    |
| M4G | 15,570 | 2,033,042            | 860           | 580                | 660                  | 730                  | 830                  | 680                  | 550                  | 510                  | 510                  | 520                  | 460                  | 470                  | 800                  | 800                  | 720                  | 690                  | 2,000                  | 1,500                  | 1,710              |    |
| M4H | 14,030 | 416,821              | 2,310         | 780                | 1,050                | 1,730                | 1,850                | 1,290                | 960                  | 730                  | 550                  | 480                  | 380                  | 350                  | 450                  | 320                  | 230                  | 170                  | 320                    | 80                     | 20                 |    |
| M4J | 27,710 | 1,778,246            | 1,590         | 1,040              | 1,590                | 2,590                | 2,650                | 1,810                | 1,370                | 1,240                | 1,040                | 1,010                | 890                  | 800                  | 1,440                | 1,270                | 1,140                | 1,160                | 2,930                  | 1,520                  | 620                |    |
| M4K | 24,400 | 1,896,559            | 1,180         | 800                | 1,360                | 1,980                | 2,090                | 1,600                | 1,250                | 1,140                | 990                  | 960                  | 870                  | 800                  | 1,290                | 1,150                | 930                  | 920                  | 2,370                  | 1,590                  | 1,130              |    |
| M4L | 24,120 | 1,938,144            | 1,150         | 900                | 1,350                | 1,720                | 1,880                | 1,440                | 1,100                | 1,000                | 880                  | 870                  | 740                  | 720                  | 1,310                | 1,220                | 1,060                | 1,030                | 2,880                  | 1,760                  | 1,100              |    |
| M4M | 19,440 | 1,434,836            | 990           | 730                | 1,200                | 1,720                | 1,710                | 1,160                | 920                  | 790                  | 710                  | 630                  | 620                  | 490                  | 970                  | 900                  | 780                  | 770                  | 2,270                  | 1,350                  | 720                |    |
| M4N | 12,590 | 2,835,710            | 770           | 480                | 550                  | 630                  | 650                  | 530                  | 440                  | 410                  | 370                  | 380                  | 340                  | 290                  | 590                  | 530                  | 470                  | 460                  | 1,380                  | 1,360                  | 1,970              |    |
| M4P | 19,350 | 1,505,134            | 1,340         | 670                | 850                  | 1,280                | 1,310                | 1,090                | 970                  | 870                  | 790                  | 790                  | 730                  | 690                  | 1,250                | 1,170                | 1,010                | 840                  | 2,010                  | 1,000                  | 690                |    |
| M4R | 9,280  | 1,232,251            | 580           | 350                | 420                  | 450                  | 520                  | 420                  | 380                  | 330                  | 320                  | 270                  | 270                  | 260                  | 510                  | 470                  | 430                  | 380                  | 1,140                  | 840                    | 950                |    |
| M4S | 23,610 | 2,094,236            | 1,480         | 780                | 990                  | 1,250                | 1,400                | 1,080                | 980                  | 920                  | 890                  | 880                  | 790                  | 800                  | 1,480                | 1,450                | 1,330                | 1,150                | 2,960                  | 1,800                  | 1,200              |    |
| M4T | 9,300  | 1,759,185            | 430           | 280                | 330                  | 380                  | 440                  | 350                  | 330                  | 320                  | 310                  | 310                  | 290                  | 260                  | 500                  | 520                  | 450                  | 420                  | 1,120                  | 950                    | 1,330              |    |
| M4V | 15,310 | 2,736,207            | 780           | 470                | 480                  | 630                  | 810                  | 660                  | 610                  | 540                  | 540                  | 530                  | 500                  | 490                  | 890                  | 830                  | 750                  | 620                  | 1,820                  | 1,480                  | 1,880              |    |
| M4W | 12,390 | 2,561,950            | 930           | 460                | 450                  | 530                  | 630                  | 490                  | 430                  | 410                  | 350                  | 380                  | 350                  | 290                  | 650                  | 590                  | 580                  | 450                  | 1,460                  | 1,250                  | 1,720              |    |
| M4X | 16,340 | 801,973              | 1,290         | 800                | 1,250                | 1,750                | 1,670                | 1,350                | 1,080                | 900                  | 780                  | 670                  | 570                  | 500                  | 740                  | 600                  | 600                  | 340                  | 800                    | 380                    | 260                |    |
| M4Y | 28,270 | 1,707,978            | 3,370         | 1,290              | 1,480                | 1,720                | 1,960                | 1,610                | 1,340                | 1,130                | 1,110                | 1,060                | 970                  | 940                  | 1,690                | 1,590                | 1,490                | 1,190                | 2,710                  | 1,130                  | 520                |    |
| M5A | 37,310 | 2,421,729            | 2,500         | 1,790              | 2,580                | 3,250                | 3,310                | 2,450                | 1,860                | 1,580                | 1,330                | 1,230                | 1,140                | 1,100                | 1,900                | 1,790                | 1,580                | 1,410                | 3,780                  | 1,850                  | 890                |    |
| M5B | 12,590 | 689,797              | 1,490         | 680                | 770                  | 1,030                | 1,000                | 730                  | 580                  | 520                  | 430                  | 450                  | 410                  | 350                  | 630                  | 650                  | 570                  | 500                  | 1,130                  | 470                    | 210                |    |
| M5C | 3,380  | 574,637              | 210           | 110                | 130                  | 150                  | 210                  | 150                  | 140                  | 90                   | 90                   | 90                   | 90                   | 90                   | 180                  | 200                  | 170                  | 160                  | 460                    | 320                    | 340                |    |
| M5E | 9,500  | 1,278,174            | 500           | 250                | 350                  | 460                  | 510                  | 360                  | 270                  | 270                  | 290                  | 270                  | 260                  | 530                  | 550                  | 550                  | 490                  | 1,590                | 1,020                  | 700                    | 700                |    |
| M5G | 20,810 | 690,030              | 2,000         | 1,330              | 4,800                | 3,720                | 2,870                | 910                  | 550                  | 470                  | 390                  | 320                  | 280                  | 260                  | 440                  | 460                  | 410                  | 300                  | 750                    | 400                    | 160                |    |
| M5H | 3,100  | 754,438              | 270           | 110                | 90                   | 140                  | 140                  | 110                  | 100                  | 90                   | 80                   | 80                   | 70                   | 70                   | 170                  | 160                  | 140                  | 150                  | 420                    | 310                    | 440                |    |
| M5J | 13,240 | 1,386,760            | 940           | 370                | 410                  | 590                  | 600                  | 490                  | 430                  | 420                  | 390                  | 370                  | 400                  | 420                  | 800                  | 800                  | 790                  | 750                  | 2,280                  | 1,240                  | 750                |    |
| M5K | 190    | 66,348               | 10            | 10                 | 10                   | 10                   | 20                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 20                     | 20                     | 40                 |    |
| M5L | 40     | 10,374               |               | 10                 |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    | 10 |
| M5M | 20,290 | 2,705,542            | 1,200         | 850                | 910                  | 1,110                | 1,130                | 950                  | 780                  | 660                  | 640                  | 630                  | 580                  | 460                  | 940                  | 900                  | 770                  | 730                  | 2,390                  | 2,240                  | 2,430              |    |
| M5N | 12,800 | 1,622,246            | 780           | 560                | 580                  | 770                  | 830                  | 710                  | 590                  | 540                  | 490                  | 430                  | 430                  | 370                  | 610                  | 580                  | 450                  | 400                  | 1,210                  | 1,130                  | 1,350              |    |
| M5P | 15,910 | 2,425,836            | 840           | 510                | 580                  | 770                  | 910                  | 720                  | 680                  | 650                  | 570                  | 580                  | 550                  | 480                  | 960                  | 840                  | 720                  | 630                  | 1,800                  | 1,420                  | 1,710              |    |
| M5R | 20,330 | 2,891,462            | 1,130         | 720                | 970                  | 1,210                | 1,420                | 1,050                | 800                  | 730                  | 650                  | 680                  | 580                  | 550                  | 1,130                | 1,070                | 850                  | 770                  | 2,200                  | 1,8                    |                    |    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total  | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-----|--------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| M9C | 32,210 | 1,855,459            | 1,740         | 1,230              | 1,790                | 2,420                | 2,790                | 2,050                | 1,830                | 1,680                | 1,590                | 1,500                | 1,360                | 1,240                | 2,210                | 1,790                | 1,480                | 1,240                | 2,840                  | 1,000                  | 430                |
| M9L | 10,470 | 387,723              | 940           | 480                | 870                  | 1,150                | 1,280                | 950                  | 760                  | 630                  | 490                  | 510                  | 380                  | 350                  | 480                  | 360                  | 290                  | 180                  | 280                    | 60                     | 50                 |
| M9M | 19,870 | 758,238              | 1,570         | 980                | 1,460                | 2,030                | 2,220                | 1,730                | 1,410                | 1,310                | 1,090                | 990                  | 830                  | 680                  | 1,050                | 750                  | 560                  | 370                  | 670                    | 120                    | 50                 |
| M9N | 21,220 | 860,877              | 1,360         | 1,010              | 1,620                | 2,170                | 2,440                | 1,850                | 1,490                | 1,290                | 1,090                | 1,020                | 810                  | 780                  | 1,130                | 860                  | 620                  | 490                  | 920                    | 220                    | 60                 |
| M9P | 17,070 | 970,759              | 990           | 660                | 1,000                | 1,440                | 1,690                | 1,150                | 1,020                | 930                  | 850                  | 740                  | 690                  | 590                  | 1,010                | 830                  | 730                  | 600                  | 1,330                  | 560                    | 270                |
| M9R | 28,210 | 1,276,236            | 2,060         | 1,260              | 1,770                | 2,580                | 3,040                | 2,420                | 1,890                | 1,620                | 1,390                | 1,340                | 1,130                | 960                  | 1,660                | 1,190                | 880                  | 720                  | 1,620                  | 500                    | 190                |
| M9V | 47,180 | 1,595,542            | 4,490         | 2,780              | 3,850                | 5,230                | 5,380                | 4,250                | 3,640                | 3,090                | 2,500                | 2,130                | 1,820                | 1,450                | 2,200                | 1,450                | 940                  | 670                  | 1,070                  | 220                    | 50                 |
| M9W | 36,080 | 1,484,785            | 2,770         | 1,830              | 2,600                | 3,750                | 3,870                | 3,100                | 2,600                | 2,180                | 2,010                | 1,720                | 1,520                | 1,220                | 1,900                | 1,420                | 1,030                | 750                  | 1,400                  | 320                    | 100                |
| NOA | 30,560 | 1,410,865            | 3,160         | 1,070              | 1,950                | 2,390                | 2,750                | 1,920                | 1,710                | 1,810                | 1,670                | 1,680                | 1,280                | 1,110                | 1,910                | 1,550                | 1,210                | 970                  | 1,740                  | 500                    | 200                |
| NOB | 66,450 | 4,586,424            | 3,080         | 2,020              | 3,310                | 3,940                | 4,640                | 3,720                | 3,310                | 3,360                | 3,320                | 3,420                | 2,870                | 2,710                | 4,950                | 4,130                | 3,390                | 2,820                | 7,040                  | 2,960                  | 1,490              |
| NOC | 12,990 | 624,501              | 770           | 440                | 830                  | 1,080                | 1,300                | 860                  | 790                  | 860                  | 790                  | 740                  | 580                  | 600                  | 860                  | 680                  | 490                  | 340                  | 670                    | 240                    | 90                 |
| NOE | 28,830 | 1,512,532            | 1,760         | 1,010              | 1,680                | 2,100                | 2,520                | 1,790                | 1,800                | 1,740                | 1,550                | 1,640                | 1,370                | 1,210                | 2,070                | 1,590                | 1,140                | 1,050                | 1,860                  | 670                    | 290                |
| NOG | 65,570 | 3,298,327            | 3,500         | 2,170              | 4,250                | 5,040                | 6,070                | 4,230                | 4,060                | 4,000                | 3,900                | 3,910                | 3,210                | 2,760                | 4,630                | 3,570                | 2,520                | 1,880                | 3,740                  | 1,630                  | 510                |
| NOH | 42,380 | 2,526,595            | 2,090         | 1,280              | 2,480                | 3,030                | 3,650                | 2,760                | 2,490                | 2,570                | 2,420                | 2,370                | 1,840                | 1,610                | 2,730                | 2,280                | 1,630                | 1,330                | 3,120                  | 2,060                  | 640                |
| NOJ | 25,530 | 1,303,517            | 1,650         | 890                | 1,490                | 1,770                | 2,180                | 1,640                | 1,470                | 1,450                | 1,390                | 1,520                | 1,290                | 1,130                | 1,970                | 1,430                | 1,130                | 790                  | 1,520                  | 480                    | 220                |
| NOK | 18,970 | 964,816              | 1,140         | 640                | 1,120                | 1,220                | 1,530                | 1,140                | 1,100                | 1,160                | 1,180                | 1,230                | 1,060                | 880                  | 1,500                | 1,130                | 770                  | 580                  | 1,060                  | 380                    | 160                |
| NOL | 40,500 | 2,240,690            | 2,220         | 1,350              | 2,350                | 2,690                | 3,320                | 2,350                | 2,230                | 2,310                | 2,230                | 2,280                | 1,920                | 1,750                | 3,060                | 2,380                | 1,890                | 1,480                | 3,200                  | 1,070                  | 460                |
| NOM | 54,830 | 3,101,708            | 2,230         | 1,550              | 3,070                | 3,710                | 4,630                | 3,290                | 3,250                | 3,270                | 3,250                | 3,480                | 2,690                | 2,460                | 4,250                | 3,320                | 2,450                | 1,960                | 3,920                  | 1,410                  | 680                |
| NON | 33,330 | 1,995,637            | 1,650         | 1,000              | 1,760                | 2,010                | 2,400                | 1,860                | 1,880                | 1,860                | 1,840                | 2,050                | 1,540                | 1,370                | 2,440                | 2,000                | 1,550                | 1,330                | 2,930                  | 1,500                  | 360                |
| NOP | 42,840 | 2,078,264            | 2,620         | 1,480              | 2,700                | 2,980                | 3,770                | 2,910                | 2,910                | 3,070                | 2,920                | 3,260                | 1,990                | 1,830                | 2,770                | 2,220                | 1,560                | 1,170                | 2,230                  | 760                    | 340                |
| NOR | 38,840 | 2,291,904            | 1,720         | 1,130              | 1,900                | 2,290                | 2,910                | 2,200                | 2,210                | 2,210                | 2,390                | 2,330                | 1,910                | 1,710                | 2,920                | 2,300                | 1,960                | 1,760                | 3,430                  | 1,130                  | 460                |
| N1A | 9,980  | 448,016              | 540           | 360                | 710                  | 870                  | 1,040                | 760                  | 640                  | 630                  | 600                  | 550                  | 440                  | 400                  | 680                  | 510                  | 360                  | 290                  | 450                    | 130                    | 50                 |
| N1C | 3,090  | 225,057              | 140           | 120                | 140                  | 190                  | 170                  | 150                  | 120                  | 130                  | 130                  | 150                  | 120                  | 130                  | 220                  | 190                  | 150                  | 180                  | 410                    | 200                    | 70                 |
| N1E | 33,580 | 1,874,143            | 1,590         | 1,070              | 1,780                | 2,070                | 2,570                | 2,030                | 1,880                | 1,870                | 1,830                | 2,010                | 1,730                | 1,650                | 2,800                | 2,080                | 1,570                | 1,310                | 2,600                  | 860                    | 280                |
| N1G | 22,500 | 1,385,283            | 1,430         | 910                | 1,210                | 1,400                | 1,620                | 1,270                | 1,190                | 1,100                | 1,120                | 1,140                | 990                  | 900                  | 1,610                | 1,340                | 1,070                | 870                  | 2,050                  | 910                    | 380                |
| N1H | 33,530 | 1,803,787            | 1,650         | 1,120              | 2,000                | 2,250                | 2,920                | 2,290                | 2,100                | 2,140                | 1,960                | 2,000                | 1,850                | 1,560                | 2,350                | 1,710                | 1,280                | 1,000                | 2,140                  | 860                    | 360                |
| N1K | 8,840  | 443,484              | 480           | 340                | 540                  | 680                  | 610                  | 540                  | 510                  | 510                  | 470                  | 520                  | 520                  | 480                  | 730                  | 470                  | 340                  | 290                  | 610                    | 150                    | 50                 |
| N1L | 12,690 | 817,597              | 910           | 560                | 680                  | 810                  | 860                  | 650                  | 590                  | 570                  | 550                  | 580                  | 510                  | 480                  | 870                  | 730                  | 590                  | 560                  | 1,350                  | 600                    | 240                |
| N1M | 14,230 | 773,130              | 610           | 380                | 740                  | 890                  | 1,100                | 860                  | 930                  | 850                  | 830                  | 850                  | 760                  | 680                  | 1,220                | 870                  | 620                  | 560                  | 1,060                  | 310                    | 120                |
| N1P | 5,900  | 309,529              | 360           | 210                | 320                  | 390                  | 420                  | 360                  | 350                  | 330                  | 330                  | 280                  | 280                  | 260                  | 420                  | 380                  | 280                  | 280                  | 490                    | 130                    | 30                 |
| N1R | 33,660 | 1,528,114            | 1,940         | 1,150              | 2,330                | 2,610                | 3,440                | 2,640                | 2,410                | 2,120                | 2,110                | 1,880                | 1,680                | 1,450                | 2,360                | 1,580                | 1,120                | 800                  | 1,450                  | 420                    | 180                |
| N1S | 15,450 | 873,620              | 700           | 490                | 840                  | 1,020                | 1,360                | 970                  | 920                  | 840                  | 840                  | 860                  | 740                  | 680                  | 1,170                | 910                  | 700                  | 550                  | 1,260                  | 440                    | 160                |
| N1T | 14,760 | 825,175              | 1,030         | 610                | 900                  | 1,080                | 1,120                | 960                  | 850                  | 780                  | 670                  | 690                  | 580                  | 550                  | 960                  | 800                  | 650                  | 570                  | 1,300                  | 490                    | 180                |
| N2A | 24,970 | 1,374,186            | 1,430         | 840                | 1,470                | 1,870                | 2,120                | 1,570                | 1,480                | 1,390                | 1,390                | 1,320                | 1,170                | 1,020                | 1,670                | 1,310                | 1,070                | 900                  | 2,020                  | 690                    | 250                |
| N2B | 13,920 | 683,713              | 720           | 410                | 790                  | 1,000                | 1,220                | 970                  | 930                  | 940                  | 800                  | 860                  | 760                  | 640                  | 1,040                | 750                  | 540                  | 440                  | 820                    | 220                    | 70                 |
| N2C | 14,710 | 598,998              | 1,070         | 640                | 1,080                | 1,300                | 1,510                | 1,220                | 1,150                | 1,120                | 920                  | 860                  | 770                  | 610                  | 740                  | 520                  | 360                  | 260                  | 410                    | 100                    | 70                 |
| N2E | 31,500 | 1,425,367            | 2,160         | 1,280              | 1,950                | 2,410                | 2,650                | 2,150                | 2,000                | 1,970                | 1,870                | 1,820                | 1,670                | 1,380                | 2,290                | 1,710                | 1,230                | 890                  | 1,670                  | 350                    | 90                 |
| N2G | 11,690 | 566,951              | 690           | 450                | 870                  | 980                  | 1,120                | 860                  | 740                  | 720                  | 650                  | 610                  | 520                  | 430                  | 730                  | 580                  | 430                  | 320                  | 630                    | 240                    | 120                |
| N2H | 17,230 | 904,889              | 920           | 560                | 1,000                | 1,190                | 1,540                | 1,220                | 1,080                | 1,050                | 1,000                | 920                  | 830                  | 690                  | 1,250                | 970                  | 710                  | 570                  | 1,170                  | 400                    | 160                |
| N2J | 15,770 | 884,480              | 1,220         | 600                | 890                  | 1,160                | 1,430                | 1,090                | 950                  | 830                  | 750                  | 770                  | 700                  | 580                  | 970                  | 810                  | 640                  | 490                  | 1,180                  | 500                    | 220                |
| N2K | 23,020 | 1,697,390            | 1,400         | 850                | 1,180                | 1,430                | 1,440                | 1,200                | 1,080                | 1,070                | 1,040                | 1,060                | 880                  | 840                  | 1,590                | 1,340                | 1,060                | 1,020                | 2,650                  | 1,220                  | 670                |
| N2L | 28,150 | 1,476,709            | 3,710         | 1,540              | 1,950                | 2,050                | 2,150                | 1,730                | 1,500                | 1,340                | 1,280                | 1,180                | 980                  | 890                  | 1,480                | 1,280                | 950                  | 740                  | 1,920                  | 1,020                  | 450                |
| N2M | 27,750 | 1,313,009            | 1,900         | 1,100              | 1,800                | 2,130                | 2,610                | 1,980                | 1,870                | 1,840                | 1,710                | 1,640                | 1,450                | 1,120                | 1,800                | 1,250                | 880                  | 670                  | 1,280                  | 480                    | 220                |
| N2N | 21,030 | 1,091,320            | 1,340         | 800                | 1,160                | 1,440                | 1,650                | 1,290                | 1,200                | 1,200                | 1,120                | 1,190                | 1,000                | 910                  | 1,580                | 1,190                | 890                  | 790                  | 1,650                  | 450                    | 140                |
| N2P | 19,470 | 1,187,377            | 1,350         | 820                | 1,140                | 1,340                | 1,450                | 1,230                | 1,070                | 1,030                | 880                  | 950                  | 850                  | 730                  | 1,260                | 950                  | 790                  | 690                  | 1,710                  | 800                    | 450                |
| N2R | 12,390 | 671,809              | 990           | 470                | 670                  | 820                  | 800                  | 720                  | 660                  | 610                  | 600                  | 600                  | 610                  | 500                  | 910                  | 730                  | 630                  | 530                  | 1,100                  | 360                    | 90                 |
| N2T | 16,770 | 1,165,030            | 1,270         | 780                | 940                  | 1,000                | 1,070                | 880                  | 710                  | 720                  | 650                  | 700                  | 620                  | 580                  | 1,040                | 960                  | 790                  | 680                  | 1,950                  | 940                    | 500                |
| N2V | 15,010 | 990,777              | 1,360         | 740                | 830                  | 920                  | 1,010                | 820                  | 710                  | 640                  | 630                  | 600                  | 480                  | 480                  | 930                  | 830                  | 660                  | 590                  | 1,670                  | 760                    | 360                |
| N2Z | 9,670  | 691,552              | 420           | 300                | 480                  | 540                  | 680                  | 500                  | 420                  | 510                  | 480                  | 540                  | 380                  | 320                  | 650                  | 590                  | 440                  | 380                  | 1,040                  | 840                    | 180                |
| N3A | 13,150 | 818,528              | 490           | 350                | 590                  | 700                  | 850                  | 720                  | 690                  | 770                  | 700                  | 780                  | 640                  | 610                  | 1,080                | 930                  | 700                  | 600                  | 1,360                  | 420                    | 180                |
| N3B | 9,850  | 579,011              | 450           | 270                | 510                  | 610                  | 740                  | 580                  | 550                  | 510                  | 500                  | 530                  | 450                  | 480                  | 850                  | 650                  | 500                  | 410                  | 880                    | 280                    | 100                |
| N3C | 21,090 | 1,217,261            | 1,160         | 700                | 1,050                | 1,270                | 1,630                | 1,270                | 1,160                | 1,180                | 1,090                | 1,070                | 1,040                | 910                  | 1,640                | 1,330                | 1,060                | 850                  | 1,930                  | 570                    | 200                |
| N3E | 1,620  | 90,209               | 130           | 70                 | 100                  | 130                  | 120                  | 100                  | 90                   | 80                   | 70                   | 60                   | 60                   | 60                   | 100                  | 90                   | 80                   | 60                   | 140                    | 50                     | 20                 |
| N3H | 19,670 | 919,815              | 1,080         | 690                | 1,300                | 1,610                | 1,980                | 1,600                | 1,330                | 1,240                | 1,130                | 1,080                | 900                  | 790                  | 1,340                | 990                  | 720                  | 540                  | 970                    | 270                    | 120                |
| N3L | 13,030 | 729,574              | 580           | 370                | 700                  | 850                  | 1,130                | 870                  | 760                  | 750                  | 710                  | 740                  | 610                  | 590                  | 910                  | 760                  | 600                  | 530                  | 1,080                  | 350                    | 140                |
| N3P | 6,740  | 311,693              | 350           | 250                | 410                  | 490                  | 600                  | 480                  | 460                  | 460                  | 410                  | 420                  | 320                  | 290                  | 520                  | 370                  | 270                  | 190                  | 330                    | 80                     | 20                 |
| N3R | 28,800 | 1,401,485            | 1,310         | 870                | 1,730                | 2,140                | 2,860                | 2,080                | 1,950                | 1,880                | 1,640                | 1,680                | 1,470                | 1,210                | 2,110                | 1,480                | 1,1                  |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total  | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |  |
|-----|--------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|--|
| N6C | 24,330 | 1,300,928            | 1,210         | 710                | 1,360                | 1,670                | 2,110                | 1,670                | 1,520                | 1,530                | 1,380                | 1,430                | 1,230                | 1,020                | 1,770                | 1,410                | 1,010                | 810                  | 1,680                  | 570                    | 250                |  |
| N6E | 21,060 | 807,605              | 1,710         | 930                | 1,560                | 1,830                | 2,130                | 1,680                | 1,510                | 1,400                | 1,320                | 1,290                | 1,060                | 860                  | 1,250                | 890                  | 570                  | 360                  | 600                    | 100                    | 40                 |  |
| N6G | 37,520 | 2,150,920            | 3,620         | 1,830              | 2,270                | 2,610                | 2,760                | 2,190                | 1,920                | 1,800                | 1,540                | 1,800                | 1,470                | 1,390                | 2,310                | 1,960                | 1,520                | 1,230                | 3,190                  | 1,390                  | 720                |  |
| N6H | 34,400 | 1,822,040            | 3,240         | 1,500              | 2,050                | 2,480                | 3,040                | 2,280                | 1,950                | 1,850                | 1,710                | 1,660                | 1,440                | 1,170                | 2,070                | 1,790                | 1,320                | 1,080                | 2,380                  | 880                    | 500                |  |
| N6J | 21,940 | 1,001,381            | 1,190         | 770                | 1,440                | 1,750                | 2,360                | 1,570                | 1,480                | 1,480                | 1,340                | 1,330                | 1,090                | 900                  | 1,490                | 1,090                | 720                  | 560                  | 1,050                  | 260                    | 80                 |  |
| N6K | 29,650 | 1,986,320            | 1,450         | 1,000              | 1,340                | 1,720                | 2,060                | 1,520                | 1,440                | 1,510                | 1,500                | 1,610                | 1,310                | 1,160                | 2,190                | 1,940                | 1,490                | 1,330                | 3,130                  | 1,340                  | 620                |  |
| N6L | 3,410  | 169,125              | 290           | 140                | 210                  | 290                  | 290                  | 220                  | 210                  | 170                  | 170                  | 170                  | 150                  | 120                  | 210                  | 190                  | 150                  | 120                  | 230                    | 60                     | 30                 |  |
| N6M | 5,900  | 305,872              | 370           | 220                | 300                  | 410                  | 430                  | 370                  | 360                  | 330                  | 320                  | 320                  | 270                  | 290                  | 460                  | 370                  | 280                  | 220                  | 440                    | 90                     | 40                 |  |
| N6N | 570    | 35,713               | 20            | 10                 | 30                   | 40                   | 50                   | 40                   | 40                   | 30                   | 40                   | 30                   | 30                   | 30                   | 40                   | 40                   | 30                   | 20                   | 50                     | 20                     | 10                 |  |
| N6P | 8,090  | 589,083              | 390           | 210                | 350                  | 430                  | 500                  | 440                  | 380                  | 440                  | 390                  | 420                  | 340                  | 300                  | 570                  | 500                  | 370                  | 360                  | 1,010                  | 460                    | 220                |  |
| N7A | 10,380 | 537,182              | 330           | 330                | 660                  | 820                  | 980                  | 700                  | 720                  | 710                  | 620                  | 650                  | 520                  | 420                  | 690                  | 520                  | 350                  | 280                  | 700                    | 320                    | 70                 |  |
| N7G | 15,470 | 775,966              | 630           | 490                | 880                  | 1,120                | 1,560                | 980                  | 960                  | 980                  | 990                  | 990                  | 770                  | 730                  | 1,180                | 830                  | 560                  | 490                  | 960                    | 270                    | 110                |  |
| N7L | 20,580 | 953,853              | 860           | 690                | 1,420                | 1,630                | 2,150                | 1,610                | 1,510                | 1,490                | 1,330                | 1,220                | 910                  | 780                  | 1,270                | 1,010                | 630                  | 580                  | 1,030                  | 330                    | 110                |  |
| N7M | 20,030 | 970,048              | 970           | 770                | 1,430                | 1,520                | 1,890                | 1,540                | 1,410                | 1,350                | 1,280                | 1,170                | 860                  | 810                  | 1,240                | 920                  | 680                  | 550                  | 1,050                  | 390                    | 190                |  |
| N7S | 22,710 | 1,304,847            | 1,090         | 780                | 1,210                | 1,460                | 1,840                | 1,460                | 1,430                | 1,350                | 1,170                | 1,340                | 1,030                | 880                  | 1,580                | 1,230                | 920                  | 840                  | 1,930                  | 950                    | 230                |  |
| N7T | 20,660 | 901,962              | 1,100         | 850                | 1,640                | 1,790                | 2,270                | 1,730                | 1,660                | 1,410                | 1,180                | 1,090                | 840                  | 720                  | 1,160                | 840                  | 580                  | 430                  | 890                    | 380                    | 120                |  |
| N7V | 9,830  | 604,293              | 350           | 260                | 500                  | 530                  | 770                  | 610                  | 590                  | 630                  | 530                  | 610                  | 490                  | 400                  | 770                  | 810                  | 670                  | 450                  | 340                    | 810                    | 130                |  |
| N7W | 2,270  | 136,549              | 60            | 40                 | 80                   | 120                  | 210                  | 120                  | 160                  | 170                  | 140                  | 160                  | 100                  | 90                   | 190                  | 140                  | 90                   | 80                   | 190                    | 110                    | 20                 |  |
| N7X | 950    | 104,894              | 30            | 20                 | 30                   | 30                   | 50                   | 50                   | 40                   | 40                   | 40                   | 40                   | 40                   | 30                   | 60                   | 80                   | 60                   | 50                   | 130                    | 100                    | 70                 |  |
| N8A | 11,110 | 444,560              | 990           | 440                | 940                  | 1,060                | 1,340                | 840                  | 770                  | 700                  | 610                  | 550                  | 420                  | 390                  | 550                  | 420                  | 280                  | 240                  | 410                    | 130                    | 40                 |  |
| N8H | 21,740 | 1,000,515            | 1,740         | 770                | 1,430                | 1,670                | 1,930                | 1,500                | 1,510                | 1,620                | 1,590                | 1,460                | 1,050                | 890                  | 1,320                | 940                  | 590                  | 440                  | 850                    | 300                    | 170                |  |
| N8M | 9,300  | 484,914              | 410           | 270                | 590                  | 610                  | 770                  | 590                  | 560                  | 610                  | 580                  | 540                  | 520                  | 410                  | 680                  | 540                  | 390                  | 310                  | 690                    | 190                    | 60                 |  |
| N8N | 20,390 | 1,387,120            | 840           | 610                | 950                  | 1,120                | 1,400                | 1,170                | 1,010                | 1,120                | 1,120                | 1,200                | 1,010                | 860                  | 1,520                | 1,270                | 990                  | 950                  | 1,950                  | 890                    | 430                |  |
| N8P | 11,310 | 636,682              | 660           | 410                | 510                  | 720                  | 830                  | 660                  | 600                  | 670                  | 640                  | 700                  | 530                  | 460                  | 830                  | 650                  | 520                  | 500                  | 930                    | 370                    | 110                |  |
| N8R | 10,220 | 449,607              | 740           | 350                | 630                  | 780                  | 910                  | 710                  | 740                  | 700                  | 680                  | 670                  | 510                  | 470                  | 620                  | 480                  | 320                  | 280                  | 480                    | 130                    | 30                 |  |
| N8S | 18,200 | 919,417              | 890           | 510                | 960                  | 1,260                | 1,620                | 1,240                | 1,250                | 1,280                | 1,310                | 1,200                | 960                  | 820                  | 1,260                | 980                  | 670                  | 570                  | 1,000                  | 310                    | 120                |  |
| N8T | 13,830 | 527,972              | 1,030         | 630                | 1,020                | 1,280                | 1,490                | 1,160                | 1,020                | 1,000                | 940                  | 800                  | 600                  | 530                  | 490                  | 520                  | 330                  | 220                  | 390                    | 90                     | 30                 |  |
| N8V |        |                      |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |  |
| N8W | 19,430 | 870,589              | 1,260         | 660                | 1,110                | 1,500                | 1,710                | 1,490                | 1,360                | 1,390                | 1,260                | 1,190                | 940                  | 900                  | 1,290                | 940                  | 730                  | 510                  | 920                    | 230                    | 50                 |  |
| N8X | 12,900 | 482,858              | 980           | 560                | 1,110                | 1,280                | 1,390                | 1,100                | 1,010                | 910                  | 850                  | 680                  | 550                  | 470                  | 630                  | 420                  | 270                  | 200                  | 350                    | 110                    | 30                 |  |
| N8Y | 15,030 | 675,154              | 910           | 480                | 1,060                | 1,240                | 1,570                | 1,240                | 1,140                | 1,080                | 940                  | 880                  | 750                  | 580                  | 880                  | 580                  | 420                  | 320                  | 590                    | 270                    | 110                |  |
| N9A | 19,760 | 625,260              | 2,100         | 1,170              | 2,120                | 2,570                | 2,480                | 1,840                | 1,420                | 1,220                | 950                  | 680                  | 610                  | 480                  | 620                  | 440                  | 280                  | 210                  | 420                    | 140                    | 50                 |  |
| N9B | 16,560 | 521,936              | 2,340         | 1,260              | 1,610                | 1,810                | 1,890                | 1,430                | 1,190                | 870                  | 690                  | 580                  | 480                  | 380                  | 530                  | 390                  | 270                  | 190                  | 400                    | 220                    | 30                 |  |
| N9C | 9,830  | 306,938              | 1,080         | 610                | 950                  | 1,070                | 1,190                | 910                  | 720                  | 650                  | 550                  | 450                  | 320                  | 270                  | 350                  | 230                  | 150                  | 80                   | 200                    | 40                     | 10                 |  |
| N9E | 17,570 | 960,686              | 1,370         | 810                | 1,030                | 1,250                | 1,330                | 1,100                | 990                  | 950                  | 890                  | 900                  | 710                  | 660                  | 1,100                | 950                  | 720                  | 640                  | 1,370                  | 600                    | 220                |  |
| N9G | 16,270 | 878,387              | 1,430         | 790                | 930                  | 1,230                | 1,300                | 1,030                | 900                  | 840                  | 800                  | 780                  | 610                  | 560                  | 800                  | 630                  | 550                  | 1,350                | 670                    | 180                    |                    |  |
| N9H | 10,230 | 686,932              | 570           | 370                | 510                  | 670                  | 710                  | 570                  | 550                  | 520                  | 480                  | 540                  | 410                  | 390                  | 650                  | 550                  | 480                  | 410                  | 1,070                  | 560                    | 250                |  |
| N9J | 16,190 | 1,079,784            | 730           | 510                | 750                  | 900                  | 1,080                | 870                  | 850                  | 820                  | 870                  | 860                  | 810                  | 690                  | 1,060                | 970                  | 820                  | 790                  | 1,670                  | 830                    | 300                |  |
| N9K | 2,180  | 137,543              | 140           | 80                 | 110                  | 140                  | 140                  | 140                  | 120                  | 100                  | 100                  | 100                  | 100                  | 60                   | 130                  | 120                  | 100                  | 120                  | 230                    | 110                    | 30                 |  |
| N9V | 17,330 | 1,003,592            | 720           | 440                | 870                  | 1,040                | 1,400                | 1,070                | 1,080                | 1,050                | 1,050                | 990                  | 860                  | 790                  | 1,270                | 1,030                | 810                  | 740                  | 1,460                  | 450                    | 200                |  |
| N9Y | 12,410 | 732,922              | 600           | 350                | 620                  | 700                  | 1,020                | 800                  | 730                  | 780                  | 900                  | 820                  | 630                  | 540                  | 890                  | 730                  | 520                  | 460                  | 850                    | 330                    | 160                |  |
| POA | 14,130 | 612,616              | 690           | 510                | 990                  | 1,340                | 1,680                | 1,040                | 970                  | 970                  | 890                  | 840                  | 650                  | 580                  | 900                  | 610                  | 390                  | 260                  | 570                    | 190                    | 70                 |  |
| POB | 7,420  | 438,086              | 340           | 220                | 410                  | 530                  | 660                  | 450                  | 430                  | 490                  | 480                  | 450                  | 370                  | 350                  | 580                  | 400                  | 300                  | 200                  | 450                    | 220                    | 110                |  |
| POC | 3,230  | 173,996              | 190           | 120                | 200                  | 260                  | 320                  | 220                  | 200                  | 200                  | 180                  | 180                  | 150                  | 120                  | 230                  | 180                  | 110                  | 90                   | 140                    | 80                     | 60                 |  |
| POE | 2,700  | 140,957              | 130           | 90                 | 180                  | 200                  | 280                  | 180                  | 170                  | 190                  | 150                  | 180                  | 110                  | 110                  | 180                  | 120                  | 110                  | 90                   | 160                    | 60                     | 30                 |  |
| POG | 2,700  | 141,680              | 210           | 100                | 140                  | 230                  | 250                  | 150                  | 200                  | 190                  | 150                  | 170                  | 110                  | 110                  | 190                  | 100                  | 90                   | 60                   | 150                    | 50                     | 40                 |  |
| POH | 26,340 | 1,264,711            | 1,380         | 830                | 1,800                | 2,240                | 2,630                | 1,740                | 1,650                | 1,560                | 1,540                | 1,530                | 1,160                | 1,050                | 1,900                | 1,340                | 940                  | 740                  | 1,670                  | 510                    | 130                |  |
| POJ | 16,850 | 814,484              | 890           | 590                | 1,300                | 1,560                | 1,760                | 1,160                | 1,070                | 950                  | 830                  | 820                  | 740                  | 570                  | 1,040                | 840                  | 630                  | 470                  | 1,210                  | 330                    | 100                |  |
| POK | 8,940  | 452,849              | 490           | 310                | 610                  | 720                  | 880                  | 560                  | 490                  | 460                  | 500                  | 500                  | 420                  | 320                  | 560                  | 420                  | 300                  | 290                  | 850                    | 220                    | 40                 |  |
| POL | 18,320 | 766,478              | 2,570         | 780                | 1,390                | 1,560                | 1,840                | 1,040                | 930                  | 910                  | 780                  | 760                  | 640                  | 590                  | 1,070                | 880                  | 650                  | 500                  | 1,110                  | 270                    | 60                 |  |
| POM | 40,240 | 2,091,595            | 2,010         | 1,220              | 2,270                | 2,680                | 3,450                | 2,410                | 2,420                | 2,480                | 2,510                | 2,300                | 1,890                | 1,710                | 3,010                | 2,320                | 1,610                | 1,400                | 3,530                  | 870                    | 150                |  |
| PON | 7,250  | 399,652              | 350           | 280                | 470                  | 440                  | 580                  | 410                  | 420                  | 400                  | 360                  | 380                  | 310                  | 290                  | 500                  | 390                  | 320                  | 250                  | 900                    | 170                    | 40                 |  |
| POP | 15,440 | 574,319              | 2,320         | 760                | 1,340                | 1,460                | 1,550                | 1,000                | 860                  | 860                  | 760                  | 720                  | 550                  | 470                  | 690                  | 570                  | 410                  | 290                  | 620                    | 170                    | 50                 |  |
| POR | 10,450 | 467,197              | 710           | 410                | 750                  | 950                  | 1,110                | 750                  | 650                  | 650                  | 570                  | 550                  | 430                  | 390                  | 620                  | 460                  | 390                  | 270                  | 620                    | 140                    | 50                 |  |
| POS | 8,120  | 406,245              | 410           | 280                | 510                  | 540                  | 740                  | 490                  | 490                  | 510                  | 460                  | 450                  | 370                  | 320                  | 570                  | 470                  | 420                  | 310                  | 640                    | 120                    | 30                 |  |
| POT | 24,740 | 1,162,836            | 2,660         | 920                | 1,700                | 1,820                | 2,130                | 1,470                | 1,460                | 1,320                | 1,250                | 1,250                | 1,020                | 890                  | 1,500                | 1,250                | 900                  | 750                  | 1,810                  | 510                    | 140                |  |
| POV | 15,040 | 415,727              | 6,700         | 730                | 980                  | 1,030                | 690                  | 470                  | 380                  | 400                  | 350                  | 330                  | 290                  | 280                  | 470                  | 390                  | 280                  | 250                  | 750                    | 230                    | 70                 |  |
| POW | 4,960  | 219,965              | 600           | 230                | 340                  | 420                  | 450                  | 270                  | 260                  | 240                  | 260                  | 230                  | 190                  | 180                  | 290                  | 250                  | 200                  | 160                  | 300                    | 80                     | 20                 |  |
| POX | 5,630  | 232,843              | 1,220         | 260                | 380                  | 380                  | 370                  | 250                  | 240                  | 230                  | 210                  | 280                  | 210                  | 180                  | 340                  | 290                  | 200                  | 150                  | 290                    | 110                    | 40                 |  |
| POY | 60     | 2,339                |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |  |
| P1A | 13,490 | 645,079              | 640           | 470                | 980                  | 1,030                | 1,220                | 860                  | 880                  | 890                  | 830                  | 790                  | 630                  | 600                  | 1,010                |                      |                      |                      |                        |                        |                    |  |





Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA   | Total      | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-------|------------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| P6C   | 15,440     | 689,068               | 630           | 480                | 960                  | 1,140                | 1,600                | 1,220                | 1,200                | 1,180                | 1,070                | 970                  | 720                  | 560                  | 980                  | 750                  | 600                  | 480                  | 750                    | 130                    | 30                 |
| P7A   | 22,540     | 1,134,354             | 1,090         | 630                | 1,240                | 1,460                | 2,070                | 1,490                | 1,480                | 1,390                | 1,360                | 1,420                | 1,070                | 980                  | 1,750                | 1,350                | 1,010                | 780                  | 1,480                  | 390                    | 110                |
| P7B   | 18,470     | 918,732               | 1,280         | 830                | 1,230                | 1,390                | 1,710                | 1,320                | 1,140                | 1,070                | 990                  | 920                  | 740                  | 680                  | 1,160                | 910                  | 660                  | 590                  | 1,210                  | 470                    | 170                |
| P7C   | 16,940     | 770,627               | 1,020         | 610                | 1,050                | 1,260                | 1,600                | 1,290                | 1,130                | 1,100                | 1,040                | 1,020                | 800                  | 710                  | 1,120                | 900                  | 640                  | 480                  | 910                    | 200                    | 50                 |
| P7E   | 16,520     | 752,245               | 840           | 560                | 1,050                | 1,140                | 1,570                | 1,250                | 1,080                | 1,160                | 990                  | 1,020                | 880                  | 780                  | 1,270                | 880                  | 610                  | 460                  | 770                    | 180                    | 50                 |
| P7G   | 10,170     | 650,309               | 410           | 290                | 480                  | 480                  | 690                  | 500                  | 480                  | 510                  | 510                  | 550                  | 480                  | 440                  | 850                  | 730                  | 550                  | 510                  | 1,190                  | 410                    | 120                |
| P7J   | 3,870      | 233,137               | 350           | 120                | 190                  | 240                  | 280                  | 160                  | 170                  | 170                  | 170                  | 220                  | 150                  | 160                  | 310                  | 220                  | 200                  | 160                  | 420                    | 150                    | 50                 |
| P7K   | 5,410      | 359,807               | 170           | 130                | 200                  | 270                  | 350                  | 290                  | 250                  | 300                  | 290                  | 350                  | 280                  | 220                  | 470                  | 370                  | 300                  | 270                  | 590                    | 240                    | 80                 |
| P7L   | 1,630      | 92,517                | 80            | 40                 | 80                   | 100                  | 100                  | 70                   | 100                  | 100                  | 80                   | 110                  | 80                   | 100                  | 130                  | 110                  | 90                   | 70                   | 120                    | 50                     | 10                 |
| P8N   | 8,630      | 452,510               | 450           | 280                | 460                  | 510                  | 700                  | 490                  | 540                  | 530                  | 510                  | 520                  | 430                  | 370                  | 610                  | 560                  | 390                  | 380                  | 710                    | 140                    | 40                 |
| P8T   | 3,930      | 218,474               | 510           | 150                | 190                  | 190                  | 220                  | 150                  | 150                  | 170                  | 140                  | 200                  | 180                  | 160                  | 310                  | 320                  | 200                  | 170                  | 390                    | 90                     | 40                 |
| P9A   | 8,000      | 413,998               | 670           | 300                | 450                  | 490                  | 640                  | 430                  | 410                  | 440                  | 410                  | 480                  | 380                  | 370                  | 630                  | 430                  | 370                  | 290                  | 600                    | 160                    | 50                 |
| P9N   | 11,250     | 587,059               | 830           | 370                | 630                  | 710                  | 850                  | 590                  | 620                  | 620                  | 570                  | 670                  | 550                  | 580                  | 890                  | 720                  | 520                  | 390                  | 860                    | 200                    | 90                 |
| TOTAL | 11,356,750 | 640,537,043           | 739,890       | 449,900            | 696,970              | 890,600              | 994,150              | 755,960              | 672,760              | 624,870              | 571,740              | 555,850              | 471,150              | 416,460              | 717,900              | 582,240              | 457,630              | 381,000              | 870,140                | 343,600                | 163,950            |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total           | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|--------------|-----------------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| <b>PR 46</b> | <b>Manitoba</b> |                      |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| ROA          | 29,590          | 1,335,024            | 2,570         | 1,330              | 1,970                | 2,220                | 2,510                | 2,060                | 1,890                | 1,730                | 1,600                | 1,620                | 1,370                | 1,190                | 1,990                | 1,540                | 1,140                | 890                  | 1,470                  | 360                    | 150                |
| ROB          | 27,490          | 422,957              | 13,700        | 2,400              | 2,640                | 2,670                | 1,700                | 760                  | 560                  | 420                  | 300                  | 260                  | 210                  | 180                  | 280                  | 270                  | 190                  | 200                  | 530                    | 220                    | 10                 |
| ROC          | 41,080          | 1,701,012            | 5,350         | 2,010              | 2,790                | 3,320                | 3,930                | 2,760                | 2,530                | 2,330                | 2,040                | 2,000                | 1,620                | 1,370                | 2,150                | 1,830                | 1,350                | 1,030                | 1,890                  | 600                    | 210                |
| ROE          | 28,780          | 1,337,984            | 2,720         | 1,020              | 1,640                | 2,010                | 2,580                | 1,930                | 1,910                | 1,840                | 1,570                | 1,620                | 1,290                | 1,140                | 1,840                | 1,470                | 1,160                | 860                  | 1,630                  | 440                    | 130                |
| ROG          | 32,060          | 1,582,476            | 2,300         | 1,430              | 1,870                | 2,300                | 2,610                | 2,230                | 2,270                | 2,000                | 1,800                | 1,890                | 1,600                | 1,340                | 2,150                | 1,660                | 1,210                | 910                  | 1,590                  | 570                    | 340                |
| ROH          | 10,210          | 377,927              | 1,520         | 570                | 850                  | 1,070                | 980                  | 630                  | 600                  | 490                  | 420                  | 440                  | 370                  | 340                  | 550                  | 370                  | 280                  | 230                  | 350                    | 100                    | 40                 |
| ROJ          | 21,590          | 937,104              | 1,780         | 970                | 1,400                | 1,910                | 2,030                | 1,550                | 1,380                | 1,300                | 1,250                | 1,280                | 1,040                | 950                  | 1,280                | 960                  | 690                  | 490                  | 900                    | 320                    | 110                |
| ROK          | 19,890          | 976,954              | 1,070         | 700                | 1,130                | 1,380                | 1,730                | 1,450                | 1,340                | 1,210                | 1,150                | 1,170                | 1,010                | 880                  | 1,620                | 1,240                | 860                  | 590                  | 990                    | 240                    | 140                |
| ROL          | 20,310          | 773,821              | 2,150         | 940                | 1,670                | 2,180                | 2,420                | 1,550                | 1,370                | 1,130                | 960                  | 910                  | 750                  | 590                  | 940                  | 760                  | 560                  | 430                  | 730                    | 190                    | 100                |
| ROM          | 14,580          | 687,502              | 1,210         | 620                | 940                  | 1,150                | 1,340                | 1,000                | 980                  | 800                  | 770                  | 800                  | 660                  | 510                  | 940                  | 780                  | 530                  | 420                  | 760                    | 280                    | 110                |
| RIA          | 16,930          | 907,446              | 920           | 620                | 910                  | 1,110                | 1,410                | 1,250                | 1,150                | 980                  | 950                  | 990                  | 820                  | 660                  | 1,170                | 1,010                | 800                  | 560                  | 1,130                  | 340                    | 160                |
| RIB          | 250             | 13,160               |               |                    | 10                   |                      | 20                   | 20                   | 20                   | 10                   | 20                   | 20                   | 10                   | 10                   | 30                   | 20                   | 10                   | 10                   | 20                     |                        |                    |
| R1C          | 3,170           | 178,658              | 160           | 90                 | 130                  | 170                  | 240                  | 210                  | 190                  | 170                  | 210                  | 170                  | 170                  | 170                  | 250                  | 170                  | 150                  | 160                  | 250                    | 100                    | 30                 |
| R1N          | 15,070          | 627,023              | 860           | 1,390              | 1,310                | 1,290                | 1,330                | 1,140                | 980                  | 920                  | 710                  | 750                  | 660                  | 560                  | 840                  | 670                  | 480                  | 370                  | 580                    | 160                    | 90                 |
| R2C          | 25,640          | 1,232,092            | 1,390         | 810                | 1,280                | 1,390                | 1,910                | 1,850                | 1,770                | 1,770                | 1,740                | 1,620                | 1,450                | 1,330                | 2,100                | 1,590                | 1,220                | 840                  | 1,300                  | 230                    | 60                 |
| R2E          | 7,920           | 674,661              | 350           | 230                | 300                  | 400                  | 430                  | 370                  | 390                  | 360                  | 330                  | 390                  | 350                  | 290                  | 570                  | 570                  | 450                  | 400                  | 940                    | 490                    | 330                |
| R2G          | 27,480          | 1,384,465            | 1,340         | 840                | 1,280                | 1,760                | 2,590                | 2,150                | 1,830                | 1,820                | 1,700                | 1,650                | 1,390                | 1,210                | 2,020                | 1,570                | 1,230                | 900                  | 1,570                  | 440                    | 190                |
| R2H          | 12,560          | 613,490              | 630           | 500                | 680                  | 890                  | 1,190                | 1,000                | 850                  | 830                  | 730                  | 750                  | 590                  | 500                  | 830                  | 660                  | 510                  | 420                  | 730                    | 180                    | 100                |
| R2J          | 21,470          | 1,135,316            | 1,150         | 710                | 990                  | 1,180                | 1,580                | 1,510                | 1,360                | 1,390                | 1,310                | 1,370                | 1,120                | 980                  | 1,630                | 1,170                | 1,050                | 790                  | 1,350                  | 440                    | 140                |
| R2K          | 26,390          | 1,144,817            | 1,600         | 970                | 1,460                | 1,790                | 2,450                | 2,170                | 2,070                | 1,940                | 1,730                | 1,730                | 1,380                | 1,190                | 1,850                | 1,240                | 920                  | 700                  | 920                    | 230                    | 60                 |
| R2L          | 11,060          | 417,827              | 810           | 470                | 740                  | 920                  | 1,170                | 980                  | 970                  | 870                  | 750                  | 670                  | 590                  | 420                  | 650                  | 370                  | 270                  | 160                  | 210                    | 50                     | 10                 |
| R2M          | 30,310          | 1,510,865            | 2,000         | 1,060              | 1,630                | 1,970                | 2,730                | 2,470                | 2,140                | 1,900                | 1,860                | 1,760                | 1,450                | 1,250                | 2,160                | 1,610                | 1,160                | 850                  | 1,600                  | 470                    | 260                |
| R2N          | 25,680          | 1,502,506            | 1,350         | 770                | 1,000                | 1,370                | 1,770                | 1,630                | 1,550                | 1,520                | 1,370                | 1,560                | 1,270                | 1,150                | 1,970                | 1,730                | 1,300                | 1,140                | 2,210                  | 740                    | 280                |
| R2P          | 27,730          | 1,077,169            | 2,290         | 1,240              | 1,750                | 2,320                | 2,590                | 2,600                | 2,240                | 1,920                | 1,790                | 1,620                | 1,270                | 1,030                | 1,620                | 1,110                | 760                  | 520                  | 840                    | 170                    | 60                 |
| R2R          | 20,310          | 810,244              | 1,510         | 860                | 1,140                | 1,560                | 1,820                | 1,720                | 1,630                | 1,440                | 1,470                | 1,220                | 1,090                | 900                  | 1,360                | 990                  | 590                  | 390                  | 520                    | 100                    | 20                 |
| R2V          | 29,450          | 1,371,844            | 1,700         | 1,030              | 1,560                | 1,940                | 2,590                | 2,290                | 2,140                | 1,970                | 1,940                | 1,820                | 1,600                | 1,360                | 2,120                | 1,540                | 1,130                | 910                  | 1,350                  | 350                    | 130                |
| R2W          | 20,130          | 643,270              | 1,740         | 1,120              | 1,730                | 2,100                | 2,530                | 1,980                | 1,720                | 1,410                | 1,210                | 1,040                | 790                  | 580                  | 860                  | 500                  | 320                  | 190                  | 230                    | 50                     | 20                 |
| R2X          | 15,080          | 552,159              | 1,040         | 640                | 900                  | 1,130                | 1,390                | 1,410                | 1,450                | 1,320                | 1,200                | 1,060                | 840                  | 620                  | 860                  | 500                  | 300                  | 160                  | 200                    | 40                     | 10                 |
| R2Y          | 15,200          | 738,849              | 780           | 470                | 680                  | 830                  | 1,230                | 1,120                | 1,060                | 1,070                | 990                  | 1,010                | 830                  | 660                  | 1,290                | 980                  | 700                  | 500                  | 770                    | 180                    | 50                 |
| R3A          | 3,310           | 89,704               | 420           | 310                | 340                  | 430                  | 410                  | 340                  | 260                  | 200                  | 140                  | 110                  | 80                   | 50                   | 80                   | 50                   | 30                   | 20                   | 30                     | 10                     | 10                 |
| R3B          | 9,560           | 352,750              | 830           | 740                | 930                  | 1,090                | 1,140                | 1,020                | 850                  | 600                  | 440                  | 350                  | 290                  | 190                  | 310                  | 200                  | 150                  | 110                  | 230                    | 90                     | 80                 |
| R3C          | 15,780          | 593,552              | 1,670         | 980                | 1,660                | 1,970                | 1,710                | 1,300                | 1,100                | 930                  | 750                  | 630                  | 510                  | 400                  | 620                  | 420                  | 300                  | 210                  | 350                    | 160                    | 120                |
| R3E          | 14,260          | 485,323              | 1,140         | 720                | 1,020                | 1,320                | 1,540                | 1,420                | 1,280                | 1,110                | 1,070                | 820                  | 640                  | 480                  | 680                  | 410                  | 250                  | 140                  | 190                    | 30                     | 10                 |
| R3G          | 19,210          | 825,653              | 1,290         | 790                | 1,230                | 1,500                | 1,810                | 1,670                | 1,530                | 1,290                | 1,250                | 1,120                | 930                  | 710                  | 1,180                | 830                  | 630                  | 460                  | 740                    | 180                    | 80                 |
| R3H          | 170             | 10,950               | 10            | 10                 | 10                   | 10                   | 10                   | 20                   | 20                   | 10                   | 20                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                     | 10                     | 10                 |
| R3J          | 22,150          | 1,077,683            | 1,150         | 670                | 1,040                | 1,250                | 1,770                | 1,670                | 1,570                | 1,580                | 1,410                | 1,450                | 1,240                | 1,020                | 1,750                | 1,370                | 990                  | 720                  | 1,150                  | 270                    | 90                 |
| R3K          | 10,250          | 615,377              | 410           | 300                | 470                  | 540                  | 760                  | 690                  | 700                  | 620                  | 600                  | 610                  | 550                  | 470                  | 780                  | 670                  | 490                  | 420                  | 770                    | 250                    | 160                |
| R3L          | 16,070          | 823,764              | 880           | 670                | 790                  | 1,030                | 1,350                | 1,230                | 1,100                | 1,040                | 920                  | 930                  | 780                  | 670                  | 1,200                | 890                  | 700                  | 540                  | 920                    | 280                    | 150                |
| R3M          | 17,460          | 1,177,502            | 900           | 540                | 800                  | 970                  | 1,400                | 1,210                | 1,120                | 1,020                | 900                  | 950                  | 770                  | 680                  | 1,250                | 1,000                | 780                  | 630                  | 1,390                  | 630                    | 510                |
| R3N          | 13,060          | 919,498              | 660           | 420                | 580                  | 670                  | 850                  | 750                  | 740                  | 630                  | 610                  | 670                  | 590                  | 470                  | 1,030                | 890                  | 720                  | 650                  | 1,280                  | 530                    | 320                |
| R3P          | 17,280          | 1,758,599            | 960           | 620                | 710                  | 850                  | 1,150                | 940                  | 870                  | 790                  | 710                  | 840                  | 660                  | 630                  | 1,120                | 1,050                | 810                  | 690                  | 1,740                  | 1,120                  | 1,020              |
| R3R          | 20,430          | 1,315,722            | 880           | 630                | 770                  | 1,020                | 1,270                | 1,220                | 1,070                | 1,220                | 1,040                | 1,210                | 1,010                | 920                  | 1,670                | 1,490                | 1,120                | 960                  | 1,870                  | 710                    | 350                |
| R3S          | 450             | 62,596               | 30            | 20                 | 30                   | 20                   | 20                   | 30                   | 20                   | 20                   | 20                   | 20                   | 10                   | 20                   | 30                   | 20                   | 20                   | 20                   | 50                     | 40                     | 30                 |
| R3T          | 40,930          | 1,805,296            | 5,320         | 2,270              | 2,490                | 3,020                | 3,700                | 3,110                | 2,580                | 2,230                | 1,970                | 1,940                | 1,530                | 1,330                | 2,210                | 1,720                | 1,330                | 1,110                | 2,030                  | 770                    | 290                |
| R3V          | 5,130           | 262,552              | 340           | 180                | 270                  | 340                  | 410                  | 380                  | 300                  | 360                  | 290                  | 290                  | 210                  | 240                  | 390                  | 320                  | 230                  | 170                  | 300                    | 80                     | 50                 |
| R3W          | 11,190          | 561,106              | 670           | 370                | 520                  | 660                  | 790                  | 800                  | 770                  | 690                  | 640                  | 650                  | 610                  | 490                  | 910                  | 720                  | 550                  | 420                  | 740                    | 170                    | 40                 |
| R3X          | 15,940          | 1,119,134            | 980           | 550                | 630                  | 800                  | 910                  | 760                  | 760                  | 710                  | 720                  | 720                  | 680                  | 610                  | 1,170                | 1,060                | 970                  | 820                  | 1,980                  | 720                    | 370                |
| R3Y          | 23,520          | 1,443,583            | 2,630         | 1,110              | 1,170                | 1,380                | 1,670                | 1,550                | 1,250                | 1,070                | 1,040                | 970                  | 840                  | 790                  | 1,370                | 1,230                | 1,060                | 960                  | 2,110                  | 820                    | 480                |
| R4A          | 3,820           | 240,769              | 170           | 120                | 170                  | 190                  | 250                  | 200                  | 240                  | 220                  | 180                  | 210                  | 160                  | 160                  | 300                  | 250                  | 230                  | 200                  | 390                    | 140                    | 60                 |
| R4G          | 1,250           | 102,325              | 50            | 30                 | 50                   | 60                   | 60                   | 60                   | 70                   | 50                   | 50                   | 60                   | 40                   | 40                   | 90                   | 90                   | 80                   | 90                   | 190                    | 90                     | 40                 |
| R4H          | 2,040           | 183,509              | 130           | 60                 | 70                   | 80                   | 110                  | 80                   | 100                  | 80                   | 90                   | 100                  | 100                  | 90                   | 140                  | 130                  | 110                  | 100                  | 220                    | 130                    | 120                |
| R4J          | 950             | 68,321               | 40            | 60                 | 30                   | 70                   | 40                   | 60                   | 70                   | 40                   | 40                   | 40                   | 30                   | 30                   | 70                   | 60                   | 60                   | 50                   | 100                    | 40                     | 40                 |
| R4K          | 700             | 36,591               | 40            | 140                | 50                   | 60                   | 40                   | 30                   | 40                   | 30                   |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total               | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|--------------|---------------------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| <b>PR 47</b> | <b>Saskatchewan</b> |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| S0A          | 41,160              | 1,894,482             | 3,340         | 1,740              | 2,910                | 3,580                | 4,850                | 2,830                | 2,400                | 2,190                | 2,030                | 2,040                | 1,680                | 1,400                | 2,210                | 1,800                | 1,310                | 1,050                | 2,500                  | 1,060                  | 230                |
| S0C          | 16,210              | 894,115               | 1,100         | 670                | 850                  | 1,070                | 1,310                | 1,040                | 900                  | 910                  | 860                  | 850                  | 760                  | 610                  | 1,070                | 890                  | 720                  | 570                  | 1,330                  | 530                    | 170                |
| S0E          | 26,200              | 1,199,919             | 2,330         | 1,140              | 1,710                | 2,080                | 2,700                | 1,780                | 1,540                | 1,440                | 1,350                | 1,320                | 1,080                | 970                  | 1,650                | 1,190                | 1,020                | 780                  | 1,430                  | 520                    | 170                |
| S0G          | 49,960              | 2,584,962             | 4,040         | 1,910              | 2,790                | 3,470                | 4,530                | 3,130                | 2,820                | 2,720                | 2,470                | 2,640                | 2,260                | 2,070                | 3,250                | 2,660                | 2,150                | 1,710                | 3,660                  | 1,210                  | 450                |
| S0H          | 16,490              | 826,646               | 960           | 610                | 1,220                | 1,240                | 1,550                | 1,180                | 1,030                | 930                  | 890                  | 950                  | 770                  | 640                  | 1,080                | 820                  | 630                  | 490                  | 1,020                  | 320                    | 170                |
| S0J          | 36,110              | 1,227,009             | 7,610         | 2,160              | 3,060                | 3,340                | 3,850                | 2,090                | 1,710                | 1,470                | 1,340                | 1,300                | 1,080                | 840                  | 1,390                | 1,210                | 940                  | 720                  | 1,400                  | 500                    | 120                |
| S0K          | 68,100              | 3,595,118             | 4,410         | 2,690              | 3,730                | 4,620                | 5,680                | 4,380                | 3,850                | 3,740                | 3,500                | 3,620                | 3,190                | 2,690                | 4,860                | 3,920                | 3,080                | 2,420                | 5,270                  | 1,980                  | 490                |
| S0L          | 24,130              | 1,320,708             | 1,130         | 790                | 1,410                | 1,760                | 1,910                | 1,620                | 1,470                | 1,380                | 1,310                | 1,410                | 1,100                | 1,030                | 1,710                | 1,350                | 1,120                | 870                  | 1,820                  | 720                    | 220                |
| S0M          | 34,660              | 1,326,420             | 5,580         | 1,820              | 2,620                | 3,150                | 4,120                | 2,280                | 1,790                | 1,620                | 1,430                | 1,300                | 1,090                | 970                  | 1,560                | 1,220                | 940                  | 780                  | 1,610                  | 630                    | 140                |
| S0N          | 16,140              | 769,665               | 970           | 670                | 1,540                | 1,650                | 1,360                | 1,030                | 1,030                | 830                  | 800                  | 960                  | 710                  | 600                  | 930                  | 780                  | 560                  | 450                  | 790                    | 340                    | 140                |
| S0P          | 4,900               | 145,864               | 1,390         | 390                | 480                  | 490                  | 450                  | 210                  | 180                  | 130                  | 130                  | 130                  | 100                  | 70                   | 100                  | 120                  | 100                  | 100                  | 250                    | 60                     | 20                 |
| S2V          | 650                 | 50,974                | 20            | 20                 | 20                   | 30                   | 30                   | 30                   | 30                   | 30                   | 30                   | 40                   | 40                   | 20                   | 50                   | 40                   | 30                   | 30                   | 100                    | 40                     | 20                 |
| S3N          | 15,330              | 754,601               | 850           | 510                | 860                  | 1,150                | 1,550                | 1,100                | 990                  | 910                  | 840                  | 840                  | 700                  | 620                  | 1,080                | 770                  | 610                  | 530                  | 1,020                  | 330                    | 70                 |
| S4A          | 9,810               | 619,194               | 470           | 330                | 440                  | 470                  | 700                  | 610                  | 570                  | 490                  | 530                  | 540                  | 430                  | 390                  | 670                  | 600                  | 510                  | 400                  | 1,070                  | 490                    | 110                |
| S4H          | 9,650               | 558,488               | 440           | 290                | 480                  | 570                  | 810                  | 680                  | 600                  | 550                  | 530                  | 530                  | 480                  | 470                  | 670                  | 560                  | 480                  | 340                  | 800                    | 280                    | 90                 |
| S4K          |                     |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| S4L          | 4,730               | 404,358               | 190           | 100                | 210                  | 190                  | 250                  | 200                  | 170                  | 160                  | 190                  | 190                  | 180                  | 180                  | 340                  | 300                  | 300                  | 270                  | 790                    | 390                    | 160                |
| S4M          |                     |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| S4N          | 23,540              | 1,109,929             | 1,570         | 780                | 1,180                | 1,500                | 2,020                | 1,770                | 1,610                | 1,580                | 1,410                | 1,390                | 1,170                | 1,010                | 1,780                | 1,390                | 990                  | 740                  | 1,310                  | 290                    | 60                 |
| S4P          | 11,740              | 561,428               | 680           | 450                | 650                  | 1,190                | 1,850                | 940                  | 740                  | 650                  | 560                  | 520                  | 410                  | 340                  | 600                  | 500                  | 350                  | 300                  | 640                    | 240                    | 120                |
| S4R          | 27,120              | 1,310,678             | 1,600         | 910                | 1,250                | 1,640                | 2,270                | 1,930                | 1,870                | 1,770                | 1,790                | 1,770                | 1,430                | 1,260                | 2,140                | 1,600                | 1,210                | 860                  | 1,420                  | 310                    | 90                 |
| S4S          | 28,100              | 1,683,207             | 1,890         | 1,110              | 1,260                | 1,670                | 2,050                | 1,780                | 1,540                | 1,500                | 1,330                | 1,500                | 1,300                | 1,090                | 1,920                | 1,660                | 1,370                | 1,190                | 2,470                  | 1,040                  | 440                |
| S4T          | 23,060              | 1,065,202             | 1,400         | 780                | 1,190                | 1,620                | 2,380                | 1,800                | 1,600                | 1,480                | 1,400                | 1,180                | 1,160                | 1,000                | 1,660                | 1,240                | 930                  | 680                  | 1,170                  | 300                    | 80                 |
| S4V          | 25,500              | 1,923,491             | 1,460         | 850                | 940                  | 1,160                | 1,420                | 1,300                | 1,130                | 1,050                | 1,070                | 1,290                | 990                  | 1,000                | 1,920                | 1,740                | 1,500                | 1,330                | 3,200                  | 1,490                  | 690                |
| S4W          | 9,940               | 572,833               | 890           | 350                | 380                  | 520                  | 600                  | 560                  | 530                  | 460                  | 480                  | 500                  | 460                  | 450                  | 780                  | 680                  | 560                  | 430                  | 910                    | 310                    | 100                |
| S4X          | 22,210              | 1,404,614             | 1,060         | 600                | 810                  | 980                  | 1,260                | 1,060                | 1,100                | 1,120                | 1,140                | 1,280                | 1,140                | 1,010                | 1,930                | 1,960                | 1,390                | 1,170                | 2,530                  | 750                    | 210                |
| S4Y          | 4,110               | 296,266               | 170           | 110                | 130                  | 140                  | 170                  | 180                  | 160                  | 160                  | 200                  | 220                  | 180                  | 180                  | 350                  | 320                  | 280                  | 260                  | 620                    | 230                    | 50                 |
| S4Z          | 1,030               | 57,078                | 50            | 30                 | 30                   | 40                   | 50                   | 60                   | 60                   | 60                   | 60                   | 60                   | 60                   | 50                   | 120                  | 80                   | 60                   | 50                   | 80                     | 20                     | 20                 |
| S6H          | 23,110              | 1,154,104             | 1,110         | 830                | 1,290                | 1,610                | 2,230                | 1,810                | 1,670                | 1,520                | 1,370                | 1,340                | 1,030                | 900                  | 1,490                | 1,160                | 970                  | 700                  | 1,490                  | 470                    | 130                |
| S6J          | 4,200               | 263,580               | 200           | 150                | 210                  | 290                  | 320                  | 270                  | 210                  | 230                  | 210                  | 210                  | 180                  | 150                  | 270                  | 230                  | 180                  | 160                  | 470                    | 220                    | 70                 |
| S6K          | 970                 | 63,374                | 50            | 30                 | 30                   | 50                   | 60                   | 50                   | 40                   | 50                   | 50                   | 50                   | 40                   | 30                   | 70                   | 60                   | 60                   | 50                   | 130                    | 50                     | 20                 |
| S6V          | 30,880              | 1,411,034             | 2,510         | 1,360              | 1,820                | 2,220                | 3,150                | 2,380                | 2,020                | 1,830                | 1,650                | 1,590                | 1,370                | 1,080                | 1,760                | 1,490                | 1,240                | 980                  | 1,770                  | 530                    | 150                |
| S6W          | 230                 | 20,139                | 10            | 10                 | 10                   | 10                   | 20                   | 10                   | 20                   | 10                   | 10                   | 20                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 20                     | 20                     | 20                 |
| S6X          | 1,730               | 127,467               | 90            | 60                 | 60                   | 70                   | 90                   | 70                   | 60                   | 70                   | 60                   | 70                   | 70                   | 70                   | 140                  | 100                  | 130                  | 130                  | 260                    | 110                    | 30                 |
| S7A          | 100                 | 9,714                 |               |                    |                      |                      | 10                   |                      | 10                   |                      |                      |                      |                      | 10                   | 10                   |                      | 10                   | 10                   | 20                     | 10                     | 10                 |
| S7B          | 340                 | 14,080                | 30            | 20                 | 10                   | 30                   | 30                   | 30                   | 30                   | 30                   | 20                   | 20                   | 30                   | 10                   | 30                   | 10                   | 10                   | 10                   | 10                     | 10                     | 10                 |
| S7C          | 740                 | 59,853                | 30            | 20                 | 30                   | 30                   | 40                   | 20                   | 20                   | 30                   | 40                   | 40                   | 20                   | 20                   | 60                   | 60                   | 40                   | 40                   | 130                    | 60                     | 20                 |
| S7H          | 29,000              | 1,511,313             | 2,100         | 1,220              | 1,420                | 1,880                | 2,420                | 2,100                | 1,880                | 1,770                | 1,560                | 1,520                | 1,320                | 1,140                | 2,000                | 1,520                | 1,260                | 950                  | 1,880                  | 820                    | 260                |
| S7J          | 24,530              | 1,392,326             | 1,300         | 840                | 1,050                | 1,380                | 2,100                | 1,550                | 1,480                | 1,510                | 1,350                | 1,390                | 1,140                | 1,090                | 1,820                | 1,520                | 1,140                | 970                  | 1,890                  | 710                    | 290                |
| S7K          | 32,920              | 2,008,527             | 1,830         | 1,080              | 1,560                | 2,050                | 2,700                | 2,060                | 1,880                | 1,870                | 1,640                | 1,690                | 1,470                | 1,340                | 2,330                | 2,020                | 1,610                | 1,300                | 2,640                  | 1,320                  | 560                |
| S7L          | 30,920              | 1,314,547             | 2,100         | 1,170              | 1,740                | 2,240                | 3,080                | 2,610                | 2,340                | 2,160                | 1,910                | 1,730                | 1,480                | 1,340                | 2,100                | 1,520                | 1,110                | 780                  | 1,180                  | 300                    | 40                 |
| S7M          | 23,710              | 1,031,509             | 1,710         | 990                | 1,460                | 1,930                | 2,510                | 2,010                | 1,770                | 1,640                | 1,380                | 1,250                | 960                  | 910                  | 1,410                | 1,030                | 800                  | 550                  | 950                    | 340                    | 120                |
| S7N          | 20,720              | 1,251,626             | 1,540         | 860                | 1,050                | 1,260                | 1,540                | 1,320                | 1,190                | 1,090                | 1,010                | 980                  | 880                  | 790                  | 1,330                | 1,200                | 970                  | 800                  | 1,620                  | 900                    | 400                |
| S7P          | 210                 | 28,187                | 10            | 10                 | 10                   |                      |                      |                      |                      |                      | 10                   | 10                   | 10                   | 10                   | 10                   | 20                   | 10                   | 10                   | 30                     | 30                     | 30                 |
| S7R          | 6,160               | 323,628               | 380           | 220                | 270                  | 340                  | 410                  | 370                  | 370                  | 400                  | 320                  | 320                  | 320                  | 310                  | 500                  | 430                  | 330                  | 270                  | 480                    | 130                    | 20                 |
| S7S          | 4,790               | 302,010               | 270           | 200                | 240                  | 230                  | 310                  | 250                  | 260                  | 250                  | 220                  | 230                  | 180                  | 190                  | 360                  | 300                  | 260                  | 240                  | 500                    | 260                    | 70                 |
| S7T          | 11,950              | 846,574               | 870           | 500                | 450                  | 550                  | 700                  | 660                  | 580                  | 550                  | 520                  | 570                  | 520                  | 420                  | 800                  | 750                  | 650                  | 580                  | 1,380                  | 660                    | 260                |
| S7V          | 11,270              | 793,220               | 810           | 430                | 450                  | 580                  | 690                  | 580                  | 530                  | 500                  | 440                  | 500                  | 460                  | 410                  | 830                  | 720                  | 670                  | 540                  | 1,160                  | 700                    | 300                |
| S7W          | 12,290              | 825,515               | 880           | 500                | 510                  | 580                  | 730                  | 660                  | 620                  | 570                  | 490                  | 480                  | 480                  | 460                  | 850                  | 710                  | 690                  | 600                  | 1,490                  | 750                    | 240                |
| S9A          | 11,640              | 549,788               | 850           | 450                | 670                  | 830                  | 1,140                | 900                  | 800                  | 690                  | 640                  | 620                  | 550                  | 490                  | 760                  | 590                  | 420                  | 360                  | 600                    | 220                    | 70                 |
| S9H          | 15,530              | 860,645               | 610           | 540                | 810                  | 1,090                | 1,340                | 1,060                | 1,010                | 920                  | 900                  | 980                  | 750                  | 620                  | 1,160                | 870                  | 710                  | 510                  | 1,030                  | 440                    | 190                |
| S9V          | 10,650              | 550,715               | 620           | 350                | 620                  | 590                  | 830                  | 690                  | 700                  | 700                  | 660                  | 620                  | 520                  | 470                  | 760                  | 610                  | 470                  | 380                  | 720                    | 290                    | 50                 |
| S9X          | 6,360               | 292,240               | 640           | 250                | 390                  | 490                  | 670                  | 430                  | 330                  | 340                  | 310                  | 310                  | 250                  | 230                  | 370                  | 310                  | 260                  | 200                  | 440                    | 130                    | 30                 |
| <b>TOTAL</b> | <b>865,520</b>      | <b>45,163,582</b>     | <b>66,160</b> | <b>33,860</b>      | <b>48,280</b>        | <b>59,640</b>        | <b>76,790</b>        | <b>57,440</b>        | <b>51,210</b>        | <b>48,040</b>        | <b>44,420</b>        | <b></b>              |                      |                      |                      |                      |                      |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total          | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|--------------|----------------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| <b>PR 48</b> | <b>Alberta</b> |                      |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| TOA          | 44,230         | 2,188,379            | 4,410         | 1,660              | 2,510                | 2,960                | 4,900                | 3,230                | 2,590                | 2,300                | 2,010                | 1,780                | 1,570                | 1,430                | 2,560                | 2,280                | 1,820                | 1,460                | 3,090                  | 1,360                  | 320                |
| TOB          | 47,180         | 2,410,624            | 3,160         | 1,800              | 3,010                | 3,010                | 4,870                | 3,490                | 2,940                | 2,480                | 2,370                | 2,410                | 1,950                | 1,740                | 2,910                | 2,430                | 1,890                | 1,520                | 3,470                  | 1,360                  | 380                |
| TOC          | 46,360         | 2,166,326            | 4,330         | 2,010              | 3,110                | 3,510                | 5,230                | 3,490                | 2,830                | 2,520                | 2,190                | 2,080                | 1,630                | 1,530                | 2,520                | 2,030                | 1,630                | 1,370                | 2,830                  | 1,200                  | 340                |
| TOE          | 29,250         | 1,487,862            | 2,270         | 1,000              | 1,630                | 1,810                | 3,170                | 2,240                | 1,780                | 1,670                | 1,450                | 1,270                | 1,120                | 970                  | 1,730                | 1,470                | 1,230                | 1,020                | 2,390                  | 850                    | 210                |
| TOD          | 30,180         | 1,365,174            | 3,570         | 1,280              | 1,800                | 2,140                | 3,490                | 2,110                | 1,740                | 1,530                | 1,350                | 1,150                | 990                  | 910                  | 1,660                | 1,390                | 1,180                | 980                  | 2,080                  | 710                    | 130                |
| TOH          | 59,060         | 2,928,559            | 7,950         | 2,350              | 3,390                | 3,550                | 5,630                | 3,710                | 3,060                | 2,830                | 2,490                | 2,310                | 2,160                | 1,880                | 3,390                | 2,780                | 2,420                | 2,060                | 4,840                  | 1,810                  | 460                |
| TOJ          | 38,140         | 1,878,226            | 3,100         | 1,550              | 3,090                | 2,690                | 3,690                | 2,680                | 2,270                | 2,050                | 1,800                | 1,750                | 1,560                | 1,280                | 2,220                | 1,780                | 1,420                | 1,200                | 2,670                  | 990                    | 360                |
| TOK          | 43,060         | 1,920,294            | 4,380         | 2,210              | 3,670                | 3,380                | 4,590                | 3,130                | 2,520                | 2,150                | 1,980                | 1,970                | 1,500                | 1,350                | 2,400                | 1,860                | 1,340                | 1,040                | 2,350                  | 880                    | 340                |
| TOL          | 41,750         | 2,109,637            | 3,950         | 1,890              | 3,280                | 2,900                | 4,490                | 2,850                | 2,440                | 2,150                | 2,000                | 1,910                | 1,580                | 1,440                | 2,350                | 1,890                | 1,420                | 1,070                | 2,530                  | 1,080                  | 560                |
| TOM          | 50,190         | 2,655,672            | 3,170         | 1,710              | 2,790                | 3,110                | 5,060                | 3,900                | 3,210                | 2,880                | 2,550                | 2,480                | 2,090                | 1,900                | 3,220                | 2,650                | 2,040                | 1,780                | 3,680                  | 1,500                  | 470                |
| TOP          | 1,700          | 76,285               | 340           | 90                 | 100                  | 140                  | 240                  | 110                  | 80                   | 70                   | 40                   | 40                   | 40                   | 30                   | 40                   | 50                   | 30                   | 50                   | 120                    | 100                    | 10                 |
| TOV          | 10             | 691                  |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| T1A          | 20,750         | 1,002,741            | 990           | 660                | 1,150                | 1,270                | 2,710                | 1,850                | 1,680                | 1,400                | 1,190                | 1,070                | 940                  | 760                  | 1,260                | 960                  | 670                  | 560                  | 1,060                  | 400                    | 170                |
| T1B          | 25,540         | 1,493,838            | 1,200         | 780                | 1,090                | 1,380                | 2,370                | 1,920                | 1,650                | 1,520                | 1,430                | 1,380                | 1,140                | 960                  | 1,370                | 1,380                | 1,060                | 1,000                | 2,190                  | 990                    | 330                |
| T1C          | 7,110          | 418,275              | 320           | 190                | 280                  | 340                  | 570                  | 490                  | 410                  | 430                  | 410                  | 430                  | 350                  | 300                  | 580                  | 410                  | 350                  | 300                  | 650                    | 250                    | 70                 |
| T1G          | 8,500          | 408,173              | 730           | 360                | 600                  | 520                  | 770                  | 630                  | 520                  | 450                  | 420                  | 410                  | 400                  | 340                  | 550                  | 520                  | 340                  | 250                  | 450                    | 170                    | 70                 |
| T1H          | 21,620         | 979,973              | 1,190         | 620                | 920                  | 1,180                | 2,460                | 1,950                | 1,570                | 1,480                | 1,400                | 1,330                | 1,160                | 1,030                | 1,630                | 1,180                | 760                  | 550                  | 960                    | 200                    | 60                 |
| T1J          | 20,520         | 1,136,647            | 1,040         | 670                | 990                  | 1,120                | 2,190                | 1,620                | 1,300                | 1,150                | 1,070                | 970                  | 920                  | 770                  | 1,390                | 1,180                | 890                  | 810                  | 1,690                  | 550                    | 220                |
| T1K          | 35,630         | 2,035,087            | 2,000         | 1,210              | 1,480                | 1,970                | 3,310                | 2,610                | 2,330                | 2,120                | 1,930                | 1,840                | 1,530                | 1,390                | 2,410                | 2,180                | 1,540                | 1,300                | 2,980                  | 1,150                  | 440                |
| T1L          | 6,960          | 364,459              | 240           | 270                | 280                  | 360                  | 490                  | 640                  | 710                  | 710                  | 520                  | 440                  | 420                  | 310                  | 440                  | 280                  | 210                  | 150                  | 310                    | 110                    | 80                 |
| T1M          | 7,890          | 407,797              | 590           | 300                | 420                  | 430                  | 730                  | 550                  | 460                  | 410                  | 410                  | 430                  | 350                  | 330                  | 570                  | 450                  | 370                  | 290                  | 590                    | 190                    | 50                 |
| T1P          | 13,490         | 759,296              | 800           | 450                | 700                  | 710                  | 1,310                | 1,030                | 880                  | 750                  | 660                  | 670                  | 540                  | 510                  | 900                  | 700                  | 630                  | 530                  | 1,140                  | 430                    | 150                |
| T1R          | 13,550         | 693,919              | 870           | 480                | 610                  | 630                  | 1,060                | 950                  | 800                  | 830                  | 750                  | 990                  | 1,160                | 820                  | 940                  | 610                  | 490                  | 420                  | 780                    | 260                    | 110                |
| T1S          | 33,080         | 2,561,387            | 1,960         | 1,130              | 1,390                | 1,650                | 2,320                | 1,990                | 1,730                | 1,620                | 1,530                | 1,520                | 1,290                | 1,180                | 2,060                | 1,720                | 1,450                | 1,420                | 3,640                  | 2,180                  | 1,270              |
| T1V          | 13,190         | 714,273              | 670           | 390                | 610                  | 740                  | 1,290                | 990                  | 850                  | 780                  | 790                  | 750                  | 610                  | 590                  | 1,090                | 760                  | 550                  | 420                  | 830                    | 350                    | 140                |
| T1W          | 12,890         | 1,014,611            | 420           | 330                | 410                  | 510                  | 760                  | 800                  | 870                  | 860                  | 730                  | 740                  | 650                  | 610                  | 950                  | 770                  | 620                  | 510                  | 1,250                  | 710                    | 400                |
| T1X          | 17,340         | 1,113,078            | 1,090         | 670                | 780                  | 960                  | 1,350                | 1,110                | 950                  | 880                  | 780                  | 770                  | 700                  | 630                  | 1,190                | 1,000                | 790                  | 640                  | 1,810                  | 900                    | 330                |
| T1Y          | 43,840         | 1,694,056            | 3,670         | 1,780              | 2,500                | 3,310                | 5,480                | 4,050                | 3,520                | 3,040                | 2,630                | 2,250                | 1,930                | 1,610                | 2,620                | 1,780                | 1,170                | 800                  | 1,310                  | 300                    | 80                 |
| T1Z          | 1,110          | 55,276               | 70            | 60                 | 80                   | 90                   | 110                  | 80                   | 60                   | 60                   | 50                   | 40                   | 40                   | 30                   | 70                   | 60                   | 40                   | 40                   | 70                     | 30                     | 10                 |
| T2A          | 45,920         | 1,772,865            | 3,410         | 1,850              | 2,440                | 3,190                | 5,860                | 4,410                | 3,930                | 3,410                | 2,890                | 2,540                | 2,140                | 1,800                | 2,770                | 1,890                | 1,160                | 730                  | 1,230                  | 240                    | 60                 |
| T2B          | 17,540         | 714,206              | 1,130         | 650                | 880                  | 1,150                | 2,300                | 1,630                | 1,250                | 1,070                | 960                  | 830                  | 740                  | 1,130                | 830                  | 740                  | 520                  | 370                  | 580                    | 120                    | 20                 |
| T2C          | 16,700         | 1,110,104            | 850           | 530                | 650                  | 850                  | 1,470                | 1,190                | 1,010                | 950                  | 910                  | 850                  | 810                  | 740                  | 1,210                | 960                  | 750                  | 620                  | 1,360                  | 560                    | 440                |
| T2E          | 27,850         | 1,836,538            | 1,390         | 800                | 1,000                | 1,400                | 2,970                | 2,160                | 1,650                | 1,520                | 1,290                | 1,280                | 1,130                | 1,030                | 1,750                | 1,510                | 1,220                | 1,020                | 2,750                  | 1,360                  | 640                |
| T2G          | 12,340         | 883,249              | 590           | 420                | 470                  | 660                  | 1,820                | 800                  | 620                  | 510                  | 470                  | 450                  | 390                  | 360                  | 730                  | 600                  | 530                  | 470                  | 1,390                  | 710                    | 360                |
| T2H          | 7,820          | 457,567              | 430           | 240                | 310                  | 440                  | 820                  | 670                  | 560                  | 550                  | 430                  | 400                  | 380                  | 300                  | 520                  | 410                  | 280                  | 260                  | 490                    | 240                    | 100                |
| T2J          | 34,390         | 2,546,352            | 1,700         | 990                | 1,310                | 1,590                | 2,740                | 2,180                | 1,950                | 1,750                | 1,710                | 1,760                | 1,550                | 1,390                | 2,470                | 1,640                | 1,270                | 3,470                | 1,840                  | 1,030                  |                    |
| T2K          | 26,860         | 1,432,732            | 1,600         | 930                | 1,190                | 1,540                | 2,880                | 2,200                | 1,840                | 1,630                | 1,440                | 1,450                | 1,220                | 1,040                | 1,780                | 1,370                | 1,040                | 840                  | 1,820                  | 750                    | 300                |
| T2L          | 11,040         | 739,880              | 1,000         | 460                | 490                  | 570                  | 890                  | 730                  | 550                  | 530                  | 490                  | 480                  | 430                  | 390                  | 610                  | 580                  | 450                  | 400                  | 1,090                  | 650                    | 320                |
| T2M          | 16,320         | 1,289,951            | 1,050         | 570                | 660                  | 900                  | 1,450                | 1,060                | 870                  | 730                  | 710                  | 660                  | 580                  | 530                  | 910                  | 820                  | 630                  | 610                  | 1,740                  | 1,160                  | 690                |
| T2N          | 19,260         | 1,924,307            | 1,360         | 680                | 710                  | 820                  | 1,490                | 1,110                | 970                  | 740                  | 670                  | 720                  | 620                  | 560                  | 1,070                | 960                  | 770                  | 710                  | 2,150                  | 1,750                  | 1,410              |
| T2P          | 13,900         | 1,662,694            | 1,110         | 400                | 510                  | 660                  | 1,740                | 1,140                | 790                  | 690                  | 620                  | 510                  | 460                  | 400                  | 660                  | 590                  | 480                  | 460                  | 1,140                  | 780                    | 770                |
| T2R          | 13,440         | 1,071,661            | 680           | 310                | 390                  | 490                  | 1,050                | 820                  | 740                  | 660                  | 600                  | 620                  | 520                  | 490                  | 900                  | 850                  | 710                  | 600                  | 1,680                  | 940                    | 380                |
| T2S          | 11,350         | 1,533,124            | 440           | 330                | 370                  | 420                  | 680                  | 630                  | 560                  | 460                  | 460                  | 420                  | 380                  | 390                  | 650                  | 630                  | 520                  | 490                  | 1,400                  | 970                    | 1,150              |
| T2T          | 22,200         | 2,660,978            | 1,080         | 660                | 650                  | 790                  | 1,510                | 1,240                | 1,100                | 950                  | 820                  | 790                  | 770                  | 680                  | 1,260                | 1,120                | 1,010                | 890                  | 2,670                  | 2,180                  | 2,040              |
| T2V          | 25,680         | 2,123,368            | 1,350         | 760                | 1,000                | 1,120                | 2,250                | 1,790                | 1,550                | 1,360                | 1,250                | 1,290                | 1,010                | 960                  | 1,600                | 1,460                | 1,060                | 900                  | 2,460                  | 1,440                  | 1,090              |
| T2W          | 32,410         | 2,003,546            | 1,960         | 1,060              | 1,250                | 1,650                | 2,650                | 2,270                | 1,960                | 1,820                | 1,670                | 1,670                | 1,480                | 1,310                | 2,340                | 2,010                | 1,450                | 1,200                | 2,860                  | 1,230                  | 580                |
| T2X          | 39,940         | 2,618,189            | 2,640         | 1,490              | 1,600                | 1,920                | 2,820                | 2,470                | 2,130                | 2,010                | 1,960                | 1,830                | 1,590                | 1,540                | 2,810                | 2,350                | 1,990                | 1,730                | 4,370                  | 1,910                  | 800                |
| T2Y          | 47,740         | 2,805,558            | 3,440         | 1,980              | 2,030                | 2,460                | 3,920                | 3,200                | 2,970                | 2,710                | 2,480                | 2,410                | 2,140                | 1,940                | 3,380                | 2,630                | 1,970                | 1,700                | 3,950                  | 1,810                  | 620                |
| T2Z          | 51,930         | 3,452,542            | 3,120         | 1,680              | 1,980                | 2,480                | 3,440                | 2,960                | 2,600                | 2,530                | 2,370                | 2,530                | 2,230                | 2,130                | 3,930                | 3,360                | 2,850                | 2,490                | 5,890                  | 2,480                  | 910                |
| T3A          | 42,700         | 2,866,096            | 3,130         | 1,980              | 1,980                | 2,370                | 3,370                | 2,720                | 2,200                | 1,900                | 1,900                | 1,850                | 1,570                | 1,410                | 2,580                | 2,300                | 1,820                | 1,620                | 4,280                  | 2,280                  | 1,160              |
| T3B          | 28,870         | 2,027,051            | 1,710         | 1,010              | 1,120                | 1,340                | 2,640                | 1,830                | 1,630                | 1,510                | 1,420                | 1,280                | 1,080                | 1,040                | 1,840                | 1,580                | 1,220                | 1,100                | 2,980                  | 1,700                  | 840                |
| T3C          | 18,470         | 1,318,498            | 1,130         | 620                | 730                  | 900                  | 1,630                | 1,390                | 1,140                | 1,090                | 950                  | 900                  | 770                  | 640                  | 1,120                | 940                  | 760                  | 640                  | 1,620                  | 930                    | 580                |
| T3E          | 31,180         | 2,344,919            | 1,650         | 950                | 1,220                | 1,500                | 2,870                | 2,130                | 1,840                | 1,440                | 1,440                | 1,150                | 1,100                | 1,930                | 1,640                | 1,270                | 1,130                | 3,205                | 2,020                  | 1,100                  |                    |
| T3G          | 46,040         | 2,901,841            | 3,450         | 2,060              | 2,150                | 2,520                | 3,600                | 2,950                | 2,400                | 2,130                | 2,000                | 2,090                | 1,780                | 1,650                | 2,800                | 2,430                | 2,060                | 1,870                | 4,800                  | 2,300                  | 990                |
| T3H          | 55,150         | 5,317,433            | 4,120         | 2,270              | 2,420                | 2,710                | 3,580                | 2,920                | 2,360                | 2,150                | 2,010                | 2,060                | 1,680                | 1,610                | 2,910                | 2,610                | 2,210                | 2,140                | 6,630                  | 5,120                  | 3,640              |
| T3J          | 63,430         | 2,362,268            | 6,340         | 3,000              | 3,900                | 4,910                | 7,370                | 5,680                | 4,830                | 4,270                | 3,730                | 3,280                | 2,850                | 2,390                | 3,640                | 2,400                | 1,600                | 1,100                | 1,690                  | 370                    | 100                |
| T3K          | 61,900         | 3,242,259            | 4,440         | 2,450              | 2,990                | 3,780                | 5,                   |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total  | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-----|--------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| T5G | 9,550  | 407,742              | 610           | 320                | 550                  | 640                  | 1,240                | 980                  | 810                  | 630                  | 550                  | 430                  | 380                  | 350                  | 610                  | 390                  | 300                  | 230                  | 400                    | 100                    | 40                 |
| T5H | 20,850 | 860,749              | 1,290         | 790                | 1,300                | 1,440                | 3,540                | 2,140                | 1,640                | 1,340                | 1,100                | 880                  | 760                  | 600                  | 1,040                | 810                  | 540                  | 420                  | 850                    | 290                    | 90                 |
| T5J | 8,180  | 759,960              | 580           | 200                | 280                  | 420                  | 1,770                | 860                  | 440                  | 300                  | 250                  | 230                  | 250                  | 230                  | 380                  | 330                  | 300                  | 240                  | 640                    | 280                    | 230                |
| T5K | 17,360 | 1,152,971            | 900           | 440                | 560                  | 750                  | 1,770                | 1,250                | 1,040                | 900                  | 810                  | 760                  | 760                  | 690                  | 1,270                | 1,100                | 920                  | 760                  | 1,650                  | 690                    | 360                |
| T5L | 13,180 | 624,242              | 810           | 400                | 550                  | 800                  | 1,370                | 1,180                | 990                  | 850                  | 810                  | 700                  | 630                  | 590                  | 950                  | 700                  | 530                  | 400                  | 700                    | 180                    | 50                 |
| T5M | 11,680 | 635,969              | 640           | 340                | 450                  | 670                  | 1,430                | 970                  | 850                  | 710                  | 580                  | 610                  | 460                  | 390                  | 740                  | 580                  | 440                  | 420                  | 940                    | 320                    | 150                |
| T5N | 11,260 | 974,900              | 560           | 300                | 410                  | 470                  | 910                  | 750                  | 580                  | 530                  | 490                  | 470                  | 430                  | 410                  | 780                  | 630                  | 550                  | 460                  | 1,220                  | 730                    | 600                |
| T5P | 16,020 | 676,486              | 860           | 520                | 800                  | 950                  | 2,210                | 1,560                | 1,280                | 1,140                | 1,000                | 890                  | 770                  | 670                  | 1,030                | 700                  | 490                  | 370                  | 610                    | 160                    | 30                 |
| T5R | 19,010 | 1,287,097            | 960           | 570                | 730                  | 950                  | 1,600                | 1,340                | 1,160                | 1,130                | 1,020                | 1,020                | 860                  | 790                  | 1,300                | 1,020                | 810                  | 680                  | 1,710                  | 860                    | 520                |
| T5S | 5,340  | 359,244              | 260           | 120                | 180                  | 210                  | 400                  | 310                  | 250                  | 260                  | 230                  | 270                  | 220                  | 210                  | 380                  | 390                  | 300                  | 280                  | 720                    | 260                    | 80                 |
| T5T | 58,010 | 3,197,180            | 3,480         | 1,860              | 2,410                | 2,940                | 4,980                | 4,250                | 3,800                | 3,410                | 3,120                | 3,120                | 2,800                | 2,510                | 4,480                | 3,430                | 2,600                | 2,160                | 4,700                  | 1,460                  | 500                |
| T5V | 300    | 19,922               | 20            | 10                 | 20                   | 10                   | 30                   | 20                   | 20                   | 10                   | 20                   | 10                   | 10                   | 10                   | 10                   | 30                   | 10                   | 10                   | 30                     | 10                     | 10                 |
| T5W | 15,340 | 729,643              | 980           | 490                | 730                  | 880                  | 1,890                | 1,410                | 1,090                | 900                  | 840                  | 730                  | 650                  | 620                  | 1,030                | 810                  | 620                  | 460                  | 890                    | 240                    | 80                 |
| T5X | 32,250 | 1,589,798            | 2,310         | 1,110              | 1,530                | 1,850                | 3,210                | 2,530                | 2,050                | 1,870                | 1,680                | 1,620                | 1,380                | 1,330                | 2,260                | 1,940                | 1,450                | 1,100                | 2,280                  | 620                    | 140                |
| T5Y | 39,090 | 2,021,041            | 2,530         | 1,330              | 1,670                | 2,280                | 3,550                | 2,720                | 2,480                | 2,200                | 1,990                | 1,970                | 1,740                | 1,700                | 2,970                | 2,560                | 1,850                | 1,500                | 3,040                  | 860                    | 150                |
| TSZ | 26,360 | 1,397,779            | 1,580         | 880                | 1,210                | 1,590                | 2,430                | 1,860                | 1,530                | 1,480                | 1,270                | 1,260                | 1,140                | 1,020                | 1,990                | 1,740                | 1,290                | 1,120                | 2,190                  | 650                    | 130                |
| T6A | 11,360 | 703,673              | 480           | 320                | 410                  | 510                  | 1,050                | 810                  | 620                  | 590                  | 600                  | 560                  | 500                  | 410                  | 840                  | 750                  | 530                  | 550                  | 1,260                  | 440                    | 120                |
| T6B | 7,600  | 447,511              | 330           | 220                | 300                  | 350                  | 750                  | 540                  | 450                  | 420                  | 400                  | 360                  | 360                  | 320                  | 530                  | 460                  | 410                  | 350                  | 750                    | 240                    | 70                 |
| T6C | 15,390 | 984,275              | 700           | 400                | 560                  | 680                  | 1,660                | 1,080                | 900                  | 840                  | 730                  | 680                  | 610                  | 630                  | 1,040                | 870                  | 770                  | 720                  | 1,590                  | 670                    | 280                |
| T6E | 17,670 | 1,065,846            | 1,250         | 600                | 720                  | 860                  | 1,740                | 1,270                | 1,010                | 910                  | 870                  | 790                  | 690                  | 650                  | 1,180                | 1,050                | 800                  | 720                  | 1,620                  | 660                    | 300                |
| T6G | 8,520  | 610,444              | 1,420         | 470                | 450                  | 390                  | 610                  | 440                  | 380                  | 290                  | 230                  | 290                  | 230                  | 220                  | 380                  | 400                  | 310                  | 300                  | 760                    | 590                    | 370                |
| T6H | 21,280 | 1,440,349            | 1,560         | 820                | 920                  | 1,070                | 1,750                | 1,490                | 1,220                | 1,080                | 940                  | 930                  | 840                  | 800                  | 1,340                | 1,190                | 900                  | 810                  | 2,040                  | 1,050                  | 510                |
| T6J | 36,180 | 2,247,689            | 2,400         | 1,350              | 1,550                | 1,890                | 3,030                | 2,530                | 2,130                | 2,010                | 1,800                | 1,800                | 1,540                | 1,410                | 2,420                | 2,010                | 1,610                | 1,400                | 3,330                  | 1,340                  | 640                |
| T6K | 21,440 | 967,360              | 1,650         | 820                | 1,060                | 1,300                | 2,160                | 1,720                | 1,460                | 1,380                | 1,210                | 1,170                | 1,040                | 920                  | 1,510                | 1,120                | 790                  | 620                  | 1,180                  | 280                    | 50                 |
| T6L | 39,370 | 1,863,464            | 2,640         | 1,400              | 1,800                | 2,560                | 4,050                | 3,190                | 2,460                | 2,290                | 2,100                | 1,850                | 1,670                | 1,510                | 2,790                | 2,130                | 1,550                | 1,230                | 2,250                  | 580                    | 140                |
| T6M | 24,410 | 1,843,643            | 1,370         | 750                | 880                  | 1,120                | 1,590                | 1,380                | 1,230                | 1,190                | 1,090                | 1,100                | 990                  | 1,020                | 1,820                | 1,570                | 1,370                | 1,190                | 2,880                  | 1,260                  | 630                |
| T6N | 80     | 6,079                | 10            | 10                 | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                     | 10                     | 10                 |
| T6P | 1,430  | 69,743               | 100           | 40                 | 60                   | 90                   | 190                  | 110                  | 100                  | 100                  | 90                   | 70                   | 70                   | 60                   | 110                  | 60                   | 40                   | 50                   | 60                     | 10                     | 10                 |
| T6R | 35,650 | 2,987,570            | 2,370         | 1,410              | 1,410                | 1,700                | 2,310                | 1,940                | 1,540                | 1,420                | 1,380                | 1,460                | 1,260                | 1,120                | 2,270                | 2,090                | 1,830                | 1,700                | 4,530                  | 2,480                  | 1,430              |
| T6S | 40     | 2,847                | 10            | 10                 | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                     | 10                     | 10                 |
| T6T | 36,860 | 1,682,926            | 2,930         | 1,530              | 1,910                | 2,460                | 3,440                | 2,870                | 2,560                | 2,290                | 2,050                | 1,840                | 1,720                | 1,540                | 2,470                | 1,870                | 1,350                | 1,190                | 2,180                  | 570                    | 100                |
| T6V | 16,570 | 898,716              | 1,150         | 600                | 740                  | 950                  | 1,360                | 1,120                | 970                  | 870                  | 800                  | 760                  | 680                  | 720                  | 1,240                | 1,040                | 810                  | 710                  | 1,480                  | 460                    | 110                |
| T6W | 55,470 | 3,613,812            | 3,990         | 1,950              | 1,990                | 2,540                | 3,610                | 3,100                | 2,810                | 2,630                | 2,310                | 2,410                | 2,340                | 2,320                | 4,000                | 3,660                | 3,090                | 2,830                | 6,480                  | 2,500                  | 900                |
| T6X | 34,610 | 1,984,013            | 2,640         | 1,160              | 1,340                | 1,680                | 2,520                | 2,080                | 2,050                | 1,850                | 1,770                | 1,650                | 1,490                | 1,410                | 2,560                | 2,150                | 1,800                | 1,570                | 3,490                  | 1,110                  | 300                |
| T6Y | 190    | 14,978               | 10            | 10                 | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 10                   | 20                   | 10                   | 10                   | 10                   | 20                     | 10                     | 10                 |
| T7A | 9,850  | 567,322              | 630           | 320                | 430                  | 480                  | 930                  | 680                  | 630                  | 620                  | 490                  | 450                  | 400                  | 360                  | 630                  | 530                  | 430                  | 430                  | 890                    | 430                    | 90                 |
| T7E | 10,870 | 649,207              | 690           | 330                | 470                  | 550                  | 1,010                | 760                  | 680                  | 590                  | 500                  | 450                  | 400                  | 400                  | 630                  | 590                  | 500                  | 480                  | 1,180                  | 540                    | 100                |
| T7N | 6,650  | 319,457              | 390           | 200                | 340                  | 410                  | 810                  | 530                  | 450                  | 420                  | 360                  | 370                  | 310                  | 270                  | 430                  | 340                  | 280                  | 210                  | 370                    | 130                    | 40                 |
| T7P | 6,110  | 286,619              | 360           | 280                | 360                  | 420                  | 870                  | 510                  | 430                  | 330                  | 360                  | 270                  | 220                  | 200                  | 350                  | 250                  | 200                  | 170                  | 350                    | 140                    | 50                 |
| T7S | 9,770  | 594,147              | 590           | 260                | 410                  | 470                  | 880                  | 710                  | 610                  | 520                  | 440                  | 430                  | 340                  | 330                  | 610                  | 530                  | 530                  | 470                  | 1,120                  | 430                    | 100                |
| T7V | 8,400  | 530,465              | 440           | 220                | 300                  | 380                  | 660                  | 550                  | 560                  | 440                  | 450                  | 400                  | 300                  | 290                  | 520                  | 420                  | 410                  | 400                  | 1,220                  | 390                    | 70                 |
| T7X | 35,160 | 2,164,032            | 2,370         | 1,000              | 1,410                | 1,740                | 2,750                | 2,200                | 1,930                | 1,870                | 1,730                | 1,650                | 1,430                | 1,340                | 2,510                | 2,170                | 1,730                | 1,580                | 3,760                  | 1,590                  | 430                |
| T7Y | 13,950 | 996,759              | 830           | 420                | 570                  | 720                  | 1,030                | 870                  | 740                  | 670                  | 620                  | 680                  | 550                  | 510                  | 830                  | 760                  | 660                  | 630                  | 1,650                  | 880                    | 350                |
| T7Z | 15,150 | 883,538              | 810           | 470                | 640                  | 820                  | 1,410                | 1,110                | 920                  | 810                  | 800                  | 740                  | 640                  | 610                  | 1,050                | 900                  | 650                  | 600                  | 1,410                  | 610                    | 150                |
| T8A | 33,910 | 2,394,288            | 1,600         | 840                | 1,200                | 1,420                | 2,250                | 1,950                | 1,670                | 1,690                | 1,610                | 1,680                | 1,510                | 1,340                | 2,540                | 2,240                | 1,820                | 1,660                | 4,260                  | 1,970                  | 670                |
| T8B | 5,810  | 632,234              | 270           | 180                | 230                  | 290                  | 360                  | 310                  | 230                  | 250                  | 250                  | 220                  | 190                  | 210                  | 330                  | 340                  | 260                  | 220                  | 690                    | 550                    | 420                |
| T8C | 3,510  | 279,611              | 170           | 90                 | 140                  | 170                  | 270                  | 180                  | 190                  | 160                  | 170                  | 170                  | 130                  | 110                  | 240                  | 190                  | 150                  | 170                  | 450                    | 240                    | 120                |
| T8E | 6,450  | 462,189              | 360           | 200                | 250                  | 310                  | 460                  | 360                  | 320                  | 300                  | 290                  | 320                  | 240                  | 230                  | 450                  | 380                  | 320                  | 280                  | 790                    | 460                    | 150                |
| T8G | 3,750  | 254,172              | 230           | 120                | 110                  | 170                  | 260                  | 220                  | 190                  | 170                  | 200                  | 160                  | 170                  | 130                  | 260                  | 220                  | 200                  | 190                  | 440                    | 240                    | 60                 |
| T8H | 23,320 | 1,615,773            | 1,030         | 600                | 760                  | 1,000                | 1,500                | 1,390                | 1,150                | 1,200                | 1,060                | 1,100                | 960                  | 860                  | 1,700                | 1,510                | 1,350                | 1,240                | 3,150                  | 1,410                  | 350                |
| T8L | 21,610 | 1,461,059            | 1,110         | 500                | 690                  | 890                  | 1,540                | 1,310                | 1,190                | 1,130                | 1,050                | 1,060                | 950                  | 840                  | 1,500                | 1,360                | 1,150                | 1,000                | 2,510                  | 1,540                  | 300                |
| T8N | 52,740 | 3,738,614            | 2,340         | 1,440              | 1,740                | 2,230                | 3,520                | 3,080                | 2,650                | 2,520                | 2,660                | 2,290                | 2,090                | 3,930                | 3,480                | 2,780                | 2,750                | 6,770                | 2,890                  | 1,070                  | 1,070              |
| T8R | 12,180 | 706,465              | 870           | 390                | 520                  | 580                  | 960                  | 780                  | 610                  | 650                  | 610                  | 590                  | 520                  | 470                  | 810                  | 840                  | 650                  | 570                  | 1,220                  | 450                    | 80                 |
| T8S | 7,170  | 423,199              | 590           | 250                | 390                  | 370                  | 630                  | 450                  | 380                  | 350                  | 330                  | 300                  | 270                  | 230                  | 460                  | 350                  | 340                  | 310                  | 780                    | 310                    | 90                 |
| T8T | 5,730  | 514,190              | 290           | 180                | 220                  | 270                  | 400                  | 300                  | 270                  | 240                  | 220                  | 250                  | 210                  | 180                  | 360                  | 320                  | 270                  | 240                  | 720                    | 480                    | 330                |
| T8V | 25,550 | 1,420,808            | 1,380         | 660                | 960                  | 1,200                | 2,550                | 2,000                | 1,710                | 1,590                | 1,360                | 1,300                | 1,190                | 1,020                | 1,780                | 1,430                | 1,180                | 1,040                | 2,320                  | 720                    | 190                |
| T8W | 15,600 | 1,160,919            | 830           | 400                | 530                  | 600                  | 920                  | 830                  | 770                  | 700                  | 680                  | 700                  | 660                  | 570                  | 1,060                | 980                  | 900                  | 880                  | 2,270                  | 1,000                  | 310                |
| T8X | 17,150 | 1,159,395            | 880           | 430                | 580                  | 780                  | 1,130                | 950                  | 900                  | 810                  | 800                  | 790                  | 720                  | 670                  | 1,190                | 1,100                | 960                  | 890                  | 2,400                  | 960                    | 220                |
| T9A | 12,000 | 578,846              | 760           | 380                | 660                  | 680                  | 1,490                | 1,040                | 830                  | 720                  | 650                  | 630                  | 500                  | 430                  | 830                  | 590                  | 470                  | 340                  | 700                    | 210                    | 80                 |
| T9C | 5,     |                      |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total                   | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |  |
|--------------|-------------------------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|--|
| <b>PR 59</b> | <b>British Columbia</b> |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |  |
| VOA          | 12,180                  | 639,303               | 500           | 310                | 510                  | 760                  | 980                  | 930                  | 920                  | 910                  | 790                  | 720                  | 600                  | 530                  | 830                  | 680                  | 610                  | 410                  | 840                    | 280                    | 90                 |  |
| VOB          | 28,530                  | 1,522,975             | 1,550         | 860                | 1,390                | 2,280                | 2,820                | 2,230                | 1,850                | 1,700                | 1,560                | 1,420                | 1,170                | 970                  | 1,540                | 1,270                | 1,010                | 880                  | 2,930                  | 900                    | 200                |  |
| VOC          | 18,620                  | 1,065,502             | 1,870         | 680                | 990                  | 1,240                | 1,460                | 1,010                | 1,000                | 920                  | 810                  | 730                  | 650                  | 580                  | 1,040                | 950                  | 820                  | 810                  | 2,050                  | 870                    | 150                |  |
| VOE          | 58,400                  | 2,683,437             | 3,470         | 1,830              | 3,260                | 5,310                | 6,310                | 4,770                | 4,230                | 3,790                | 3,500                | 3,050                | 2,550                | 2,130                | 3,420                | 2,710                | 2,060                | 1,520                | 3,180                  | 1,020                  | 300                |  |
| VOG          | 22,470                  | 1,084,478             | 1,080         | 720                | 1,210                | 2,050                | 2,490                | 1,820                | 1,520                | 1,420                | 1,300                | 1,210                | 970                  | 800                  | 1,260                | 1,050                | 800                  | 690                  | 1,540                  | 440                    | 130                |  |
| VOH          | 48,850                  | 2,346,618             | 2,140         | 1,410              | 2,520                | 4,330                | 5,460                | 4,100                | 3,520                | 3,330                | 3,030                | 2,830                | 2,330                | 1,940                | 3,010                | 2,260                | 1,640                | 1,250                | 2,390                  | 990                    | 360                |  |
| VOJ          | 40,430                  | 1,908,990             | 4,460         | 1,620              | 2,340                | 3,180                | 3,500                | 2,750                | 2,270                | 2,010                | 1,940                | 1,770                | 1,420                | 1,330                | 2,470                | 2,090                | 1,770                | 1,450                | 3,120                  | 780                    | 190                |  |
| VOK          | 27,620                  | 1,145,502             | 2,510         | 1,020              | 1,730                | 2,890                | 3,230                | 2,280                | 1,920                | 1,690                | 1,420                | 1,270                | 990                  | 880                  | 1,370                | 1,080                | 860                  | 610                  | 1,400                  | 380                    | 100                |  |
| VOL          | 3,770                   | 122,041               | 800           | 190                | 290                  | 450                  | 460                  | 240                  | 210                  | 180                  | 150                  | 100                  | 100                  | 70                   | 120                  | 90                   | 70                   | 60                   | 150                    | 30                     | 10                 |  |
| VOM          | 9,640                   | 412,039               | 1,020         | 330                | 490                  | 800                  | 1,000                | 780                  | 680                  | 620                  | 570                  | 510                  | 360                  | 370                  | 540                  | 390                  | 330                  | 240                  | 440                    | 130                    | 50                 |  |
| VON          | 59,850                  | 3,342,930             | 3,520         | 1,830              | 2,880                | 4,570                | 5,650                | 4,400                | 3,850                | 3,590                | 3,430                | 3,140                | 2,750                | 2,300                | 3,830                | 3,090                | 2,250                | 1,880                | 4,330                  | 1,800                  | 770                |  |
| VOP          | 5,850                   | 232,867               | 440           | 210                | 440                  | 680                  | 740                  | 540                  | 410                  | 380                  | 280                  | 260                  | 200                  | 190                  | 270                  | 190                  | 160                  | 140                  | 240                    | 70                     | 20                 |  |
| VOR          | 58,710                  | 2,955,381             | 3,090         | 1,660              | 2,880                | 4,890                | 5,720                | 4,630                | 4,010                | 3,780                | 3,480                | 3,300                | 2,730                | 2,390                | 3,840                | 3,050                | 2,260                | 1,780                | 3,570                  | 1,230                  | 400                |  |
| VOS          | 310                     | 12,071                | 40            | 10                 | 20                   | 20                   | 40                   | 20                   | 20                   | 20                   | 20                   | 20                   | 10                   | 10                   | 20                   | 10                   | 10                   | 10                   | 10                     | 10                     | 10                 |  |
| VOT          | 6,280                   | 222,237               | 1,180         | 310                | 430                  | 610                  | 680                  | 460                  | 350                  | 290                  | 270                  | 230                  | 200                  | 160                  | 260                  | 210                  | 150                  | 130                  | 270                    | 80                     | 20                 |  |
| VOV          | 1,280                   | 35,647                | 350           | 80                 | 110                  | 130                  | 140                  | 80                   | 60                   | 40                   | 40                   | 40                   | 20                   | 20                   | 50                   | 30                   | 20                   | 20                   | 40                     | 20                     | 20                 |  |
| VOW          | 350                     | 15,659                | 30            | 10                 | 30                   | 20                   | 50                   | 30                   | 30                   | 10                   | 10                   | 10                   | 10                   | 20                   | 30                   | 20                   | 10                   | 10                   | 20                     | 10                     | 10                 |  |
| VOX          | 18,500                  | 816,208               | 1,250         | 620                | 1,080                | 2,060                | 2,280                | 1,550                | 1,280                | 1,250                | 990                  | 860                  | 670                  | 570                  | 940                  | 710                  | 540                  | 480                  | 1,000                  | 280                    | 90                 |  |
| V1A          | 7,040                   | 375,029               | 300           | 180                | 260                  | 460                  | 630                  | 560                  | 500                  | 490                  | 470                  | 390                  | 290                  | 320                  | 480                  | 420                  | 310                  | 250                  | 520                    | 190                    | 40                 |  |
| V1B          | 18,770                  | 1,140,635             | 790           | 620                | 850                  | 1,230                | 1,400                | 1,230                | 1,120                | 1,120                | 1,060                | 1,080                | 830                  | 790                  | 1,280                | 1,120                | 910                  | 740                  | 1,580                  | 730                    | 290                |  |
| V1C          | 21,450                  | 1,157,586             | 990           | 570                | 870                  | 1,600                | 2,030                | 1,560                | 1,450                | 1,370                | 1,300                | 1,210                | 1,010                | 880                  | 1,360                | 1,150                | 860                  | 730                  | 1,750                  | 600                    | 170                |  |
| V1E          | 17,410                  | 863,852               | 780           | 520                | 840                  | 1,440                | 1,920                | 1,470                | 1,270                | 1,130                | 1,110                | 930                  | 790                  | 690                  | 1,090                | 820                  | 660                  | 480                  | 970                    | 390                    | 130                |  |
| V1G          | 12,160                  | 687,365               | 690           | 320                | 490                  | 930                  | 990                  | 870                  | 760                  | 710                  | 610                  | 580                  | 550                  | 450                  | 850                  | 700                  | 550                  | 480                  | 1,060                  | 490                    | 100                |  |
| V1H          | 12,310                  | 698,046               | 600           | 310                | 540                  | 940                  | 1,140                | 960                  | 820                  | 800                  | 770                  | 690                  | 600                  | 530                  | 820                  | 610                  | 500                  | 350                  | 790                    | 380                    | 170                |  |
| V1J          | 19,610                  | 1,277,517             | 1,230         | 570                | 730                  | 1,060                | 1,300                | 1,100                | 1,040                | 970                  | 960                  | 870                  | 820                  | 700                  | 1,370                | 1,200                | 1,020                | 950                  | 2,340                  | 1,130                  | 250                |  |
| V1K          | 8,070                   | 355,696               | 700           | 280                | 480                  | 850                  | 920                  | 610                  | 570                  | 500                  | 450                  | 340                  | 300                  | 250                  | 370                  | 340                  | 270                  | 220                  | 490                    | 110                    | 40                 |  |
| V1L          | 14,760                  | 764,701               | 570           | 410                | 670                  | 1,280                | 1,540                | 1,190                | 1,080                | 970                  | 880                  | 810                  | 710                  | 590                  | 960                  | 750                  | 560                  | 430                  | 900                    | 310                    | 130                |  |
| V1M          | 25,510                  | 1,702,544             | 1,420         | 830                | 1,010                | 1,500                | 1,830                | 1,510                | 1,390                | 1,290                | 1,310                | 1,240                | 1,110                | 1,020                | 1,750                | 1,570                | 1,290                | 1,150                | 2,660                  | 1,200                  | 450                |  |
| V1N          | 10,950                  | 569,748               | 530           | 350                | 500                  | 820                  | 1,070                | 770                  | 720                  | 700                  | 570                  | 580                  | 500                  | 440                  | 670                  | 550                  | 470                  | 420                  | 980                    | 270                    | 60                 |  |
| V1P          | 7,540                   | 433,636               | 360           | 260                | 320                  | 500                  | 550                  | 490                  | 450                  | 460                  | 450                  | 420                  | 360                  | 310                  | 570                  | 470                  | 350                  | 280                  | 590                    | 270                    | 100                |  |
| V1R          | 8,330                   | 418,698               | 380           | 220                | 300                  | 720                  | 790                  | 660                  | 600                  | 590                  | 530                  | 520                  | 410                  | 320                  | 500                  | 350                  | 290                  | 270                  | 680                    | 170                    | 40                 |  |
| V1S          | 10,390                  | 662,299               | 490           | 280                | 360                  | 590                  | 680                  | 620                  | 570                  | 560                  | 570                  | 550                  | 480                  | 460                  | 760                  | 630                  | 540                  | 440                  | 1,220                  | 470                    | 140                |  |
| V1T          | 24,790                  | 1,109,501             | 1,010         | 630                | 1,100                | 2,450                | 2,950                | 2,100                | 1,950                | 1,780                | 1,600                | 1,410                | 1,250                | 1,000                | 1,570                | 1,120                | 790                  | 630                  | 1,020                  | 330                    | 110                |  |
| V1V          | 19,790                  | 1,239,980             | 1,060         | 610                | 780                  | 1,140                | 1,340                | 1,230                | 1,110                | 1,060                | 1,130                | 1,160                | 910                  | 910                  | 1,400                | 1,220                | 1,040                | 730                  | 1,790                  | 830                    | 350                |  |
| V1W          | 30,180                  | 2,095,721             | 1,300         | 890                | 1,300                | 1,930                | 2,440                | 2,020                | 1,700                | 1,690                | 1,620                | 1,570                | 1,300                | 1,170                | 1,990                | 1,670                | 1,340                | 1,100                | 2,710                  | 1,600                  | 850                |  |
| V1X          | 28,340                  | 1,235,829             | 1,320         | 820                | 1,370                | 2,450                | 3,090                | 2,460                | 2,280                | 2,080                | 1,900                | 1,710                | 1,430                | 1,200                | 1,930                | 1,320                | 930                  | 630                  | 1,050                  | 280                    | 90                 |  |
| V1Y          | 31,620                  | 1,739,420             | 1,130         | 790                | 1,260                | 2,570                | 3,240                | 2,580                | 2,180                | 2,140                | 1,880                | 1,850                | 1,580                | 1,350                | 2,050                | 1,610                | 1,310                | 950                  | 1,960                  | 800                    | 390                |  |
| V1Z          | 12,760                  | 740,845               | 560           | 400                | 580                  | 900                  | 1,070                | 910                  | 780                  | 800                  | 700                  | 700                  | 560                  | 520                  | 880                  | 710                  | 580                  | 460                  | 1,040                  | 480                    | 150                |  |
| V2A          | 34,720                  | 1,727,659             | 1,250         | 970                | 1,490                | 3,020                | 3,880                | 2,880                | 2,590                | 2,450                | 2,230                | 2,060                | 1,680                | 1,350                | 2,310                | 1,670                | 1,260                | 880                  | 1,770                  | 680                    | 310                |  |
| V2B          | 32,960                  | 1,530,240             | 1,600         | 880                | 1,410                | 2,900                | 3,290                | 2,570                | 2,310                | 2,120                | 1,980                | 1,840                | 1,570                | 1,360                | 2,170                | 1,660                | 1,260                | 880                  | 1,950                  | 520                    | 100                |  |
| V2C          | 21,980                  | 1,204,529             | 1,110         | 630                | 900                  | 1,760                | 2,110                | 1,650                | 1,450                | 1,310                | 1,170                | 1,170                | 980                  | 890                  | 1,450                | 1,100                | 960                  | 710                  | 1,780                  | 630                    | 220                |  |
| V2E          | 12,720                  | 792,944               | 650           | 430                | 520                  | 820                  | 880                  | 740                  | 720                  | 670                  | 660                  | 640                  | 590                  | 540                  | 850                  | 780                  | 640                  | 540                  | 1,310                  | 580                    | 180                |  |
| V2G          | 14,750                  | 739,810               | 970           | 470                | 720                  | 1,180                | 1,370                | 1,060                | 970                  | 930                  | 790                  | 760                  | 580                  | 530                  | 830                  | 630                  | 480                  | 1,220                | 760                    | 280                    | 90                 |  |
| V2H          | 6,240                   | 369,190               | 490           | 170                | 230                  | 340                  | 480                  | 370                  | 310                  | 370                  | 350                  | 370                  | 310                  | 270                  | 410                  | 390                  | 310                  | 240                  | 530                    | 230                    | 90                 |  |
| V2J          | 18,390                  | 876,167               | 1,180         | 580                | 970                  | 1,680                | 1,950                | 1,430                | 1,310                | 1,150                | 1,020                | 790                  | 730                  | 610                  | 990                  | 960                  | 690                  | 580                  | 1,410                  | 290                    | 90                 |  |
| V2K          | 16,730                  | 1,016,824             | 870           | 450                | 620                  | 950                  | 1,170                | 1,080                | 900                  | 900                  | 880                  | 870                  | 750                  | 700                  | 1,170                | 1,070                | 910                  | 790                  | 1,870                  | 640                    | 150                |  |
| V2L          | 8,130                   | 362,473               | 430           | 210                | 420                  | 920                  | 930                  | 750                  | 640                  | 570                  | 460                  | 380                  | 330                  | 300                  | 470                  | 320                  | 270                  | 200                  | 380                    | 120                    | 40                 |  |
| V2M          | 18,510                  | 934,892               | 910           | 590                | 810                  | 1,490                | 1,670                | 1,370                | 1,240                | 1,140                | 1,040                | 980                  | 840                  | 720                  | 1,380                | 1,080                | 840                  | 660                  | 1,310                  | 370                    | 90                 |  |
| V2N          | 26,530                  | 1,561,992             | 1,390         | 780                | 1,020                | 1,610                | 1,980                | 1,620                | 1,510                | 1,490                | 1,390                | 1,390                | 1,240                | 1,090                | 1,840                | 1,680                | 1,380                | 1,240                | 2,800                  | 860                    | 230                |  |
| V2P          | 30,010                  | 1,328,542             | 1,790         | 890                | 1,570                | 2,970                | 3,430                | 2,430                | 2,200                | 2,030                | 1,880                | 1,600                | 1,370                | 1,140                | 1,780                | 1,330                | 1,020                | 780                  | 1,290                  | 370                    | 150                |  |
| V2R          | 42,720                  | 2,235,665             | 2,550         | 1,260              | 1,950                | 3,040                | 3,690                | 3,170                | 2,730                | 2,490                | 2,440                | 1,980                | 1,700                | 1,570                | 2,930                | 2,390                | 1,820                | 1,580                | 3,170                  | 960                    | 300                |  |
| V2S          | 40,040                  | 1,930,238             | 2,350         | 1,360              | 2,000                | 3,320                | 4,150                | 3,070                | 2,680                | 2,490                | 2,240                | 2,050                | 1,850                | 1,700                | 2,720                | 2,090                | 1,600                | 1,190                | 2,290                  | 710                    | 210                |  |
| V2T          | 48,730                  | 1,967,285             | 3,240         | 1,930              | 3,310                | 5,180                | 5,660                | 4,230                | 3,590                | 3,180                | 2,670                | 2,370                | 2,080                | 1,770                | 2,690                | 2,070                | 1,370                | 950                  | 1,620                  | 460                    | 170                |  |
| V2V          | 27,410                  | 1,319,259             | 1,760         | 860                | 1,370                | 2,390                | 2,650                | 1,950                | 1,810                | 1,590                | 1,440                | 1,500                | 1,190                | 1,070                | 1,850                | 1,590                | 1,190                | 860                  | 1,780                  | 470                    | 110                |  |
| V2W          | 16,820                  | 1,018,069             | 1,030         | 570                | 790                  | 1,010                | 1,210                | 960                  | 870                  | 810                  | 840                  | 790                  | 720                  | 680                  | 1,200                | 1,030                | 830                  | 790                  | 1,760                  | 700                    | 210                |  |
| V2X          | 39,530                  | 2,043,701             | 1,960         | 1,080              | 1,620                | 2,940                | 3,610                | 2,840                | 2,570                | 2,470                | 2,290                | 2,150                | 1,810                | 1,690                | 2,940                | 2,350                | 1,810                | 1,440                | 2,940                  | 810                    | 220                |  |
| V2Y          | 32,280                  | 1,909,612             | 2,400         | 1,190              | 1,480                | 2,000                | 2,400                | 1,950                | 1,910                | 1,730                | 1,640                | 1,570                | 1,490                | 1,360                | 2,420                | 2,010                | 1,710                | 1,450                | 3,190                  | 1,050                  | 350                |  |
| V2Z          | 13,760                  | 856,347               | 630           | 390                | 590                  | 880                  | 1,160                | 840                  | 730                  | 660                  | 600                  |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |  |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA | Total  | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-----|--------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| V4N | 66,580 | 3,453,247             | 4,990         | 2,830              | 3,510                | 4,860                | 5,650                | 4,490                | 3,850                | 3,680                | 3,440                | 3,170                | 3,040                | 2,630                | 4,480                | 3,610                | 2,850                | 2,310                | 4,920                  | 1,700                  | 570                |
| V4P | 10,910 | 794,981               | 730           | 410                | 520                  | 730                  | 930                  | 680                  | 530                  | 500                  | 510                  | 550                  | 420                  | 400                  | 690                  | 590                  | 510                  | 350                  | 950                    | 580                    | 360                |
| V4R | 12,430 | 766,815               | 750           | 420                | 560                  | 780                  | 860                  | 720                  | 630                  | 640                  | 610                  | 580                  | 530                  | 470                  | 890                  | 740                  | 630                  | 610                  | 1,320                  | 520                    | 170                |
| V4S | 5,890  | 315,522               | 400           | 180                | 320                  | 460                  | 520                  | 360                  | 360                  | 310                  | 310                  | 280                  | 270                  | 250                  | 380                  | 320                  | 290                  | 200                  | 480                    | 140                    | 60                 |
| V4T | 24,610 | 1,304,775             | 1,130         | 680                | 1,060                | 1,820                | 2,200                | 1,810                | 1,610                | 1,620                | 1,570                | 1,460                | 1,230                | 1,050                | 1,770                | 1,410                | 1,040                | 770                  | 1,520                  | 650                    | 210                |
| V4V | 13,980 | 798,684               | 590           | 380                | 640                  | 1,050                | 1,220                | 980                  | 940                  | 850                  | 800                  | 760                  | 670                  | 580                  | 980                  | 820                  | 600                  | 440                  | 1,050                  | 470                    | 170                |
| V4W | 16,570 | 860,284               | 970           | 540                | 770                  | 1,200                | 1,540                | 1,180                | 1,070                | 1,050                | 950                  | 950                  | 800                  | 670                  | 1,150                | 890                  | 710                  | 550                  | 1,030                  | 420                    | 140                |
| V4X | 11,080 | 620,193               | 730           | 420                | 600                  | 870                  | 930                  | 720                  | 680                  | 660                  | 630                  | 560                  | 500                  | 430                  | 700                  | 570                  | 450                  | 330                  | 760                    | 380                    | 170                |
| V4Z | 4,060  | 233,070               | 260           | 150                | 200                  | 290                  | 330                  | 250                  | 220                  | 220                  | 210                  | 210                  | 170                  | 180                  | 260                  | 220                  | 210                  | 160                  | 340                    | 130                    | 50                 |
| V5A | 20,190 | 1,189,645             | 2,190         | 960                | 1,100                | 1,370                | 1,760                | 1,260                | 1,000                | 930                  | 880                  | 850                  | 810                  | 750                  | 1,180                | 1,020                | 800                  | 640                  | 1,710                  | 750                    | 350                |
| V5B | 18,720 | 1,044,263             | 1,560         | 770                | 1,000                | 1,470                | 1,690                | 1,240                | 1,050                | 950                  | 900                  | 880                  | 780                  | 670                  | 1,180                | 960                  | 770                  | 580                  | 1,380                  | 640                    | 280                |
| V5C | 28,790 | 1,729,405             | 2,000         | 950                | 1,330                | 1,950                | 2,450                | 1,930                | 1,610                | 1,490                | 1,300                | 1,260                | 1,220                | 1,110                | 1,940                | 1,600                | 1,400                | 1,110                | 2,580                  | 1,110                  | 450                |
| V5E | 22,830 | 1,153,185             | 2,040         | 930                | 1,280                | 2,000                | 2,330                | 1,630                | 1,410                | 1,220                | 1,170                | 1,100                | 890                  | 780                  | 1,330                | 1,030                | 850                  | 600                  | 1,400                  | 600                    | 260                |
| V5H | 17,270 | 896,512               | 1,270         | 660                | 940                  | 1,460                | 1,730                | 1,210                | 1,050                | 930                  | 840                  | 830                  | 730                  | 640                  | 1,040                | 820                  | 720                  | 550                  | 1,190                  | 500                    | 160                |
| V5G | 35,440 | 1,614,105             | 3,910         | 1,660              | 1,990                | 2,840                | 3,620                | 2,520                | 2,210                | 1,960                | 1,790                | 1,620                | 1,390                | 1,180                | 2,010                | 1,250                | 1,250                | 950                  | 2,040                  | 730                    | 320                |
| V5J | 19,810 | 958,934               | 1,770         | 830                | 1,180                | 1,600                | 2,010                | 1,430                | 1,250                | 1,080                | 990                  | 980                  | 790                  | 720                  | 1,150                | 880                  | 690                  | 610                  | 1,210                  | 470                    | 180                |
| V5K | 19,090 | 1,025,445             | 1,060         | 670                | 1,050                | 1,630                | 2,050                | 1,450                | 1,150                | 1,100                | 1,010                | 880                  | 780                  | 670                  | 1,170                | 910                  | 700                  | 620                  | 1,360                  | 570                    | 240                |
| V5L | 15,440 | 902,013               | 630           | 360                | 630                  | 1,260                | 1,540                | 1,060                | 1,020                | 860                  | 760                  | 750                  | 720                  | 610                  | 1,090                | 860                  | 720                  | 580                  | 1,250                  | 540                    | 200                |
| V5M | 19,820 | 871,376               | 1,280         | 790                | 1,170                | 1,960                | 2,510                | 1,610                | 1,460                | 1,190                | 1,010                | 960                  | 820                  | 710                  | 1,100                | 790                  | 580                  | 500                  | 930                    | 320                    | 130                |
| V5N | 29,170 | 1,508,607             | 1,610         | 960                | 1,470                | 2,500                | 3,210                | 2,270                | 1,980                | 1,650                | 1,500                | 1,380                | 1,250                | 1,080                | 1,770                | 1,500                | 1,140                | 890                  | 2,020                  | 790                    | 330                |
| V5P | 28,010 | 1,226,240             | 2,000         | 1,150              | 1,750                | 2,710                | 3,510                | 2,420                | 2,070                | 1,700                | 1,620                | 1,310                | 1,120                | 970                  | 1,440                | 1,080                | 770                  | 630                  | 1,170                  | 440                    | 160                |
| V5R | 41,760 | 1,792,670             | 2,950         | 1,580              | 2,440                | 3,740                | 4,740                | 3,540                | 3,140                | 2,670                | 2,310                | 2,090                | 1,810                | 1,540                | 2,480                | 1,760                | 1,340                | 1,010                | 1,850                  | 600                    | 150                |
| V5S | 26,030 | 1,304,219             | 1,740         | 970                | 1,320                | 2,110                | 2,650                | 1,830                | 1,610                | 1,470                | 1,360                | 1,260                | 1,130                | 1,040                | 1,740                | 1,290                | 1,120                | 820                  | 1,820                  | 580                    | 200                |
| V5T | 20,360 | 1,347,498             | 760           | 470                | 1,300                | 1,640                | 1,230                | 1,180                | 1,060                | 1,010                | 920                  | 900                  | 850                  | 1,530                | 1,340                | 1,150                | 980                  | 2,120                | 870                    | 400                    |                    |
| V5V | 19,420 | 1,256,344             | 990           | 620                | 930                  | 1,440                | 1,700                | 1,290                | 1,130                | 1,030                | 970                  | 970                  | 800                  | 750                  | 1,240                | 1,000                | 800                  | 680                  | 1,770                  | 900                    | 440                |
| V5W | 17,440 | 919,115               | 1,160         | 630                | 890                  | 1,500                | 1,790                | 1,360                | 1,230                | 1,060                | 920                  | 860                  | 730                  | 640                  | 990                  | 770                  | 570                  | 500                  | 1,130                  | 510                    | 220                |
| V5X | 26,460 | 1,142,157             | 2,010         | 1,090              | 1,610                | 2,370                | 3,120                | 1,790                | 1,360                | 1,170                | 1,520                | 1,290                | 1,080                | 910                  | 1,280                | 1,020                | 790                  | 560                  | 1,180                  | 440                    | 150                |
| V5Y | 15,170 | 1,276,402             | 920           | 470                | 550                  | 900                  | 990                  | 790                  | 730                  | 610                  | 580                  | 630                  | 530                  | 510                  | 950                  | 880                  | 770                  | 700                  | 1,840                  | 1,180                  | 650                |
| V5Z | 20,270 | 1,588,485             | 1,280         | 640                | 820                  | 1,220                | 1,450                | 1,070                | 950                  | 900                  | 830                  | 820                  | 750                  | 760                  | 1,230                | 1,210                | 1,090                | 880                  | 2,280                  | 1,290                  | 800                |
| V6A | 17,810 | 954,591               | 760           | 450                | 990                  | 2,690                | 3,150                | 1,380                | 1,070                | 910                  | 630                  | 510                  | 480                  | 450                  | 700                  | 590                  | 530                  | 440                  | 1,230                  | 570                    | 310                |
| V6B | 27,510 | 2,241,996             | 1,940         | 870                | 1,030                | 1,750                | 2,040                | 1,490                | 1,340                | 1,230                | 1,020                | 940                  | 900                  | 850                  | 1,550                | 1,520                | 1,350                | 1,160                | 3,440                  | 2,020                  | 1,090              |
| V6C | 6,720  | 940,475               | 590           | 270                | 290                  | 830                  | 1,040                | 410                  | 310                  | 240                  | 200                  | 170                  | 140                  | 120                  | 240                  | 190                  | 160                  | 140                  | 420                    | 390                    | 600                |
| V6E | 24,590 | 1,888,055             | 1,530         | 670                | 880                  | 1,470                | 2,020                | 1,540                | 1,420                | 1,240                | 1,170                | 1,130                | 1,030                | 1,040                | 1,660                | 1,440                | 1,120                | 940                  | 2,320                  | 1,240                  | 740                |
| V6G | 23,480 | 1,583,833             | 1,240         | 580                | 800                  | 1,420                | 1,970                | 1,580                | 1,430                | 1,320                | 1,270                | 1,150                | 1,070                | 1,000                | 1,610                | 1,400                | 1,090                | 910                  | 2,070                  | 1,040                  | 550                |
| V6H | 17,760 | 1,890,659             | 870           | 440                | 550                  | 790                  | 1,070                | 850                  | 800                  | 760                  | 790                  | 780                  | 770                  | 630                  | 1,290                | 1,120                | 1,030                | 810                  | 2,060                  | 1,300                  | 1,050              |
| V6J | 19,580 | 1,815,232             | 1,010         | 560                | 690                  | 960                  | 1,270                | 1,020                | 850                  | 830                  | 780                  | 820                  | 770                  | 780                  | 1,350                | 1,280                | 1,120                | 910                  | 2,350                  | 1,330                  | 910                |
| V6K | 21,060 | 1,744,519             | 1,090         | 630                | 760                  | 1,040                | 1,310                | 1,050                | 930                  | 930                  | 930                  | 900                  | 880                  | 830                  | 1,440                | 1,340                | 1,180                | 960                  | 2,430                  | 1,470                  | 850                |
| V6L | 8,350  | 744,904               | 790           | 440                | 490                  | 560                  | 620                  | 470                  | 410                  | 320                  | 290                  | 300                  | 260                  | 240                  | 400                  | 360                  | 290                  | 260                  | 760                    | 610                    | 500                |
| V6M | 13,730 | 1,168,522             | 1,370         | 690                | 710                  | 810                  | 1,080                | 790                  | 660                  | 590                  | 550                  | 560                  | 450                  | 410                  | 730                  | 620                  | 550                  | 420                  | 1,190                  | 870                    | 700                |
| V6N | 11,160 | 1,206,608             | 1,210         | 700                | 590                  | 690                  | 710                  | 550                  | 470                  | 400                  | 370                  | 360                  | 300                  | 300                  | 520                  | 480                  | 390                  | 310                  | 1,070                  | 880                    | 880                |
| V6P | 26,930 | 1,684,930             | 2,660         | 1,250              | 1,510                | 2,070                | 2,490                | 1,760                | 1,510                | 1,420                | 1,300                | 1,210                | 1,080                | 870                  | 1,460                | 1,220                | 930                  | 690                  | 1,840                  | 980                    | 680                |
| V6R | 15,150 | 1,524,878             | 1,290         | 760                | 710                  | 930                  | 1,030                | 730                  | 590                  | 590                  | 540                  | 560                  | 530                  | 480                  | 830                  | 760                  | 630                  | 550                  | 1,460                  | 1,120                  | 1,030              |
| V6S | 10,940 | 817,436               | 1,570         | 720                | 660                  | 710                  | 690                  | 510                  | 450                  | 350                  | 320                  | 360                  | 310                  | 300                  | 520                  | 440                  | 400                  | 310                  | 1,050                  | 750                    | 530                |
| V6T | 10,520 | 659,882               | 2,900         | 920                | 740                  | 680                  | 660                  | 450                  | 370                  | 310                  | 270                  | 270                  | 230                  | 190                  | 340                  | 320                  | 240                  | 210                  | 620                    | 480                    | 330                |
| V6V | 9,890  | 483,737               | 860           | 390                | 580                  | 840                  | 960                  | 630                  | 630                  | 560                  | 520                  | 480                  | 370                  | 390                  | 610                  | 500                  | 400                  | 280                  | 610                    | 200                    | 90                 |
| V6W | 1,970  | 102,198               | 170           | 50                 | 110                  | 150                  | 160                  | 130                  | 120                  | 110                  | 110                  | 90                   | 90                   | 90                   | 140                  | 120                  | 90                   | 60                   | 120                    | 40                     | 20                 |
| V6X | 35,260 | 1,503,464             | 4,130         | 1,720              | 2,210                | 3,280                | 3,620                | 2,650                | 2,390                | 1,960                | 1,670                | 1,550                | 1,340                | 1,170                | 1,800                | 1,360                | 1,060                | 800                  | 1,710                  | 570                    | 260                |
| V6Y | 42,460 | 1,774,129             | 4,740         | 2,150              | 2,900                | 3,920                | 4,790                | 3,220                | 2,720                | 2,330                | 2,030                | 1,870                | 1,550                | 1,430                | 2,140                | 1,600                | 1,250                | 910                  | 1,970                  | 680                    | 280                |
| V6Z | 16,680 | 1,441,712             | 1,220         | 490                | 690                  | 1,020                | 1,130                | 890                  | 810                  | 670                  | 660                  | 590                  | 550                  | 550                  | 790                  | 890                  | 780                  | 710                  | 1,970                  | 1,330                  | 790                |
| V7A | 22,680 | 1,069,124             | 2,040         | 1,050              | 1,440                | 1,970                | 2,250                | 1,680                | 1,510                | 1,290                | 1,180                | 1,110                | 860                  | 790                  | 1,260                | 970                  | 790                  | 550                  | 1,250                  | 470                    | 220                |
| V7B | 710    | 44,149                | 40            | 20                 | 20                   | 40                   | 60                   | 50                   | 30                   | 40                   | 40                   | 30                   | 40                   | 30                   | 50                   | 40                   | 30                   | 40                   | 80                     | 30                     | 10                 |
| V7C | 34,320 | 1,652,985             | 3,780         | 1,810              | 2,250                | 2,920                | 3,470                | 2,460                | 2,010                | 1,720                | 1,570                | 1,470                | 1,270                | 1,060                | 1,850                | 1,440                | 1,080                | 860                  | 2,000                  | 870                    | 450                |
| V7E | 31,500 | 1,829,156             | 2,630         | 1,360              | 1,730                | 2,240                | 2,720                | 1,930                | 1,700                | 1,560                | 1,400                | 1,450                | 1,280                | 1,190                | 1,940                | 1,580                | 1,370                | 1,150                | 2,620                  | 1,130                  | 530                |
| V7G | 9,850  | 914,943               | 500           | 290                | 380                  | 500                  | 540                  | 420                  | 470                  | 400                  | 450                  | 450                  | 400                  | 360                  | 620                  | 580                  | 520                  | 440                  | 1,280                  | 770                    | 490                |
| V7H | 9,950  | 770,608               | 600           | 320                | 390                  | 540                  | 660                  | 540                  | 490                  | 430                  | 480                  | 460                  | 400                  | 370                  | 640                  | 580                  | 490                  | 420                  | 1,170                  | 640                    | 350                |
| V7J | 13,430 | 905,417               | 770           | 420                | 550                  | 760                  | 1,050                | 800                  | 700                  | 690                  | 670                  | 650                  | 540                  | 500                  | 900                  | 770                  | 650                  | 540                  | 1,430                  | 700                    | 320                |
| V7K | 9,890  | 810,134               | 560           | 350                | 390                  | 530                  | 600                  | 570                  | 470                  | 450                  | 400                  | 450                  | 390                  | 340                  | 610                  | 560                  | 470                  | 430                  | 1,170                  | 740                    | 410                |
| V7L | 22,480 | 1,521,528             | 1,200         | 710                | 830                  | 1,400                | 1,830                | 1,440                | 1,250                | 1,130                | 1,180                | 1,130                | 1,020                | 970                  | 1,550                |                      |                      |                      |                        |                        |                    |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA   | Total     | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-------|-----------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| V8Y   | 8,550     | 682,751               | 320           | 260                | 320                  | 400                  | 500                  | 420                  | 390                  | 370                  | 420                  | 490                  | 410                  | 340                  | 660                  | 580                  | 470                  | 370                  | 1,020                  | 530                    | 290                |
| V8Z   | 25,860    | 1,415,594             | 970           | 660                | 1,010                | 1,740                | 2,000                | 1,790                | 1,540                | 1,560                | 1,600                | 1,570                | 1,430                | 1,270                | 2,130                | 1,660                | 1,280                | 950                  | 1,930                  | 620                    | 160                |
| V9A   | 31,570    | 1,694,874             | 1,250         | 630                | 1,080                | 2,160                | 2,730                | 2,080                | 2,130                | 2,030                | 1,990                | 1,950                | 1,730                | 1,440                | 2,570                | 2,060                | 1,670                | 1,170                | 2,050                  | 650                    | 200                |
| V9B   | 40,020    | 2,261,340             | 1,540         | 1,010              | 1,400                | 2,460                | 2,970                | 2,580                | 2,470                | 2,420                | 2,380                | 2,410                | 2,250                | 1,930                | 3,410                | 2,740                | 2,130                | 1,590                | 3,110                  | 940                    | 290                |
| V9C   | 20,500    | 1,233,044             | 890           | 480                | 720                  | 1,110                | 1,360                | 1,210                | 1,080                | 1,150                | 1,130                | 1,200                | 1,040                | 990                  | 1,740                | 1,540                | 1,310                | 1,000                | 1,840                  | 530                    | 190                |
| V9E   | 4,290     | 307,672               | 140           | 120                | 170                  | 210                  | 270                  | 260                  | 210                  | 210                  | 250                  | 240                  | 220                  | 190                  | 360                  | 300                  | 220                  | 170                  | 410                    | 220                    | 110                |
| V9G   | 13,020    | 652,632               | 650           | 410                | 620                  | 1,030                | 1,240                | 990                  | 840                  | 850                  | 850                  | 820                  | 600                  | 540                  | 870                  | 650                  | 520                  | 390                  | 810                    | 270                    | 90                 |
| V9H   | 8,210     | 452,430               | 440           | 240                | 400                  | 570                  | 650                  | 560                  | 500                  | 500                  | 520                  | 460                  | 370                  | 330                  | 540                  | 450                  | 380                  | 310                  | 650                    | 270                    | 80                 |
| V9J   | 7,620     | 401,426               | 370           | 260                | 370                  | 560                  | 700                  | 570                  | 490                  | 490                  | 450                  | 460                  | 360                  | 340                  | 460                  | 370                  | 310                  | 230                  | 530                    | 240                    | 70                 |
| V9K   | 14,540    | 750,803               | 510           | 350                | 600                  | 1,140                | 1,430                | 1,180                | 960                  | 1,050                | 980                  | 1,020                | 680                  | 620                  | 990                  | 780                  | 570                  | 410                  | 820                    | 340                    | 110                |
| V9L   | 29,590    | 1,405,004             | 1,750         | 930                | 1,460                | 2,690                | 3,080                | 2,240                | 2,060                | 1,960                | 1,750                | 1,660                | 1,330                | 1,200                | 1,770                | 1,410                | 1,090                | 860                  | 1,630                  | 540                    | 190                |
| V9M   | 14,910    | 818,271               | 540           | 360                | 560                  | 890                  | 1,260                | 1,110                | 1,030                | 1,010                | 970                  | 950                  | 810                  | 680                  | 1,130                | 910                  | 690                  | 480                  | 1,010                  | 400                    | 130                |
| V9N   | 27,160    | 1,355,598             | 990           | 620                | 1,080                | 2,230                | 2,630                | 2,230                | 2,030                | 2,000                | 1,740                | 1,720                | 1,400                | 1,170                | 1,840                | 1,440                | 1,050                | 790                  | 1,510                  | 540                    | 170                |
| V9P   | 24,440    | 1,308,682             | 790           | 500                | 990                  | 1,790                | 2,480                | 2,000                | 1,640                | 1,700                | 1,690                | 1,600                | 1,270                | 1,010                | 1,700                | 1,360                | 960                  | 690                  | 1,460                  | 590                    | 240                |
| V9R   | 25,730    | 1,240,160             | 1,220         | 740                | 1,170                | 2,380                | 2,710                | 2,150                | 1,950                | 1,840                | 1,580                | 1,440                | 1,170                | 920                  | 1,560                | 1,200                | 920                  | 680                  | 1,380                  | 550                    | 180                |
| V9S   | 13,740    | 642,464               | 530           | 320                | 570                  | 1,230                | 1,500                | 1,120                | 1,040                | 1,000                | 920                  | 890                  | 720                  | 600                  | 890                  | 670                  | 480                  | 370                  | 640                    | 200                    | 60                 |
| V9T   | 29,020    | 1,531,328             | 1,240         | 730                | 1,190                | 1,960                | 2,630                | 2,180                | 1,900                | 1,920                | 1,830                | 1,820                | 1,560                | 1,240                | 2,070                | 1,690                | 1,290                | 910                  | 2,020                  | 680                    | 210                |
| V9V   | 9,180     | 522,977               | 420           | 280                | 410                  | 610                  | 730                  | 610                  | 570                  | 520                  | 590                  | 540                  | 450                  | 350                  | 700                  | 520                  | 430                  | 310                  | 730                    | 300                    | 110                |
| V9W   | 25,350    | 1,227,015             | 1,160         | 680                | 1,140                | 2,100                | 2,540                | 2,130                | 1,970                | 1,800                | 1,560                | 1,470                | 1,210                | 1,080                | 1,560                | 1,300                | 900                  | 720                  | 1,400                  | 520                    | 130                |
| V9X   | 8,640     | 456,834               | 440           | 250                | 390                  | 620                  | 690                  | 620                  | 550                  | 550                  | 510                  | 460                  | 460                  | 390                  | 650                  | 480                  | 400                  | 310                  | 650                    | 190                    | 50                 |
| V9Y   | 21,260    | 924,006               | 1,100         | 620                | 1,010                | 2,140                | 2,330                | 1,800                | 1,660                | 1,560                | 1,300                | 1,180                | 990                  | 850                  | 1,270                | 970                  | 710                  | 520                  | 960                    | 240                    | 60                 |
| V9Z   | 15,260    | 787,786               | 720           | 390                | 660                  | 1,120                | 1,360                | 1,110                | 970                  | 950                  | 960                  | 850                  | 780                  | 690                  | 1,120                | 920                  | 740                  | 530                  | 1,040                  | 290                    | 70                 |
| TOTAL | 4,033,140 | 225,808,230           | 258,500       | 137,070            | 195,910              | 309,570              | 371,740              | 284,440              | 252,070              | 233,350              | 217,650              | 205,200              | 177,320              | 156,050              | 259,180              | 209,230              | 165,780              | 130,870              | 293,040                | 121,650                | 54,540             |





Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total         | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|--------------|---------------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| <b>PR 60</b> | <b>Yukon</b>  |                      |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| Y0A          | 1,340         | 71,321               | 60            | 40                 | 60                   | 100                  | 120                  | 80                   | 100                  | 90                   | 90                   | 50                   | 50                   | 40                   | 90                   | 80                   | 60                   | 50                   | 120                    | 40                     | 10                 |
| Y0B          | 5,310         | 290,932              | 220           | 150                | 230                  | 310                  | 480                  | 400                  | 330                  | 320                  | 290                  | 250                  | 250                  | 210                  | 380                  | 360                  | 260                  | 230                  | 490                    | 130                    | 20                 |
| Y1A          | 23,670        | 1,598,802            | 810           | 500                | 730                  | 1,050                | 1,520                | 1,140                | 1,230                | 1,260                | 1,130                | 1,110                | 960                  | 950                  | 1,910                | 1,900                | 1,660                | 1,460                | 3,160                  | 930                    | 270                |
| <b>TOTAL</b> | <b>30,320</b> | <b>1,961,055</b>     | <b>1,090</b>  | <b>700</b>         | <b>1,020</b>         | <b>1,450</b>         | <b>2,120</b>         | <b>1,620</b>         | <b>1,660</b>         | <b>1,670</b>         | <b>1,510</b>         | <b>1,410</b>         | <b>1,260</b>         | <b>1,210</b>         | <b>2,380</b>         | <b>2,350</b>         | <b>1,990</b>         | <b>1,730</b>         | <b>3,780</b>           | <b>1,090</b>           | <b>300</b>         |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total                        | Total Income (\$000) | Under \$5,000 | \$5,000      | \$10,000     | \$15,000     | \$20,000     | \$25,000     | \$30,000     | \$35,000     | \$40,000     | \$45,000    | \$50,000     | \$55,000    | \$60,000     | \$70,000     | \$80,000     | \$90,000     | \$100,000    | \$150,000    | \$250,000  |
|--------------|------------------------------|----------------------|---------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|--------------|-------------|--------------|-------------|--------------|--------------|--------------|--------------|--------------|--------------|------------|
|              |                              |                      |               | to \$9,999   | to \$14,999  | to \$19,999  | to \$24,999  | to \$29,999  | to \$34,999  | to \$39,999  | to \$44,999  | to \$49,999 | to \$54,999  | to \$59,999 | to \$69,999  | to \$79,999  | to \$89,999  | to \$99,999  | to \$149,999 | to \$249,999 | and over   |
| <b>PR 61</b> | <b>Northwest Territories</b> |                      |               |              |              |              |              |              |              |              |              |             |              |             |              |              |              |              |              |              |            |
| XOE          | 15,750                       | 903,546              | 1,010         | 600          | 850          | 1,140        | 1,530        | 1,260        | 950          | 730          | 620          | 500         | 460          | 430         | 800          | 740          | 590          | 580          | 2,130        | 750          | 90         |
| XOG          | 390                          | 13,560               | 50            | 40           | 40           | 30           | 50           | 30           | 20           | 20           | 20           | 10          | 10           | 10          | 10           | 10           | 10           | 10           | 30           | 10           |            |
| X1A          | 15,820                       | 1,264,742            | 740           | 430          | 490          | 630          | 860          | 670          | 600          | 560          | 570          | 490         | 540          | 490         | 960          | 1,010        | 910          | 920          | 3,480        | 1,210        | 280        |
| <b>TOTAL</b> | <b>31,960</b>                | <b>2,181,848</b>     | <b>1,810</b>  | <b>1,060</b> | <b>1,380</b> | <b>1,800</b> | <b>2,430</b> | <b>1,970</b> | <b>1,570</b> | <b>1,310</b> | <b>1,210</b> | <b>990</b>  | <b>1,010</b> | <b>930</b>  | <b>1,770</b> | <b>1,750</b> | <b>1,510</b> | <b>1,500</b> | <b>5,630</b> | <b>1,960</b> | <b>370</b> |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA          | Total          | Total Income (\$'000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|--------------|----------------|-----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| <b>PR 62</b> | <b>Nunavut</b> |                       |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| X0A          | 11,790         | 722,566               | 1,040         | 760                | 850                  | 890                  | 930                  | 710                  | 490                  | 390                  | 330                  | 270                  | 250                  | 220                  | 440                  | 430                  | 490                  | 470                  | 2,010                  | 730                    | 100                |
| X0B          | 4,040          | 192,078               | 330           | 290                | 350                  | 400                  | 430                  | 330                  | 240                  | 170                  | 140                  | 110                  | 80                   | 90                   | 150                  | 130                  | 120                  | 110                  | 400                    | 160                    | 20                 |
| X0C          | 6,520          | 334,484               | 650           | 530                | 510                  | 540                  | 590                  | 430                  | 320                  | 260                  | 180                  | 170                  | 150                  | 140                  | 250                  | 230                  | 240                  | 240                  | 830                    | 250                    | 40                 |
| <b>TOTAL</b> | <b>22,360</b>  | <b>1,249,127</b>      | <b>2,020</b>  | <b>1,580</b>       | <b>1,700</b>         | <b>1,830</b>         | <b>1,940</b>         | <b>1,460</b>         | <b>1,050</b>         | <b>830</b>           | <b>640</b>           | <b>550</b>           | <b>490</b>           | <b>440</b>           | <b>830</b>           | <b>790</b>           | <b>850</b>           | <b>830</b>           | <b>3,240</b>           | <b>1,140</b>           | <b>160</b>         |



Table 1b - FSA Statistics for All Returns, by Total Income - 2020 Tax Year

| FSA   | Total      | Total Income (\$000) | Under \$5,000 | \$5,000 to \$9,999 | \$10,000 to \$14,999 | \$15,000 to \$19,999 | \$20,000 to \$24,999 | \$25,000 to \$29,999 | \$30,000 to \$34,999 | \$35,000 to \$39,999 | \$40,000 to \$44,999 | \$45,000 to \$49,999 | \$50,000 to \$54,999 | \$55,000 to \$59,999 | \$60,000 to \$69,999 | \$70,000 to \$79,999 | \$80,000 to \$89,999 | \$90,000 to \$99,999 | \$100,000 to \$149,999 | \$150,000 to \$249,999 | \$250,000 and over |
|-------|------------|----------------------|---------------|--------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|------------------------|------------------------|--------------------|
| PR    | Canada     |                      |               |                    |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                      |                        |                        |                    |
| TOTAL | 29,373,450 | 1,599,911,746        | 1,799,350     | 1,147,320          | 1,697,580            | 2,216,610            | 2,650,020            | 2,045,450            | 1,834,100            | 1,721,270            | 1,584,550            | 1,523,880            | 1,287,650            | 1,127,750            | 1,886,380            | 1,502,900            | 1,186,940            | 930,210              | 2,049,750              | 810,890                | 370,870            |