

Tableau 1c - RTA pour toutes les déclarations produites, hommes - année d'imposition 2020

| RTA   | Total    | Revenu total<br>(000\$) | Moins de<br>5 000\$ | 5 000\$<br>à<br>9 999\$ | 10 000\$<br>à<br>14 999\$ | 15 000\$<br>à<br>19 999\$ | 20 000\$<br>à<br>24 999\$ | 25 000\$<br>à<br>29 999\$ | 30 000\$<br>à<br>34 999\$ | 35 000\$<br>à<br>39 999\$ | 40 000\$<br>à<br>44 999\$ | 45 000\$<br>à<br>49 999\$ | 50 000\$<br>à<br>54 999\$ | 55 000\$<br>à<br>59 999\$ | 60 000\$<br>à<br>69 999\$ | 70 000\$<br>à<br>79 999\$ | 80 000\$<br>à<br>89 999\$ | 90 000\$<br>à<br>99 999\$ | 100 000\$<br>à<br>149 999\$ | 150 000\$<br>à<br>249 999\$ | Plus de<br>250 000\$ |
|-------|----------|-------------------------|---------------------|-------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|-----------------------------|-----------------------------|----------------------|
| PR 46 | Manitoba |                         |                     |                         |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                             |                             |                      |
| ROA   | 14 900   | 821 330                 | 650                 | 520                     | 750                       | 930                       | 970                       | 840                       | 810                       | 810                       | 840                       | 940                       | 810                       | 750                       | 1 340                     | 1 080                     | 780                       | 600                       | 1 130                       | 270                         | 110                  |
| ROB   | 13 620   | 245 729                 | 6 630               | 1 200                   | 1 340                     | 1 240                     | 750                       | 360                       | 260                       | 190                       | 170                       | 130                       | 120                       | 100                       | 170                       | 170                       | 120                       | 120                       | 370                         | 190                         | 10                   |
| ROC   | 20 270   | 992 358                 | 2 190               | 910                     | 1 190                     | 1 470                     | 1 580                     | 1 170                     | 1 040                     | 1 090                     | 1 000                     | 980                       | 890                       | 780                       | 1 300                     | 1 180                     | 860                       | 630                       | 1 420                       | 450                         | 150                  |
| ROE   | 14 610   | 798 542                 | 1 090               | 430                     | 660                       | 910                       | 1 080                     | 800                       | 800                       | 800                       | 770                       | 810                       | 700                       | 690                       | 1 130                     | 950                       | 780                       | 570                       | 1 210                       | 330                         | 100                  |
| ROG   | 16 030   | 944 662                 | 600                 | 540                     | 740                       | 940                       | 1 050                     | 920                       | 950                       | 920                       | 950                       | 1 070                     | 970                       | 850                       | 1 400                     | 1 100                     | 740                       | 530                       | 1 130                       | 410                         | 230                  |
| ROH   | 5 170    | 224 477                 | 670                 | 200                     | 360                       | 530                       | 430                       | 280                       | 270                       | 250                       | 230                       | 250                       | 220                       | 210                       | 360                       | 240                       | 190                       | 130                       | 260                         | 70                          | 30                   |
| ROJ   | 10 830   | 547 239                 | 750                 | 450                     | 610                       | 830                       | 770                       | 590                       | 600                       | 580                       | 580                       | 690                       | 630                       | 610                       | 830                       | 610                       | 430                       | 290                       | 670                         | 230                         | 80                   |
| ROK   | 10 040   | 576 234                 | 350                 | 270                     | 470                       | 580                       | 680                       | 580                       | 530                       | 530                       | 530                       | 620                       | 560                       | 540                       | 1 100                     | 820                       | 520                       | 390                       | 720                         | 170                         | 100                  |
| ROL   | 10 010   | 427 013                 | 1 020               | 450                     | 740                       | 1 030                     | 1 030                     | 670                       | 620                       | 500                       | 430                       | 450                       | 400                       | 330                       | 590                       | 480                       | 310                       | 260                       | 500                         | 140                         | 70                   |
| ROM   | 7 160    | 404 691                 | 490                 | 260                     | 380                       | 510                       | 480                       | 370                       | 390                       | 340                       | 360                       | 420                       | 370                       | 290                       | 570                       | 490                       | 330                       | 270                       | 560                         | 220                         | 80                   |
| RIA   | 8 130    | 514 483                 | 340                 | 280                     | 350                       | 470                       | 540                       | 460                       | 450                       | 400                       | 430                       | 470                       | 390                       | 350                       | 630                       | 610                       | 510                       | 310                       | 780                         | 260                         | 110                  |
| R1B   |          |                         |                     |                         |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                           |                             |                             |                      |
| R1C   | 1 590    | 102 635                 | 70                  | 50                      | 50                        | 60                        | 110                       | 90                        | 80                        | 60                        | 100                       | 60                        | 90                        | 90                        | 150                       | 100                       | 90                        | 100                       | 160                         | 80                          | 20                   |
| R1N   | 7 180    | 348 937                 | 330                 | 620                     | 550                       | 590                       | 520                       | 460                       | 400                       | 380                       | 310                       | 360                       | 360                       | 310                       | 500                       | 410                       | 280                       | 220                       | 410                         | 120                         | 70                   |
| R2C   | 12 450   | 696 521                 | 450                 | 340                     | 490                       | 540                       | 720                       | 670                       | 670                       | 750                       | 790                       | 780                       | 780                       | 720                       | 1 220                     | 1 010                     | 820                       | 550                       | 940                         | 180                         | 40                   |
| R2E   | 3 900    | 411 094                 | 130                 | 100                     | 140                       | 160                       | 150                       | 140                       | 160                       | 140                       | 130                       | 170                       | 160                       | 140                       | 280                       | 290                       | 230                       | 210                       | 600                         | 330                         | 250                  |
| R2G   | 12 600   | 739 051                 | 480                 | 360                     | 510                       | 660                       | 880                       | 770                       | 690                       | 730                       | 730                       | 730                       | 700                       | 630                       | 1 120                     | 910                       | 730                       | 520                       | 1 050                       | 300                         | 130                  |
| R2H   | 5 930    | 320 199                 | 270                 | 240                     | 300                       | 370                       | 460                       | 420                       | 380                       | 390                       | 350                       | 370                       | 270                       | 250                       | 450                       | 340                       | 260                       | 220                       | 430                         | 120                         | 70                   |
| R2J   | 10 280   | 619 650                 | 420                 | 310                     | 420                       | 470                       | 630                       | 630                       | 540                       | 610                       | 600                       | 590                       | 520                       | 510                       | 920                       | 780                       | 600                       | 450                       | 880                         | 310                         | 100                  |
| R2K   | 12 670   | 623 367                 | 600                 | 390                     | 600                       | 720                       | 970                       | 890                       | 850                       | 850                       | 860                       | 830                       | 720                       | 680                       | 1 130                     | 760                       | 560                       | 440                       | 620                         | 170                         | 50                   |
| R2L   | 5 390    | 232 942                 | 290                 | 200                     | 320                       | 380                       | 510                       | 410                       | 410                       | 420                       | 380                       | 350                       | 350                       | 240                       | 420                       | 250                       | 180                       | 100                       | 160                         | 30                          | 10                   |
| R2M   | 14 400   | 823 840                 | 770                 | 460                     | 660                       | 820                       | 1 090                     | 1 010                     | 920                       | 850                       | 870                       | 820                       | 770                       | 610                       | 1 190                     | 930                       | 670                       | 510                       | 970                         | 310                         | 180                  |
| R2N   | 12 160   | 832 441                 | 540                 | 330                     | 410                       | 570                       | 700                       | 630                       | 630                       | 600                       | 580                       | 650                       | 570                       | 560                       | 990                       | 910                       | 710                       | 610                       | 1 450                       | 520                         | 210                  |
| R2P   | 13 610   | 593 440                 | 840                 | 510                     | 730                       | 980                       | 1 130                     | 1 210                     | 1 000                     | 930                       | 900                       | 880                       | 700                       | 630                       | 1 030                     | 700                       | 490                       | 290                       | 520                         | 120                         | 30                   |
| R2R   | 10 120   | 450 649                 | 560                 | 390                     | 490                       | 690                       | 800                       | 720                       | 740                       | 680                       | 740                       | 620                       | 600                       | 530                       | 870                       | 660                       | 380                       | 230                       | 330                         | 70                          | 20                   |
| R2V   | 14 160   | 740 102                 | 720                 | 470                     | 660                       | 820                       | 990                       | 930                       | 880                       | 860                       | 970                       | 860                       | 790                       | 730                       | 1 220                     | 930                       | 660                       | 500                       | 850                         | 260                         | 90                   |
| R2W   | 9 820    | 340 244                 | 760                 | 570                     | 840                       | 860                       | 1 140                     | 810                       | 790                       | 690                       | 620                       | 550                       | 430                       | 380                       | 520                       | 330                       | 210                       | 110                       | 160                         | 30                          | 10                   |
| R2X   | 7 280    | 294 223                 | 440                 | 310                     | 380                       | 440                       | 570                       | 560                       | 590                       | 640                       | 590                       | 550                       | 480                       | 360                       | 570                       | 330                       | 200                       | 100                       | 140                         | 30                          | 10                   |
| R2Y   | 7 070    | 388 955                 | 300                 | 200                     | 270                       | 320                       | 470                       | 420                       | 380                       | 430                       | 450                       | 420                       | 400                       | 350                       | 700                       | 570                       | 420                       | 290                       | 510                         | 130                         | 40                   |
| R3A   | 1 680    | 51 146                  | 180                 | 150                     | 180                       | 190                       | 190                       | 160                       | 140                       | 120                       | 70                        | 70                        | 50                        | 40                        | 50                        | 30                        | 20                        | 10                        | 20                          | 10                          | 10                   |
| R3B   | 5 110    | 209 673                 | 370                 | 380                     | 510                       | 530                       | 590                       | 530                       | 440                       | 350                       | 250                       | 190                       | 180                       | 100                       | 180                       | 110                       | 90                        | 70                        | 140                         | 50                          | 60                   |
| R3C   | 8 220    | 347 432                 | 840                 | 530                     | 910                       | 950                       | 790                       | 610                       | 570                       | 460                       | 410                       | 320                       | 260                       | 230                       | 340                       | 250                       | 180                       | 120                       | 240                         | 120                         | 80                   |
| R3E   | 6 960    | 262 058                 | 490                 | 340                     | 440                       | 540                       | 640                       | 620                       | 590                       | 530                       | 560                       | 450                       | 340                       | 310                       | 430                       | 280                       | 150                       | 90                        | 130                         | 20                          | 10                   |
| R3G   | 9 230    | 433 116                 | 540                 | 360                     | 580                       | 640                       | 760                       | 740                       | 680                       | 640                       | 610                       | 560                       | 490                       | 380                       | 680                       | 460                       | 320                       | 230                       | 410                         | 110                         | 50                   |
| R3H   | 90       | 7 881                   | 10                  |                         |                           |                           | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        |                           | 10                        |                           | 10                          |                             |                      |
| R3J   | 10 630   | 584 222                 | 440                 | 290                     | 460                       | 510                       | 670                       | 630                       | 650                       | 660                       | 680                       | 650                       | 620                       | 560                       | 960                       | 830                       | 590                       | 430                       | 740                         | 200                         | 70                   |
| R3K   | 4 820    | 342 603                 | 150                 | 140                     | 190                       | 200                       | 290                       | 260                       | 240                       | 230                       | 270                       | 250                       | 250                       | 250                       | 420                       | 390                       | 290                       | 230                       | 510                         | 180                         | 100                  |
| R3L   | 7 760    | 442 049                 | 400                 | 310                     | 360                       | 430                       | 540                       | 540                       | 500                       | 500                       | 440                       | 460                       | 370                       | 330                       | 640                       | 450                       | 380                       | 290                       | 530                         | 180                         | 110                  |
| R3M   | 8 110    | 654 286                 | 340                 | 230                     | 370                       | 390                       | 550                       | 500                       | 460                       | 430                       | 370                       | 430                       | 350                       | 320                       | 620                       | 510                       | 380                       | 320                       | 800                         | 390                         | 340                  |
| R3N   | 6 080    | 514 856                 | 260                 | 190                     | 250                       | 260                       | 330                       | 310                       | 290                       | 240                       | 250                       | 290                       | 250                       | 220                       | 520                       | 460                       | 360                       | 320                       | 730                         | 350                         | 230                  |
| R3P   | 7 960    | 1 112 495               | 380                 | 280                     | 290                       | 360                       | 430                       | 380                       | 340                       | 310                       | 280                       | 290                       | 300                       | 270                       | 520                       | 480                       | 390                       | 320                       | 940                         | 690                         | 730                  |
| R3R   | 9 750    | 742 040                 | 340                 | 280                     | 320                       | 440                       | 500                       | 430                       | 410                       | 450                       | 440                       | 480                       | 470                       | 450                       | 870                       | 820                       | 640                       | 520                       | 1 160                       | 480                         | 260                  |
| R3S   | 230      | 47 320                  | 10                  | 10                      | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 20                        | 10                        | 10                        | 30                          | 30                          | 20                   |
| R3T   | 20 610   | 1 021 443               | 2 510               | 1 110                   | 1 200                     | 1 470                     | 1 700                     | 1 410                     | 1 180                     | 1 040                     | 930                       | 960                       | 780                       | 710                       | 1 260                     | 930                       | 780                       | 630                       | 1 260                       | 550                         | 210                  |
| R3V   | 2 490    | 146 018                 | 140                 | 90                      | 120                       | 150                       | 150                       | 150                       | 120                       | 160                       | 120                       | 150                       | 110                       | 130                       | 220                       | 180                       | 120                       | 100                       | 190                         | 60                          | 40                   |
| R3W   | 5 310    | 305 573                 | 220                 | 160                     | 210                       | 280                       | 300                       | 300                       | 280                       | 280                       | 280                       | 280                       | 300                       | 260                       | 510                       | 430                       | 320                       | 240                       | 500                         | 120                         | 30                   |
| R3X   | 7 750    | 660 346                 | 370                 | 240                     | 260                       | 330                       | 380                       | 270                       | 310                       | 270                       | 300                       | 280                       | 290                       | 280                       | 600                       | 550                       | 520                       | 430                       | 1 280                       | 530                         | 280                  |
| R3Y   | 11 610   | 883 017                 | 1 080               | 530                     | 510                       | 610                       | 740                       | 640                       | 540                       | 470                       | 460                       | 450                       | 380                       | 390                       | 720                       | 670                       | 580                       | 540                       | 1 340                       | 580                         | 370                  |
| R4A   | 1 890    | 142 158                 | 70                  | 50                      | 70                        | 70                        | 100                       | 80                        | 80                        | 100                       | 70                        | 80                        | 80                        | 70                        | 150                       | 150                       | 130                       | 120                       | 270                         | 100                         | 50                   |
| R4G   | 630      | 61 827                  | 20                  | 10                      | 10                        | 20                        | 30                        | 20                        | 30                        | 20                        | 20                        | 30                        | 20                        | 20                        | 40                        | 40                        | 50                        | 50                        | 130                         | 70                          | 30                   |
| R4H   | 1 030    | 116 464                 | 50                  | 20                      | 30                        | 30                        | 50                        | 30                        | 40                        | 30                        | 40                        | 40                        | 50                        | 40                        | 70                        | 70                        | 70                        | 50                        | 140                         | 100                         | 80                   |
| R4J   | 470      | 44 789                  | 20                  | 10                      | 10                        | 50                        | 10                        | 30                        | 20                        | 20                        | 10                        | 20                        | 10                        | 20                        | 30                        | 30                        | 30                        | 30                        | 70                          | 30                          | 30                   |
| R4K   | 350      | 23 681                  | 10                  | 60                      | 20                        | 40                        | 10                        | 10                        | 10                        | 10                        | 10                        | 20                        | 10                        | 10                        | 30                        | 20                        | 10                        | 20                        | 30                          | 20                          | 10                   |
| R4L   | 490      | 35 622                  | 10                  | 10                      | 20                        | 20                        | 30                        | 20                        | 20                        | 20                        | 30                        | 20                        | 20                        | 20                        | 50                        | 40                        | 40                        | 30                        | 60                          | 30                          | 10                   |
| R5A   | 1 480    | 106 852                 | 50                  | 40                      | 40                        | 60                        | 70                        | 60                        | 70                        | 70                        | 70                        | 60                        | 80                        | 70                        | 130                       | 120                       | 110                       | 100                       | 190                         | 60                          | 30                   |
| R5G   | 9 370    | 530 321                 | 370                 | 300                     | 480                       | 550                       | 670                       | 520                       | 600                       | 600                       | 610                       | 630                       | 570                       | 450                       | 820                       | 630                       | 440                       | 310                       | 540                         | 180                         | 90                   |
| R5H   | 2 040    | 107 191                 | 80                  | 50                      | 80                        | 150                       | 150                       | 120                       | 110                       | 140                       | 120                       | 140                       | 120                       | 110                       | 200                       | 140                       | 110                       | 90                        | 130                         | 30                          | 10                   |
| R5J   | 490      | 26 893                  | 20                  | 20                      | 30                        | 30                        | 30                        | 10                        | 30                        | 20                        | 20                        | 40                        | 30                        | 30                        | 50                        | 40                        | 30                        | 20                        | 30                          | 10                          |                      |
| R5K   | 1 990    | 136 862                 | 70                  | 50                      | 70                        | 100                       | 90                        | 80                        | 100                       | 110                       | 100                       | 100                       | 100                       | 90                        | 180                       | 160                       | 140                       | 120                       | 250                         | 80                          | 20                   |
| R5L   | 760      | 42 474                  | 10                  | 40                      | 30                        | 60                        | 50                        | 50                        | 40                        | 30                        | 40                        | 40                        | 50                        | 40                        | 60                        | 70                        | 40                        | 40                        | 70                          | 10                          |                      |
| R5M   | 790      | 52 778                  | 20                  | 20                      | 30                        | 60                        | 40                        | 40                        | 30                        | 30                        | 30                        | 50                        | 40                        | 40                        | 60                        | 60                        | 50                        | 40                        | 100                         | 30                          | 10                   |
| R5N   | 1 660    | 131 069                 | 40                  | 30                      | 50                        | 60                        | 60                        | 70                        | 80                        | 50                        | 70                        | 60                        | 80                        | 70                        | 150                       | 130                       | 150                       | 100                       | 310                         | 90                          | 30                   |
| R5P   | 230      | 12 889                  | 10                  |                         | 10                        | 10                        | 20                        | 20                        | 20                        | 10                        | 20                        | 20                        | 10                        | 10                        | 10                        | 10                        | 10                        | 10                        | 20                          | 10                          |                      |
| R5R   | 410      | 36 653                  | 10                  | 10                      | 20                        | 20                        | 20                        | 10                        | 20                        | 20                        | 20                        | 30                        | 20                        | 20                        | 40                        | 30                        | 20                        | 20                        | 50                          | 20                          | 20                   |
| R5T   | 260      | 18 362                  | 10                  |                         | 20                        | 20                        | 20                        | 20                        | 20                        | 10                        | 10                        | 10                        | 10                        | 20                        | 20                        | 10                        |                           |                           |                             |                             |                      |